



中国国家强制性产品认证证书

证书编号: 2021010902360056

发证日期: 2021年01月05日

有效期至: 2026年01月05日

认证委托人 华硕电脑股份有限公司
中国台湾台北市北投区立德路 15 号 1 楼

产品生产者 华硕电脑股份有限公司
中国台湾台北市北投区立德路 15 号 1 楼

生产企业 旭硕科技(重庆)有限公司
重庆市渝北区两路寸滩保税港区空港功能区 C 区 B01

产品名称和系列、规格、型号 笔记本电脑
X515xxxxxxxxxxxxxxxxx, A516xxxxxxxxxxxxxxxxx, F515xxxxxxxxxxxxxxxxx,
R565xxxxxxxxxxxxxxxxx, V5200xxxxxxxxxxxxxxxxx ("x" 可以为 A-Z, a-z, - 或空格; "y" 可
以为 0-9, A-Z, a-z, - 或空格, 仅用于市场目的, 不影响产品的安全和电磁兼容性能): 19Vdc, 2.37A 或
3.42A (电线组件可选) (电源适配器见附件)

产品标准和技术要求 GB 17625.1-2012;GB 4943.1-2011;GB/T 9254-2008

上述产品符合 CNCA-C09-01:2014 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。
经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn) 查验证书信息, 以后查验结果为准



签发:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2021010902360056

Valid from: Jan.05,2021

Valid until: Jan.05,2026

APPLICANT ASUSTek Computer Inc.
1F., No. 15, Lide Rd., Beitou Dist., Taipei City 112, Taiwan, China

MANUFACTURER ASUSTek Computer Inc.
1F., No. 15, Lide Rd., Beitou Dist., Taipei City 112, Taiwan, China

FACTORY Digitek (Chongqing) Limited
B01,Section C, Airport Function Zone, Lianglu Cuntan Free Trade Port Area, Yubei District Chongqing City

PRODUCT Notebook PC

MODEL(S) X515xxxxxxxxxxxxxxxx, A516xxxxxxxxxxxxxxxx, F515xxxxxxxxxxxxxxxx, R565xxxxxxxxxxxxxxxx, V5200xxxxxxxxxxxxxxxx ("x" = A-Z,a-z,- or blank ; " y" =0-9,A-Z,a-z,-or blank, for marketing purpose and no impact safety and EMC related construction and critical components) :19Vdc, 2.37A or 3.42A(Cord set is optional)
(Adapter see attachment)

STANDARDS AND TECHNICAL REQUIREMENTS GB 17625.1-2012;GB 4943.1-2011;GB/T 9254-2008

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C09-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA' s website: www.cnca.gov.cn (the latter result prevails)



SIGNATURE:



CHINA QUALITY CERTIFICATION CENTRE



中国国家强制性产品认证证书

证书编号: 2021010902360056

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

ADP-45ZE B	规格:输入: 100-240VAC/1.2A, 50-60Hz; 输出: 19Vdc/2.37A. (适用于海拔 5000 米及以下,不带电线组件销售)
ADP-45BW X	规格:输入: 100-240VAC/1.2A, 50-60Hz; 输出: 19Vdc/2.37A. (适用于海拔 5000 米及以下)
W16-045N3C	输入: 100-240Vac, 50-60Hz, 1.2A 输出: 19Vdc, 2.37A(仅适用于海拔 5000 米及以下)
AD10280	规 格: 输入: 100-240V~, 50/60Hz, 1.0A 输出: 19Vdc, 2.37A(仅适用于海拔 5000 米及以下) (不带电线组件销售)
ADP-65GD D	输入: 100-240VAC, 50-60Hz, 1.5A; 输出: 19VDC/3.42 A,产品 销售时不配备电线组件; Class I 仅适用于海拔 5000 米及以下
ADP-65DW A, ADP-65DW X	输入: 100-240VAC,1.5A,50-60Hz ; 输出:19Vdc,3.42A. (适用于 海拔 5000 米及以下,不带电线组件销售)
AD2087520	输入: 100-240VAC 50/60Hz 1.5A, 输出: 19VDC,3.42A; (仅 适用于海拔 5000 米及以下)
AD10500	输入: 100-240Vac, 50/60Hz, 1.5A; 输出: 19Vdc, 3.42A (仅适 用于海拔 5000 米及以下; 不带电线组件销售)
W19-045N3C	输入: 100-240Vac, 50-60Hz, 1.2A ; 输出: 19Vdc, 2.37A(仅 适用于海拔 5000 米及以下
AD2108520	输入: 100-240Vac, 50/60Hz, 1.0A 输出: 19.0Vdc, 2.37A (仅适用于海拔 5000 米及以下)



中国质量认证中心