

Poly Studio R30 USB Video Bar No Radio GSA/TAA JITC (980F2AA)



Simply better meetings

Transform your collaboration with advanced video capabilities and superb audio quality that are simple for anyone on your team to use. The result is meetings that start on time, increase inclusivity, and improve communication and productivity.



Smooth meetings

The Poly Studio R30 Plus solution includes a dynamic video bar, easy-connect dock, and remote control to simplify meetings. Anyone can connect their compatible laptop to the video system which makes it easy for everyone in the room to participate [1].

Boardroom-quality conferencing

Bring stunning video quality and audio excellence to meetings in your smaller rooms. Intelligent camera framing, a wide 120-degree field of view, exceptional voice clarity, and smart noise reduction make collaboration productive [2].

Reduce wasted time

Eliminate technology headaches with one USB Type-C® cable that easily connects a laptop to the in-room devices and powers your computer. Keep things moving with a remote that lets anyone easily control mute and volume and adjust the camera.

Featuring

Never miss a moment

Poly DirectorAI smart camera framing works behind the scenes to keep you framed how you want—whether that's switching between people speaking, following a presenter, or a close up view of everyone in the room. Keep everyone engaged and involved.

Impeccable noise reduction

Poly NoiseBlock AI and Acoustic Fence Technologies reduce background noise and provide an interference-free audio experience. Minimize distractions, such as keyboard typing, or nearby conversations so you can focus on collaboration.

Quick and effortless setup

Swiftly set up your Poly Studio R30: just two cords are needed. Plug in the power and connect your PC via USB and you are ready to go. Remember you may want to connect your PC to the monitor, which would require a separate HDMI cable.

Clear resolution

Say goodbye to grainy, blurry videos that make it hard to focus and connect. Our stunning 4K resolution, provides you with lifelike visuals that capture every expression, gesture, and nuance for a truly engaging meeting experience.

Bring everyone together

Gather the team without feeling cramped. The impressive 120-degree field of view allows everyone to be seen. This wide angle eliminates the need for camera adjustments or awkward

Specifications

Audio	Poly NoiseBlockAI technology; Poly Acoustic Fence technology; Poly Acoustic Clarity technology
Minimum dimensions (W x D x H)	445 x 86 x 81 mm (with monitor clamp); 445 x 68 x 81 mm (without monitor clamp)
Minimum dimensions (W x D x H)	17.5 x 3.4 x 3.2 in (with monitor clamp); 17.5 x 2.7 x 3.2 in (without monitor clamp)
Weight	822 g (with monitor clamp); 737 g (without monitor clamp)
Weight	1 lb (with monitor clamp); 1 lb (without monitor clamp)
Ports	1 USB Type-C® 5Gbps signaling rate; 2 USB 2.0 Type-A; 1 4.5 mm power adapter
Package dimensions (W x D x H)	225 x 525 x 100 mm
Package weight	300 g
Power supply type	External
UPC number	197961119220
Manufacturer Warranty	Poly standard one-year limited warranty
What's in the box	Poly Studio R30; Monitor clamp; AC power adapter; Power cable; USB Type-C® to USB Type-A cable (5 m/16.4 ft); Setup sheet; Removable privacy cap

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] The Poly Studio R30+ video conferencing solution includes: Poly Studio R30, HP USB-C Dock G5 and Poly Studio Bluetooth® remote control. Compatible laptop operating systems include Windows 10 and higher.; macOS; Chrome OS™.

[2] For optimal performance we recommend using the Poly Studio R30 Plus in a small room approximately 10' x15'/3.05m x 4.57m.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

