



HP Z8 Fury G5 Workstation Desktop PC

Extreme performance. Infinite possibilities

Experience a new echelon in high performance. Transformative single socket technology delivers extreme performance with up to 56 cores in a single CPU, to also unleash the power of up to 4 high-end GPUs. Now you can breeze through even the most complex deep learning, virtual production, and VFX.



*Product image may differ from actual product

HP recommends Windows 11 Pro for business

Relentless power. Extraordinary expandability

- Tackle the most complex workflows with up to a 56 core Intel® Xeon® W CPU¹, up to 4 high-end GPUs, 2TB DDR5 RAM, 120 TB storage and 2,250W of power.² Easily expand as work evolves with 8 PCIe slots (up to Gen 5), and 4 front accessible NVMe bays.³

Engineered to stay cool and quiet

- Push your desktop workstation without disruptive noise. Smart fan control keeps the system whisper-quiet by tuning fan speeds in real-time using over 20 temperature sensors. Precisely placed vents and ducts streamline airflow and heat removal.

Solutions for smarter workflows

- Remotely access the power of your Z with HP Anyware⁶. Get fast responsiveness and image quality even in high-end workflows. Save time with WSL 2⁷, enabling Linux to run in Windows. Get easy access to tools from the Z by HP Data Science Stack Manager⁸.
- Support your unique user needs with a choice of Windows 11 Pro, WSL2 or Linux® operating systems.⁹
- Power extreme professional workloads with a transformative single socket Intel® Xeon® W CPU (up to 56 cores¹), Intel vPro®¹⁰ manageability and security, and ECC Memory¹¹ for reliability.
- A first for Z desktop PCs - tackle complex renderings, simulations and datasets with up to 4 NVIDIA RTX™ A6000 or 2 AMD Radeon™ Pro W6800 GPUs.¹³
- Accelerate workflows. Power through memory-intensive workloads with up to 2 TB DDR5 memory¹⁴ for fast rendering, simulation, film and video editing, and deep learning performance.
- Get up to 120TB of storage across a variety of devices, including new front-accessible, hot-swappable NVMe devices with status information via external LED and email notifications.¹⁵
- Use redundant power to stay up and running during critical workflow. Or switch to aggregate power to combine two power supplies for 2,250W power when you need it.¹⁶
- Thunderbolt™ 4 technology¹⁷ for fast data transfers, two optional USB3.2 SuperSpeed Type-C® connectors for transfer rates up to 20Gbps, and two ports of 10 GbE network connection.
- Access the power of your Z from any device with HP Anyware¹⁸—remote access software delivering fast responsiveness and image quality, even in film editing and data visualizations.
- Get enhanced support and reduce downtime. HP Smart Support¹⁹ provides support agents, secure access to device health insights, and configuration data for faster troubleshooting.
- Z by HP Data Science Stack Manager provides easy access to popular data science tools and updates them automatically, to help you customize your environment on Windows or Ubuntu.²⁰
- Work with confidence knowing your desktop is certified with leading software applications to ensure peak performance even with complex projects.
- Keep quiet, cool and focused even at peak performance. Smart fan control keeps the system whisper-quiet by tuning fan speeds in real-time using 20 temperature sensors.

HP Z8 Fury G5 Workstation Desktop PC Specifications Table



*Product image may differ from actual product

Available Operating Systems	Windows 11 Pro for Workstations ^{2,3} Ubuntu 22.04 LTS Linux® Ready ³ Red Hat® Enterprise Linux® ⁵
Processor family	Intel® Xeon® processor
Available Processors⁷	Intel® Xeon® W9-3495X (1.9 GHz base frequency, up to 4.8 GHz with Intel® Turbo Boost Technology, 105 MB L3 cache, 56 cores, 112 threads); Intel® Xeon® W9-3475X (2.2 GHz base frequency, up to 4.8 GHz with Intel® Turbo Boost Technology, 82.5 MB L3 cache, 36 cores, 72 threads); Intel® Xeon® W7-3465X (2.5 GHz base frequency, up to 4.8 GHz with Intel® Turbo Boost Technology, 75 MB L3 cache, 28 cores, 56 threads); Intel® Xeon® W7-3455 (2.5 GHz base frequency, up to 4.8 GHz with Intel® Turbo Boost Technology, 67.5 MB L3 cache, 24 cores, 48 threads); Intel® Xeon® W7-3445 (2.6 GHz base frequency, up to 4.8 GHz with Intel® Turbo Boost Technology, 52.5 MB L3 cache, 20 cores, 40 threads); Intel® Xeon® W5-3435X (3.1 GHz base frequency, up to 4.7 GHz with Intel® Turbo Boost Technology, 45 MB L3 cache, 16 cores, 32 threads); Intel® Xeon® W5-3433 (2.0 GHz base frequency, up to 4.2 GHz with Intel® Turbo Boost Technology, 45 MB L3 cache, 16 cores, 32 threads); Intel® Xeon® W5-3425 (3.2 GHz base frequency, up to 4.6 GHz with Intel® Turbo Boost Technology, 30 MB L3 cache, 12 cores, 24 threads); Intel® Xeon® W5-3423 (2.1 GHz base frequency, up to 4.2 GHz with Intel® Turbo Boost Technology, 30 MB L3 cache, 12 cores, 24 threads)
Chipset	Intel® W790
Form factor	Tower
Maximum memory	1 TB DDR5-4800 ECC SDRAM ¹¹ Transfer rates up to 4800 MT/s.
Memory slots	16 DIMM
Internal storage	1 TB up to 12 TB 7200 rpm SATA Enterprise HDD ⁸ 512 GB up to 2 TB HP Z Turbo Drive PCIe® SSD M.2 ⁸ 512 GB up to 2 TB HP Z Turbo Drive PCIe® SED Opal 2 M.2 SSD ⁸ 512 GB up to 2 TB HP Z Turbo Drive Dual Pro PCIe® SSD ⁸
Optical drive	HP Slim DVD-ROM; HP Slim Blu-ray Writer; HP Slim DVD-Writer ^{9,10}
Available Graphics	Ultra High-End: NVIDIA RTX™ A6000 (48 GB GDDR6 dedicated); NVIDIA RTX™ A5000 (24 GB GDDR6 dedicated); AMD Radeon™ Pro W6800 (32 GB GDDR6 dedicated); NVIDIA RTX™ 6000 Ada Generation (48 GB GDDR6 dedicated) ³⁰ High-End: NVIDIA RTX™ A4500 (20 GB GDDR6 dedicated); NVIDIA RTX™ A4000 (16 GB GDDR6 dedicated); NVIDIA RTX™ A2000 (12 GB GDDR6 dedicated); NVIDIA RTX™ A2000E (12 GB GDDR6 dedicated) ³⁰ Mid-Range: NVIDIA® T1000 (8 GB GDDR6 dedicated); NVIDIA® T1000E (8 GB GDDR6 dedicated); AMD Radeon™ Pro W6600 (8 GB GDDR6 dedicated) ³⁰ Entry: NVIDIA® T1000 (4 GB GDDR6 dedicated); NVIDIA® T400 (4 GB GDDR6 dedicated); AMD Radeon™ RX 6400 (4 GB GDDR6 dedicated); Intel® Arc™ Pro A40 (6 GB GDDR6 dedicated)
Audio	Realtek ALC3205-CG
Expansion slots	1 PCIe 3 x8; 2 PCIe 5 x16; 1 PCIe 5 x4; 2 PCIe 4 x16; 2 PCIe 4 x4; 2 PCIe 4 x8 (Rear bulkhead access can be achieved through all slots but 2 PCIe 4 x8, and 2 PCIe 4 x8 are internal access only for M.2 (1 PCIe 4 x16 available when 2nd CPU is not installed; 1 PCIe 3 x16 available only when 2nd CPU is installed).)
Memory card device	1 SD card reader (optional)
Ports and Connectors	Front (Premium version): 2 SuperSpeed USB Type-C® 20Gbps signaling rate (USB Power Delivery); 2 SuperSpeed USB Type-A 5Gbps signaling rate; 1 headset/microphone combo ²⁹ ; Rear: 6 SuperSpeed USB Type-A 5Gbps signaling rate; 1 audio-in/out; 2 RJ-45 (1 GbE AMT, 1GbE, optional 10GbE)
Input devices	HP USB Business Slim SmartCard CCID Keyboard; HP USB 320K Keyboard; HP 125 Black Wired Keyboard ¹³ ; HP Wired Desktop 320M mouse; HP wired desktop 128 laser mouse ¹³ ;
Communications	LAN: Intel® Ethernet Network Adapter I225-T1; Integrated Intel® I219-LM PCIe® GbE, vPro®; Integrated Intel® I210-AT PCIe® GbE, non-vPro®; Intel® X550-T2 dual-port 10GbE NIC; NVIDIA® Mellanox ConnectX-6 DX Dual Port 10/25GbE SFP28 NIC; Allied Telesis AT-2911T/2-901 dual-port 1GbE NIC; Allied Telesis AT-2914SX/LC PCIe Fiber NIC; HP dual-port 10 GBASE-T NIC (PCIe slot not required) ; WLAN: Intel® Wi-Fi 6E AX210 (2x2) and Bluetooth® 5.3 wireless card, non-vPro® with external antenna ^{12,31} ;
Drive Bays	Two 3.5" HDD; Two 9.5 mm ODD; Six PCIe® M.2 SSD; Four PCIe® M.2 SSD
Software	HP PC Hardware Diagnostics UEFI; HP Performance Advisor; HP Support Assistant; HP PC Hardware Diagnostics Windows; HP Image Assistant; HP Manageability Integration Kit; HP Anyware; HP Data Science Stack Manager ^{17,18,19,33}
Security management	Full volume encryption; HP Secure Erase; Kensington lock slot; Secure authentication; TPM 2.0 certified; HP BIOSphere; HP Sure Run; HP Sure Click; HP Sure Sense; HP Sure Admin; HP Platform Certificate; HP Sure Start; HP Sure Recover; Self-Encrypted Drives; ^{20,21,22,23,24,25,26,27}
Security Software Licenses	HP Wolf Pro Security Edition ²⁸
Management features	HP Driver Packs; HP System Software Manager (download); HP BIOS Configuration Utility (download); HP Smart Support
Power	1450 W internal power supply, up to 90% efficiency; 2250 W aggregate internal power supply, up to 90% efficiency, active PFC; 1450 W redundant internal power supply, up to 90% efficiency, active PFC; 1125 W internal power supply, up to 90% efficiency, active PFC; 1125 W redundant internal power supply, up to 90% efficiency, active PFC
Dimensions	21.59 x 55.12 x 44.45 cm
Weight	Starting at 22 kg; (Exact weights depend upon configuration (System weight only))
Ecolabels	EPEAT® registered configurations available; TCO Certified configurations available ^{14,15}
Energy star certified (series fixed)	ENERGY STAR® certified (configurations available)
Sustainable impact specifications	Low Halogen; 40% post-consumer recycled plastic; 25% ITE-derived closed loop plastic; Bulk packaging available; External power supply 90% efficiency; Plastic cushion inserts contain 80% recycled content; Ocean-bound plastic in system fan; 10% post-industrial recycled metal ¹⁶
Compatible displays	All HP Z Displays and HP DreamColor Displays are supported. For more information see http://www.hp.com/go/zdisplays

HP Z8 Fury G5 Workstation Desktop PC

Messaging Footnotes

¹ Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and branding is not a measurement of higher performance.

² 2TB DDR5 memory is planned to be available by the first half of 2023.

³ Optional, configurable features. Two front accessible NVMe bays require a 5.25 bay carrier. Configuration for 120TB requires separate additional purchase. For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 35GB is reserved for system recovery software.

⁴ Optional, configurable feature. Redundant and aggregate power requires configuring two 1125W power supplies at hardware purchase.

⁵ Testing is not intended to demonstrate fitness of U.S. Department of Defense (DoD) contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.

⁶ Network access required. HP Anyware software and licensing are available through a 1- or 3-year subscription. Renewal is required after the subscription term. HP Anyware subscriptions are based on the number of concurrent PCoIP connections used (pay for the number of host connections, not the software) with a minimum order quantity of 5. For a limited time, an HP Anyware Professional subscription also includes access and support for ZCentral RemoteBoost and ZCentral Connect and is available for purchase through an HP reseller or contact sales at hp.com/Anyware. ZCentral RemoteBoost Sender requires Windows 10 and 11, RHEL/CentOS (7 or 8), or UBUNTU 18.04 or 20.04 LTS operating systems. macOS (10.14 or newer) operating system and ThinPro 7.2 are only supported on the receiver side. ZCentral Connect requires Windows (10 or 11) or Windows Server (2016 or 2019) operating system, Microsoft Active Directory and Intel Active Management Technology for select features. For system requirements and to install HP Anyware and Anyware Manager, refer to the Admin Guides at: <https://docs.teradici.com/find/product/hp-anyware>.

⁷ Optional, configurable feature that must be configured at purchase. Requires Windows 10 or higher, Intel Core i5 processor or higher and is available on select Z workstations. You must be running Windows 10 version 21H2 and higher (Build 19044 and higher) or Windows 11.

⁸ Z by HP Data Science Stack Manager requires Windows 10 version 21H2 (Build 19044) and higher or 64-bit Ubuntu 20.04 and is available on select Z workstations.

⁹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

¹⁰ Intel vPro® Enterprise technologies are available only on Intel® Xeon® W-3400 and Intel® Xeon® W-2400 processors. Intel vPro® requires Windows 10 Pro 64 bit or higher, vPro enabled processor, vPro enabled chipset, vPro enabled wired LAN and/or Wi-Fi 6E WLAN and TPM 2.0. Some functionality requires additional 3rd party software in order to run. Features of vPro® Essentials and Enterprise vary. See <http://intel.com/vpro>.

¹¹ Error Correction Code (ECC) memory enables enhanced data reliability. ECC memory is only available on Intel® Xeon® processor options.

¹² NVIDIA RTX™ A6000 and AMD Radeon™ Pro W6800 GPUs are sold separately or as an optional feature.

¹³ 2TB DDR5 memory is planned to be available in the first half of 2023.

¹⁴ Optional, configurable features. Configurations for 120TB storage and for front accessible NVMe bays are planned to be available in the first half of 2023. Configuration for 120TB requires separate additional purchase. For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 35GB is reserved for system recovery software.

¹⁵ Redundant and aggregate power requires configuring two 1125W power supplies at hardware purchase.

¹⁶ Two ports of 10 GbE network connection is planned to be available by the first half of 2023. SuperSpeed USB 20Gbps is not available with Thunderbolt™ 4.

¹⁷ Network access required. HP Anyware software and licensing are available through a 1- or 3-year subscription. Renewal is required after the subscription term. HP Anyware subscriptions are based on the number of concurrent PCoIP connections used (pay for the number of host connections, not the software) with a minimum order quantity of 5. For a limited time, an HP Anyware Professional subscription also includes access and support for ZCentral RemoteBoost and ZCentral Connect and is available for purchase through an HP reseller or contact sales at hp.com/Anyware. ZCentral RemoteBoost Sender requires Windows 10 and 11, RHEL/CentOS (7 or 8), or UBUNTU 18.04 or 20.04 LTS operating systems. macOS (10.14 or newer) operating system and ThinPro 7.2 are only supported on the receiver side. ZCentral Connect requires Windows (10 or 11) or Windows Server (2016 or 2019) operating system, Microsoft Active Directory and Intel Active Management Technology for select features. For system requirements and to install HP Anyware and Anyware Manager, refer to the Admin Guides at: <https://docs.teradici.com/find/product/hp-anyware>.

Technical Specifications Footnotes

¹ Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

² Windows 11 Pro for Workstations can be preinstalled. You may only use one version of the Windows software at a time. Switching between versions will require you to uninstall one version and install the other version. You must back up all data (files, photos, etc.) before uninstalling and installing operating systems to avoid loss of your data.

³ Note: Windows 7 and Windows 8 operating systems are not supported on this product. No Windows 7 or Windows 8 drivers will be provided on <http://www.support.hp.com>.

⁴ Note: For detailed Linux® OS/hardware support information, see http://www.hp.com/support/linux_hardware_matrix.

⁵ Intel vPro® requires Windows 10 Pro 64 bit or higher, vPro enabled processor, vPro enabled chipset, vPro enabled wired LAN and/or Wi-Fi 6E WLAN and TPM 2.0. Some functionality requires additional 3rd party software in order to run. Features of vPro® Essentials and Enterprise vary. See <http://intel.com/vpro>.

⁶ For storage drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 35GB (for Windows) is reserved for system recovery software.

⁷ Duplication of copyrighted material is strictly prohibited. Actual speeds may vary. Double Layer media compatibility will widely vary with some home DVD players and DVD-ROM drives. No support for DVD RAM.

⁸ With Blu-Ray, certain disc, digital connection, compatibility and/or performance issues may arise, and do not constitute defects in the product. Flawless playback on all systems is not guaranteed. In order for some Blu-ray titles to play, they may require a DVI or HDMI digital connection and your display may require HDCP support. HD-DVD movies cannot be played on this Desktop PC.

⁹ The 2TB memory configuration requires 128GB DIMMs which is planned to be available in the first half of 2023.

¹⁰ Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6E (802.11ax) is backwards compatible with prior 802.11 specs.

¹¹ Optional add-on feature.

¹² Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.

¹³ TCO Certified configurations available when ENERGY STAR configurations are selected with a USB Type-C® connector. ENERGY STAR available with a combination of high-performance CPUs, high-performance GPUs and select memory configurations.

¹⁴ External power supplies, power cords, cables and peripherals are not low halogen. Service parts obtained after purchase may not be low halogen.

¹⁵ HP Performance Advisor Software - HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at:

<https://www.hp.com/us/en/workstations/performance-advisor.html>.

¹⁶ HP Support Assistant requires Windows and Internet access.

¹⁷ HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/view.html>.

¹⁸ HP SureClick requires Windows 11 Pro or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

¹⁹ HP SureStart Gen7 is available on select HP PCs and Workstations. See product specifications for availability.

²⁰ HP SureRecover Gen4 is available on select HP PCs and requires an open network connection. You must back up important files, data, photos, videos, etc. before using HP SureRecover to avoid loss of data.

²¹ HP SureSense requires Windows 11 Pro or Enterprise and supports Microsoft Internet Explorer, Google Chrome™, and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

²² HP SureRun Gen5 is available on select HP PCs and requires Windows 10 and higher.

²³ HP SureAdmin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP SureAdmin Local Access Authenticator smartphone app from the Android or Apple store.

²⁴ HP SecureErase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88.

²⁵ HP BIOSphere Gen6 features may vary depending on the platform and configurations.

²⁶ HP Wolf Pro Security Edition (including HP SureClick Pro and HP SureSense Pro) is available preloaded on select SKUs and, depending on the HP product purchased, includes a paid 1-year or 3-year license. The HP Wolf Pro Security Edition software is licensed under the license terms of the HP Wolf Security Software - End-User License Agreement (EULA) that can be found at: https://support.hp.com/us-en/document/sh_3875769-3873014-16 as that EULA is modified by the following: "7. Term. Unless otherwise terminated earlier pursuant to the terms contained in this EULA, the license for the HP Wolf Pro Security Edition (HP SureSense Pro and HP SureClick Pro) is effective upon activation and will continue for either a twelve (12) month or thirty-six (36) month license term ("Initial Term"). At the end of the Initial Term you may either (a) purchase a renewal license for the HP Wolf Pro Security Edition from HP.com, HP Sales or an HP Channel Partner, or (b) continue using the standard versions of HP SureClick and HP SureSense at no additional cost with no future software updates or HP Support.

²⁷ Front entry contain: 1 head set connector; 4 SuperSpeed USB Type-A 5Gbps signaling rate. Front Entry and Front Premium offer Battery Charging 1.2 through one of the USB Type-A ports.

²⁸ NVIDIA graphics cards denoting a letter "E" refer to long-life variants of the card.

²⁹ Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs. And available in countries where Wi-Fi 6E is supported.

³⁰ HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www.hp.com/us-en/workstations/performanceadvisor.html>.

³¹ Percentage of ocean-bound plastic contained in each component varies by product.

³² Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.

³³ 100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.

³⁴ Fiber cushions made from 100% recycled wood fiber and organic materials.

Sign up for updates hp.com/go/getupdated

The product could differ from the images shown. © 2014 Hewlett-Packard Development Company, L.P. The Information contained herein is subject to change without notice. Warranties for HP products and services are set out in the express warranty statements accompanying such products and services. In addition, our products and services come with guarantees that cannot be excluded under the Australian Consumer Law. Subject to the foregoing, nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA is trademark and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® is registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

February 2023

