

2U Vented Server Rack Shelf, 12" (31.5cm) Mounting Depth, Cantilever Tray For 19" Rack/Cabinet, Heavy-Duty Steel, Up To 25lb/11.3kg, Includes Cage Nuts/Screws

Product ID: CABSHELFV2U-12-RACK



This 2U vented rack shelf adds 12.4" (31.5 cm) of mounting depth to any EIA-310-compliant 19-inch rack or cabinet. The vented design helps to improve airflow and maintain optimal temperatures for the mounted equipment. The cantilever tray includes cage nuts and screws for quick deployment.

The fixed-rack shelf is made of 16-gauge (1.4mm) SPCC steel for long-term durability and sturdiness while supporting up to 25lb (11.3kg) of equipment. Accommodate server rack equipment, accessories, or non-mountable devices for ease of access and connectivity.

The large venting holes on the shelf surface enable improved airflow to dissipate heat and helps maintain optimal equipment temperatures.

Certifications, Reports and Compatibility

Applications

Features

- **UNIVERSAL 19" FIT:** 2U vented rack-mount shelf is designed to fit EIA-310-compliant 19-inch server racks or cabinets; Mounting depth of 12.4 inches (31.5cm) for data, IT, networking, or non-rack mountable equipment
- **MAXIMIZE VENTILATION:** The venting holes help promote passive airflow for optimal heat dissipation, maintaining consistent temperatures for the mounted equipment
- **HEAVY-DUTY & DURABLE DESIGN:** Made of 16-gauge (1.4mm) SPCC cold-rolled steel, the sturdy front-mounted

cabinet shelf is designed for long-term durability; Max weight capacity of 25lb (11.3kg); Cage nuts and screws are included

- **VERSATILE FUNCTIONALITY:** Designed to fit in 2 and 4-post server racks; Create a storage space for tools, accessories, or non-rack mountable equipment, enhancing workspace efficiency and accessibility during maintenance tasks

- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this ventilated rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	No
Frame Type	Steel
U Height	2U
Cable Management	No
Tools Included	No
Industry Standards	EIA/ECA-310-E
Mounting Surface Thickness	1.8mm (0.07in)

Performance

Air Flow Rate	Vented
Weight Capacity of Work Surface	24.9 lb [11.3 kg]

Physical Characteristics

Color	Black
Construction Material	Steel
Product Length	12.4 in [31.5 cm]
Product Width	17.3 in [44.0 cm]
Product Height	3.5 in [8.8 cm]
Weight of Product	6.6 lb [3.0 kg]

Packaging

Information

Flat Pack (Assembly Required)	Yes
Package Length	13.5 in [34.3 cm]
Package Width	20.5 in [52.0 cm]
Package Height	4.1 in [10.5 cm]
Shipping (Package) Weight	6.8 lb [3.1 kg]

What's in the Box

Included in Package	1 - 2U 2-Post Vented Shelf
	4 - M5 Screws
	4 - M5 Cage Nuts
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***