

## Overview

## **HP t540 Thin Client**



#### **FRONT**

- 1 Power Button
- 2 (1) USB-A 3.1 Gen1 (5Gbps)
- 3 (1) USB-C® 3.1 Gen1 (5Gbps)
- 4 3.5mm Universal Audio Jack
- 5 System stand



#### **BACK**

- 1 (2) USB-A 3.1 Gen2 (10Gbps)
- 2 (2) USB-A 2.0
- 3 (1) RJ45 1Gb Ethernet
- 4 (2) DisplayPort™ 1.2
- 5 Configurable Option Port supporting one of the following:
  - Serial
  - VGA
  - External Wi-Fi® antenna
  - HDMI
  - 2x USB-A 3.1 Gen1(5Gbps)
  - DisplayPort<sup>™</sup> over USB-C<sup>®</sup>
  - No optional port
- 6 DC 4.5mm
- 7 Cable Lock support

## **Overview**

### **AT A GLANCE**

- AMD Ryzen™ Embedded R1305G with Radeon™ Vega 3 Graphics (1.5 GHz base clock, up to 2.8 GHz max boost clock, 4 MB L3 cache, 2 cores)
- DDR4 single channel SDRAM system memory; up to 2400 MT/s transfer rate; t1 SODIMM slot
- 2 x DisplayPort™ 1.2 video outputs supporting up to UHD/4K (3840 x 2160) resolutions

**NOTE:** DisplayPort<sup>™</sup> cables and displays sold separately.

- 16 GB up to 512 GB NAND flash memory; non-volatile; M.2 form factor module
- RJ45 Gigabit Ethernet (GbE) network connection
- Optional Wi-Fi® 6 AX200 ax 2x2 +BT 5including antennas integrated internally in the chassis

**NOTE:** Wireless features, performance and support may vary depending on environmental variables such placement, settings and firmware of your access points. Please contact your wireless vendor for support of your wireless environment

- Option Port with a selection of available factory options (see detailed listing later in this document)
- 3.5 mm combo headset audio jack
- 45W non-PFC external power adapter
- TPM version 2.0 (available with WIN 10 IoT system): UEFI (BIOS). cable lock slot
- Passive thermal design (no cooling fans) and active thermal management technology that monitors the system operating temperatures, throttles SOC operation if appropriate and prevents unit thermal shutdown.
- Rated for a maximum ambient operating temperature of 40 degree C
- ENERGY STAR® certified and EPEAT® Silver registered in the United States. Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. Visit www.epeat.net for more information.
- Post-consumer recycled plastics content 45% total unit plastics (by weight)
- Low halogen<sup>2</sup> material content
- All models TAA compliant in North America

## Warranty

HP Customer Support: limited three-year hardware limited warranty in most regions; Optional HP Care Packs are available and are extended service contracts that go beyond your standard limited warranties; for more details visit http://www.hp.com/go/cpc

<sup>&</sup>lt;sup>1</sup> Wireless access point and Internet access is required; availability of public wireless access points is limited

<sup>&</sup>lt;sup>2</sup> This product is low halogen except for power cords, cables and peripherals; service parts obtained aftermarket may not be low halogen <sup>3</sup> Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

## **OPERATING SYSTEMS**

- HP ThinPro, including HP Smart Zero Core
- Windows 10 IoT Enterprise LTSC 2021
- Windows 10 IoT Enterprise LTSC 2019
- IGEL

## **PROCESSOR**

Model	CPU Frequency Max/Base	Cores/Threads	GPU Type	GPU Frequency
AMD Ryzen™ R1305G	1.5/2.8 GHz	2/4	Radeon™ Vega 3	1000 MHz

## **GRAPHICS**

Number of displays supported: Up to 2x simultaneous displays

Video outputs: Standard: (2) DisplayPort™ 1.2

Optional: (1) DisplayPort™ over USB-C® with USB Power Delivery

(1) VGA analog output(1) HDMI digital output

**NOTE:** adding and optional output does not increase the number of displays supported.

Max. screen resolution: DP and HDMI max: 3840x2160

VGA max: 2048x1152@50Hz / 1920x1080

Windows 10 IoT	≤2 x 1080p FHD (1920x1080) 60Hz	1 x 4K UHD (3840x2160) 30Hz	2 x 4K UHD (3840x2160) 30Hz	1 x 4K UHD (3840x2160) 60Hz
Static screen (no video)	√	V	√	√
Play 1080p 30fps (or below) video	√	V	√	√
Play 1080p 60fps video				
Play 4k @ 30fps video				

Thinpro7.1+SP8	≤2 x 1080p FHD (1920x1080) 60Hz			1 x 4K UHD (3840x2160) 60Hz
Static screen (no video)	√	√	V	V



## **MEMORY**

Type: DDR4 Single Channel SODIMM

**Data Transfer Rate:** Up to 2,400 MT/s

Number of Slots 1 x SODIMM

Capacities: 4, 8, 16 GB

#### **NOTEs:**

• The system's Graphics Processing Unit (GPU) uses part of the total system memory. System memory dedicated to graphics performance is not available for use by other programs



**UEFI** 

**UEFI Specification Revision** 2.7

TPM 2.0 Meets requirements for Common Criteria, an independent third-party certification of

trustworthiness

Meets requirements for FIPS 140-2, a standard for cryptographic integrity

Security features System UEFI designed to address NIST SP 800-147 guidelines

**STORAGE** 

**Type:** NAND flash memory; non-volatile

Number of Sockets: 1 x M.2

Capacities: 16 GB M.2 eMMC Flash Memory\*

32 GB M.2 eMMC Flash Memory 64 GB M.2 eMMC Flash Memory 128 GB M.2 NVMe Flash Memory 256 GB M.2 NVMe Flash Memory 512 GB M.2 NVMe Flash Memory

\*This option is only for ThinPro and Smart Zero.

Input/Output

Front access: (1) USB-A 3.1 Gen 1 (5Gbps signaling rate)

(1) USB-C® 3.1 Gen 1 port (5Gbps signaling rate)

(1) 3.5mm Universal Audio Jack

Rear access: (2) DisplayPort™ 1.2

(2) USB-A 3.1 Gen2 (10Gbps)

(2) 2xUSB-A 2.0 RJ45 1Gb Ethernet Cable Lock support

**Video Outputs:** Standard: (2) DisplayPort™ 1.2 digital outputs

Optional: (1) VGA analog output

(1) HDMI digital output

(1) DisplayPort™ over USB-C® with USB Power Delivery

**NOTE:** adding an optional output does not increase the number of displays supported.

**I/O Interfaces:** Standard: (1) RJ45 1Gb Ethernet (Rear)

(1) 3.5 mm universal audio jack (front)

**Option Port:** The rear I/O panel includes an Option Port that can be configured with one of the following factory

options:

Serial

VGA

• External Wi-Fi® antenna

HDMI

2x USB-A 3.1 Gen1(5Gbps signaling rate)

- DisplayPort™ over USB-C® with USB Power Delivery
- No optional port

## **AUDIO/VIDEO**

#### **Audio**

- Integrated PC speaker for basic audio playback
- 3.5 mm headset audio port on front supporting headphones, headset, external speaker systems, or microphone.
- Realtek ALC3247 high definition audio Codec; 4-channel DAC supports 16/20/24-bit PCM for independent stereo sound output (streaming playback); the 4-channel ADC supports 16/20/24bit
- PCM format for two stereo and independent analog sound inputs; incorporating Realtek converter technology achieves a 97dB dynamic range playback quality and a 90dB dynamic range recording quality. It meets WLP (Windows Logo Program) requirements for Windows systems.

#### **Video CODECs**

- MPEG-4 part 2 (DivX, Xvid)
- MPEG-4 part 10 (H.264, AVC), Advanced Video Coding (AVC) (H.264 encode)
- MPEG-H part 2, High Efficiency Video Coding (HEVC) (H.265 decode)
- WMV 7/8/9 VC-1 & ASF Demuxer
- Includes hardware acceleration support

## HARDWARE SECURITY

- Security lock support (cable lock sold separately)
- Trusted Platform Module (version 1.2 or 2.0 depending on the model's operating system)

### **NETWORKING**

Local Area Networking Realtek RTL8111HSH Gigabit Ethernet (GbE) Controller

Wi-Fi® Networking Intel® Wireless-AX200 ax 2x2 and Bluetooth 5

Realtek 8852AE Wi-Fi6 +BT5.2 WLAN

#### **NOTES:**

Wireless access point and internet access required. Availability of public wireless access points limited
Wireless features, performance and support may vary depending on environmental variables such placement, settings and
firmware of your access points. Please contact your wireless vendor for support of your wireless environment

## Non-volatile Storage:

The MAC address is unique for each system; assigned from the board assembly manufacturer's IEEE registered allocation.

The PCI subsystem ID is unique to HP and unique to each design to allow Windows Update to be finely controlled.

# **Technical Specifications**

## **SOFTWARE SUPPORT**

Host Environment	HP Protocol ThinPro	НР	Microsoft
nost Environment		ThinPro	Windows 10 IoT LTSC 64 Bit
Remote Desktop Services	Remote FX (RFX), RDP	✓	✓
Citrix®	ICA, HDX	✓	✓
VMware® Horizon	RDP, PCoIP, Blast Extreme	✓	✓

Ductoral Clients	НР	Microsoft
Protocol Clients	ThinPro	Windows 10 IoT LTSC 64 Bit
Citrix® Workspace app	✓	✓
Microsoft Remote Desktop Client		✓
Free Remote Desktop Client	✓	
VMware™ Horizon View™ Client	✓	✓
HP ZCentral Remote Boost	via add-on	via add-on
Turbosoft TTerm for Linux® Terminal emulation Software	via add-on	
Turbosoft TTWin Terminal emulation software		via add-on

Browsey Cumpart	НР	Microsoft
Browser Support	ThinPro	Windows 10 IoT LTSC 64 Bit
Internet Browser	✓	
Internet Explorer		✓

Committee	HP	Microsoft
Security	ThinPro	Windows 10 IoT LTSC 64 Bit
Smart Card	✓	✓
Log-on Manager	✓	✓
Read only Operating System	✓	
802.1x	✓	✓
Microsoft Windows Defender		✓
HP Write Manager		✓



## **Technical Specifications**

Microsoft Unified Write Filter	✓	

**NOTE:** the HP Write Manager is the default active write filter. The Microsoft Unified Write Filter is disabled by default but can be enabled by the user if required.

W	НР	Microsoft
Management Tools	ThinPro	Windows 10 IoT LTSC 64 Bit
HP Device Manager	✓	<b>√</b>
HP ThinUpdate		✓
HP Easy Tools	✓	
HP Smart Zero Client Services	✓	
Microsoft SCCM/EDM agent		<b>√</b>
HP USB Port Manager		<b>√</b>

Additional Windows Components	HP	Microsoft
Additional Windows Components	ThinPro	Windows 10 IoT LTSC 64 Bit
HP Easy Shell		<b>✓</b>
Windows Media Player		<b>✓</b>
Microsoft Direct Access		<b>✓</b>
Microsoft BranchCache		<b>✓</b>
Microsoft AppLocker		<b>✓</b>
Microsoft Sideloading		<b>✓</b>
CyberLink		<b>✓</b>
Microsoft BitLocker		<b>√</b>

**NOTE:** Other add-on software available (see: http://www.hp.com/support for latest list of available add-ons). Software performance and support may vary depending on customer environment and backend.

Audio/Video CODECs	НР	Microsoft
	ThinPro	Windows 10 IoT LTSC 64 Bit
MP3	✓	✓
WMA stereo	✓	✓
AAC stereo & HE AAC	✓	
Microsoft AC3 encoder		✓
MPEG-1		



## **Technical Specifications**

MPEG-4 part 2 (DivX, Xvid, H.263)		✓
MPEG-4 part 10 (H.264, AVC)	✓	✓
WMV 7/8/9/ VC-1 & ASF Demuxer	✓	✓

Recommended TC config for Microsoft Teams media optimization

	TC CPU	VMware Teams Optimization	Citrix Teams Optimization
t430	1.10 GHz 2 Core	-	-
t530	1.50 GHz 2 Core	-	-
t540	1.50 GHz 2 Core	-	-
t630	2.00 GHz 4 Core	✓	✓
t628	1.99 GHz 4 Core	-	✓
t638	2.00 GHz 4 Core	✓	✓
t640	2.40 GHz 2 Core	✓	✓
t730	2.70 GHz 4 Core	✓	✓
t740	3.25 GHz 4 Core	✓	✓
mt21	1.80 GHz 2 Core	-	✓
mt22	1.90 GHz 2 Core	-	✓
mt31	1.80 GHz 2 Core	-	✓
mt32	2.70 GHz 4 Core	✓	✓
mt45	2.10 GHz 4 Core	✓	✓
mt46	2.50 GHz 4 Core	✓	✓

## **WEIGHTS & DIMENSIONS**

WxDxH:

35 x 200 x200 mm; (1.38 x 7.87 x 7.87 in.) (vertical orientation)

1.4 liter Volume:

**System Weight** 969g (unit with stand) **Shipping Weight** 2,879g

NOTE: All measurements are approximate; the addition of optional modules will increase the weight



## **Technical Specifications**

## **EXTERNAL POWER SUPPLY**

45W non-PFC Smart external power adapter; 4.5mm Right Angle 1.8m output cable Worldwide auto-sensing 100 - 240 VAC; nominal voltage is 120 VAC; 50 - 60 Hz Entergy saving automatic power-down; surge tolerant

External power adapters are sourced from several suppliers in order to ensure adequate supply and availability is maintained. The actual dimensions of the power brick will vary by supplier.

HP P/N	Vendor	Dimensions:
L25296-001	Lite-On	94 x 40 x 26.5 mm
L25296-002	Chicony	95 x 40 x 26.5 mm
L25296-003	Delta	94 x 39 x 26.5 mm
L25296-004	AcBel	91.4 x 44 x 26.8 mm



## **COMPLIANCE/CERTIFICATIONS**

Accessibility: Section 508 Accessibility; VPAT report available.

**Environmental Stewardship:** Worldwide (ENERGY STAR®, EPEAT® 2.0, RoHS2, ERP, TCO, CECP& SEPA, HP GSE, WEEE,

Low Halogen, etc.)

**Product Safety:** Worldwide (UL, CB, GS, CCC, BSMI, etc.)

**Electromagnetic Compliance (EMC):** Worldwide (FCC/CISPR/EN/VCCI/ICES/AS/NZS/CNS/KCC) "Class B" EMI regulations

Eco-Label Certifications & declarations This product has received or is in the process of being certified to the following

approvals and may be labeled with one or more of these marks:

• US ENERGY STAR®

• EPEAT® Silver registered in the United States. Based on US EPEAT®

registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country.

Visit www.epeat.net for more information.

• IT ECO declaration

### **ENVIRONMENTAL**

Operating Temperature Range: 50° to 104° F 10° to 40° C Non-operating Temperature -22° to 140° F Range: -30° to 60° C

Humidity: Condensing: 20% to 80% Non-condensing: 10% to 90%

**NOTE:** Specifications are at sea level with altitude derating of 1° C/300m (1.8° F/1000ft) to a maximum of 3 Km (10,000 ft), with no direct, sustained sunlight. Upper limit may be limited by the type and number of options installed.

### **Basic Configuration:**

Energy Consumption (in accordance with US ENERGY STAR® test method)	115 V ac, 60 Hz	230 V ac, 50 Hz	100 <b>V</b> ac, 60 Hz
Normal Operation (Short idle)	7.03W	7.04W	7.03W
Normal Operation (Long idle)	6.63W	6.63W	6.63W
Sleep	0.82W	0.86W	0.86W
Off	0.77W	0.78W	0.77W
Heat Dissipation*	115 V ac, 60 Hz	230 V ac, 50 Hz	100 V ac, 60 Hz
Heat Dissipation*	115 V ac, 60 Hz	230 V ac, 50 Hz	100 V ac, 60

Normal Operation (Short idle)

Normal Operation (Long idle)

Sleep

3 BTU/hr

3 BTU/hr

230 V ac, 50 Hz

100 V ac, 60 Hz

26 BTU/hr

26 BTU/hr

21 BTU/hr

21 BTU/hr

2 BTU/hr

2 BTU/hr

**NOTE:** Heat dissipation is calculated based on the measured watts, assuming the service level is attained for one hour.

System configuration includes: ThinPro- 64 bit, 16/32/64/128/256 GB storage, 4/8/16 GB of system memory, USB Keyboard and USB Mouse



#### **Additional Information**

- This product is in compliance with the Restrictions of Hazardous Substances (RoHS) directive -2011/65/EC.
- This HP product is designed to comply with the Waste Electrical and Electronic Equipment (WEEE) Directive 2002/96/EC.
- This product is in compliance with California Proposition 65 (State of California; Safe Drinking Water and Toxic Enforcement Act of 1986).
- This product is in compliance with the IEEE 1680 (EPEAT) standard at the silver level, see www.epeat.net
- Plastics parts weighing over 25 grams used in the product are marked per ISO 11469 and ISO1043.
- This product contains 13.9 % post-consumer recycled plastic (by wt.) | Plastic declaration for main chassis is 45% PCR
- This product is 93.4 % recycle-able when properly disposed of at end of life.

Packaging Materials External: PAPER/Corrugated 455 g Internal: PLASTIC/Polyethylene Expanded - EPE 44 g PLASTIC/Polyethylene low density - LDPE 5 g

RoHS Compliance HP Inc. is committed to compliance with all applicable environmental laws and regulations, including the European Union Restriction of Hazardous Substances (RoHS) Directive. HP's goal is to exceed compliance obligations by meeting the requirements of the RoHS Directive on a worldwide basis. By July 1, 2006, RoHS substances will be virtually eliminated (virtually = to levels below legal limits) for all HP electronic products subject to the RoHS Directive, except where it is widely recognized that there is no technically feasible alternative (as indicated by an exemption under the EU RoHS Directive).

### **Material Usage**

This product does not contain any of the following substances in excess of regulatory limits (refer to the HP General Specification for the Environment at <a href="http://www.hp.com/hpinfo/globalcitizenship/environment/supplychain/gen\_specifications.html">http://www.hp.com/hpinfo/globalcitizenship/environment/supplychain/gen\_specifications.html</a>):

- Ashestos
- Certain Azo Colorants
- • Certain Brominated Flame Retardants may not be used as flame retardants in plastics | t540 uses only Low VOC coatings
- Cadmium
- Chlorinated Hydrocarbons
- Chlorinated Paraffins
- Formaldehyde
- Halogenated Diphenyl Methanes
- Lead carbonates and sulfates
- Lead and Lead compounds
- Mercuric Oxide Batteries
- Nickel finishes must not be used on the external surface designed to be frequently handled or carried by the user.
- Ozone Depleting Substances
- Polybrominated Biphenyls (PBBs)
- Polybrominated Biphenyl Ethers (PBBEs)
- Polybrominated Biphenyl Oxides (PBBOs)
- Polychlorinated Biphenyl (PCB)
- Polychlorinated Terphenyls (PCT)
- Polyvinyl Chloride (PVC) except for wires and cables, and certain retail packaging has been voluntarily removed from most applications.
- Radioactive Substances



• Tributyl Tin (TBT), Triphenyl Tin (TPT), Tributyl Tin Oxide (TBTO)

#### **Packaging**

HP follows these guidelines to decrease the environmental impact of product packaging:

- Eliminate the use of heavy metals such as lead, chromium, mercury and cadmium in packaging materials.
- Eliminate the use of ozone-depleting substances (ODS) in packaging materials.
- Design packaging materials for ease of disassembly.
- Maximize the use of post-consumer recycled content materials in packaging materials.
- Use readily recyclable packaging materials such as paper and corrugated materials.
- Reduce size and weight of packages to improve transportation fuel efficiency.
- Plastic packaging materials are marked according to ISO 11469 and DIN 6120 standards.

#### **End-of-life Management and Recycling**

HP Inc. offers end-of-life HP product return and recycling programs in many geographic areas. To recycle your product, please go to: <a href="http://www.hp.com/go/reuserecycle">http://www.hp.com/go/reuserecycle</a> or contact your nearest HP sales office. Products returned to HP will be recycled, recovered or disposed of in a responsible manner.

The EU WEEE directive (2002/95/EC) requires manufacturers to provide treatment information for each product type for use by treatment facilities. This information (product disassembly instructions) is posted on the HP Inc. web site at: <a href="http://www.hp.com/go/recyclers">http://www.hp.com/go/recyclers</a>. These instructions may be used by recyclers and other WEEE treatment facilities as well as HP 0EM customers who integrate and re-sell HP equipment.

# HP, Inc. Corporate Environmental Information

For more information about HP's commitment to the environment: Global Citizenship Report

http://www.hp.com/hpinfo/globalcitizenship/gcreport/index.html

Eco-label certifications

http://www.hp.com/hpinfo/globalcitizenship/environment/productdesign/ecolabels.html

ISO 14001 certificates:

http://h20195.www2.hp.com/V2/GetDocument.aspx?docname=c04755842 and

http://www.hp.com/hpinfo/globalcitizenship/environment/pdf/cert.pdf

# Summary of Changes

Date of change:	Version History:	Type of change	Description of change:
November 23, 2020	From v1 to v2	Changed	At a Glance and GRAPHICS sections
January 14, 2021	From v2 to v3	Changed	SOFTWARE SUPPORT section
October 8, 2021	From v3 to v4	Changed	NETWORKING section
February 6, 2023	From v4 to v5	Changed	OPERATING SYSTEMS section
April 3, 2023	From v5 to v6	Changed	OPERATING SYSTEMS section



© 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express limited warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Amazon Web Services, the "Powered by Amazon Web Services" logo, and Amazon WorkSpaces are trademarks of Amazon.com, Inc. or its affiliates in the United States and/or other countries. Bluetooth® is a trademark owned by its proprietor and used by HP Inc. under license. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency. Linux® is the registered trademark of Linus Torvalds in the U.S. and other countries. Microsoft and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Intel® is a trademark of Intel Corporation in the U.S and other countries. VMware Horizon and VMware Horizon View are registered trademarks of Citrix Systems, Inc. in the United States and/or other jurisdictions. Citrix and Citrix Workspace are trademark Office and in other countries.

