



4-Port USB 3.0 Type-C / Type-A Combo Hub 2x2

USB-C Male and USB-A Male to Two USB-C Ports and Two USB-A Ports, 5 Gbps SuperSpeed USB (USB 3.2 Gen 1), Bus Powered, Aluminum, Space Gray

Part No.: [181075](#)

EAN-13: 0766623181075 | UPC: 766623181075

4-Port USB-C / USB-A Hub with Combo Plug: More Ways to Connect Your USB-A and USB-C Devices

The Manhattan 4-Port USB 3.0 Type-C / Type-A Combo Hub expands one of your device's USB ports into two USB-A ports and two USB-C ports, so you can easily connect a keyboard, mouse, flash drive or phone. Devices that support the USB 3.2 Gen 1 spec (formerly known as USB 3.0) can reach transfer speeds up to 5 Gbps for external storage, printing and more. The Hub's SuperSpeed ports are backward compatible with USB versions 2.0 or even 1.1. You can also charge your phone or tablet since the Hub supplies up to 5 V / 0.9 A of power.

Versatile 2-in-1 USB-A and USB-C connection for many operating systems

This hub has a built-in USB-A cable with an attached USB-C adapter plug for enhanced connectivity to more devices. Thanks to this versatile combination, you can connect this hub to a maximum variety of USB host devices. Pick the connector that works with your PC, laptop, tablet, MacBook®, Chromebook™ and Surface®, and plug right in.

Sleek aluminum housing and bus power for connectivity you can take with you

This USB hub's durable case, compact size and bus power mean greater portability for you when you have to pack up and go. You don't have to worry about carrying an additional power supply, which makes the hub an ideal travel

companion. Simply unplug it from your upstream device, disconnect your peripherals and put what you need in your laptop bag to be on your way.

Universal compatibility for easy installation

This universal USB 3.0 hub will work with a wide range of computers because it requires no additional software or drivers. It installs automatically when you connect it to your laptop or desktop, so you can be up and running quickly. It also works with a range of operating systems such as Windows®, macOS®, Linux and Chrome OS, so it's multi-platform compatible.

Features:

- Adds two USB-A ports and two USB-C ports to connect mice, keyboards, flash drives and more or to charge and sync mobile devices
- USB 3.2 Gen 1 (formerly USB 3.0) USB ports with SuperSpeed transfer rates up to 5 Gbps and charging up to 4.5 W (5 V / 0.9 A)
- 2-in-1 combo cable with USB-C and USB-A plugs
- Bus powered: no external power supply needed
- Great for desktop PCs, Ultrabooks™, laptops, Chromebooks™, MacBooks®, Surface® devices and more
- Compatible with Windows®, macOS®, Linux® and Chrome OS™
- Plug-and-play installation; no configuration or drivers required
- Backward compatible with USB 2.0 and USB 1.1
- Supports Hot Swapping
- Built-in, sturdy 25 cm (10 in.) cable
- Sleek aluminum housing with small footprint, great for desktop placement and travel
- Portable, compact and lightweight design that easily fits into laptop bag pockets
- Three-year warranty

Specifications:

Standards and Certifications

- USB 3.2 Gen 1 (USB 3.0)
- CE
- FCC
- RoHS
- REACH
- UKCA

General

- Data transfer speeds: 5 Gbps
- USB charging power output: 4.5 W (5.0 V at 0.9 A) max.

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Withstanding voltage: 300.0 V DC
- Insulation resistance: 10 MOhm
- Conductive resistance: 5 Ohm

Connections

- One USB-C 24-pin, male
- One USB-A 9-pin, male
- Two USB-A 9-pin, female
- Two USB-C 24-pin, female

Physical

- Dimensions (L x W x H): 104 x 25 x 9 mm (4.09 x 0.98 x 0.35 in.)
- Net weight: 42 g (1.76 oz.)
- Gross weight: 60 g (2.65 oz.)
- Cable length: 25 cm (10 in.)
- Cable diameter: 24 AWG
- Housing: aluminum

Operating Environment

- Operation Temperature: 0 - 50°C (32 - 122°F)
- Storage Temperature: -40 - 85°C (-40 - 185°F)
- Humidity (non-condensing): 0 - 85%

System Requirements

- Windows XP/Vista/7/8.1/10/11, Linux, Chrome OS or macOS

Package Contents

- 4-Port USB 3.0 Type-C / Type-A Combo Hub 2x2
- Instructions



