


OVERVIEW



|                                              |                                         |
|----------------------------------------------|-----------------------------------------|
| 1. Optical drive *                           | 9. DisplayPort 1.4a                     |
| 2. Power button                              | 10. HDMI 2.1 TMDS                       |
| 3. Microphone (3.5mm)                        | 11. 2x PS/2 ports (keyboard / mouse) *  |
| 4. Card reader *                             | 12. 4x USB-A (Hi-Speed USB)             |
| 5. Headphone / microphone combo jack (3.5mm) | 13. Ethernet (RJ-45)                    |
| 6. USB-C (USB 5Gbps), data transfer only     | 14. Optional ports on expansion cards * |
| 7. 2x USB-A (USB 5Gbps)                      | 15. Power connector                     |
| 8. 2x USB-A (USB 5Gbps)                      |                                         |

- Notes:
- Items with \* are only available on selected models
  - More ports are available through the optional expansion cards (not shown on the sample product above)

PERFORMANCE

Processor

Processor Family

13th / 14th Generation Intel® Core™ i3 / i5 / i7 Processor

Processor\*\*

| Processor Name  | Cores                     | Threads | Base Frequency                | Max Frequency                                          | Cache | Processor Graphics      |
|-----------------|---------------------------|---------|-------------------------------|--------------------------------------------------------|-------|-------------------------|
| Core™ i3-13100  | 4 (4 P-core + 0 E-core)   | 8       | P-core 3.4GHz                 | P-core 4.5GHz                                          | 12MB  | Intel® UHD Graphics 730 |
| Core™ i5-13400  | 10 (6 P-core + 4 E-core)  | 16      | P-core 2.5GHz / E-core 1.8GHz | P-core 4.6GHz / E-core 3.3GHz                          | 20MB  | Intel® UHD Graphics 730 |
| Core™ i5-13500  | 14 (6 P-core + 8 E-core)  | 20      | P-core 2.5GHz / E-core 1.8GHz | P-core 4.8GHz / E-core 3.5GHz                          | 24MB  | Intel® UHD Graphics 770 |
| Core™ i7-13700  | 16 (8 P-core + 8 E-core)  | 24      | P-core 2.1GHz / E-core 1.5GHz | Max Turbo up to 5.2GHz / P-core 5.1GHz / E-core 4.1GHz | 30MB  | Intel® UHD Graphics 770 |
| Core™ i3-14100  | 4 (4 P-core + 0 E-core)   | 8       | P-core 3.5GHz                 | P-core 4.7GHz                                          | 12MB  | Intel® UHD Graphics 730 |
| Core™ i5-14400  | 10 (6 P-core + 4 E-core)  | 16      | P-core 2.5GHz / E-core 1.8GHz | P-core 4.7GHz / E-core 3.5GHz                          | 20MB  | Intel® UHD Graphics 730 |
| Core™ i5-14400F | 10 (6 P-core + 4 E-core)  | 16      | P-core 2.5GHz / E-core 1.8GHz | P-core 4.7GHz / E-core 3.5GHz                          | 20MB  | -                       |
| Core™ i5-14500  | 14 (6 P-core + 8 E-core)  | 20      | P-core 2.6GHz / E-core 1.9GHz | P-core 5.0GHz / E-core 3.7GHz                          | 24MB  | Intel® UHD Graphics 770 |
| Core™ i5-14600  | 14 (6 P-core + 8 E-core)  | 20      | P-core 2.7GHz / E-core 2.0GHz | P-core 5.2GHz / E-core 3.9GHz                          | 24MB  | Intel® UHD Graphics 770 |
| Core™ i7-14700  | 20 (8 P-core + 12 E-core) | 28      | P-core 2.1GHz / E-core 1.5GHz | Max Turbo up to 5.4GHz / P-core 5.3GHz / E-core 4.2GHz | 33MB  | Intel® UHD Graphics 770 |
| Core™ i7-14700F | 20 (8 P-core + 12 E-core) | 28      | P-core 2.1GHz / E-core 1.5GHz | Max Turbo up to 5.4GHz / P-core 5.3GHz / E-core 4.2GHz | 33MB  | -                       |
| Intel® 300      | 2                         | 4       | 3.9 GHz                       | -                                                      | 6MB   | Intel® UHD Graphics 710 |

Operating System

Operating System\*\*

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Windows® 11 IoT Enterprise LTSC 2024
- Windows® 11 DG Windows® 10 Pro 64
- Ubuntu Linux
- No preload operating system

Graphics

Graphics\*\*\*[]

| Graphics                | Type       | Memory | Connector                                    | Max Resolution                               | Key Features |
|-------------------------|------------|--------|----------------------------------------------|----------------------------------------------|--------------|
| Intel® UHD graphics 710 | Integrated | Shared | 1x DP 1.4a (HBR2, DSC),<br>1x HDMI® 2.1 TMDS | 4096x2304@60Hz(DP),<br>4096x2160@60Hz(HDMI®) | DirectX® 12  |
| Intel® UHD graphics 730 | Integrated | Shared | 1x DP 1.4a (HBR2, DSC),<br>1x HDMI® 2.1 TMDS | 4096x2304@60Hz(DP),<br>4096x2160@60Hz(HDMI®) | DirectX® 12  |
| Intel® UHD graphics 770 | Integrated | Shared | 1x DP 1.4a (HBR2, DSC),<br>1x HDMI® 2.1 TMDS | 4096x2304@60Hz(DP),<br>4096x2160@60Hz(HDMI®) | DirectX® 12  |
| Intel® Arc™ A310        | Discrete   | 4GB    | 2x DisplayPort™ 1.4a                         | 5120x2880@60Hz(DP)                           | DirectX® 12, |

|             |  |       |  |  |            |
|-------------|--|-------|--|--|------------|
| LP Graphics |  | GDDR6 |  |  | OpenGL 4.6 |
|-------------|--|-------|--|--|------------|

Notes:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

Monitor Support

Monitor Support

Supports up to 2 independent displays via onboard ports (1x DP and 1x HDMI®), more displays support via discrete graphics

Chipset

Chipset

Intel® Q670 chipset

Memory

Max Memory<sup>[1]</sup>

Up to 64GB DDR5

Memory Slots

Two DDR5 UDIMM slots, dual-channel capable

Memory Type

- DDR5-4800
- DDR5-5200
- DDR5-5600

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Storage Support<sup>[1]</sup>

Up to three drives, 1x 3.5" HDD + 1x 2.5" HDD + 1x M.2 SSD

- 3.5" HDD up to 2TB
- 2.5" HDD bay is only for customer self upgrade
- M.2 SSD up to 2TB each<sup>[2]</sup>

Storage Type<sup>\*\*\*</sup>

| Disk Type     | Interface                 | RPM  | Security |
|---------------|---------------------------|------|----------|
| 3.5" SATA HDD | SATA 6Gb/s                | 7.2K | -        |
| M.2 2280 SSD  | PCIe® NVMe®, PCIe® 4.0 x4 | -    | Opal 2.0 |

RAID

No support

Notes:

[1] The max capacity of each disk type is based on the test results with current Lenovo® storage offerings.

[2] 2.5" HDD bay is optional part, only for customer self upgrade purpose and the hard drive is sold separately. Two onboard SATA ports support up to two drives of 2.5" HDD, 3.5" HDD and ODD.

Removable Storage

Optical<sup>\*\*</sup>

- DVD-ROM, SATA connector, slim (9.0mm)
- DVD burner (DVD±RW), SATA connector, slim (9.0mm)
- None

Card Reader

- 3-in-1 card reader (SD, SDHC, SDXC)
- No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

Single speaker, 1W x1

Power Supply

Power Supply\*\*

| Power | Type  | Efficiency | Key Features      |
|-------|-------|------------|-------------------|
| 180W  | Fixed | 85%        | 100-240V, 50-60Hz |
| 260W  | Fixed | 90%        | 100-240V, 50-60Hz |
| 310W  | Fixed | 92%        | 100-240V, 50-60Hz |

DESIGN

Input Device

Keyboard\*\*

- EOS Wireless Keyboard, black
- Lenovo® Calliope Keyboard (USB connector), black
- Lenovo® Traditional Keyboard (USB connector), black
- No keyboard

Mouse\*\*

- Lenovo® Calliope Mouse (USB connector), black
- EOS Wireless Mouse, Black
- No mouse

Mechanical

Form Factor

SFF (8.2L)

Dimensions (WxDxH)<sup>[1]</sup>

92.5 x 297.7 x 339.5 mm (3.6 x 11.7 x 13.4 inches)

Packaging Dimensions (WxDxH)

195 x 395 x 530 mm (7.68 x 15.55 x 20.87 inches)

Weight<sup>[2]</sup>

Around 5.3 kg (11.7 lbs)

Packaging Weight

Around 7.6 kg (16.76 lbs)

Case Color

Black

Bays<sup>[3]</sup>

- 1x 2.5" disk bay (optional)
- 1x 3.5" disk bay
- 1x slim ODD bay

Expansion Slots

- One PCIe® 3.0 x16, low-profile, length ≤ 155mm, height ≤ 70mm
- One PCIe® 3.0 x1, low-profile, length ≤ 155mm, height ≤ 70mm
- Two M.2 slots (one for WLAN, one for SSD)

EOU

Toolless cover, memory, disk, optical, extension card assembly / removal

Stand

- Vertical stand
- No stand

Others

- (Optional) Dust filter
- Supports Smart Power On

---

**Notes:**

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[3] 2.5" HDD bay is optional part, only for customer self upgrade purpose and the hard drive is sold separately. Two onboard SATA ports support up to two drives of 2.5" HDD, 3.5" HDD and ODD.

## CONNECTIVITY

### Network

#### Onboard Ethernet

Gigabit Ethernet, Intel® Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

#### Optional Ethernet

- 2.5 Gigabit Ethernet, Realtek® RTL8125BGS, 1x RJ-45, PCIe® x1
- No optional Ethernet

#### WLAN + Bluetooth®\*\*

- Realtek® Wi-Fi® 6 RTL8852BE, 802.11ax Dual Band 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card
- Intel® Wi-Fi® 6 AX201, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 Card
- Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, Intel® vPro® technology support, M.2 Card
- No WLAN and Bluetooth®

### Ports<sup>[1]</sup>

#### Front Ports

- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with 15W charging
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

#### Optional Front Ports

1x card reader

#### Rear Ports<sup>[2]</sup>

- 4x USB-A (Hi-Speed USB / USB 2.0)
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2, DSC)
- 1x Ethernet (RJ-45)

#### Optional Rear Ports\*\*\*

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), via 2-port USB expansion card, PCIe® x1
- 1x parallel
- 1x serial
- 1x 2nd serial
- 4x serial (via 4-port serial expansion card, PCIe® x1)
- 2x PS/2

---

**Notes:**

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

[2] For video ports on discrete graphics, please see graphics section.

## SECURITY & PRIVACY

## Security

### Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

### Physical Locks

- (Optional) E-lock
- (Optional) Smart Cable Clip
- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

### Chassis Intrusion Switch

- Chassis intrusion switch
- No chassis intrusion switch

### Fingerprint Reader

No fingerprint reader

### BIOS Security

- Administrator password
- Boot sequence control
- Boot without keyboard and mouse
- Certificate based BIOS authentication
- Hard disk password
- Individual USB port disablement
- Power-on password
- Self-healing BIOS
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)

## MANAGEABILITY

### System Management

#### System Management<sup>[1]</sup>

- Intel® vPro® Enterprise
- Non-vPro®

Notes:

[1] Intel® vPro® offers a superset of DASH's defined capabilities.

## SERVICE

### Warranty<sup>[1]</sup>

#### Base Warranty\*\*

- 1-year courier or carry-in service
- 1-year limited onsite service
- 3-year limited onsite service
- No base warranty

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

## ACCESSORIES

### Bundled Accessories

#### Bundled Accessories\*\*\*

- DP to DVI dongle
- DP to HDMI® dongle
- HDMI® to HDMI® cable (1.5m)

- HDMI® to VGA dongle
- Smart Cable (USB-A to USB-C®)
- None

## OPERATING REQUIREMENTS

### Operating Environment

#### Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

#### Relative Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

#### Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

## CERTIFICATIONS

### Green Certifications<sup>[1]</sup>

#### Green Certifications

- (Optional) ENERGY STAR® 8.0
- (Optional) EPEAT™ Silver Registered
- (Optional) EPEAT™ Gold Registered
- ErP Lot 3
- GREENGUARD®
- RoHS compliant
- TCO Certified 9.0

#### Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

### Other Certifications

#### Other Certifications

(Optional) TÜV Rheinland® Ultra Low Noise

#### Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

- Feature with \*\* means that only one offering listed under the feature is configured on selected models.
- Feature with \*\*\* means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



