


HONEYWELL SMART VIEWER

For 35 Series NVRs

Honeywell Smart Viewer (HSV) is designed to connect and manage multiple 35 Series Embedded NVRs.

Featuring a user-friendly interface, HSV can be deployed for device management and configuration, video live view and playback, event management, PTZ control, fisheye camera de-warping and E-map.

This view also features multiple monitor support, multiple display layouts, customized views and tours, two-way audio and global P2P remote connection for efficiency monitoring and operation. HSV supports up to 2048 cameras and multiple NVRs making it ideal for medium to large scale video surveillance systems. With HTTPS and TLS 1.2 encryption streaming and communication between HSV and 35 Series NVRs, customers can increase compliance, reduce potential liability costs and realize the benefits of an end-to-end encrypted and secure video surveillance.



MARKET OPPORTUNITIES

The intuitive user interface, full set of features, HTTPS encryption, multiple site management, and global P2P enabled remote connection make this video management viewer perfect for a wide range of medium and large scale security applications where efficiency is important, compliance is essential and data is protected.

FEATURES AND BENEFITS



- Supports Honeywell 35 Series Embedded NVRs
- Connection to NVR anytime anywhere (local, remote, global P2P)
- Multi-NVR management supports up to 2048 video channel connections



- Supports two way audio through 35S NVR with 35S cameras
- Supports up to 64 live view windows in one single screen
- Supports Windows® 10 (64-bit)
- Auto streaming size to save decode and streaming bandwidth



- Supports receiving video analytic events from 35S cameras through 35S NVR
- Dual monitors configurable to display live view, tour, E-map or event views




- Editable display information on live view
- End to end HTTPS stream encryption
- Video recording and playback management



- Event management and event trigger
- Device management
- PTZ Control
- MFZ and digital zoom
- Fisheye dewarping
- E-map

SMART VIEWER FOR 35 SERIES NVRs

SYSTEM DIAGRAM



TECHNICAL SPECIFICATIONS

SYSTEM	
Supported Device	35 Series NVR
Maximum Video Channels	2048 channels
Max Video Channels Viewed Concurrently	128 channels*
Decoding	CPU, GPU*
Max Managed Devices	32 devices
Device Management	Add, delete, edit, import, export, device group, reboot, restore
User Management	Privileges set based on user and role, according to group / menu / channel / function
Health Report	Device status, CPU status, MEM status
Video Display Split	Equal: 1 / 2 / 4 / 6 / 9 / 16 / 25 / 36 / 64 Focus: 1+5, 1+7, 1+3+28
Live View Screen	Maximum 4
MANAGEMENT	
PTZ Control	Direction Control, Home, Zoom, Focus, Iris, Preset, Pan, Stop, Speed
Live View Operation	Snapshot, Record, Audio, Talk, 3D PTZ, E-PTZ
Video Playback	Device Itself
Max Playback Channels	16
Search Type	Time Line, Out Grid
Local Recording	Yes
E-Map	Map Type : Picture, GIS Layout : Map+3 Video, Map+5 Video
E-Map Format	Picture: Png/JPEG/JPG GIS: OpenStreetMap
Alarm Type	Motion Detection, Smart Motion Detection, Camera Alarm In, NVR Alarm In, Video Lost, Perimeter , Multi Loiter, Tamper Alarm, Crowd Detection, Disk Exception, Disk Full
Alarm Trigger	UI Event : Alarm Pop-Up Window / Video Border Flickers / Video Window Enlarge / Speech / Buzzer Linkage Event : Send E-Mail/PTZ Control / Relay Out
Video Export	MP4
PC/MAC REQUIREMENT	
CPU	Windows version: Intel® Core™ i5-8500 or above Mac version: 2.6 GHz Dual-core Intel Core i5 or above
Memory	Windows version: 8 GB or above Mac version: 8 GB or above
Display Card	Windows version: D1*16 ch display : Intel HD Graphics or above D1*64 ch display : NVIDIA GTX 1050Ti or above Mac version: 16 ch display : Intel HD Graphics 6000 1536 MB or above 64 ch display : AMD Radeon Pro 5300 4 GB or above
Hard Drive	50 GB free space or above
OS	Windows version: Windows 10 / Windows 11 Mac version: Mac OS : Big Sur 11, Monterey 12, or above
Screen Resolution	720P or above

* For more hardware and integration details, please refer to user manual

SMART VIEWER FOR 35 SERIES NVRs

ORDERING	
HN35040100	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 0 TB, 1HD
HN35040101	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 1 TB, 1HD
HN35040102	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 2 TB, 1HD
HN35040104	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 4 TB, 1HD
HN35040106	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 6 TB, 1HD
HN35040108	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 8 TB, 1HD
HN35040110	4 Chs NVR 4k (8 Mp) Support, H.265/H.264, 4 Chs POE, Stream Encryption, 10 TB, 1HD
HN35080200	8 Chs NVR 4K (8 MP) Support, H.265/H.264, 8 Chs POE, Stream Encryption, 0 TB, 2HD
HN35080202	8 Chs NVR 4K (8 MP) Support, H.265/H.264, 8 Chs POE, Stream Encryption, 2 TB, 2HD
HN35080204	8 Chs NVR 4K (8 MP) Support, H.265/H.264, 8 Chs POE, Stream Encryption, 4 TB, 2HD
HN35080208	8 Chs NVR 4K (8 MP) Support, H.265/H.264, 8 Chs POE, Stream Encryption, 8 TB, 2HD
HN35080210	8 Chs NVR 4K (8 MP) Support, H.265/H.264, 8 Chs POE, Stream Encryption, 10 TB, 2HD
HN35080216	8 Chs NVR 4K (8 MP) Support, H.265/H.264, 8 Chs POE, Stream Encryption, 16 TB, 2HD
HN35160200	16 Chs NVR 4K (8 MP) Support, H.265/H.264, 16 Chs POE, Stream Encryption, 0 TB, 2HD
HN35160204	16 Chs NVR 4K (8 MP) Support, H.265/H.264, 16 Chs POE, Stream Encryption, 4 TB, 2HD
HN35160208	16 Chs NVR 4K (8 MP) Support, H.265/H.264, 16 Chs POE, Stream Encryption, 8 TB, 2HD
HN35160210	16 Chs NVR 4K (8 MP) Support, H.265/H.264, 16 Chs POE, Stream Encryption, 10TB, 2HD
HN35160216	16 Chs NVR 4K (8 MP) Support, H.265/H.264, 16 Chs POE, Stream Encryption, 16 TB, 2HD
HN35160220	16 Chs NVR 4K (8 MP) Support, H.265/H.264, 16 Chs POE, Stream Encryption, 20 TB, 2HD


DOWNLOAD HSV



HSV
Productivity

OPEN

Computer version available on <https://myhoneywellbuildingsuniversity.com>



HEVCAdvance™

Android™ is a trademark or registered trademark of Google Inc. in the United States and/or other countries.

Apple® is a trademark or registered trademark of Apple, Inc. in the United States and/or other countries.

Intel® and Core™ are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and/or other countries.

Microsoft® and Windows® are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

ONVIF and the ONVIF logo are trademarks of ONVIF Inc.

HEVC Advance logo is a trademark of HEVC Advance.

Honeywell reserves the right, without notification, to make changes in product design or specifications.

For More Information

buildings.honeywell.com/security

Honeywell Commercial Security

715 Peachtree St NE
Atlanta, GA 30308
1.800.323.4576
www.honeywell.com

HVS-35HSV-01-US(0522)DS-Y
© 2022 Honeywell International Inc.

Honeywell