



Poly Studio R30 USB Video Bar

This document covers Poly Studio R30 (Regulatory Models P032 & P032NR).

Service Agreements

Please contact your Poly Authorized Reseller for information about service agreements applicable to your product.

Safety, Compliance, and Disposal Information

- This equipment is intended for indoor use only.
- This equipment is not intended to be directly connected to outdoor cables.
- Always disconnect the system from power before cleaning or servicing.
- In order to remove all power from this unit, disconnect the power supply mains cord.
- Do not spray liquids directly onto the system when cleaning. Always apply the liquid first to a static-free cloth.
- Do not immerse the system in any liquids or place any liquids on it.
- Do not disassemble this system. To maintain the warranty on the system, a qualified technician must perform service or repair work.
- There are no user serviceable parts inside this product.
- This product is intended to be powered by an external (LPS) power supply - use only the type which is supplied with this product.
- Do not use a power cord that is damaged. This could cause fire or electric shock. Contact the manufacturer for a replacement cord, if necessary.
- Only use a power cord which is appropriately rated and approved relevant to the country of use.
- This equipment is not intended to be operated by children.
- When connecting to the mains supply, connect only to an earthed supply outlet which is installed near the equipment and is easily accessible.
- Keep ventilation openings free from any obstructions.
- The ambient operating temperature rating of this equipment is 0 - 40°C and should not be exceeded.

Installation Instructions

Installation must be performed in accordance with all relevant national wiring rules.

L'Installation doit être exécutée conformément à tous les règlements nationaux applicable au filage électrique.

Plug Acts as Disconnect Device

The socket outlet to which this apparatus is connected must be installed near the equipment and must always be readily accessible.

Part 15 FCC Rules

This device is compliant with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- This device may not cause harmful interference.
- This device must accept any interferences received, including interference that may cause undesired operation.

Class B Digital Device or Peripheral

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Modifications

In accordance with Part 15 of the FCC Rules, the user is cautioned that any changes or modifications not expressly approved by Polycom, Inc. could void the user's authority to operate the equipment.

Radiation Exposure Statement

The antenna used for this transmitter must be installed to provide a separation distance of at least 20 centimeters from all persons and must not be co located or operating in conjunction with any other antenna or transmitter. This device with its antenna complies with FCC's RF radiation exposure limits set

forth for an uncontrolled environment. To maintain compliance, this transmitter must not be co-located or operating in conjunction with any other antenna or transmitter.

Industry Canada

This device complies with RSS210 of the Industry Canada rules. Operation is subject to the two following conditions:

- 1 This device does not cause harmful interference.
- 2 This device must accept any interference received, including interference that may cause undesired operation.

L'émetteur/récepteur exempt de licence contenu dans le présent appareil est conforme aux CNR d'Innovation, Sciences et Développement économique Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

- 1) L'appareil ne doit pas produire de brouillage;
- 2) L'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

The device meets the exemption from the routine evaluation limits in section 2.5 of RSS 102 and compliance with RSS-102 RF exposure, users can obtain Canadian information on RF exposure and compliance.

Le dispositif rencontre l'exemption des limites courantes d'évaluation dans la section 2.5 de RSS 102 et la conformité à l'exposition de RSS-102 rf, utilisateurs peut obtenir l'information canadienne sur l'exposition et la conformité de rf.

This transmitter must not be co-located or operating in conjunction with any other antenna or transmitter. This equipment should be installed and operated with a minimum distance of 20 centimeters between the radiator and your body.

Cet émetteur ne doit pas être Co-placé ou ne fonctionnant en même temps qu'aucune autre antenne ou émetteur. Cet équipement devrait être installé et actionné avec une distance minimum de 20 centimètres entre le radiateur et votre corps.

the device for operation in the band 5150–5250 MHz is only for indoor use to reduce the potential for harmful interference to co-channel mobile satellite systems;


les dispositifs fonctionnant dans la bande 5150-5250 MHz sont réservés uniquement pour une utilisation à l'intérieur afin de réduire les risques de brouillage préjudiciable aux systèmes de satellites mobiles utilisant les mêmes canaux;

FCC and Industry Canada Example Label

See an example of the Poly Studio R30 regulatory labels below.

FCC ID: M72-P032















IC ID:1849C-P032






Poly Studio R30 IC ID: 1849C-P032
 FCC ID: M72-P032
 기가재명칭: USB Video Bar

USB Video Bar / 会议影音设备
 Model No/ 型号/ 모델명 : P032
 Cnsl PN : 2201-69390-001
 Input / 输入 : 12VDC --- 3A

This device complies with Part 15 of the FCC Rules.
 Operation is subject to the following two conditions:
 (1) this device may not cause harmful interference and
 (2) this device must accept any interference received,
 including interference that may cause undesired operation.

CAN ICES-3 (B)/NMB-3(B) CCAH22LP2500T1
 Made in China / 中国制造 / 제조국가: 중국
 Manufacturer / 制造商 / 상호명: POLYCOM, INC.


Poly Studio R30




USB Video Bar
 Model No : P032NR
 Cnsl PN : J2201-69360-001
 Input : 12VDC --- 3A

This device complies with Part 15 of the FCC Rules.
 Operation is subject to the following two conditions:
 (1) this device may not cause harmful interference and
 (2) this device must accept any interference received,
 including interference that may cause undesired operation.

CAN ICES-3 (B)/NMB-3(B)
 Manufacturer : POLYCOM, INC.

Made in Taiwan
 Country of Manufacturer: Mexico
 1668-08416-422A

Japan VCCI

This device is only approved to transmit indoors within the W52 and W53 bands for Japan:

- W52(5180MHz / 5200MHz / 5220MHz / 5240MHz)
- W53(5260MHz / 5280MHz / 5300MHz / 5320MHz)

Polycom, Inc. is a fully-owned subsidiary of Plantronics Inc., Plantronics Limited is 100% owned by Plantronics BV.

Polycom is a trademark of Plantronics Inc. registered in the EU, UK, US and other countries.

この装置は、クラスB機器です。この装置は、住宅環境で使用することを目的としていますが、この装置がラジオやテレビジョン受信機に近接して使用されると、受信障害を引き起こすことがあります。

取扱説明書に従って正しい取り扱いをして下さい。

VCCI – B

EEA

CE Mark

P032 is marked with the CE mark. This mark indicates compliance with EU Radio Equipment Directive (RED) 2014/53/EU, RoHS Directive 2011/65/EU, and Commission Regulation 278/2009.

P032NR is marked with the CE mark. This indicates compliance with the EU EMC Directive (EMCD) 2014/30/EU, Low Voltage Directive (LVD) 2014/35/EU, RoHS Directive 2011/65/EU and Commission Regulation 278/2009.

A full copy of the Declaration of Conformity for each model can be obtained at www.poly.com/conformity

Poly Studio R30 (P032) Radio Operating Frequency

The frequency ranges in the following table apply to Poly Studio R30 (P032).

Radio Operating Frequency

Frequency Range	Maximum Transmit Power
2.400GHz – 2.483GHz	16.8 dBm e.i.r.p
5.180GHz – 5.825GHz	17.2 dBm e.i.r.p

Operating Ambient Temperatures

- Operating temperature: +32 to 104°F (0 to 40°C)
- Relative humidity: 5% to 95%, noncondensing
- Storage temperature: -40 to +160°F (-40 to +70°C)

Waste Electrical and Electronic Equipment (WEEE)



All Polycom products that fall within the scope of the EU WEEE Directive carry the crossed wheeled bin symbol which advises customers not to recycle electronic products in the domestic waste stream but to recycle them safely as e-waste.

Restriction of Hazardous Substances Directive (RoHS)

All Polycom products comply with the requirements of the EU RoHS Directive. Statements of compliance can be obtained by contacting TypeApproval@poly.com.

United Kingdom

UK Declaration of Conformity

Hereby, Plantronics Limited (UK) declares that the radio equipment type P032 is in compliance with the relevant statutory requirements.

A copy of the Declaration of Conformity to the essential requirements may be found at www.poly.com/conformity

Taiwan

Radio statements:

取得審驗證明之低功率射頻器材，非經核准，公司、商號或使用者均不得擅自變更頻率、加大功率或變更原設計之特性及功能□

低功率射頻器材之使用不得影響飛航安全及干擾合法通信；經發現有干擾現象時，應立即停用，並改善至無干擾時方得繼續使用。前述合法通信，指依電信管理法規定作業之無線電通信。低功率射頻器材須忍受合法通信或工業、科學及醫療用電波輻射性電機設備之干擾。

使用此產品時應避免影響附近雷達系統之操作。

Taiwan RoHS Table

設備名稱 Equipment name: 會議影音設備 型號 (型式) Type designation (Type): P032						
單元 Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛 Lead (Pb)	汞 Mercury (Hg)	鎘 Cadmium (Cd)	六價鉻 Hexavalent chromium(Cr ⁺⁶)	多溴聯苯 Polybrominated biphenyls(PBB)	多溴二苯醚 Polybrominated diphenyl ethers(PBDE)
金屬部件 Metal Parts	-	○	○	○	○	○
印刷電路板組件 Circuit Modules	-	○	○	○	○	○
外殼 Shell	○	○	○	○	○	○
攝像頭組件 Camera Modules	-	○	○	○	○	○
電源 Power Supply	-	○	○	○	○	○

備考 1. “超出 0.1 wt %” 及 “超出 0.01 wt %” 係指限用物質之百分比含量超出百分比含量基準值。
Note 1: “Exceeding 0.1 wt %” and “exceeding 0.01 wt %” indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.

備考 2. “○” 係指該項限用物質之百分比含量未超出百分比含量基準值。
Note 2: “○” indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence.

備考 3. “-” 係指該項限用物質為排除項目。
Note 3: The “-” indicates that the restricted substance corresponds to the exemption.

Brazil

Este equipamento não tem direito à proteção contra interferência prejudicial e não pode causar interferência em sistemas devidamente autorizados.

China

China RoHS Table

所有在中华人民共和国境内进口或销售的电子信息产品必须附上本文件 Include this document with all Electronic Information Products Imported or sold in the People's Republic of China						
视频会议设备, 话筒和会议电话 Video Conference Equipment, Handset, and Conference Phones	有毒有害物质或元素 Hazardous Substances					
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr6+)	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
金属部件 Metal Parts	X	0	0	0	0	0
印刷电路板组件 Circuit Modules	X	0	0	0	0	0
外壳 Shell	0	0	0	0	0	0
摄像头组件 Camera Modules	X	0	0	0	0	0
电源 Power Supply	X	0	0	0	0	0

本表格依据 SJ/T 11364 的规定编制。

0: 表示该有害物质在该部件所有均质材料中的含量均在 GB/T 26572 规定的限量要求以下。Indicates that the concentration of the hazardous substance in all homogeneous materials in the part is below the relevant threshold of the GB/T 26572 standard.

X: 表示该有害物质至少在该部件的某一均质材料中的含量超出 GB/T 26572 规定的限制要求。Indicates that the concentration of the hazardous substance in all homogeneous materials in the part is above the relevant threshold of the GB/T 26572 standard.

本表显示, 宝利通公司 (Polycom, Inc.) 生产的该电子信息产品, 由零部件供应商提供的部件中可能包含有毒有害物质, 其含量满足或超出 SJ/T11364 标准规定的限量要求。This table shows some hazardous substances may be found in the supply chain of Polycom, Inc. and indicate the concentration is below or above the SJ/T11364 standard.

环保使用期 (如无标记) Environment Friendly Use Period (If Unmarked)

会议影音设备	
--------	---

Singapore

P032 complies with the relevant IMDA radio standards (DA101619).

Mexico

IFETEL RF Statement

“La operación de este equipo está sujeta a las siguientes dos condiciones:

- (1) es posible que este equipo o dispositivo no cause interferencia perjudicial y
- (2) este equipo o dispositivo debe aceptar cualquier interferencia, incluyendo la que pueda causar su operación no deseada.

Poly Take Back

In addition to any mandated take back requirement, Poly offers free recycling of its branded products to business users. Detailed information is available at <https://www.poly.com/ie/en/company/corporate-responsibility/environment/takeback-recycle-program>

Getting Help and Copyright Information

GETTING HELP

For more information about installing, configuring, and administering Poly products or services, go to [Poly Online Support Center](#).

Poly
345 Encinal Street
Santa Cruz, California
95060

©2022 Poly. All other trademarks are the property of their respective owners.