





## Applications

## Features

- **Thunderbolt Certified, USB4 Compatible Dock**: Provides driverless compatibility with Windows 11 and macOS 15 / 26 for seamless plug-and-play use; Works with Thunderbolt 5/4 and USB4 host devices, ensuring high-performance connectivity across modern systems
- **Triple 4K Display Support on Windows**: Connect up to three extended 4K 144Hz displays via HDMI, DisplayPort, and USB-C, delivering a high-performance multi-monitor workspace for productivity, creative workflows, and multitasking; Max Dual 6K 60Hz on Mac
- **140W Laptop Power Delivery**: Includes a 180W power adapter to simultaneously charge high-powered laptops, such as the MacBook Pro (140W PD), and power all downstream ports; Features a 30W USB-C Port for charging mobile devices, tablets, or other devices
- **2.5Gbps Ethernet and SD 4.0**: Transfer large files or work directly from the cloud with a wired 2.5GbE connection that supports 9k Jumbo Frames for lower CPU overhead; Built-in SD 4.0 and microSD 4.0 slots deliver fast transfers from UHS-II memory cards
- **The IT Pro's Choice**: Our docking stations are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and cross-platform compatibility; Built to support large-scale deployments, Windows 11 upgrades, and the shift to AI-enabled PCs

---

### Hardware

Warranty	3 Years
4K Support	Yes
Displays Supported	3
Audio	Yes
Interface	Thunderbolt 5 Thunderbolt 4 USB4 (40Gbps)

Compatible Lock Slot	Kensington Standard Slot (K-Slot) Kensington Nano Slot
----------------------	---

---

**Performance**

Wake On Lan	Yes
Maximum Data Transfer Rate	40Gbps
Maximum Digital Resolutions	DisplayPort: 3840x2160 @ 144hz  HDMI: 3840x2160 @ 60hz
Type and Rate	Thunderbolt 5 - 40 Gbit/s  USB4 - 40 Gbit/s  USB4 - 40 Gbit/s  Thunderbolt 5 - 40 Gbit/s
UASP Support	Yes
Supported Charging Outputs	USB-C (30W)  BC 1.2 (1.5A)  USB-C (18W)  USB-C (30W)
Compatible Networks	2.5G/1G/100Mbps/10Mbps
PXE	Yes
Full Duplex Support	Yes

---

**Connector(s)**

External Ports	1 - 3.5mm Stereo Female 4 pos  1 - DisplayPort  1 - microSD
----------------	---

- 1 - HDMI
- 1 - SD Slot
- 2 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)
- 2 - USB 3.2 Type-C (24 pin, Gen 2, 10Gbps)
- 1 - USB 3.2 Type-A (9 pin, Gen 2, 10Gbps)
- 2 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)
- 1 - USB 3.2 Type-A (9 pin, Gen 2, 10Gbps)
- 1 - 3.5mm Stereo Female 4 pos
- 2 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)
- 1 - RJ-45
- 1 - RJ-45
- 1 - Thunderbolt 5
- 1 - Thunderbolt 5
- 1 - DisplayPort
- 1 - HDMI
- 1 - Thunderbolt 5
- 1 - Thunderbolt / USB4

Host Connectors

---

**Software**

- |                  |  |
|------------------|--|
| OS Compatibility | Windows 11<br>macOS Sequoia (15.0)<br>macOS Tahoe (26.0) |
|------------------|--|

---

**Special Notes / Requirements**

- |                               |   |
|-------------------------------|---|
| System and Cable Requirements | , * Thunderbolt 3 (TB3) is not supported (other than on TB3-based Apple M1/M2/M3 Standard chipsets., ** M1, M2, and M3 Standard chipsets will work with a single display, while M4 Standard an M1/M2/M3/M4 Pro/Max chipsets will work with dual displays., , *** Achieving high refresh rates may require DSC (Display Stream Compression) support from both the monitor and the host GPU. The bit depth and color depth may be adjusted to enable higher refresh rates, and results may vary depending on OS updates. , , **** If monitor recognition issues |
|-------------------------------|---|

occur, connect the monitor with the lowest refresh rate first, as high refresh rate monitors may consume all available bandwidth.,  
\*\*\*\* For external display compatibility over a single Thunderbolt connection on different Windows systems, please consult the computer manufacturer's website.,

Note This docking station is not supported on Thunderbolt 3 host devices

It is recommended that all connected monitors are of the same make and model

---

### Indicators

LED Indicators	1 - Power LED: , Orange Powered On , Blue Powered On and Connected to Host , Off when not Powered On  2 - RJ45 LEDs: , , Right LED Link/Activiy: , Solid Green = Network Port is Connected , Flashing Green = Network Port is Active , , Left LED Link Speed: , Solid Green = 2.5Gbps , Solid Amber = 1000/100/10Mbps ,
----------------	---

---

### Power

Output Voltage	20V DC
Output Current	9A
Center Tip Polarity	Positive
Plug Type	N

---

### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0% to 90% (non-condensing)

---

### Physical Characteristics

Color	Space Gray
Material	Plastic
Cable Length	31.5 in [800 mm]
Product Length	3.5 in [90 mm]
Product Width	0.9 in [2.2 cm]
Product Height	1.2 in [3 cm]

Weight of Product 2.2 oz [62 g]

---

**Packaging Information**

Package Length 6.7 in [16.9 cm]  
Package Width 11.9 in [30.2 cm]  
Package Height 2.3 in [5.9 cm]  
Shipping (Package) Weight 3.4 lb [1.5 kg]

---

**What's in the Box**

Included in Package

- 1 - Thunderbolt 5 Docking Station
- 1 - Thunderbolt 5 Host Cable
- 1 - Universal Power Adapter (North America)
- 1 - Product Documentation

---

***\*Product appearance and specifications are subject to change without notice.***