

# ThinkStation P3 Tiny

Designed for ultimate productivity, this compact 1-liter form factor powered by up to 13th Gen Intel Core i9 Processor lets users handle the most demanding workloads without compromising on efficiency. Enhance productivity with optional Wi-Fi 6E that enables faster connection speeds even in densely congested areas while with optional Thunderbolt 4 port, connect devices and share files at high speed. Security features including discrete TPM 2.0, Kensington security slot, and BIOS security keeps data well-protected.



## Professional machines for advanced users

ThinkStation P3 Series workstations provide affordable power-computing with a choice of processor technologies, expansion bays and support for multiple storage drives.

Configured with up to 4TB of high-speed storage via 2x M.2 PCIe SSD modules and up to 64GB DDR5 memory, this device offers powerful processing capabilities enabling users to multitask and store memory-intensive files without any hassle.

To view and compare detailed spreadsheets, professionals can connect to up to 4 independent displays via an onboard Display Port, HDMI, VGA, or USB-C port.

EPEAT Gold, ENERGY STAR 8.0, ErP Lot 3, TCO Certified 9.0, RoHS compliant makes this device energy-efficient.

## Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### On-site Service

If a problem can't be fixed remotely, we will visit your location  
 Normally next business day service  
 Agreed appointment times

## Accessories

### ThinkCentre Tiny VESA Mount II

Supports mounting of a ThinkCentre Tiny to the back of VESA-compatible displays  
 Can be used separately or combined with other options for secure mounting  
 Simple 4-screw design keeps the device securely attached to the mount



PN: 4XF0N03161

# ThinkStation P3 Tiny

## Performance

### Processor

Up to one 13th Gen Intel Core i3/i5/i7/i9

### Operating System

Windows 11 Pro for Workstations  
 Windows 11 DG Windows 10 Pro 64 for Workstations  
 Ubuntu Linux LTS  
 Red Hat Enterprise Linux (certified only)

### Graphics

Intel UHD Graphics 730 (integrated) Intel UHD Graphics 770 (integrated)  
 NVIDIA T400  
 NVIDIA T1000 4GB  
 NVIDIA T1000 8GB

### Chipset

Intel Q670 Chipset

### Memory <sup>1</sup>

Up to 64GB, 2x SO-DIMM

<sup>1</sup>The max memory is based on the test results with current Lenovo memory offerings.

### Storage <sup>2</sup>

Up to 2x 2TB M.2 PCIe NVMe SSD

<sup>2</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings.

## Design

### Dimensions <sup>3</sup>

179 x 182.9 x 37mm (7.05 x 7.2 x 1.5 inches, with rubber feet)

<sup>3</sup>The system dimensions may vary depending on configurations.

### Weight <sup>4</sup>

1.4 kg (3 lbs, maximum configuration)

<sup>4</sup>The system weight is approximate and may vary depending on configurations

## Connectivity

### Ethernet

One onboard Gigabit Ethernet  
 Additional Ethernet options via PCIe adapter

### WLAN + Bluetooth <sup>5</sup>

802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.1\*  
 Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1

<sup>5</sup>Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

## Security & Privacy

Discrete TPM 2.0  
 Cable lock\*  
 Kensington Security Slot, 3 x 7 mm  
 Chassis intrusion switch

## Manageability

Intel vPro Enterprise with Intel AMT 16.0\*

<sup>6</sup>Intel vPro offers a superset of DASH's defined capabilities.

## Certifications

### Green Certifications <sup>7 8</sup>

EPEAT Gold Registered  
 ENERGY STAR 8.0  
 ErP Lot 3  
 TCO Certified 9.0  
 RoHS compliant

<sup>7</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>8</sup>EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

### Other Certifications

MIL-STD-810H