

Product data sheet

Specifications



Roof Fan Tray 120V 50/60HZ for NetShelter WX Enclosures



AR8206ABLK

Overview

Presentation	The Rack Fan Tray is a low cost solution that aids in heat removal from a NetShelter Enclosure. The system easily installs into the top of the enclosure and expels heat from the roof of the rack. Wall-mounted enclosures have the additional option of installing the rack fan tray systems in the base of the rack as well. The fan trays are designed to promote bottom to top airflow within the enclosure.
Lead time	Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Number of cables	1
Provided equipment	Installation guide 1 x IEC to NEMA 5-15P power cord 2 x Fans

Physical

Color	Black
Height	2.1 in (5.4 cm)
Width	12.5 in (31.8 cm)
Depth	6.9 in (17.5 cm)
Net Weight	4.01 lb(US) (1.82 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
------------------------	-------

Conformance

Product Certifications	CSA UL Listed
-------------------------------	------------------

Ordering and shipping details

GTIN	731304225201
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number of Units in Package 1	1
Package 1 Height	2.6 in (6.5 cm)
Package 1 Width	9.4 in (23.8 cm)
Package 1 Length	13.1 in (33.4 cm)
Package 1 Weight	6.02 lb(US) (2.73 kg)

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH


Resource performance


 Take-Back Program Available

Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
