
OVERVIEW



1. Power button (with fingerprint reader)	6. USB-A (USB 5Gbps), Always On
2. microSD card reader	7. HDMI
3. USB-A (USB 5Gbps)	8. Thunderbolt 4
4. Kensington Nano Security Slot	9. Headphone / microphone combo jack (3.5mm)
5. USB-C (USB 10Gbps), with USB PD 3.0 & DP 1.4	

PERFORMANCE

Processor

Processor Family

Intel® U Series Core Ultra 5 / 7 Processor (Series 2)

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	NPU
Core Ultra 5 225U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 1.5GHz / E-core 1.3GHz / LPE-core 700MHz	P-core 4.8GHz / E-core 3.8GHz / LPE-core 2.4GHz	12MB	Intel® Graphics	Intel® AI Boost, up to 12 TOPS
Core Ultra 7 255U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 2GHz / E-core 1.7GHz / LPE-core 700MHz	P-core 5.2GHz / E-core 4.2GHz / LPE-core 2.4GHz	12MB	Intel® Graphics	Intel® AI Boost, up to 12 TOPS

AI (Artificial Intelligence)

AI PC Category

AI PC[1]

NPU

Integrated Intel® AI Boost, up to 12 TOPS

Notes:

[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft® Copilot key or using Win + C.

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- No preload operating system

Graphics

Graphics

Graphics	Type	Memory	TGP	Key Features
Intel® Graphics	Integrated	Shared	Share CPU TDP	DirectX® 12.2

Monitor Support

Monitor Support[1]

Supports up to 4 independent displays (native display and 3 external monitors via HDMI®, USB-C® and Thunderbolt™)
• HDMI® supports up to 4096x2160@60Hz
• USB-C® supports up to 5120x2880@60Hz
• Thunderbolt™ supports up to 5120x2880@60Hz

Notes:

[1] Refresh rates >60hz also supported, however max resolution will be limited.

Chipset

Chipset

Intel® SoC (System on Chip) platform

Memory

Max Memory[1]

Up to 32GB DDR5-5600 offering

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type

DDR5-5600

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Max Storage Support[1]

Up to two drives, 2x M.2 SSD
• M.2 2280 SSD up to 2TB each

Storage Slot[2]

Two M.2 2280 PCIe® 4.0 x4 slots

Storage Type**

Disk Type	Interface	Offering	Security
M.2 2242 SSD[3]	PCIe® NVMe®, PCIe® 4.0 x4	512GB / 1TB	Opal 2.0
M.2 2242 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB	-

Notes:

[1] The system supports dual SSD via two M.2 slots, but Lenovo® only offers one SSD configuration, another SSD slot for user self-extension.
The max storage capacity is only technical readiness and may be different from current Lenovo® storage offerings.
[2] The actual data transfer rate of the following PCIe® interface also depends on the capabilities of the connected PCIe® device. The listed values represent theoretical maximums.
PCIe® 3.0 (x2 / x4): 2 GB/s (16 Gbps) / 4 GB/s (32 Gbps);
PCIe® 4.0 (x2 / x4): 4 GB/s (32 Gbps) / 8 GB/s (64 Gbps);
PCIe® 5.0 (x2 / x4): 8 GB/s (64 Gbps) / 16 GB/s (128 Gbps).
[3] SSD with Opal 2.0 is available for Romania only.

Removable Storage

Card Reader

microSD card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®, audio by HARMAN

Microphone

Dual-microphone array with smart noise-cancelling

Camera**

- FHD 1080p + IR hybrid, with privacy shutter, fixed focus
- FHD 1080p, with privacy shutter, fixed focus

Battery

Battery

60Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr)[1]

Max Battery Life[2]

MobileMark® 30@250nits: 11.2 hr
PCMark 10@120nits: 19 hr

Notes:

[1] Rapid charge is only guaranteed when the computer is turned off or in standby mode or in hibernation mode. When the computer is powered on, the Charge Time will vary depending on system power consumption and AC adapter power.
[2] All battery life claims are approximate maximum and based on results using the MobileMark® 2014, MobileMark® 2018,

MobileMark® 25, MobileMark® 30, JEITA 2.0, JEITA 3.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary depending on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter[**][1]

- 65W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® slim (2-pin, wall-mount) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

[1] AC adapter offerings depend on the country.

Special Features

Special Features

Modern Standby

DESIGN

Display

Display

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
14"	WUXGA (1920x1200)	Multi-touch	IPS[1]	300nits	Glossy, Anti-fingerprint	16:10	1000:1	100% sRGB	60Hz	89° / 89° / 89° / 89°	Corning® Gorilla® Glass, Dolby Vision®, Eyesafe® Certified 2.0

Touchscreen

OGM (One Glass Metal mesh) multi-touch, supports 10-point touch

Screen-to-Body Ratio

90%

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Multi-mode

Multi-mode

Laptop, tent, stand, and tablet modes supported by 360° hinge

Input Device

Pen

- Lenovo® Yoga® Pen
- No pen (purchase separately)

Keyboard

6-row, spill-resistant, multimedia Fn keys, key travel 1.5mm, Copilot key

Keyboard Backlight

LED backlight

Touchpad

Buttonless glass-like Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Mechanical

Dimensions (WxDxH)[1]

313 x 224 x 16.9-18.5 mm (12.32 x 8.82 x 0.67-0.73 inches)

Weight[2]

Starting at 1.64 kg (3.62 lbs)

Case Color

Luna grey, dual-tone design

Case Material

Aluminium (top), aluminium (bottom)

Surface Treatment

Anodizing sandblasting

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth®[1]

- Wi-Fi® 6, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 card
- Wi-Fi® 6E, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card[2]

WWAN

No support

Ethernet

No onboard Ethernet

Notes:

[1] Bluetooth® may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

[2] Wi-Fi® 6E operation is subject to the regulation rules in each country.

Ports[1]

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 and DisplayPort™ 1.4
- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

Docking

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.
For more compatible docking solutions, please visit Docking for ThinkBook® 14 2-in-1 G5 IAU

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader

Touch style fingerprint reader on side power button, match-on-chip

BIOS Security

- Hard disk password
- Power-on password
- Supervisor password
- User password
- Self-healing BIOS
- More BIOS security features, please visit BIOS Simulator[1]

Other Security

- Camera privacy shutter
- (Optional) IR camera for Windows® Hello (facial recognition)

Notes:

[1] The BIOS simulator is just for reference. Default settings and some options may vary depending on the hardware, operating system and BIOS version.

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 2-year (1-yr battery) courier or carry-in service
- No base warranty

ACCESSORIES

Bundled Accessories

Bundled Accessories[1]

None

Notes:

[1] For more compatible accessory solutions, please visit Accessories for ThinkBook® 14 2-in-1 G5 IAU.

OPERATING REQUIREMENTS

Operating Environment

Temperature[1]

- At altitudes up to 2438 m (8,000 ft)
  - Operating: 5°C to 35°C (41°F to 95°F)
  - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
  - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ENVIRONMENTAL

Sustainability

Material[1]

50% recycled aluminum on top cover and bottom cover
25% PCC recycled plastic used in the battery pack enclosure
50% PCC recycled plastic used in keycaps
30% PCC recycled plastic used in speaker enclosure
90% PCC recycled plastic used in standard 65W adapter
FSC certified content in carton and accessory box
Dry pressed pulp cushion
100% use of paper in sealing label and tape
Bamboo fiber bag and screen sheet

Notes:

[1] PCC: Post Consumer Content, recycled materials from customers.

CERTIFICATIONS

Green Certifications[1]

Green Certifications[2]

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered[3]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit https://compliance.lenovo.com.
[2] EPEAT™ registration and ENERGY STAR® certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.
[3] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.


intel.


intel.


intel.


intel.


ThinkBook
intel.


intel.