




NetShelter™ SX Advanced Enclosures

Get ready for AI workloads with even higher density racks


Taller, deeper, stronger racks designed for AI workloads and ready for rack, stack, and ship. NetShelter SX Advanced offers:

- **Uncompromised shipping protection** designed to safely load, transport, unload, and deploy a rack with IT equipment pre-installed
- **Maximized space** to build high-density AI infrastructure, accommodating large-depth servers and seamless integration of liquid cooling components
- **Higher weight loading capacity** to fit more equipment in each rack for a smaller IT footprint, reducing data center costs




Hassle-free onsite deployment:


Safely load, transport, unload, and deploy a rack with up to 3500 lbs. (1600 kg) of IT equipment installed.



Remove outer wrap layers



Install and test IT equipment



Reapply protective packaging

NetShelter SX Advanced technical specifications

	NetShelter SX Advanced	
Static load	4250 lb. / 1950 kg	
Dynamic load	3500 lb. / 1600 kg	NEW
Shipping load (with Shock Packaging only)	3500 lb. / 1600 kg	NEW
Shock packaging	✓	NEW
Equipment mounting rails	19" EIA, adjust in .5 in. (12.7 mm) increments	NEW
Door perforation	80%	
Front door swing	130°, reversible, curved front	
Rear door swing	130°, flat front	
Side panels	Split, lockable	
Baying kit	Included	
Roof	4 extra large cable entry points	
Bottom plate	Optional	
Locking	3-point locking	
Casters & leveling feet	Included	
Rear accessory	Full-height 0U accessory channels*	
Door handles**	Key locking**	
Doors and sides	Spare doors and sides available (check se.com or contact sales representative)	
Toolless features	Doors, roof, roof cable trough (optional)	
Certifications	UL, ISTA, RoHS, REACH	
Warranty	5 years	



Top view:
4 extra-large cable entry points.



*See SKUs for exact model specification. **Options for combination lock, keycard access, and unique key cylinders available.

Model Without Shock Packaging	Available in*		Model With Shock Packaging	Available in*			Rack Units	Dimensions (mm)			Max Equipment Depth (mm)	0U Accessory Channels	Doors & Sides
								H	W	D			
AR9550B2	INTL		AR9550SPB2	NAM	EUR	INTL	42	1991	750	1295	1143	4	✓
AR9580B2	INTL		AR9580SPB2	NAM	EUR	INTL	42	1991	800	1295	1143	4	✓
AR9555B2	INTL		AR9555SPB2	INTL			45	2124	750	1295	1143	4	✓
AR9585B2	INTL		AR9585SPB2	INTL			45	2124	800	1295	1143	4	✓
AR9557B2	EUR	INTL	AR9557SPB2	NAM	EUR	INTL	48	2258	750	1295	1143	4	✓
AR9587B2	EUR	INTL	AR9587SPB2	NAM	EUR	INTL	48	2258	800	1295	1143	4	✓
AR9657B2	EUR	INTL	AR9657SPB2	NAM	EUR	INTL	48	2258	750	1470	1318	4	✓
			AR9558SPB2	NAM	EUR		52	2436	750	1295	1143	4	✓
			AR9588SPB2	NAM	EUR		52	2436	800	1295	1143	4	✓
			AR9658SPB2	NAM	EUR		52	2436	750	1470	1318	4	✓

Regional availability key: **NAM** = North America; **EUR** = Europe; **INTL** = International (locations other than NAM or EUR)

*Commercial Reference (CR) availability is generalized and may not cover all countries. Please check our website to confirm specific CR availability in your country.

Learn more

Life Is On

Schneider
Electric