0**0111011011**00101010190111



Compact VGA Switches (2 x 1 and 4 x 1)



Switch between two or four VGA video sources to a single monitor.

FEATURES

- Control manually by pushing a button or via an RS-232 control device (serial cable is included).
- Buffered video output protects the signal integrity.
- You can also blank and unblank an output via a serial port command.
- LED indicates selected input source.
- Fit into tight spaces and withstand heavy use.
- Audio versions feature an RFI shielded steel enclosure.

AC505A-2A-R2, AC506A, AC506A-4A only:

- Set up the switch to cycle between video sources automatically.
- Automode detects active inputs and switches to them automatically. You assign port priority.

Compact VGA Switches support video cable distances up to 150 feet at up to 1600 x 1200 resolution.



OVERVIEW

Compact VGA Switches from Black Box go much farther than ordinary video switches in both the distance and resolution they support.

These solid-state, electronic switches not only use boosters to drive VGA video signals up to 150 feet (45.7 m), they also offer a crisp resolution of up to 1600 x 1200.

Use the switches, for instance, in a conference room where two or four laptop users can take turns projecting their screen images onto a single big-screen VGA monitor seen by all. They're also useful anywhere you need to use fewer monitors for displaying video sources.

Control switching via an attached RS-232 device (serial control cable is included). You can also blank output from one source or switch manually.

To scan between VGA inputs at certain time intervals or display VGA inputs based on their priority, choose the 2 x 1 switch with audio (AC505A-2A-R2) or one of the 4 x 1 switches (AC506A, AC506A-4A).

For audio support, order the 2 x 1 with Audio (AC505A-2A-R2) or 4 x 1 with Audio (AC506A-4A). They enable you to switch a single monitor with audio between two or four video/audio sources.

WHAT'S INCLUDED

AC505A, AC505A-2A-R2, AC506A, AC506A-4A:

- ◆ Compact VGA Switch
- ◆ Serial cable
- ♦ User's manual

AC505A and AC506A also include:

◆ Push button cable

TECH SPECS

Resolution (Maximum) — 1600 x 1200 Video Bandwidth — AC505A-AC506A: 250 MHz; AC505A-2A-R2, AC506A-4A: 200 MHz Video Level — 0 to 0.7 V p-p CE Approval — Yes Connectors — Video input: (2) or (4) HD15 F; Video output: (1) HD15 F;

Distance (Maximum) — 150 ft. (45.7 m)

Serial: AC505A-AC506A: (1) 3.5-mm F (RS-232); AC505A-2A-R2, AC506A-4A: (1) DB9 F (RS-232); Audio: AC505A-2A-R2: Input: (2) 3.5-mm F;

Output: (1) 3.5-mm F; AC506A-4A: Input: (4) 3.5-mm F;

Output: (1) 3.5-mm mini-stereo Power — AC505A-AC506A: Input: 110 VAC, 60 Hz; Output: 6 VDC at 300 mA center positive; AC505A-2A-R2, AC506A-4A: Input: 120 VAC, 60 Hz;

Output: 12 VDC at 300 mA center positive

Size — AC505A: 1.25"H x 4.25"W x 2.5"D (3.2 x 10.8 x 6.4 cm); AC506A: 1.25"H x 8.25"W x 2.5"D (3.2 x 21 x 6.4 cm); AC505A-2A-R2, AC506A-4A: 1.7"H x 8.4"W x 2.7"D (4.3 x 21.3 x 6.9 cm)

Code Item

Compact VGA Switches

2 x 1 2 x 1 with Audio 4 x 1

4 x 1 with Audio

AC505A AC505A-2A-R2 AC506A AC506A-4A

9/2/2009 724-746-5500 blackbox.com 2 of 2 #26661