Product data sheet

Specifications





! To be discontinued

Rack Air Removal Unit SX 100-240V 50/60HZ for NetShelter 600mm enclosures.

ACF400

! To be discontinued on: Aug 30, 2024

① To be end-of-service on: Dec 31, 2027

Product availability: Stock - Normally stocked in distribution facility

Overview

Net Weight

Mounting preference

Presentation	High-density equipment creates an environment where traditional air distribution methods are often not effective. Densely packed enclosures can cause IT equipment to overheat, resulting in downtime. The Rack Air Removal Unit SX captures exhaust heat, returns the warm air to the plenum and eliminates hot spots from the data center. Through automatic fan speed control based upon temperature, the fans will self-adjust for optimal performance. With a unit-mounted LCD display, users can view temperatures at the rack, monitor alarm conditions and adjust unit set points. The integrated network management card allows for remote monitoring and control. This space-saving solution mounts to the back of either the NetShelter SX or VX enclosure, requiring zero U space.
Lead time	Usually in Stock
Main	
Main Input Voltage	100 V 120 V 200 V 208 V 230 V
Input Connection Type	IEC 60320 C14 NEMA 5-15P
Number of cables	2
Provided Equipment	Documentation CD Installation guide Operations and maintenance manual
General	
Air Discharge Patterns	Upflow Ducted
Air flow	1600 ft³/min (755.1 l/s)
Physical	
Color	Black
	75.5 in (191.8 cm)
Width	23.5 in (59.7 cm)
Depth	10.0000000000 in (25.4 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

148.28 lb(US) (67.26 kg)

No preference

Jul 25, 2024 Life Is On Schneider

Mounting Mode Not rack-mountable

Input

Input power	1200 W	
Input Frequency	50/60 Hz	

Conformance

Listed E
55022 Class A 55024 C Part 15 class A S-003 61000-3-2

Environmental

Ambient Air Temperature for Operation	32.0000000000122.00000000000 °F (050 °C)
Ambient Air Temperature for Storage	32.0000000000122.00000000000 °F (050 °C)
Relative Humidity	095 %
Storage Relative Humidity	095 %
Storage altitude	015000 ft (0.00000000004572.0000000000 m)
Acoustic level	79 dBA

Communications & Management

Control panel Multi-function LCD status and control console

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304302155
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	198.4 lb(US) (90 kg)

Contractual warranty

Warranty 1 year (parts only)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov