

APC

Smart-UPS Modular Ultra

The most sustainable Modular UPS of its kind

The most trusted UPS brand provides more power in a smaller size than ever with the agility to scale power or runtime.

apc.com/smart-ups-modular-ultra

Life Is On



We invented the modular UPS, now we are reinventing it.



2.5x more scalable power protection in half the size with Lithium-ion batteries

The world's most popular UPS is now available with a compact, modular design and improved battery life. APC Smart-UPS Modular Ultra offers trusted, premium power protection to ensure network and data availability. Designed for local edge environments and row data centers, the Smart-UPS Modular Ultra provides consistent and reliable connectivity at the most critical moments. For the first time, scale up to 20kW of single-phase power protection in a smaller, lighter and more powerful modular UPS in a rack mount or standalone tower solution. More scalable power in less space enables you to adapt fast and scale as your business grows. Increased UPS battery life and fewer maintenance service costs provide a lower total cost of ownership over 10 years.

That's Certainty in a Connected World.

The most sustainable modular UPS of its kind

Best-in-class embedded carbon reduction, agile power & runtime scaling



50% smaller, 60% lighter, 2.5x more power Next-gen semiconductor technology gives this UPS 2.5x more power in half the size.

Redundant displays

Touchscreen display with Start-up wizard, access to status and configuration menus & data, including serial number. One-line diagram with UPS status when display is in power saving mode.

Modular, scalable & redundant

Smart-UPS Modular Ultra features more redundancy: power, battery, displays and intelligence modules.

LED status indicators

At-a-glance UPS and module status.

Universal Bays

Module Bays within the 9U UPS chassis allow you to add power or battery modules based on your current needs.

EcoStruxure Ready

Connect to EcoStruxure[™] IT via the embedded network port.

3x the battery life

Lithium-ion batteries last 8-10 years (3x VRLA), reducing Total Cost of Ownership.

Why choose a modular UPS?

The modular design allows you to scale power, runtime or redundancy






SRYL5K20RMXLT SRYL5K15RMXLT SRYL10K20RMXLT SRYL10K15RMXLT



SRYL15K20RMXLT SRYL15K15RMXLT



SRYL20K20RMXLT

SRYL20K20RMXLT N+1

5kW scalable to 15kW or 10kW N+1

Based on our most popular modular UPS

- 100A input AC Tray is backwards compatible with Symmetra LX wiring
- 9U height scales up to 15kW without changing your UPS footprint

Scalable to 20kW N+1

Up to 20kW of single phase power protection

- 125A input AC Tray scales up to 20kW power protection in a single phase UPS
- 9U height up to 15kW, 12U height for 20kW
- 3U height external battery chassis included with SRYL20K20RMXLT

Service the UPS while maintaining the IT load


Service bypass unit

- When installed on top of the UPS, the service bypass unit allows utility power to bypass the UPS
- · Lock out tag out feature to prevent unintended bypass of the UPS



SRYLSBP20KP

Which modular UPS for the application?



Smart-UPS Modular Ultra Rackmount

Incorporate the Smart-UPS Modular Ultra into a rack for an integrated solution with 2.5x more power in half the size for more U-space. The unit fits into standard racks for an organized deployment of equipment and a smooth installation.



Smart-UPS Modular Ultra Tower

Get more out of your standalone UPS with the Smart-UPS Modular Ultra tower providing 2.5x more power protection and available U-space. This unit has a flexible installation to accommodate power needs where necessary.

Designed for Certainty in a Connected World

More power, more runtime or both Scalable to 20kW N+1 (20RMXLT)

- The universal bays of the UPS allows for either power or battery modules in each slot.
- · Gain more resiliency by adding redundant power or battery modules
- Each external battery chassis has 4 battery module bays.
- · Supports up to 6 battery chassis with 4 battery modules each
- The UPS requires a 1:1 battery module to power module ratio. A fully populated 15kW UPS will need 3:3, a 20kW UPS 4:4 and a 20kW N+1 system 5:5.
- The UPS system can support more battery modules than power modules.





SRYLBM



SRYLFXBPRM4

Runtime estimates

Half/Full Loads	2500/5000W	5000/10,000W	7,500/15,000W	10,000/20,000W
Minimum batteries	(1) 12.4/5.6 min	(2) 12/5.6 min	(3) 12.7/5.7 min	(4) 12.4/5.5 min
Minimum batteries +1	(2) 24.1/11.5 min	(3) 19.1/9 min	(4) 16.4/7 min	(5) 14.8/6.9 min


Visit apc.com for additional runtime data and curves on the Smart-UPS Modular Ultra product pages.

Designed for ease of use



At-a-glance status

Colored LEDs and a touchscreen display provide instant UPS, power or battery module status.



User Selectable PDUs

Smart-UPS Modular Ultra allows you to hardwire your power protection or choose the Power Distribution Units (PDUs) that match your IT needs.



SRYLPD4

Smart-UPS software & services



EcoStruxure IT

Maximize the performance of your APC Smart-UPS

Bring your IT infrastructure to a new level of resilience, security, and sustainability with EcoStruxure IT software solutions. Gain operational excellence and ensure business continuity by enabling secure monitoring, management, insights, planning, and modeling.

se.com/dcim



EcoCare for Single Phase UPS

Unlock exclusive support provided by an EcoCare membership

Unlock exclusive support with an EcoCare membership. Get access to mySchneider, Field Services experts and more to help improve your business efficiency.

se.com/ecocare



PowerChute Serial Shutdown

UPS manageability at your fingertips

UPS management, graceful shutdown, and energy management software for computers, and servers using dedicated serial or USB connections.

apc.com/pcss



PowerChute[™] Network Shutdown

Power protection for server and hyper-converged infrastructures

APC PowerChute is a UPS management software enabling graceful system shutdowns and startup of your IT infrastructure, and providing energy management capabilities.

apc.com/pcns

Smart-UPS Modular Ultra accessories

UPS management accessories

- AP9834: APC USB Wi-Fi Device
- AP9810: dry contact I/O accessory
- AP9335T & AP9335TH: sensor
- SRYLFSU1: APC Smart-UPS Modular Ultra UPS Communication Card
- SRYLFSU2: APC Smart-UPS Modular Ultra XBP Communication Card

User Selectable PDUs

- SRYLPD1: APC Backplate Kit with 3x NEMA L5-20R Outlets for Smart-UPS Modular Ultra
- SRYLPD2: APC Backplate Kit with 6x NEMA 5-20R Outlets for Smart-UPS Modular Ultra
- SRYLPD3: APC Backplate Kit with 3x NEMA L5-30R Outlets for Smart-UPS Modular Ultra
- SRYLPD4: APC Backplate Kit with 2x NEMA L14-30R for Smart-UPS Modular Ultra SRYL
- SRYLPD5: APC Backplate Kit with 3x NEMA L6-30R Outlets for Smart-UPS Modular Ultra
- SRYLPD7: APC Backplate Kit with 3x NEMA L6-20R Outlets for Smart-UPS Modular Ultra
- SRYLPD0: APC PDU Blanking Panel rear for Smart-UPS Modular Ultra

UPS accessories

- SRYLSBP20KP: APC Smart-UPS Modular Ultra Service Bypass Unit
- SRYL5KPMT: APC Smart-UPS Modular Ultra 5kW/5kVA Power Module 208V
- SRYLBM: APC Smart-UPS Modular Ultra Lithium-ion Battery Module for Extended Runtime Options
- SRYLRMXBP: APC Smart-UPS Modular Ultra External Battery Pack with 4 Battery Modules Rackmount
- SRYLFXBPRM4: APC Smart-UPS Modular Ultra External Battery Frame Rackmount, holds 4 battery modules
- SRYLIM: APC Smart-UPS Modular Ultra Intelligence Module Replacement
- SRYLF15KRMT: APC Smart-UPS Modular Ultra UPS Frame 9U (no power or battery modules), Scalable to 15kW N+1 Redundant Rackmount 208/120V
- SRYLF20KRMT: APC Smart-UPS Modular Ultra UPS Frame and Battery Chassis 11U (no power or battery modules), Scalable to 20kW N+1 Redundant Rackmount 208/120V
- SRYLFSU6A: 125A APC Smart-UPS Modular Ultra AC Tray
- SRYLFSU6B: 100A APC Smart-UPS Modular Ultra AC Tray
- SRYLFSU7: 125A Input/Output wiring tray
- SRYLOPT1: APC Smart-UPS Modular Ultra 4 Post UPS Rail Kit
- SRYLOPT2: APC Smart-UPS Modular Ultra 2 Post UPS Rail Kit
- SRYLOPT3: APC Smart-UPS Modular Ultra 4 Post XBP Rail Kit
- SRYLOPT5: APC Smart-UPS Modular Ultra 2 Post XBP Rail Kit
- SRYLOPT8: APC Smart-UPS Modular Ultra 8 Ft. Battery Cable Ext. for External Battery Pack











SRYLPD5



SRYLSBP20KP





SRYLF15KRMT

Smart-UPS Modular Ultra



SKU technical specifications

	Smart-UPS Modular Ultra rackmount, scalable to 5-20kW					
Тороlogy	On-Line					
Output						
Output power capacity	5kVA/5kW	10kVA/10kW	15kVA/15kW	20kVA/20kW		
Nominal output voltage	120V / 208V, 120V / 240V					
Output voltage distortion	0.5% - full linear load					
Output frequency	50Hz / 60Hz \pm 3Hz (Auto Sense), 50Hz / 60Hz \pm 0.1Hz User Selectable, 50Hz / 60Hz \pm 3Hz User Selectable					
Waveform type	Sine Wave					
Output connections	Hard wire 4-wire (2P + N + E), Optional User Selectable PDUs					
Efficiency green mode		ut	o to 97%			
Input						
Nominal input voltage	120V / 208V, 120V / 240V					
Input frequency	40Hz - 70Hz Auto-Sensing					
Input connections	Hard wire 4-wire (2P + N + E)					
Input voltage range for main operations	95V - 150V /165V - 260V					
Batteries and runtime						
Battery type	Lithium-ion					
Runtime (full load/ half load)		visit apc.com fo	or runtime information			
External battery	Yes - connect up to 6 battery frames, each with 4 SRLYBM battery modules					
Communications and management						
Interface port(s)	Ethernet, Universal I/O, Smart Slot, Modbus, EPO, USB Host x 2					
Network management	Network Management Card Embedded					
DIsplay	Multicolor high resolution Capacitive LCD Touchscreen, One-line diagram, On/Off Button					
Physical						
Maximum HxWxD	UPS Frame 9U 390mm (15.4in) x 440mm (17.4in) x 700mm (28in)					
	UPS Frame 9U + Battery Chassis 3U 520mm (20.5in) x 440mm (17.4in) x 740mm (29.2in)					
Net weight	5kW 160lb (72.5kg)	10kW 202Ib (91.5kg)	15kW 244lb (110.5kg)	20kW 327.4lb (148.5kg)		
Environmental						
Operating environment	32 – 104 °F (0 – 40 °C)					
Operating elevation	0-10000 feet (0-3000 meters)					
Storage temperature	5 – 113 °F (-15 – 45 °C) short term storage					
Storage relative humidity	0 – 95%, non-condensing					
Storage elevation	0-50000 feet (0-15000 meters)					
Conformance						
Regulatory approvals	UPS: CUL listed UL1778, FCC Part 15 subpart B Class A Battery Pack : CUL recognized UL1973 and IEC 60730, UN38.3, FCC Part 15 subpart B class A, PSE, UKCA					
Standard warranty		5-Year UF	PS and batteries			

Smart-UPS Modular Ultra Tower



SKU technical specifications

	Smart-UPS Modular Ultra tower, scalable to 5-20kW					
Тороlogy		On-				
Output						
Output power capacity	5kVA/5kW	10kVA/10kW	15kVA/15kW	20kVA/20kW		
Nominal output voltage	120V / 208V, 120V / 240V					
Output voltage distortion	0.5% - full linear load					
Output Frequency	50/60 Hz \pm 3 Hz (auto sense follow input AC frequency), 50 or 60 \pm 1Hz (battery mode)					
Waveform Type	Sine Wave					
Output Connections	Hard wire 4-wire (2P + N + E), Optional User Selectable PDUs					
Efficiency green mode	up to 97%					
Input						
Nominal input voltage	120V / 208V, 120V / 240V					
Input frequency	40Hz - 70Hz Auto-Sensing					
Input connections	Hard wire 4-wire (2P + N + E)					
Input voltage range for main operations	95V - 150V /165V - 260V					
Batteries and runtime						
Battery type	Lithium-ion					
Runtime (full load/ half load)	visit apc.com for runtime information					
External battery	Yes - co	nnect up to 6 battery frames,	each with 4 SRLYBM battery	modules		
Communications and management						
Interface port(s)	Ethernet, Universal I/O, Smart Slot, Modbus, EPO, USB Host x 2					
Network management		Network Managem	ent Card Embedded			
DIsplay	Mulitcolor high resolution touch screen LCD, On/Off button					
Physical						
Tower 18U HxWxD	942mm x 600mm x 900mm					
Tower 24U HxWxD	1198mm x 600mm x 900mm					
Tower 18U net weight	184kg (SRYL5K20XLT18) 163kg (SRYL5K15XLT18)	204kg (SRYL10K20XLT18) 183kg (SRYL10K15XLT18)	223kg (SRYL15K20XLT18) 202kg (SRYL15K15XLT18)	242kg		
Tower 24U net weight	195kg (SRYL5K20XLT18) 175kg (SRYL5K15XLT18)	215kg (SRYL10K20XLT18) 194kg (SRYL10K15XLT18)	234kg (SRYL15K20XLT18) 213kg (SRYL15K15XLT18)	253kg		
Environmental						
Operating environment		32 – 104 °F (0 – 40 °C)				
Operating elevation	0-10000 feet (0-3000 meters)					
Storage temperature	5 – 113 °F (-15 – 45 °C) short term storage					
Storage relative humidity	0 – 95%, non-condensing					
Storage elevation	0-50000 feet (0-15000 meters)					
Conformance						
Regulatory approvals	UPS: CUL listed UL1778, FCC Part 15 subpart B Class A Battery Pack : CUL recognized UL1973 and IEC 60730, UN38.3, FCC Part 15 subpart B class A, PSE, UKCA					
Standard warranty	5-Year UPS and batteries					

Life Is On Schneider

Learn more today!

apc.com/smart-ups-modular-ultra

Schneider Electric

One Boston Place Floor 27 Boston, MA 02108 United States www.apc.com



©2023 Schneider Electric. All Rights Reserved.

Schneider Electric | Life Is On is a trademark and the property of Schneider Electric SE, its subsidiaries, and affiliated companies. • 998-22046474_GMA-US This document has been printed on recycled paper

