


HP 27mq 27-inch Display



Looks great. Performs even better

Enjoy a 27-inch diagonal big screen experience with this stylish, height-adjustable HP display, and get up to 178° ultra-wide viewing angles with consistent detail and vibrant color. This ultraslim, nearly borderless design with QHD¹ resolution comes at a great value and gives you the connections you need to easily hook up your laptop or desktop.



More screen in less space

Experience more desk space with this ultraslim, height-adjustable micro-edge display.

Outstanding viewing experience

See your screen with consistent detail, vibrant color, ultra-wide 178° viewing angles, and crisp QHD¹ resolution.



Easy connectivity

Conveniently connect your devices with HDMI and VGA ports.

HP 27mq 27-inch Display

Featuring

Share the panoramic view

Ultra-wide 178-degree viewing angles with consistent detail and vibrant color.

Step up to the best

IPS technology brings you clear views from almost any angle. Every seat is the best seat in the house.

QHD Display

Ultra-sharp details and captivating definition with 3.7 million pixels.¹

Off the desk and on the wall

VESA mounts for easy mounting on a wall or arm.

Three-sided micro-edge display

See more of your screen with a three-sided micro-edge display that maximizes your viewing area.

Adjust your view

Adjust your screen's height with swivel, pivot and tilt capabilities.

HP 27mq 27-inch Display



Product number	1F2J9AA
UPC number	195122299262
Swivel	±360°
Tilt	-5 to +23°
Display size	68.6 cm (27")
Aspect ratio	16:9 ¹
Display type	IPS
Pixel pitch	0.233 mm
Response time	5ms GtG ¹
Brightness	300 nits ¹
Contrast ratio	1000:1 ¹
Display contrast ratio (dynamic)	10000000:1
Product color	Silver bezel, black stand
Resolution (maximum)	QHD (2560 x 1440 @ 60 Hz)
Resolutions supported	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 1200; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200; 640 x 480; 720 x 400; 800 x 600; 2560 x 1400
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	50-60 Hz
Display features	Anti-glare; Language selection; LED backlights; On-screen controls; Pivot rotation; Plug and Play; Height adjustable; Low blue light mode
Display Input Type	1 HDMI 1.4 (with HDCP support); 1 VGA
Physical security features	Security lock-ready ³
Environmental specifications	Arsenic-free display glass; Low halogen; Mercury-free display backlights ²
Display User Control Options	Brightness; Color control; Contrast; Exit; Image control; Information; Language; Management; Power control; Input control; Menu control
Webcam	No integrated camera
Operating temperature range	5 to 35°C
Operating temperature range	41 to 95°F
Operating humidity range	20 to 80% non-condensing
Power supply	Input voltage 100 to 240 VAC
VESA mount	100 x 100 mm VESA mount compatible
Touch-enabled	Not touch-enabled
Pixels per inch (ppi)	109 ppi
Panel bit depth	8 bit (6 bit + FRC)
Vertical viewing angle	178°
Horizontal viewing angle	178°
Bezel	3-sided micro-edge
Tilt	-5 to +23°
Pivot	+90
Height adjustment range	100 mm
Hardness	3H
Screen treatment	Anti-glare
Integrated privacy filter	No
Flicker-free	Yes
Low blue light modes	Yes
Port and Connectors	1 VGA; 1 HDMI 1.4; No
HDCP	Yes, HDMI
Certifications and compliances	BSMI; CB; CCC; CEL
What's in the box	AC power cord; Documentation; HDMI cable
Dimensions (L x W x H)	24.18 x 1.984 x 14.48 in ; 61.42 x 5.05 x 36.79 cm (Without stand.)
Weight	15.08 lb; 6.84 kg (With stand.)
Package Dimensions (L x W x H)	27.75 x 9.21 x 18.81 in; 70.5 x 23.4 x 47.8 cm
Package weight	20.44 lb; 9.27 kg

HP 27mq 27-inch Display

Messaging Footnotes

¹ QHD (Quad High Definition) content required to view QHD images.

Technical Specifications Footnotes

¹ All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

² External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen.

³ Lock is sold separately.

