Poly Trio C60 IP Conference Phone Full Radio and PoE-enabled GSA/TAA

One device. Many possibilities.

Bring people together. Launch big ideas. And make sure everyone at the table can be heard, near or far with Poly signature audio. The Trio C60 plays nicely with everyone, delivering native experiences on your favorite collaboration platforms.



*Product image may differ from actual product

Poly signature audio
Get more out of your conference calls. Poly reduces distracting background noise to ensure every inflection is heard. Hear every reaction with up to 22 kHz of rich, full sound.

One-touch join
All it takes is a fingertip to get started. Join your calls in a second with a single touch of a button thanks to the truly intuitive user experience.

Datasheet

Poly Trio C60 IP Conference Phone Full Radio and PoE-enabled GSA/TAA

Specifications





Display
Aspect ratio: 16:9
Native resolution: 720 x 1280
Panel technology: Color LCD
Display size (diagonal): 5"
Display size (diagonal, metric): 12.7 cm (5")
Touch-enabled: Gesture-based, multi-touch capable touchscreen

Connectivity and communications
Wireless range: Up to 6.1 m
Wireless range (imperial): Up to 20 ft
External I/O ports:
1 USB 2.0 Type-A (for USB battery charging)
1 USB 2.0 Micro-B (for USB audio device)
2 RJ-45 (10/100/1000BASE-TX Mbps)
Wireless technologies:
Bluetooth® 4.2
Wi-Fi network connectivity: 2.4-2.4835 GHz (802.11b, 802.11g, 802.11n HT-20)
5.15-5.825 GHz (802.11a, 802.11n, HT-20, 802.11n HT-40)

Battery
Power features:
LAN IN: Built-in auto-sensing IEEE 802.3at, PoE Device (Class 4)
LAN OUT: Built-in auto-sensing IEEE 802.3af power sourcing equipment[1]

User interface features
Languages:
Arabic; Chinese; Czech; Danish; Dutch; English; French; German; Hungarian; Italian; Japanese; Korean; Norwegian; Polish; Portuguese; Romanian; Russian; Slovenian; Spanish; Swedish

Audio
Audio features:
Poly Acoustic Clarity technology provides full duplex conversations, acoustic echo cancellation, and background noise suppression
Comfort noise generation
DTMF tone generation (RFC 2833 and in-band)
Low delay audio packet transmission
Adaptive jitter buffers
Microphone type: Three cardioid microphones
Frequency response (microphone): 100 Hz to 22 kHz
Sensitivity (speaker): 92 dB
Audio codecs:
G.711 (A-law and µ-law)
G.722
G.722.1
G.722.1C
G.729AB
G.719
Polycom® Siren™ 7
Siren™ 14
iLBC
OPUS

Environmental
Certifications and compliances: AS/NZS 60950-1; AS/NZS 62368-1-17; Australia -AS/NZ4268; Australia A&C Tick; CAN/CSA C22.2 No. 60950-1-03; CAN/CSA C22.2 No. 62368-1-14; CE Mark; CISPR22 Class B; EN 301 489-1, EN 301 489-3, EN 301 489-17; EN 61000-3-2; EN 61000-3-3; EN 62368-1; ETSI EN 300 328 v1.9.1; ETSI EN 300 330; ETSI EN 301 893 v1.7.1; FCC Part 15 (CFR 47) Class B; FCC Part 15.225; FCC Part 15.247; FCC Part 15.407; ICES-003 Class B; IEC 60950-1; IEC 62368-1; Japan Item (19); Japan Item (19)-3; Japan Item (19)-3-2; Japan MIC/VCCI Class B; NZ Telepermit; ROHS compliant; RSS 247 Issue 1; UL 60950-1; UL 62368-1
Operating humidity range: 5 to 95%
Operating Temperature Range (Celsius) / Operating Temperature Range (Fahrenheit): 0 to 40°C / 32 to 104°F
Storage temperature range (Celsius) / Storage temperature range (Fahrenheit): -20 to 70 °C / -40 to 158°F
Energy star certified: ENERGY STAR® certified

Certifications
Certified collaboration software: Microsoft Teams; Skype for Business; Zoom
Special features:
Unicode UTF-8 character support

Applications supported
Management software:
Poly Zero Touch Provisioning
RealPresence Resource Manager (v. 10.1 or above) based provisioning
Polycom Device Management Service for Enterprise (PDMS-E)
Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
SDP

Display features
On-screen virtual keyboard

Security
Security management:
802.1X Authentication and EAPOL Media encryption via SRTP
Digest authentication
Encrypted configuration files
HTTPS secure provisioning
Password login
Support for signed software executables
Support for URL syntax with password
Transport Layer Security (TLS)
Wi-Fi encryption: WEP, WPA-Personal, WPA2-Personal, WPA2-Enterprise with 802.1X (EAP-TLS, PEAP-MSCHAPv2)
FIPS 140-2 compliant cryptographic module

Network
Supported network protocols:
DHCP VLAN discovery
LLDP-MED for VLAN discovery
FTP/TFTP/HTTP/HTTPS server-based central provisioning
Manual or dynamic host configuration protocol (DHCP) network setup
QoS Support – IEEE 802.1p/Q tagging (VLAN), Layer 3 TOS, and DHCP
Time and date synchronization using SNTP
Provisioning and call server redundancy support
VoIP features:
IETF SIP (RFC 3261 and companion RFCs)

Datasheet

Poly Trio C60 IP Conference Phone Full Radio and PoE-enabled GSA/TAA

Specifications







Headset and handset compatibility

Headset and handset compatibility:

Bluetooth® headset compatibility

Telephony and call handling features

Telephony and call handling features:

Bundled with Polycom UC Software: Corporate Directory Access using LDAP
Call timer and call waiting
Call transfer, hold, divert (forward), park, pickup
Called, calling, connected party information
Distinctive incoming call treatment/call waiting
Do not disturb function
Local configurable digit map/dial plan
Local five-way audio conferencing
Shared call/bridged line appearance
Visual Conference Management
Up to 3 lines (maximum one Skype for Business and Microsoft Teams)
Daisy-chain up to four
One-touch speed dial, redial and meeting join

Weight and dimensions

Product Primary Color: Black
Weight (imperial): 2.1 lb
Weight (metric): 950 g
Product dimensions (imperial): 15.1 x 2.9 x 13.1 in
Product Dimensions (metric): 38.3 x 7.5 x 33.2 cm
Package dimensions (imperial): 19 x 4.5 x 15.5 in
Package dimensions (metric): 48.3 x 11.5 x 39.4 cm
Package weight (imperial): 4.3 lb
Package Weight (metric): 1970 g
UPC number: 197497506440
Product number: 849B3AA

Warranty

Poly standard one-year limited warranty

What is in the box

Console
Network (LAN) cable-CAT-5E
USB Type-A cable
Cable wrap
Tactile overlay for improved accessibility
Setup sheet

Technical Specifications Footnotes

[1] Requires full Class 4 power input on LAN IN for operation

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

July 2023