

ThinkStation P3 Tiny

Designed for ultimate productivity, this compact 1-liter form factor powered by up to 13th Gen Intel Core i9 Processor lets users handle the most demanding workloads without compromising on efficiency. Enhance productivity with optional Wi-Fi 6E that enables faster connection speeds even in densely congested areas while with optional Thunderbolt 4 port, connect devices and share files at high speed. Security features including discrete TPM 2.0, Kensington security slot, and BIOS security keeps data well-protected.



Professional machines for advanced users

ThinkStation P3 Series workstations provide affordable power-computing with a choice of processor technologies, expansion bays and support for multiple storage drives.

Configured with up to 4TB of high-speed storage via 2x M.2 PCIe SSD modules and up to 64GB DDR5 memory, this device offers powerful processing capabilities enabling users to multitask and store memory-intensive files without any hassle.

To view and compare detailed spreadsheets, professionals can connect to up to 4 independent displays via an onboard Display Port, HDMI, VGA, or USB-C port.

EPEAT Gold, ENERGY STAR 8.0, ErP Lot 3, TCO Certified 9.0, RoHS compliant makes this device energy-efficient.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

- If a problem can't be fixed remotely, we will visit your location
- Normally next business day service
- Agreed appointment times

Accessories

ThinkCentre Tiny VESA Mount II

- Supports mounting of a ThinkCentre Tiny to the back of VESA-compatible displays
- Can be used separately or combined with other options for secure mounting
- Simple 4-screw design keeps the device securely attached to the mount



PN: 4XF0N03161

ThinkStation P3 Tiny

Performance

Processor

Up to one 13th Gen Intel Core i3/i5/i7/i9

Operating System

Windows 11 Pro for Workstations
 Windows 11 DG Windows 10 Pro 64 for Workstations
 Ubuntu Linux LTS
 Red Hat Enterprise Linux (certified only)

Graphics

Intel UHD Graphics 730 (integrated) Intel UHD Graphics 770 (integrated)
 NVIDIA T400
 NVIDIA T1000 4GB
 NVIDIA T1000 8GB

Chipset

Intel Q670 Chipset

Memory ¹

Up to 64GB, 2x SO-DIMM

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage ²

Up to 2x 2TB M.2 PCIe NVMe SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Design

Dimensions ³

179 x 182.9 x 37mm (7.05 x 7.2 x 1.5 inches, with rubber feet)

³The system dimensions may vary depending on configurations.

Weight ⁴

1.4 kg (3 lbs, maximum configuration)

⁴The system weight is approximate and may vary depending on configurations

Connectivity

Ethernet

One onboard Gigabit Ethernet
 Additional Ethernet options via PCIe adapter

WLAN + Bluetooth ⁵

802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.1*
 Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

Security & Privacy

Security

Discrete TPM 2.0
 Cable lock*
 Kensington Security Slot, 3 x 7 mm
 Chassis intrusion switch

Manageability

System Management ⁶

Intel vPro Enterprise with Intel AMT 16.0*

⁶Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications ^{7 8}

EPEAT Gold Registered
 ENERGY STAR 8.0
 ErP Lot 3
 TCO Certified 9.0
 RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

Other Certifications

MIL-STD-810H
