

Technical Specifications

HP Series 5 Pro 23.8" FHD Monitor - 524pf




1. Power Button

Front

2. Power LED

Technical Specifications

HP Series 5 Pro 23.8" FHD Monitor - 524pf



Back

1. Joypad OSD button
2. Security Cable Slot
3. Power Connector
4. DisplayPort™ 1.2
5. HDMI 1.4 Port
6. USB-B port
7. 2x SuperSpeed USB Type-A 5Gbps signaling rate
8. SuperSpeed USB Type-A 5Gbps signaling rate
9. SuperSpeed USB Type-A 5Gbps signaling rate (charging)

Technical Specifications


Model: 9D9L6UT

Panel Specifications	Display Size (Diagonal)	60.5 cm (23.8")
	Viewable Diagonal Size	60.47 cm (23.8")
	Panel Technology	IPS
	Curvature	Flat
	Max Refresh Rate	100 Hz
	Native Resolution	FHD (1920 x 1080)
	Panel Bit Depth	8 bit (6 bit + FRC)
	Aspect Ratio	16:9
	Brightness (Typical)	350 nits
	Display Contrast Ratio (Static)	1500:1
	Display Contrast Ratio (Dynamic)	10000000:1 = 10M:1
	Flicker Free	Yes
	Pixel Pitch	0.2745 x 0.2745 mm
	Pixels Per Inch (PPI)	93 PPI
	Display Colors	Up to 16.7 million colors supported <i>*Number of colors through A-FRC technology.</i>
	Backlight Lamp Life Minimum (To Half Brightness - In Hours)	30,000 hours
	Backlight Type	Edge-lit, WLED
	Screen Treatment	Anti-glare
	Hardness	3H
	Haze	25%
	Response Time (Typical)	5ms GtG (with overdrive)
	Horizontal Viewing Angle (Typical Cr>10)	178°
	Vertical Viewing Angle (Typical Cr>10)	178°
Panel Active Area Metric (W X H)	52.70 x 29.65 cm	
Panel Active Area Imperial (W X H)	20.75x11.67 in	
NOTE: Performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.		
Color	sRGB	100%
Color Management	Color Space	RGB 4:4:4, YCBCR 4:4:4, YCBCR 4:2:2
	RGB Channel Adjust	Yes, Gain
	Default Color Temperature	Neutral (6500K)
Monitor Specifications	Bezel Type	3-sided borderless
	Color Of Stand	Black and Silver
	Color Of Head	Black
	Tilt	-5 to +23°
	Swivel	±45°
	Pivot	±90
	Height Adjust Range	150 mm
	Vesa Mounting	100mm x 100mm
	Security Lock	Security lock-ready

Technical Specifications

	Detachable Stand	Yes
	Warranty	3/3/0 for AMS, EMEA, APJ (3/3/3 in select APJ countries)
	Low Blue Light	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution certified)
	Zero Bright Dot Guarantee	No* *The HP Pixel Policy allows no bright sub-pixel defects for this display. For complete details, see http://support.hp.com/us-en/document/c00288895 .
	Management Software	HP Display Manager, HP Display Center* *Host PC requires Windows 10 and above. HP Display Center is available on the Microsoft store.
On Screen Display (OSD)	On Screen Display	Brightness+, Color, Input, Image, Power, Menu, Management, Information, Exit
	Native Resolution	FHD (1920 x 1080)
	Maximum Resolution	FHD (1920 x 1080 @ 100 Hz)
	Preset Graphic Modes/Supported Resolutions	640 x 480 @ 60Hz 640 x 480 @ 75Hz 720 x 400 @ 70 Hz 720 x 480 @ 60Hz 720 x 576 @ 50Hz 800 x 600 @ 60 Hz 800 x 600 @ 75 Hz 1024 x 768 @ 60 Hz 1024 x 768 @ 75 Hz 1280 x 720 @ 50 Hz 1280 x 720 @ 60 Hz 1280 x 720 @100 Hz 1280 x 800 @ 60 Hz 1280 x 1024 @ 60 Hz 1280 x 1024 @ 75 Hz 1440 x 900 @ 60 Hz 1600 x 900 @ 60 Hz 1680 x 1050 @ 60 Hz 1920 x1080 @ 50Hz 1920 x 1080 @ 60 Hz 1920 x 1080 @ 75 Hz 1920 x 1080@ 100 Hz
	Minimum Vertical Scan Rate	50 Hz
	Maximum Vertical Scan Rate	100 Hz
	Minimum Horizontal Scan Rate	30 kHz
	Maximum Horizontal Scan Rate	120 kHz
	Maximum Pixel Clock	300 MHz
	User Programmable Modes	Yes, 18
	User-Assignable Function Buttons	Yes, 4 (6 options)
	Languages	11 (English, Spanish, German, French, Italian, Netherlands, Portuguese, Japanese, T-Chinese, S-Chinese and Russian)

Technical Specifications

Connector Types	DisplayPort™	1 DisplayPort™ 1.2
	HDMI	1 HDMI 1.4
	HDCP	Yes, DisplayPort™ and HDMI
	USB-Type-A	4 SuperSpeed USB Type-A 5Gbps signaling rate (1 charging)
	USB-B (Hub enablement)	1 USB-B
Special Features	Switch	Monitor Power button Next Active Input / Up button Information / Down button Brightness / Left button Color / Right button Menu / Enter button
	User Presets	18
	User Updateable Firmware	Yes
Power & Operating Specs	Power Supply	Internal
	Power Source	100 – 240 VAC 50/60 Hz
	Power Consumption- Max	58 W
	Energy Saving/Stand By Mode	0.5 W
Energy Star Data	Power Consumption - Typical	22 W
	Operational Mode at 100 VAC	11.6 W
	Operational Mode at 115 VAC	11.5 W
Energy Star Data	Operational Mode at 230 VAC	12.7 W
	EU Energy Efficiency Class (ErP LOT-5)	12 W
	ErP LOT5 Energy Efficiency Class for Standard Dynamic Range (SDR)	
Operating Conditions	Operating Temperature - Celsius	5~35°C
	Operating Temperature - Fahrenheit	41– 95°F
	Non-Operating Temperature - Celsius	-40 – 65°C
	Non-Operating Temperature - Fahrenheit	-4 – 149°F
	Operating Humidity	20 – 80% Relative Humidity (non-condensing)
	Non-Operating Humidity	5~95%RH
	Operating Altitude Metric	0~5,000m
	Non-operating Altitude Metric	0~12,192m
Certifications and Compliances	Operating Altitude Imperial	0~16,400ft
	Non-operating Altitude Imperial	0~40,000ft
	Low Halogen	Yes*

* External power supplies, WWAN modules, power cords, cables and peripherals excluded. Service parts obtained after purchase may not be Low Halogen.

Technical Specifications

Agency Approvals and Certifications

WW application
 CB/KC/NOM/TUV-S/ISO 9241-307/EAC/cTUVus/PSB/ISC/CCC/CECP/SEPA/TCO/TCO Certified Edge/GS/TUV HW
 LBL/UAE/Ukraine/BIS/NRCS/CE/FCC/VCCI/BSMI/EMF/KCC/ICES/RCM/Australian-New Zealand DoC/Energy Star/Korea MEPS/Ukraine EE/CEL/California CEC/WEEE/PSE
 Windows 11 (x64 only), Windows 10 (x64 only)

Microsoft WHQL Certification

ENERGY STAR® Certified

EPEAT® Registered

Regions need to verify by country

Yes
 EPEAT® Gold in United States*
 EPEAT® registered with Climate+
 *EPEAT® Gold

NOTE: Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit www.epeat.net for more information.

China Energy Label

TCO Certified Edge

TCO Certified

SmartWay Transport Partnership - NA only

CEL Grade 2

Yes

Yes

Yes (NA sku)

Contains Recycled Materials

Recycled Plastics

85% ITE-derived closed loop plastic*
 Contains Ocean-Bound Plastic**

*Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard

** All plastic parts contain ocean-bound plastic. Percentage of ocean-bound plastic contained in each component varies by product.

Recycled Metal

At least 30% recycled metal*

* Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams.

Recycled Glass

20% recycled glass*

* Percentage of recycled glass in the monitor panel varies by product. Recycled glass is expressed as a percentage of the total weight of the glass.

Recyclable Packaging (Box, packing materials)

Outside Box and corrugated cushions are 100% sustainably sourced and recyclable* & Molded Paper Pulp Cushion inside box is 100% sustainably sourced and recyclable**

*100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.

**Molded pulp cushions contains 100% recycled wood fiber and organic materials.

Technical Specifications

		Metric	Imperial	
Unit Product/Package Specifications	Product Dimensions (Unpacked with stand) (W x D x H)	53.94 x 18.95 x 50.32 cm	21.24 x 7.46 x 19.81 in	
	Product Dimensions (Packed) (W x D x H)	62.1 x 14.0 x 39.3 cm	24.45 x 5.51 x 15.47 in	
	Display Head Dimensions (Unpacked without stand) (W x D x H)	53.94 x 4.72 x 31.43 cm	21.24 x 1.86 x 12.37 in	
	Base Area Footprint (w x d mm)	242 x 189.50 mm	9.53 x 7.46 in	
	Bezel Measurements	Top: NA	Top: NA	
		Sides: NA	Sides: NA	
		Bottom: 9.25	Bottom: 0.37	
	Product Weight (Unpacked with stand)	4.9 kg	10.8 lb	
	Product Weight (Packed)	7.2 kg	15.9 lb	
	Product Weight (Head Only)	3.4 kg	7.6 lbs	
Pallet Information	Pallet Dimensions (L x W x H mm)	Slip Sheet: 1128 x 629 x 1978 mm (20' ft & 40' ft)	Slip Sheet: 44.41 x 24.76 x 77.87 inch (20' ft & 40' ft)	
		Slip Sheet: 1128 x 629 x 2372 mm (40' HQ)	Slip Sheet: 44.41 x 24.76 x 93.39 inch (40' HQ)	
		Pallet: 1128 x 629 x 2106 mm (20' ft & 40' ft)	Pallet: 44.41 x 24.76 x 82.91 inch (20' ft & 40' ft)	
		Pallet: 1128 x 629 x 2499 mm (40' HQ)	Pallet: 44.41 x 24.76 x 98.39 inch (40' HQ)	
		Pallet Total Weight	Slip Sheet: 292.5 kg (20' ft & 40' ft)	Slip Sheet: 644.8 lbs (20' ft & 40' ft)
			Slip Sheet: 350.6 kg (40 HQ)	Slip Sheet: 772.9 lbs (40' HQ)
	Pallet: 302.5 kg (20' ft & 40' ft)		Pallet: 666.9 lbs (20' ft & 40' ft)	
	Pallet: 360.6 kg (40 HQ)		Pallet: 795.0 lbs (40' HQ)	
	Pallet Layers		Slip Sheet: 5 layers (20' ft & 40' ft)	
			Slip Sheet: 6 layers (40' HQ)	
		Pallet: 5 layers (20' ft & 40' ft)		
		Pallet: 6 layers (40' HQ)		
Pallet Product per Layer		8 per layer (slip sheet)		
		8 per layer (pallet)		
	Slip Sheet: 40 sets (20' ft & 40' ft)			
	Slip Sheet: 48 sets (40' HQ)			
	Pallet: 40 sets (20' ft & 40' ft)			
	Pallet: 48 sets (40' HQ)			
Total Products per Pallet	720 sets (slip sheet)			
	720 sets (pallet)			
Container Load, 20-Foot	1520 sets (slip sheet)			
Container Load, 40-Foot	1520 sets (pallet)			
Container Load, 40-Foot HighQ	1824 sets (slip sheet)			
	1824 sets (pallet)			

Technical Specifications

What's in the box? AC power cord (1.83m) 5.9ft
HDMI 1.4 cable (1.8m) 5.9 ft
USB 3.0 B-A cable (1.8m)
DisplayPort™ 1.2 cable (1.8m)
Warranty
Quick Setup Poster

**User Guide and
Warranty Languages**

User Guide Languages

Warranty Languages

Arabic, Bahasa Indonesia, Bulgarian, Chinese-S, Chinese-T, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hebrew, Hungarian, Italian, Japanese, Kazakh, Korean, Latvian, Lithuanian, Norwegian, Polish, Portuguese (Brazilian), Portuguese (Iberian), Romanian, Russian, Serbian, Slovak, Slovenian, Spanish, Swedish, Thai, Turkey, Ukrainian
English US (EN), English AP (EN-AP), English LA (EN-LA), English UK (EN-GB), Arabic (AR) -17x, Bahasa Indonesia (ID), Bosnian (BS), Bulgarian (BG), Chinese-S (CN), Chinese-T (TW), Croatian (HR), Czech (CS), Danish (DA), Dutch (NL), Estonian (ET), Finnish (FI), French Canadian (FC), French European (FR), German (DE), Greek (EL), Hebrew (HE), Hungarian (HU), Italian (IT), Japanese (JA), Kazakh (KK), Korean (KO), Latvian (LV), Lithuanian (LT), Norwegian (NO), Polish (PL), Portuguese, Brazilian (BR), Portuguese, Iberian (PT), Romanian (RO), Russian (RU), Serbian (SR), Slovak (SK), Slovenian (SL), Spanish, Castilian (ES-ES), Spanish, Latin America (ES-MX), Swedish (SV), Thai (TH)
Turkish (TR), Ukrainian (UK), Vietnamese (VI)

Technical Specifications

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.

Summary

Change Log

Change Log			
	V1 to V2		
	V2 to V3		
	V3 to V4		