

HP ZBook Fury 16 G11 Mobile Workstation PC (B61T7UA)



So powerful you'll forget it's a laptop

Tackle your most intense workflows with the ZBook Fury—offering a desktop class CPU in a laptop. With integrated or discrete graphics, a stunning display and collaboration features you can edit 8K videos, render in 3D or train machine learning models. Experience extreme pro performance—all on the move.



Tackle multiple heavy workflows—simultaneously

Blaze through graphics-heavy projects with a desktop class Intel® CPU[2] and integrated or discrete graphics.[4]

Upgrade. Expand. Evolve

Get desktop-level storage and memory with room to grow. Expansion is easy with tool-free access to components.

Thin bezel for enhanced display area.

Bring projects to life on a brilliant display and see more of your screen with a slim-bezel design.

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [5]

Intel® Core™ i9 processor

Get high-end performance for intensive tasks like rendering and video editing with the Intel® Core™ i9 processor. [2]

NVIDIA® Graphics

Tackle your biggest projects with a choice of up to NVIDIA RTX™ 5000 Ada Laptop GPU; certified for pro apps.

HP Z Turbo Drive High-speed Storage

Work without limits in any location with local PCIe storage that's up to 6x faster than SATA SSD, and up to 21x faster than traditional HDD storage. [6]

Industry-leading security features

Advanced security features come standard. System safeguards like HP Sure Start – the industry's first self-healing BIOS – mean your device is locked down tight, so your data and identity are too.

Specifications

Operating system	Windows 11 Pro
Processor family	13th Generation Intel® Core™ i9 processor
Processor	Intel® Core™ i9-13950HX (up to 5.5 GHz with Intel® Turbo Boost Technology, 36 MB L3 cache, 24 cores, 32 threads) [6,7]
Chipset	Intel® WM790
Memory	128 GB DDR5-5600 MT/s (4 x 32 GB)
Memory Slots	4 SODIMM; supports dual channel
Internal Storage	2 TB PCIe® Gen4 NVMe™ TLC M.2 SSD
Hard drive (2nd)	2 TB PCIe® Gen4 NVMe™ TLC M.2 SSD
Graphics	Discrete
Graphics (discrete)	NVIDIA RTX™ 5000 Ada Generation (16 GB GDDR6 dedicated)
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Display	40.6 cm (16") diagonal, WQUXGA (3840 x 2400), IPS, touch, BrightView, micro-edge, Low Blue Light, 400 nits, 100% DCI-P3
Display	16" diagonal, WQUXGA (3840 x 2400), IPS, touch, BrightView, micro-edge, Low Blue Light, 400 nits, 100% DCI-P3 [21,23,32,39]
Display size (diagonal)	40.6 cm (16")
Display size (diagonal)	16"
Audio	Audio by Poly Studio, dual stereo speakers, HP World Facing Microphone dual array digital microphones, functions keys for volume up and down, combo microphone/headphone jack, HD audio
Dimensions (W x D x H)	36.3 x 25.0 x 2.86 cm (non-touch); 36.3 x 25.0 x 2.77 cm (touch)
Dimensions (W x D x H)	14.29 x 9.86 x 1.12 in (non-touch); 14.29 x 9.86 x 1.09 in (touch)
Weight	Starting at 2.35 kg (Weight varies by configuration and components.)
Weight	Starting at 5.17 lb (Weight varies by configuration and components.)
Ports	1 RJ-45; 1 headphone/microphone combo; 1 SuperSpeed USB Type-A 5Gbps signaling rate (charging); 1 SuperSpeed USB Type-A 5Gbps signaling rate
Ports	1 power connector; 2 Thunderbolt™ 4 with USB4™ Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4, HP Sleep and Charge); 1 HDMI 2.1; 1 Mini DisplayPort™ 1.4a
Package dimensions (W x D x H)	552 x 69 x 345 mm
Network interface	Integrated Intel® I219-LM GbE
Wireless	Intel® Wi-Fi 7 BE200 (2x2) and Bluetooth® 5.4 wireless card, vPro®
Power	230 W external AC power adapter [20]
Battery type	HP Long Life 8-cell, 95 Wh Li-ion polymer
Ecolabels	TCO Certified
Energy star certified	ENERGY STAR® certified
Management features	HP Power Manager [16]
Sustainable impact specifications	Low Halogen
UPC number	198990178790

Top Recommended Displays, Accessories and Services

Series 7 Pro

HP Series 7 Pro 34 inch WQHD Conferencing Monitor - 734pm	8K157AA
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9AA
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2AA

Speakerphones

Poly Sync 20+ USB-C Speakerphone	772D0AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 10 USB-A USB-C Speakerphone	772C3AA

Wireless Headset

Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter	8G7T9AA
Poly Voyager Focus 2 USB-C-C Headset +USB-C/A Adapter	9T9J3AA

Wired Headset

Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA
---	---------

Topload Bags

HP Renew Executive 16-inch Laptop Bag	6B8Y2AA
---------------------------------------	---------

Backpacks

HP Renew Executive 16 Laptop Backpack	6B8Y1UT
HP Renew Executive 16-inch Laptop Backpack	6B8Y1AA

Wireless Keyboards

HP 455 Programmable Wireless Keyboard	4R177AA
HP 975 Dual-Mode Wireless Keyboard	3Z726AA

Wireless Mice

HP 695 Rechargeable Wireless Mouse	8F1Y4AA
------------------------------------	---------

Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[4] Optional feature that must be configured at purchase.

[5] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[6] For hard drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 30GB (for Windows 10) of system disk is reserved for system recovery software.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[16] Manage and monitor your battery's performance and condition and customize charging options with the easy-to-use HP Power Manager dashboard.

[20] 150 W power adapter is configurable with Intel UMA graphics. 200 W power adapter is configurable with NVIDIA RTX A1000 and RTX A2000 configurations. 230 W power adapter is configurable with NVIDIA RTX A3000 or higher.

[21] UHD content required to view UHD images.

[23] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[32] Actual brightness will be lower with HP Sure View or touch-screen.

[39] HP Sure View Reflect integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

