

HP ProDesk 4 Tower G1i Desktop AI PC



Key Experiences and Product Specs



Enterprise tech and creative experts can stay cool under pressure with an expandable, reliable, AI-enabled tower PC.

Key Product Experiences

Essential tools, powered by AI for smooth performance: Drive productivity to complete routine tasks, freeing your time so you can dive into the work you love. Supporting an Intel® Core™ Ultra CPU¹ with 13 TOPS NPU², DDR5 RAM⁴, and a choice of discrete graphics⁵ to elevate your efficiency.

Modular options provide operational efficiency: Dynamically scale and allocate system resources based on current and future business needs. Improve performance with flexible graphics, storage, and memory options and expand functionality with multiple USB ports.

Work protected and secure: In addition to a physical security lock, HP Tamper Lock⁶ for BIOS protection and intrusion sensor for detecting and alerting to unauthorized opening of the chassis, HP Wolf Security for Business⁷ creates a hardware-enforced, always-on, resilient defense. From the BIOS to the browser, above, in, and below the OS, these constantly evolving solutions help protect your PC from modern threats.

Product Specs:

Operating System	Windows 11 Pro ⁸
Processor(s)	Intel® Core™ Ultra processors ¹ 65W up to Ultra 7/Q870, Intel vPro® Enterprise ⁹ optional Up to 13 TOPS NPU ²
Graphics	Integrated: Intel® UHD 770/730 graphics Optional discrete graphic card options: ⁵ <ul style="list-style-type: none"> • AMD Radeon™ RX 6300 2GB • NVIDIA® GeForce RTX 3050 8GB • Intel® Arc™ A380 6GB • NVIDIA® A400 4GB
Memory	4 DIMM, Up to 64 GB DDR5 4800 MT/s & 5600 MT/s (speed will vary based on configuration. Max system speed at 5600MHz if only one DIMM is installed) ¹⁰
Storage & Drive Bays	2x M.2 SSD slots, up to 4TB max ¹¹ (Up to 2TB PCIe® NVMe™ TLC M.2 SSD; Up to 512GB PCIe® NVMe™ Opal2 TLC M.2 SSD; Up to 1TB PCIe® NVMe™ M.2 SSD; up to 256GB PCIe® Opal2 NVMe M.2 SDD) ¹¹ 2 x 3.5" HDD bays, up to 4TB max (Up to 2TB SATA HDD) ¹¹ 1x 9.5mm slim SATA ODD ¹¹
Input/Connectivity	Front - (3) SuperSpeed USB Type-A 10Gbps signaling rate ¹² ports; (1) SuperSpeed USB Type-C® 10Gbps signaling rate ¹² port; (1) Combo Audio Jack; Rear - (1) audio Line-out; (1) RJ-45; (2) SuperSpeed USB Type-A 5Gbps signaling rate ¹² ports; (3) USB Type-A 480Mbps signaling rate ¹² ports; (1) DisplayPort™ 2.1; (1) HDMI 2.1; (1) Choice of Serial/DisplayPort™ 2.1/HDMI 2.1/VGA, dual USB-A (5Gbps signaling rate ¹²) or USB Type-C® 10Gbps signaling rate ¹² (alternate mode DisplayPort™), PCIe: (1) 4x serial via PCIe®; (1) serial port (optional)
Wireless technology	LAN: Integrated Intel® I219LM GbE LOM; Intel I226-T1 2.5GbE NIC WLAN: Intel® AX211 Wi-Fi 6E ^{13,14} + Bluetooth® 5.2 M.2 2230 160MHz CNVi WW WLAN; Intel® AX211 Wi-Fi 6E ^{13,14} + Bluetooth® 5.2 M.2 2230 160MHz CNVi WW WLAN Intel vPro®; Realtek 8852BE Wi-Fi 6 ¹⁵ + Bluetooth® 5.2 M.2 2230 PCI-e+USB WW WLAN; Realtek RTL8821CE ac 1x1 + Bluetooth® 4.2 LE WW
Power	180W/260W/400W
Weight and Dimensions	155 x 308 x 337 mm (6.1 x 12.13 x 13.27 in) Starting at 5.58 kg (12.3 lbs) ¹⁶
Color	Black
Expansion Slots	(1) PCIe® 4.0 x16 (dGPU), (2) PCIe® 3.0 x1
Sustainable Impact Specifications	EPEAT Climate+™ Gold ¹⁷ , ENERGY STAR® and TCO certified; at Least 60% PCR materials in total ²³ ; 20% recycle SGCC steel used in chassis & PSU ²² ; Speaker enclosure, fan housing / ducts & front I/O strip made from recycled material including ocean-bound plastics ¹⁸ ; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable ¹⁹ ; Outside box and corrugated cushions are 100% sustainably sourced and recyclable ¹⁹ ; low halogen ²⁰ ; Bulk packs available ²¹
Security & Manageability	HP Wolf Security for Business ⁷ ; HP Sure Start ²⁴ , HP Sure Run ²⁵ , HP Sure Recover ²⁶ , HP Sure Admin ²⁷ , HP Sure Click ²⁸ , HP Sure Sense ²⁹ , HP Tamper Lock ⁶

Disclaimers:

1. Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
2. AI applications that require an NPU may require software purchase, subscription or enablement by a software or platform provider, and third-party software may have specific configuration or compatibility requirements. Potential NPU inferencing performance varies by use, configuration, and other factors
3. N/A
4. For systems configured with more than 3 GB of memory and a 32-bit operating system, all memory may not be available due to system resource requirements. Addressing memory above 4 GB requires a 64-bit operating system. Memory modules support data transfer rates up to 2666 MT/s, 2933 MT/s or 3200 MT/s as depending on processor config; with 1 DIMM per channel. Additional DIMM loading on any channel may impact maximum memory speed. Actual data rate is determined by the system's configured ; See processor specifications for supported memory data rate.
5. Sold separately or as an optional feature.
6. HP Tamper Lock must be enabled by the customer or your administrator.
7. HP Wolf Security for Business requires Windows 10 or 11 Pro and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features.
8. Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.
9. Intel vPro® requires Windows 10 Pro 64 bit or higher, a vPro supported processor, vPro enabled chipset, vPro enabled wired LAN and/or Wi-Fi 6E WLAN and TPM 2.0. Some functionality requires additional 3rd party software in order to run. Features of vPro® Essentials and Enterprise vary. See <http://intel.com/vproHP> Services are sold separately. HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.
10. Modules support data transfer rates up to 5600 MT/s; system speed should follow Intel's design guideline. Actual data rate is determined by the system configuration.
11. For storage drives, GB = 1 billion bytes. Actual formatted capacity is less. Up to 30 GB (for Windows) is reserved for system recovery software.
12. Actual throughput may vary
13. Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs and available in countries where Wi-Fi 6E is supported.
14. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 6E (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.
15. Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 (802.11ax) is backwards compatible with prior 802.11 specs.
16. Actual weight will vary by configuration.
17. Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. EPEAT® status varies by country. See www.epeat.net for registration status and tier levels by country.
18. Percentage of ocean-bound plastic contained in each component varies by product. Ocean Bound plastic is expressed as a percentage of the total weight plastic. Ocean Bound plastic is based on the definition set by the UL2809 standard
19. HP paper and fiber based packaging for PCs, displays, home and office print, and supplies is reported by suppliers as recycled or certified, with a minimum of 97% by volume verified by HP. Packaging is the box that comes with the product and all paper-based materials inside the box. Packaging for personal systems accessories and spare parts is not included.
20. External power supplies, WWAN modules, power cords, cables and peripherals excluded. Service parts obtained after purchase may not be Low Halogen.
21. Bulk packaging solution may vary by region or market
22. Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams
23. Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 EPEAT standard.
24. HP Sure Start is available on select HP PCs and requires Windows 10 or 11.
25. HP Sure Run is available on select HP PCs and requires Windows 10 or higher.
26. HP Sure Recover with Embedded Reimaging is an optional feature which requires Windows 10 and higher must be configured at purchase. You must back up important files, data, photos, videos, etc. before use to avoid loss of data. Network based recovery using Wi-Fi is only available on PCs with Intel Wi-Fi Module.
27. HP Sure Admin requires Windows 10, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.
28. HP Sure Click requires Windows 10 or higher. See https://bit.ly/2PrLT6A_SureClick for complete details.
29. HP Sure Sense is available on select HP PCs and is not available with Windows10 Home.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. Microsoft®, Windows® 11, and Windows® 11 Pro are registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

Intel®, Intel® Core™, Intel vPro® and Intel® Optane™ are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. Thunderbolt is a trademark of Intel Corporation or its subsidiaries in the U.S. and/or other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries.