


OVERVIEW



1. USB-C 3.2 Gen 1	7. MicroSD card reader
2. Thunderbolt 4	8. Ethernet (RJ-45)
3. Side docking connector	9. Smart card reader *
4. USB 3.2 Gen 1 (Always On)	10. Headphone / microphone combo jack (3.5mm)
5. HDMI 2.0	11. USB 3.2 Gen 1
6. Nano-SIM card slot *	12. Kensington Security Slot

Notes:

- Ports with * are only available on selected models
- The combination of 2 and 3 is side docking connector

PERFORMANCE

Processor

Processor Family

Intel® Pentium® or 11th Generation Intel Core™ i3 / i5 / i7 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Pentium Gold 7505	2	4	2.0GHz	3.5GHz	4MB	DDR4-3200	Intel UHD Graphics
Core i3-1115G4	2	4	3.0GHz	4.1GHz	6MB	DDR4-3200	Intel UHD Graphics
Core i5-1135G7	4	8	2.4GHz	4.2GHz	8MB	DDR4-3200	Intel Iris® Xe Graphics
Core i5-1145G7	4	8	2.6GHz	4.4GHz	8MB	DDR4-3200	Intel Iris Xe Graphics
Core i7-1165G7	4	8	2.8GHz	4.7GHz	12MB	DDR4-3200	Intel Iris Xe Graphics
Core i7-1185G7	4	8	3.0GHz	4.8GHz	12MB	DDR4-3200	Intel Iris Xe Graphics

Operating System

Operating System^[1]

- Windows® 10 Pro 64
- Windows 10 Home 64
- Windows 10 IoT Enterprise LTSC
- Linux
- No operating system

Notes:

1. Windows 10 IoT Enterprise LTSC is for special bid only

Monitor Support

Monitor Support

Supports up to 3 independent displays via native display and 2 external monitors; supports external monitors via HDMI® (up to 4096x2160@60Hz), USB-C (up to 5120x3200@60Hz) or Thunderbolt™ (up to 5120x3200@60Hz)

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 64GB DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Memory Type

DDR4-3200

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Type

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	APS (Active Protection System™)
2.5" SATA HDD	SATA 6Gb/s	7.2K	APS (Active Protection System)
M.2 2242 SSD	PCIe NVMe, PCIe 3.0 x4	-	-

ThinkPad L14 Gen 2 (Intel)

M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	Opal2

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby® Audio™ Premium

Microphone^[1]

- Dual array microphone, far-field
- No microphone

Camera^[2]

- 720p, with privacy shutter, fixed focus
- IR & 720p hybrid, with privacy shutter, fixed focus
- No camera

Notes:

1. No microphone is for special bid only
2. No camera is for special bid only

Battery

Battery

Integrated Li-Polymer 45Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter

Max Battery Life^[1]

MobileMark® 2018: 9.01 hr

JEITA 2.0: 11.815 hr

Notes:

1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, and/or JEITA 2.0 battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter^[1]

- 45W USB-C (2-pin) AC adapter
- 45W USB-C (3-pin) AC adapter
- 65W USB-C slim (3-pin) AC adapter
- 65W USB-C slim (2-pin) AC adapter
- 65W USB-C (2-pin) AC adapter
- 65W USB-C (3-pin) AC adapter
- No power adapter

Notes:

1. No power adapter is for special bid only
45W USB-C AC adapter and 65W USB-C slim AC adapter are NOT available in EMEA

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
14.0"	HD (1366x768)	None	TN	220 nits	Anti-glare	16:9	400:1	45% NTSC	90°	-
14.0"	FHD	None	IPS	250 nits	Anti-	16:9	700:1	45%	170°	-

ThinkPad L14 Gen 2 (Intel)

	(1920x1080)				glare			NTSC		
14.0"	FHD (1920x1080)	None	IPS	400 nits	Anti-glare	16:9	800:1	72% NTSC	170°	Low power
14.0"	FHD (1920x1080)	Multi-touch	IPS	300 nits	Anti-glare	16:9	700:1	45% NTSC	170°	-

Touchscreen

- On-cell touch, supports 10-point touch
- Non-touch

Notes:

1. California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, spill-resistant, multimedia Fn keys with Unified Communications controls

Keyboard Backlight

- LED backlight
- No support

UltraNav™

TrackPoint® pointing device and Mylar® surface multi-touch touchpad

Mechanical

Dimensions (WxDxH)

Models	Dimensions
Aluminium models	331 x 235 x 19.1 mm (13.03 x 9.25 x 0.75 inches)
PC + ABS models	331 x 235 x 20.4 mm (13.03 x 9.25 x 0.80 inches)

Weight^[1]

Models	Weight
Aluminium models	1.74 kg (3.84 lbs)
PC + ABS models	1.59 kg (3.49 lbs)

Case Material^[2]

- Aluminium (top), PC + ABS (bottom)
- PC + ABS (top), PC + ABS (bottom)

Notes:

1. The system weight varies depending on configurations
2. Aluminium top cover is NOT available in EMEA

CONNECTIVITY

Network

Onboard Ethernet

- Gigabit Ethernet, Intel Ethernet Connection I219-V (non-vPro models)
- Gigabit Ethernet, Intel Ethernet Connection I219-LM (vPro models)

WLAN + Bluetooth^[1]

- Wi-Fi® 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 card
- Mediatek Wi-Fi 6 MT7921, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- Realtek RTL8852AE, Wi-Fi 6, 802.11ax Dual Band 2x2 Wi-Fi + Bluetooth 5.2, M.2 card
- Intel Wi-Fi 6 AX200, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 card
- Intel Wi-Fi 6E AX210, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- No WLAN and Bluetooth

ThinkPad L14 Gen 2 (Intel)

WWAN

- Wireless WAN upgradable to 4G
- Integrated Mobile Broadband 4G LTE, Quectel EM120R-GL, M.2 card, with embedded eSIM functionality
- No support

SIM Card

No SIM card inbox

NFC

- Near Field Communication
- No support

Notes:

1. Intel WiFi 6 full features might be limited by country level restrictions
6GHz Wi-Fi 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi 6E, and the regional regulatory certifications & spectrum allocation
Bluetooth 5.2 is supported with driver version 22.30 and later

Ports^[1]

Standard Ports^[2]

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x Thunderbolt 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort 1.4)
- 1x HDMI 2.0
- 1x microSD card reader
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Side docking connector

Optional Ports

- 1x Nano-SIM card slot (WWAN model)
- 1x Smart card reader

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt 3: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s
2. Depending on many factors, actual data transfer speed may be lower than theoretical speed

Monitor Cable

Monitor Cable

- Lenovo HDMI to VGA Monitor Adapter
- Lenovo USB-C to DisplayPort Adapter
- Lenovo USB-C to VGA Adapter
- No monitor cable

SECURITY & PRIVACY

Security

Security Chip

- Discrete TPM 2.0, TCG certified
- Firmware TPM 2.0 integrated in chipset
- Disabled (in some regions)

Physical Locks

Kensington® Security Slot

Smart Card Reader

- Smart card reader
- No smart card reader

Fingerprint Reader

- Touch style fingerprint reader on palm rest, match-on-chip
- No fingerprint reader

BIOS Security

- Supervisor password
- Power-on password
- Hard disk password (for HDD)
- NVMe password (for NVMe SSD)
- Self-healing BIOS

Other Security

- (Optional) Camera privacy shutter
- (Optional) IR camera for Windows Hello

MANAGEABILITY

System Management

System Management

- Intel vPro Technology, DASH
- None

SERVICE

Warranty

Base Warranty

- 1-year depot service
- 1-year depot with 2-year system board service
- 1-year limited onsite service
- 1-year + 2-year depot service
- 1-year + 2-year limited onsite service
- 3-year (1-yr battery) depot service
- 3-year (1-yr battery) limited onsite service
- No base warranty

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping package: -20°C (-4°F) to 60°C (140°F)
- Storage without package: 5°C (41°F) to 43°C (109°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F)

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- TCO
- RoHS compliant

Other Certifications

Mil-Spec Test


MIL-STD-810H military test passed



intel



intel



intel



intel



intel



intel