



243 Jubug-ri, Yangji-myeon, Cheoin-gu, Yongin-si, Gyeonggi-do 449-822, Korea
 Tel: +82-31-323-6008 Fax: +82-31-323-6010
<http://www.ltalab.com>

EMC TEST REPORT

Dates of Tests: April 23 - 26, 2019
 Test Report S/N: LR500122108A
 Test Site : LTA Co., Ltd.

Model No.

QNO-6082R

APPLICANT

Hanwha Techwin Co., Ltd.

Equipment Name : NETWORK CAMERA
Manufacturer : Hanwha Techwin Co., Ltd.
Model name : QNO-6082R
Additional Model name : QNO-6072R, QNO-6082R1, QNO-6072R1
Test Device Serial No.: : Identification
Directive : Electromagnetic Compatibility Directive 2014/30/EU
Rule Part(s) : EN 55032:2015/A11:2020
 EN 50130-4:2011/A1:2014
 EN 61000-3-2:2014
 EN 61000-3-3:2013
Data of reissue : August 10, 2021

This test report is issued under the authority of:


The test was supervised by:

Young Kyu Shin, Technical Manager

Joo Hyung Cho, Test Engineer

This test result only responds to the tested sample. It is not allowed to copy this report even partly without the allowance of the test laboratory. The report must not be used by the client to claim product certification, approval, or endorsement by NVLAP, NIST, or any agency of the Federal Government.

This test report is not related to KS Q ISO/IEC 17025 and KOLAS accreditation.



Revision	Date of issue	Test report No.	Description
0	29.04.2019	LR500121904BE	Initial
1	10.08.2021	LR500122108A	Rule Update, Delete China Factory, Add Additional Models (QNO-6082R1, QNO-6072R1)

TABLE OF CONTENTS

1. General information's.....	4
2. Information's about test item.....	5
3. Test Report.....	8
3.1 Summary of tests	8
3.2 EMISSION	9
3.2.1 Conducted emissions	9
3.2.2 Radiated Emission.....	15
3.2.3 Harmonic Current (AC power input port)	23
3.2.4 Voltage Variation and Flicking (AC power input port).....	25
3.3 IMMUNITY	28
3.3.1 Electrostatic Discharge	28
3.3.2 RF Electromagnetic Field	32
3.3.3 Electrical fast transients	34
3.3.4 Surge.....	35
3.3.5 Conducted disturbances, induced by radio-frequency fields	36
3.3.6 Mains supply voltage dips, short interruptions	37
3.3.7 Mains supply voltage variations.....	38
APPENDIX A TEST EQUIPMENT AND ANCILLARIES USED FOR TESTS	39
APPENDIX B PERFORMANCE CRITERIA.....	43
APPENDIX C PHOTOGRAPHS	46

1. General information's

1-1 Test Performed

Company name : **LTA Co., Ltd**
 Address : 4, Songju-ro 236beon-gil, Yangji-myeon, Cheoin-gu, Yongin-si, Gyeonggi-do, 17159, Korea
 Web site : <http://www.ltalab.com>
 E-mail : chahn@ltalab.com
 Telephone : +82-31-323-6008
 Facsimile : +82-31-323-6010

Quality control in the testing laboratory is implemented as per ISO/IEC 17025 which is the “General requirements for the competents of calibration and testing laboratory”.

1-2 Accredited agencies

LTA Co., Ltd. is approved to perform EMC testing by the following agencies:

Agency	Country	Accreditation No.	Validity	Reference
NVLAP	U.S.A	200723-0	2021-09-30	ECT accredited Lab.
	KOREA		-	
RRA	U.S.A	KR0049	2023-04-08	RRA accredited Lab.
	CANADA		2022-10-18	
		C-14948	2023-09-10	
VCCI	JAPAN	T-12416	2023-09-10	VCCI registration
		R-14483	2023-10-15	
		G-10847	2021-12-13	
KOLAS	KOREA	KT551	2021-08-20	KOLAS accredited Lab.

2. Information's about test item

2-1 Client/ Manufacturer

Company name : Hanwha Techwin Co., Ltd.
Address : 8-10, TECHNO 3-RO, YUSEONG-GU, DAEJEON, KOREA
Telephone / Facsimile : +82-31-723-5205 / +82-31-723-5108

Factory #1

Company name : HANWHA TECHWIN SECURITY VIETNAM CO.,LTD.
Address : Lot O-2, Que Vo Industrial Zone extended area ,Nam Son commune, Bac Ninh city,Bac Ninh province, Vietnam

Factory #2

Company name : D-TECH CO.,LTD.
Address : 173-25, Saneop-ro, Gwonseon-gu, Suwon-si, Gyeonggi-do, Korea (Suwon Industrial Complex)

2-2 Equipment Under Test (EUT)

Class : A
Equipment Name : NETWORK CAMERA
Model name : QNO-6082R
Additional Model name : QNO-6072R, QNO-6082R1, QNO-6072R1
Additional Models are different only lens specification.
Serial number : Identification
Date of receipt : April 09, 2019
EUT condition : Pre-production, not damaged
Interface ports : DC IN, LAN, Alarm IN, Alarm OUT, GND, Micro SD, MIC
Video OUT Port is a management Port.
Power rating : DC 12 V (Adapter), DC 48 V (POE)

2-3 Modification

-NONE

2-4 Test conditions

Temp. / Humid. / Pressure : +(21 - 24) °C / (31 - 41) % R.H. / (101) kPa
Tested Model : QNO-6082R
Test mode : REC mode (Adapter), REC mode (POE)
Tested Voltage : AC 230 V, 50 Hz (Adapter), DC 48 V (POE)

2-5 EUT

Equipment	Model No.	Serial No.	Manufacturer
NETWORK CAMERA	QNO-6082R	N/A	HANWHA TECHWIN SECURITY VIETNAM CO.,LTD. D-TECH CO.,LTD.

2-6 Accessory / REC mode (Adapter)

Equipment	Model No.	Serial No.	Manufacturer
EUT Adapter	F12L2-120100SPAK	N/A	SHENZHEN FRECOM ELECTRONKS CO.,LTD.
Alarm #1	N/A	N/A	N/A
Alarm #2	SPL-0030	N/A	SECOM
Smart Phone	SHV-E210L	R33C9026JXE	SAMSUNG
Notebook	P56	NKW650RB0006A02845	HANSUNG
Notebook Adapter	A10-090P3A	F180261552004253	Chicony Power Technology (SUZHOU)CO.,LTD.
Micro SD Card	MB-MP32D	MBMPBGVEODFW-F	SAMSUNG

/ REC mode (POE)

Equipment	Model No.	Serial No.	Manufacturer
Alarm #1	N/A	N/A	N/A
Alarm #2	SPL-0030	N/A	SECOM
Smart Phone	SHV-E210L	R33C9026JXE	SAMSUNG
Notebook	P56	NKW650RB0006A02845	HANSUNG
Notebook Adapter	A10-090P3A	F180261552004253	Chicony Power Technology (SUZHOU)CO.,LTD.
Micro SD Card	MB-MP32D	MBMPBGVEODFW-F	SAMSUNG
POE Injector	PSE305	N/A	N/A

2-7 Cable List / REC mode (Adapter)

From		To		Length (m)	Shielding	
Type	I/O Port	Type	I/O Port		Cable	backshell
EUT	DC IN	EUT Adapter	DC OUT	1.4	NO	Plastic
	ARM-IN	Alarm #1	-	1.2	NO	Plastic
	GND	Alarm #1	-	1.2	NO	Plastic
	ARM-OUT	Alarm #2	-	1.8	NO	Plastic
	GND	Alarm #2	-	1.8	NO	Plastic
	MIC	Smart Phone	AUX	1.6	NO	Plastic
	LAN	Notebook	LAN	3.0	NO	Plastic
	Micro SD	Micro SD Card	-	-	-	-
Notebook	DC IN	Notebook Adapter	DC OUT	1.2	NO	Plastic

/ REC mode (POE)

From		To		Length (m)	Shielding	
Type	I/O Port	Type	I/O Port		Cable	backshell
EUT	LAN	POE Injector	P+D/OUT	3.0	NO	Plastic
	ARM-IN	Alarm #1	-	1.2	NO	Plastic
	GND	Alarm #1	-	1.2	NO	Plastic
	ARM-OUT	Alarm #2	-	1.8	NO	Plastic
	GND	Alarm #2	-	1.8	NO	Plastic
	MIC	Smart Phone	AUX	1.6	NO	Plastic
	Micro SD	Micro SD Card	-	-	-	-
POE Injector	Data/IN	Notebook	LAN	3.0	NO	Plastic
	AC IN	AC Power Source	3 Pin AC Line	1.2	NO	Plastic
Notebook	DC IN	Notebook Adapter	DC OUT	1.2	NO	Plastic

3. Test Report

3.1 Summary of tests

Parameter	Applied Standard	Status
I. Emission		
Radiated Emission	EN 55032:2015/A11:2020	C
Conducted Emission	EN 55032:2015/A11:2020	C
Harmonic Current Emission	EN 61000-3-2:2014	N/A ^{Note3}
Voltage Fluctuations and Flicker	EN 61000-3-3:2013	C
II. Immunity		
Electrostatic Discharge	EN 61000-4-2:2009	C
RF Electromagnetic field	EN 61000-4-3:2006/A1:2008/A2:2010	C
Fast Transients Common mode	EN 61000-4-4:2012	C
Surges, line to line and line to ground	EN 61000-4-5:2014/A1:2017	C
RF common mode	EN 61000-4-6:2014/AC:2015	C
Voltage dips and Interruptions	EN 61000-4-11:2004/A1:2017	C
Main supply voltage variations	EN 50130-4:2011/A1:2014	C

Note 1: C=Complies NC=Not Complies NT=Not Tested NA=Not Applicable

Note 2: The data in this test report are traceable to the national or international standards.

Note 3: We did not test EN61000-3-2 (Harmonic current emissions) for the QNO-6082R because equipment whose rated power is less or equal 75W don't need to be tested.

3.2 EMISSION

3.2.1 Conducted emissions

Definition:

The test assesses the ability of the EUT to limit its internal noise from being present on the AC mains Power In/Output ports.

We were performed the test according to LTA procedure LTA-QI-04.

Measurement Frequency range	: 150 kHz – 30 MHz
Test method	: EN 55032:2015/A11:2020
Measurement RBW	: 9 kHz
Test mode	: REC mode (Adapter), REC mode (POE)
Result	: Complies

Measurement Data:

- Refer to the Next page (Maximum emission configuration)

A sample calculation:

COR. F (correction factor)= LISN Insertion loss + Cable loss + Pulse Limiter Factors

Emission Level= meter reading + COR.F

Limits for conducted disturbance at the mains ports of class A ITE

Frequency Range	Quasi-peak	Average
(0.15 – 0.5) MHz	79 dBuV	66 dBuV
(0.5 – 30) MHz	73 dBuV	60 dBuV

Note: The limits will decrease with the frequency logarithmically within 0.15MHz to 0.5MHz

Limits for conducted disturbance at the mains ports of class B ITE

Frequency Range	Quasi-peak	Average
(0.15 – 0.5) MHz	(66 – 56) dBuV	(56 - 46) dBuV
(0.5 – 5) MHz	56 dBuV	46 dBuV
(5 – 30) MHz	60 dBuV	50 dBuV

Note: The limits will decrease with the frequency logarithmically within 0.15 MHz to 0.5 MHz

Limits of conducted common mode (asymmetric mode) disturbance at telecommunication ports in the frequency range 0.15 MHz to 30 MHz for class A equipment

Frequency Range	Voltage limits		Current limits	
	Quasi-peak	Average	Quasi-peak	Average
(0.15 – 0.5) MHz	(97 – 87) dBuV	(84 – 74) dBuV	(53 – 43) dBuV	(40 – 30) dBuV
(0.5 – 30) MHz	87 dBuV	74 dBuV	43 dBuV	30 dBuV

Note 1: The limits decrease linearly with the logarithm of the frequency in the range 0.15 MHz to 0.5 MHz.

Note 2: The current and voltage disturbance limits are derived for use with an impedance stabilization network (ISN) which presents a common mode (asymmetric mode) impedance of 150Ω to the telecommunication port under test (conversion factor is $20 \log_{10} 150/I = 44$ dB)

Limits of conducted common mode (asymmetric mode) disturbance at telecommunication ports in the frequency range 0.15 MHz to 30 MHz for class B equipment

Frequency Range	Voltage limits		Current limits	
	Quasi-peak	Average	Quasi-peak	Average
(0.15 – 0.5) MHz	(84 – 74) dBuV	(74 – 64) dBuV	(40 – 30) dBuV	(30 – 20) dBuV
(0.5 – 30) MHz	74 dBuV	64 dBuV	30 dBuV	20 dBuV

Note 1: The limits decrease linearly with the logarithm of the frequency in the range 0.15 MHz to 0.5 MHz.

Note 2: The current and voltage disturbance limits are derived for use with an impedance stabilization network (ISN) which presents a common mode (asymmetric mode) impedance of 150Ω to the telecommunication port under test (conversion factor is $20 \log_{10} 150/I = 44$ dB)


Conducted emissions (LINE) / REC mode (Adapter)



4, Songjuro 236 Beon-gil, Yangji-myeon
 Cheoin-gu, Youngin-si, Gyeonggi-do
 449-822 Korea
 Tel:+82-31-3236008,9
 Fax:+82-31-3236010

EUT /Model No. : QNO-6082R	Phase : Line
Test Mode : REC mode (Adapter)	Test Power : 230 / 50
Temp./ Humi. : 24'C / 41% R.H.	Test Engineer : CHOI Y H

Date: 2019-04-25



Trace: 1

Freq	RD	RD	C.F	Result	Result	Limit	Limit	Margin	Margin
MHz	QP	AV	dB	QP	AV	QP	AV	QP	AV
	dBuV	dBuV		dBuV	dBuV	dBuV	dBuV	dB	dB

0.156	36.09	10.69	19.46	55.55	30.15	79.00	66.00	23.45	35.85
0.176	34.24	11.00	19.47	53.71	30.47	79.00	66.00	25.29	35.53
0.209	28.94	5.06	19.47	48.41	24.53	79.00	66.00	30.59	41.47
0.233	26.57	4.47	19.48	46.05	23.95	79.00	66.00	32.95	42.05
0.340	20.56	3.06	19.49	40.05	22.55	79.00	66.00	38.95	43.45
0.378	21.43	2.10	19.50	40.93	21.60	79.00	66.00	38.07	44.40

Remarks: C.F (Correction Factor) = Insertion loss + Cable loss + Pulse Limiter


Conducted emissions (NEUTRAL) / REC mode (Adapter)



4, Songjuro 236 Beon-gil, Yangji-myeon
 Cheoin-gu, Youngin-si, Gyeonggi-do
 449-822 Korea
 Tel:+82-31-3236008,9
 Fax:+82-31-3236010

EUT /Model No. : QNO-6082R	Phase : Neutral
Test Mode : REC mode (Adapter)	Test Power : 230 / 50
Temp./ Humi. : 24'C / 41% R.H.	Test Engineer : CHOI Y H

Date: 2019-04-25



Trace: 1

Freq MHz	RD QP dBuV	RD AV dBuV	C.F dB	Result QP dBuV	Result AV dBuV	Limit QP dBuV	Limit AV dBuV	Margin QP dB	Margin AV dB
0.157	36.08	11.60	19.47	55.55	31.07	79.00	66.00	23.45	34.93
0.180	32.88	10.30	19.48	52.36	29.78	79.00	66.00	26.64	36.22
0.205	30.51	8.79	19.48	49.99	28.27	79.00	66.00	29.01	37.73
0.215	28.12	9.32	19.48	47.60	28.80	79.00	66.00	31.40	37.20
0.412	21.62	13.41	19.50	41.12	32.91	79.00	66.00	37.88	33.09
0.681	12.28	1.74	19.52	31.80	21.26	73.00	60.00	41.20	38.74

Remarks: C.F (Correction Factor) = Insertion loss + Cable loss + Pulse Limiter


Conducted emissions (TEL_100 M) / REC mode (Adapter)



4, Songjuro 236 Beon-gil, Yangji-myeon
 Cheoin-gu, Youngin-si, Gyeonggi-do
 449-822 Korea
 Tel:+82-31-3236008,9
 Fax:+82-31-3236010

EUT /Model No. : QNO-6082R	Phase : TEL 100M
Test Mode : REC mode (Adapter)	Test Power : 230 / 50
Temp./ Humi. : 24'C / 41% R.H.	Test Engineer : CHOI Y H

Date: 2019-04-25



Trace: 1

Freq MHz	RD QP dBuV	RD AV dBuV	C.F dB	Result QP dBuV	Result AV dBuV	Limit QP dBuV	Limit AV dBuV	Margin QP dB	Margin AV dB
0.424	42.81	36.10	19.52	62.33	55.62	88.36	75.36	26.03	19.74
13.358	33.95	33.52	19.68	53.63	53.20	87.00	74.00	33.37	20.80
14.213	35.71	35.26	19.71	55.42	54.97	87.00	74.00	31.58	19.03
15.083	32.18	10.49	19.71	51.89	30.20	87.00	74.00	35.11	43.80
16.229	39.90	39.49	19.76	59.66	59.25	87.00	74.00	27.34	14.75
23.128	34.07	30.82	19.97	54.04	50.79	87.00	74.00	32.96	23.21


Remarks: C.F (Correction Factor) = Insertion loss + Cable loss + Pulse Limiter

Conducted emissions (TEL_100 M) / REC mode (POE)



4, Songjuro 236 Beon-gil, Yangji-myeon
 Cheoin-gu, Youngin-si, Gyeonggi-do
 449-822 Korea
 Tel:+82-31-3236008,9
 Fax:+82-31-3236010

EUT /Model No. : QNO-6082R	Phase : TEL 100M
Test Mode : REC mode (POE)	Test Power : 230 / 50
Temp./ Humi. : 24'C / 41% R.H.	Test Engineer : CHOI Y H



Date: 2019-04-25

Trace: 1									
Freq	RD	RD	C.F	Result	Result	Limit	Limit	Margin	Margin
MHz	QP	AV	dB	QP	AV	QP	AV	QP	AV
	dBuV	dBuV		dBuV	dBuV	dBuV	dBuV	dB	dB
1.301	36.44	34.11	19.41	55.85	53.52	87.00	74.00	31.15	20.48
5.861	37.82	30.46	19.49	57.31	49.95	87.00	74.00	29.69	24.05
6.728	38.40	31.42	19.52	57.92	50.94	87.00	74.00	29.08	23.06
7.378	37.35	29.01	19.54	56.89	48.55	87.00	74.00	30.11	25.45
15.628	35.29	31.58	19.73	55.02	51.31	87.00	74.00	31.98	22.69
16.243	36.55	36.14	19.81	56.36	55.95	87.00	74.00	30.64	18.05

Remarks: C.F (Correction Factor) = Insertion loss + Cable loss + Pulse Limiter

3.2.2 Radiated Emission

Definition:

The test assesses the ability of ancillary equipment to limit their internal noise from being radiated from the enclosure.

We were performed the test according to LTA procedure LTA-QI-04.

Test method	:	EN 55032:2015/A11:2020
Measuring Distance	:	10 m for below 1 GHz / 3 m for above 1 GHz
Measurement Frequency range	:	30 MHz – 6 000 MHz
Measurement RBW	:	120 kHz @ 10 m / 1 MHz @ 3 m
Test mode	:	REC mode (Adapter), REC mode (POE)
Result	:	Complies

Measurement Data:

- Refer to the Next page (Maximum emission configuration)

- The highest internal source of an EUT is higher than 108 MHz, the measurement shall be made up to 6 GHz.

(The highest internal source of an EUT : 1 GHz)

A sample calculation:

COR. F (correction factor)= Antenna factor + Cable loss- Amp.gain- Distance correction

Emission Level= meter reading + COR.F

Limit of 10 m for below 1 GHz

CLASS A

Frequency Range	Quasi-peak
(30 – 230) MHz	40 dBuV/m
(230 – 1 000) MHz	47 dBuV/m

CLASS B

Frequency Range	Quasi-peak
(30 – 230) MHz	30 dBuV/m
(230 – 1 000) MHz	37 dBuV/m

Limit of 3m for above 1 GHz

CLASS A

Frequency Range	Average Limit @ 3m (dB μ V/m)	Peak limit @ 3m (dB μ V/m)
(1 000 – 3 000) MHz	56	76
(3 000 – 6 000) MHz	60	80
NOTE:	The lower limit applies at the transition frequency.	

CLASS B

Frequency Range	Average Limit @ 3m (dB μ V/m)	Peak limit @ 3m (dB μ V/m)
(1 000 – 3 000) MHz	50	70
(3 000 – 6 000) MHz	54	74
NOTE:	The lower limit applies at the transition frequency.	

Radiated Emission (Below 1 GHz) / V _ REC mode (Adapter)




4, Songjuro 236Beon-gil, yanggi-myeon,
Yongin-si, Gyeonggi-do, Korea
Tel : +82-31-3236008,9
Fax : +82-31-3236010
www.ltalab.com

EUT/Model No. : QNO-6082R

Temp/Humi: 23 / 31

Test Mode : REC mode (Adapter)

Tested by: CHOI Y H



Date: 2019-04-23

Freq MHz	Reading dBuV	C.F dB	Result QP dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Polarity
36.06	44.61	-14.60	30.01	40.00	9.99	113	78	vertical
74.98	52.69	-16.19	36.50	40.00	3.50	100	68	vertical
660.02	41.14	-3.90	37.24	47.00	9.76	102	351	vertical

Remarks: C.F (Correction Factor) = Antenna factor + Cable loss - Preamp gain

Radiated Emission (Below 1 GHz) / H _ REC mode (Adapter)




4, Songjuro 236Beon-gil, yanggi-myeon,
Yongin-si, Gyeonggi-do, Korea
Tel : +82-31-3236008,9
Fax : +82-31-3236010
www.ltalab.com

EUT/Model No. : QNO-6082R

Temp/Humi: 23 / 31

Test Mode : REC mode (Adapter)

Tested by: CHOI Y H



Freq MHz	Reading dBuV	C.F dB	Result QP dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Polarity
252.98	44.37	-12.87	31.50	47.00	15.50	357	107	horizontal
660.02	39.73	-3.90	35.83	47.00	11.17	367	117	horizontal
700.03	38.84	-3.24	35.60	47.00	11.40	176	356	horizontal

Remarks: C.F (Correction Factor) = Antenna factor + Cable loss - Preamp gain

Radiated Emission (Below 1 GHz) / V _ REC mode (POE)




4, Songjuro 236Beon-gil, yanggi-myeon,
 Yongin-si, Gyeonggi-do, Korea
 Tel : +82-31-3236008,9
 Fax : +82-31-3236010
 www.ltalab.com

EUT/Model No.: QNO-6082R

Temp/Humi: 23 / 31

Test Mode : REC mode (POE)

Tested by: CHOI Y H



Freq MHz	Reading dBuV	C.F dB	Result QP dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Polarity
39.94	48.48	-14.04	34.44	40.00	5.56	112	107	vertical
53.52	48.12	-13.44	34.68	40.00	5.32	103	255	vertical
74.98	51.42	-16.19	35.23	40.00	4.77	100	82	vertical

Remarks: C.F (Correction Factor) = Antenna factor + Cable loss - Preamp gain

Radiated Emission (Below 1 GHz) / H _ REC mode (POE)




4, Songjuro 236Beon-gil, yanggi-myeon,
Yongin-si, Gyeonggi-do, Korea
Tel : +82-31-3236008,9
Fax : +82-31-3236010
www.ltalab.com

EUT/Model No. : QN0-6082R

Temp/Humi: 23 / 31

Test Mode : REC mode (POE)

Tested by: CHOI Y H




Freq MHz	Reading dBuV	C.F dB	Result QP dBuV/m	Limit dBuV/m	Margin dB	Height cm	Angle deg	Polarity
105.66	50.78	-16.55	34.23	40.00	5.77	364	360	horizontal
660.02	38.42	-3.90	34.52	47.00	12.48	354	289	horizontal
700.03	40.18	-3.24	36.94	47.00	10.06	112	327	horizontal

Remarks: C.F (Correction Factor) = Antenna factor + Cable loss - Preamp gain

Radiated Emission (Above 1 GHz) / REC mode (Adapter)


(Above 1 GHz) / V

EUT/Model No. : QNO-6082R Temp/Humi: 23 / 31
 Test Mode : REC mode (Adapter) Tested by: CHOI Y H



(Above 1 GHz) / H

EUT/Model No. : QNO-6082R Temp/Humi: 23 / 31
 Test Mode : REC mode (Adapter) Tested by: CHOI Y H



Manufacture : HANWHA TECHWIN SECURITY VIETNAM CO.,LTD.

Test Date

Temp.:

Humidity:

Distance

Model : QNO-6082R

2019-04-23

23

31

3.8


TEST mode : REC mode (Adapter)

Freq.(MHz)	Reading(PK)	Reading(AV)	C.F	Result(PK)	Result(AV)	Limit(PK)	Limit(AV)	Margin(PK)	Margin(AV)	Height	Angle	Polarity
MHz	dBuV	dBuV	dB	dBuV/m	dBuV/m	dBuV/m	dBuV/m	dB	dB	cm	deg	Hor/Ver
5622.50	36.9	23.9	15.39	52.31	39.24	80.0	60.0	27.69	20.76	100	351	H
5863.13	36.0	23.1	16.55	52.59	39.69	80.0	60.0	27.41	20.31	100	48	H
5969.38	36.0	22.8	17.24	53.22	40.08	80.0	60.0	26.78	19.92	100	96	H
5033.13	36.4	23.5	13.53	49.94	36.99	80.0	60.0	30.06	23.01	100	21	V
5243.13	36.6	23.7	14.01	50.57	37.66	80.0	60.0	29.43	22.34	100	33	V
5824.38	35.8	22.9	16.23	52.07	39.08	80.0	60.0	27.93	20.92	100	188	V

Radiated Emission (Above 1 GHz) / REC mode (POE)


(Above 1 GHz) / V

EUT/Model No.: QNO-6082R Temp/Humi: 23 / 31
 Test Mode : REC mode (POE) Tested by: CHOI Y H



(Above 1 GHz) / H

EUT/Model No.: QNO-6082R Temp/Humi: 23 / 31
 Test Mode : REC mode (POE) Tested by: CHOI Y H



Manufacture : HANWHA TECHWIN SECURITY VIETNAM CO.,LTD.
 Model : QNO-6082R
 TEST mode : REC mode (POE)

Test Date : 2019-04-23
 Temp.: 23 [°C]
 Humidity: 31 [%]
 Distance (m) : 3.8

Freq.(MHz)	Reading(PK)	Reading(AV)	C.F	Result(PK)	Result(AV)	Limit(PK)	Limit(AV)	Margin(PK)	Margin(AV)	Height	Angle	Polarity
MHz	dBuV	dBuV	dB	dBuV/m	dBuV/m	dBuV/m	dBuV/m	dB	dB	cm	deg	Hor/Ver
5488.13	35.8	22.7	14.98	50.79	37.63	80.0	60.0	29.21	22.37	100	312	H
5708.75	35.3	22.3	15.54	50.84	37.88	80.0	60.0	29.16	22.12	100	360	H
5990.63	35.2	22.2	17.36	52.53	39.51	80.0	60.0	27.47	20.49	100	46	II
5359.38	35.9	22.9	14.28	50.20	37.13	80.0	60.0	29.80	22.87	100	312	V
5530.00	36.3	23.2	14.75	51.02	37.90	80.0	60.0	28.98	22.10	100	278	V
5892.50	36.2	23.7	16.58	52.76	40.23	80.0	60.0	27.24	19.77	100	20	V

3.2.3 Harmonic Current (AC power input port)

Definition:

This part deals with the Limitation of harmonic currents injected into the public supply system.


We were performed the test according to LTA procedure LTA-QI-04.

Test method	:	EN 61000-3-2:2014
Test mode	:	REC mode (Adapter)
Rated power	:	3.526 W
Result	:	Not Applicable

Measurement Data:

- We did not test EN61000-3-2 (Harmonic current emissions) for the QNO-6082R because equipment whose rated power is less or equal 75W don't need to be tested.

Harmonic Current (AC power input port) / REC mode (Adapter)

25th April 2019 - 01:15:39		Page 1/1	IECSOft v2_5a
		IEC61000-3-2:2014 Fluctuating Harmonics	
Instrument Details			
Instrument Model	PPA5511		
Serial Number	162-04957		
Firmware Version	2.168		
N4L Calibration Date	18th September 2017		
Instrument Version	Standard		
Test Settings			
Class	Class A		
Mode	Measured		
Equipment Under Test			
Brand	Hanwha Techwin Co., Ltd.		
Model	QNO-6082R		
Serial	N/A		
Impedance Network ID	N/A		
Test Conditions			
	User Entered	Measured	
Rated Voltage	N/A	230.696V	
Rated Current	N/A	41.085mA	
Rated Frequency	N/A	50.000Hz	
Rated Power	N/A	3.526W	
Additional Test Information			
Measured Power Factor	0.372		
Max Current THD	325.73%		
Max THC	47.494mA		
Max Power	3.566W		
Max F.Current	16.066mA		
Average F.Current	15.380mA		
Minimum Current	100A		
Test Duration	2.5 minutes		
Additional Test Details			
Operator	N/A		
Lab Name	N/A		
Location	N/A		
Notes			
Signature			
Results	Test - N/A. Rated Power < 75W		

Test not applicable

With the exception of lighting equipment section 7 of the IEC61000-3-2:2014 standard declares that no Harmonic current limits are specified for equipment with a rated power of

3.2.4 Voltage Variation and Flicking (AC power input port)

Definition:

This section is concerned with the limitation of voltage fluctuations and flicker impressed on the public low-voltage system.



We were performed the test according to LTA procedure LTA-QI-04.

Test method	:	EN 61000-3-3:2013
Test mode	:	REC mode (Adapter)
Result	:	Complies

Measurement Data:

- Refer to the Next page

Voltage Variation and Flicking (AC power input port) / REC mode (Adapter)

25th April 2019 - 01:20:42		Page 1/2		IECSOft v2_5a	
		IEC61000-3-3:2013 Ed.3.0			
		Flickermeter			
Instrument Details					
Instrument Model	PPA5511				
Serial Number	162-04957				
Firmware Version	2.168				
N4L Calibration Date	18th September 2017				
Instrument Version	Standard				
Test Settings					
Class	Voltage				
Mode	Normal (4%)				
Minimum Current	10A				
PST	10.00 minutes				
PLT	12 PSTs				
Equipment Under Test					
Brand	Hanwha Techwin Co., Ltd.				
Model	QNO-6082R				
Serial	N/A				
Impedance Network ID	N/A				
Test Conditions					
	User Entered		Measured		
Rated Voltage	N/A		230.695V		
Rated Current	N/A		N/A		
Rated Frequency	N/A		50.000Hz		
Rated Power	N/A		N/A		
D max	0.0779% (Limit: 4.0%)				
T max	0.0000 s (Limit: 0.5 s)				
DC max	0.0078% (Limit: 3.3%)				
Additional Test Details					
Operator	N/A				
Lab Name	N/A				
Location	N/A				
Notes					
Signature					
Results	Phase1: PASS				

25th April 2019 - 01:20:42		Ph:1 Page 2/2		IECSoft v2_5a				
IEC61000-3-3:2013 Ed.3.0 Flickermeter								
Instrument Details								
Instrument Model	PPA5511							
Instrument Serial	162-04957							
Instrument Firmware	2.168							
Equipment Under Test								
Brand	Hanwha Techwin Co., Ltd.							
Model	QNO-6082R							
Serial	N/A							
Flicker Test Results								
PST no.	Status	DC (%)	Dmax (%)	Tmax (s)	PST	PST Lim	PLT	PLT Lim
1	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
2	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
3	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
4	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
5	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
6	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
7	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
8	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
9	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
10	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
11	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	N/A
12	Phase1: PASS	0.008	0.07793	0	0.082	1.00	0.082	0.65

3.3 IMMUNITY

3.3.1 Electrostatic Discharge

Definition:

The test assesses the ability of the EUT to operate as intended in the event of an electrostatic discharge.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	: 2019.04.26.
Test method	: EN 61000-4-2 :2009
Temperature / Humidity / Pressure	: 21 °C / 34 % R.H. / 101.0 kPa
Discharge Impedance	: (330 ±10%)Ω / (150 ±10%) pF
Type of Discharge (air discharge)	: ± 2kV, ± 4 kV, ± 8 kV
Type of Discharge (contact discharge)	: ± 6 kV
Number of discharges at each point	: 10 of each polarity
Discharge Repetition on Rate	: 1 / sec
Test mode	: REC mode (Adapter), REC mode (POE)
Result	: Complies

Measurement Data:

MODE : REC mode (Adapter)

1-1. Indirect Discharge

No.	Position	Kind of Discharge	Results	Remarks
1	HCP	Contact	Complies	No reaction recognized
2	VCP	Contact	Complies	No reaction recognized

1-2. Direct Discharge

No.	Position	Kind of Discharge	Result	Remarks
1	Enclosure	Contact	Complies	No reaction recognized
2	Lens	Air	Complies	No reaction recognized
3	ARM-OUT	Air	Complies	No reaction recognized
4	GND	Air	Complies	No reaction recognized
5	ARM-IN	Air	Complies	No reaction recognized
6	MIC	Air	Complies	No reaction recognized
7	LAN	Air	Complies	No reaction recognized
8	Screw	Contact	Complies	No reaction recognized
9	DC IN	Air	Complies	No reaction recognized

MODE : REC mode (POE)

2-1. Indirect Discharge

No.	Position	Kind of Discharge	Results	Remarks
1	HCP	Contact	Complies	No reaction recognized
2	VCP	Contact	Complies	No reaction recognized



2-2. Direct Discharge

No.	Position	Kind of Discharge	Result	Remarks
1	Enclosure	Contact	Complies	No reaction recognized
2	Lens	Air	Complies	No reaction recognized
3	ARM-OUT	Air	Complies	No reaction recognized
4	GND	Air	Complies	No reaction recognized
5	ARM-IN	Air	Complies	No reaction recognized
6	MIC	Air	Complies	No reaction recognized
7	LAN	Air	Complies	No reaction recognized
8	Screw	Contact	Complies	No reaction recognized

※ Results are complies in each test mode.



- ← Air discharge
- ← Contact discharge

ESD TEST POINT / REC mode (Adapter)



- ← Air discharge
- ← Contact discharge

ESD TEST POINT / REC mode (POE)



3.3.2 RF Electromagnetic Field

Definition:

The test assesses the ability of the EUT to operate as intended in the presence of a radio frequency electromagnetic field disturbance.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	:	2019.04.24.
Test method	:	EN 61000-4-3:2006/A1:2008/A2:2010
Temperature / Humidity / Pressure	:	23 °C / 33 % R.H. / 101 kPa
Frequency range	:	80 MHz to 2,700 MHz
Test level	:	10 V/m (measured unmodulated)
Amplitude Modulation	:	AM, 80 %, 1 kHz Sinusoidal PM, 1 Hz (0.5s ON : 0.5s OFF)
Step size	:	1 % of fundamental
Dwell Time	:	3 s
Test mode	:	REC mode (Adapter), REC mode (POE)
Result	:	Complies

Measurement Data:

MODE : REC mode (Adapter)

Port	Side	Result	Remarks
Horizontal	Front	Complies	No reaction recognized
	Left	Complies	No reaction recognized
	Rear	Complies	No reaction recognized
	Right	Complies	No reaction recognized
Vertical	Front	Complies	No reaction recognized
	Left	Complies	No reaction recognized
	Rear	Complies	No reaction recognized
	Right	Complies	No reaction recognized

MODE : REC mode (POE)

Port	Side	Result	Remarks
Horizontal	Front	Complies	No reaction recognized
	Left	Complies	No reaction recognized
	Rear	Complies	No reaction recognized
	Right	Complies	No reaction recognized
Vertical	Front	Complies	No reaction recognized
	Left	Complies	No reaction recognized
	Rear	Complies	No reaction recognized
	Right	Complies	No reaction recognized

※ Results are complies in each test mode.

3.3.3 Electrical fast transients

Definition:

The test assesses the ability of the EUT to operate as intended in the event of fast transients presence on one of the input/output ports.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	:	2019.04.26.
Test method	:	EN 61000-4-4:2012
Temperature / Humidity / Pressure	:	22 °C / 35 % R.H. / 101 kPa
Cable length	:	> 3 m
Test level	:	2.0 kV (AC power input port) 1.0 kV (Signal port)
Polarity	:	Negative/ positive
Repetition frequency	:	100 kHz
Test mode	:	REC mode (Adapter), REC mode (POE)
Result	:	Complies

Measurement Data:

MODE : REC mode (Adapter)

Power Line	Test level	Result	Remarks
L – N	± 2 kV	Complies	No reaction recognized

Signal Line	Test level	Result	Remarks
LAN	± 1 kV	Complies	No reaction recognized

MODE : REC mode (POE)

Signal Line	Test level	Result	Remarks
LAN	± 1 kV	Complies	No reaction recognized

※ Results are complies in each test mode.

3.3.4 Surge

Definition:

The test assesses the ability of the EUT to operate as intended in the event of surge presence on the AC main power input ports.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	:	2019.04.26.
Test method	:	EN 61000-4-5:2014/A1:2017
Temperature / Humidity / Pressure	:	22 °C / 35 % R.H. / 101 kPa
Test level	:	± 0.5 kV, ±1 kV (line to line) ± 0.5 kV, ± 1 kV, ± 2 kV (line to ground), ± 0.5 kV, ± 1 kV (signal line)
Polarity	:	Negative/ positive
Wave shape	:	1.2/ 50 µs pulse
Number of surges	:	5 (at each phase)
Test mode	:	REC mode (Adapter), REC mode (POE)
Result	:	Complies

Measurement Data:

MODE : REC mode (Adapter)

Phase	Line	level	Result	Remark
0°	Line(L) to line(N)	± 0.5, 1.0 kV	Complies	No reaction recognized
90°	Line(L) to line(N)	± 0.5, 1.0 kV	Complies	No reaction recognized
180°	Line(L) to line(N)	± 0.5, 1.0 kV	Complies	No reaction recognized
270°	Line(L) to line(N)	± 0.5, 1.0 kV	Complies	No reaction recognized

Signal Line	Test level	Result	Remarks
LAN	± 0.5, 1.0 kV	Complies	No reaction recognized

MODE : REC mode (POE)

Signal Line	Test level	Result	Remarks
LAN	± 0.5, 1.0 kV	Complies	No reaction recognized

※ Results are complies in each test mode.

3.3.5 Conducted disturbances, induced by radio-frequency fields

Definition:

The test assesses the ability of the EUT to operate as intended in the presence of a radio frequency electromagnetic disturbance on the input/output ports.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	:	2019.04.24.
Test method	:	EN 61000-4-6:2014/AC:2015
Temperature / Humidity / Pressure	:	23 °C / 37 % R.H. / 101 kPa
Frequency range	:	0.15MHz – 100 MHz
Test level	:	10 Vrms unmodulated
Amplitude Modulation	:	AM, 80 %, 1 kHz Sinusoidal PM, 1 Hz (0.5s ON : 0.5s OFF)
Step size	:	1 % of fundamental.
Test mode	:	REC mode (Adapter), REC mode (POE)
Result	:	Complies

Measurement Data:

MODE : REC mode (Adapter)

Power Port	Test level (Vrms)	Result	Remarks
Power	10	Complies	No reaction recognized

Signal Port	Test level (Vrms)	Result	Remarks
LAN	10	Complies	No reaction recognized

MODE : REC mode (POE)

Power Port	Test level (Vrms)	Result	Remarks
LAN	10	Complies	No reaction recognized

※ Results are complies in each test mode.

3.3.6 Mains supply voltage dips, short interruptions

Definition:

The test assesses the ability of the EUT to operate as intended in the event of voltage dips and interruptions present on the AC mains power input ports.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	:	2019.04.26.
Test method	:	EN 61000-4-11:2004/A1:2017
Temperature / Humidity / Pressure	:	23 °C / 34 % R.H. / 101 kPa
Ut	:	230 Vac
Test mode	:	REC mode (Adapter)
Result	:	Complies

Measurement Data:

MODE : REC mode (Adapter)

Test Level %Ut	Voltage droop and interruptions %Ut	Duration of Reduction (period)	Result	Remarks
80	20	250	Complies (A)	No reaction recognized
70	30	25	Complies (A)	No reaction recognized
40	60	10	Complies (A)	No reaction recognized
0	100	250	Complies (B)	EUT Power OFF during the test. Automatic replay without user's control. After the test, EUT was operated normally.

3.3.7 Mains supply voltage variations

Definition:

The test assesses the ability of the EUT to operate as intended in the event of voltage variations present on the AC mains power input ports.

We were performed the test according to LTA procedure LTA-QI-04.

Test date	:	2019.04.26.
Test method	:	EN 50130-4:2011/A1:2014
Temperature / Humidity / Pressure	:	23 °C / 34 % R.H. / 101 kPa
Supply Voltage maximum	:	$U_{nom} + 10 \%$
Supply Voltage minimum	:	$U_{nom} - 15 \%$
Ut	:	230 Vac
Test mode	:	REC mode (Adapter)
Result	:	Complies

Measurement Data:

U_{nom} = Nominal mains voltage. Where provision is made to adapt the equipment to suit a number of nominal supply voltages (e.g. by transformer tap changing), the above conditioning severity shall be applied for each nominal voltage, with the equipment suitably adapted. For equipment which is claimed to be suitable for a range of nominal mains voltages (e.g. 220/240 V) without adaptation, $U_{max} = (\text{Maximum } U_{nom}) + 10 \%$, and $U_{min} = (\text{Minimum } U_{nom}) - 15 \%$. In any case the range of U_{nom} must include the European nominal mains voltage of 230 V.

2 Mains supply voltage variations

MODE : REC mode (Adapter) / 230 V, 50 Hz

Test LevelCondition		Test Level (V)	Result	Remarks
Unom	+10%	253	Complies	No reaction recognized
Unom	-15%	195.5	Complies	No reaction recognized

APPENDIX A

TEST EQUIPMENT AND ANCILLARIES USED FOR TESTS

To facilitate inclusion on each page of the test equipment used for related tests, each item of test equipment are identified by the Test Laboratory.

Conducted emissions

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	EMI TEST Receiver	ESR	Rohde & Schwarz	101499	2019.07.11	1 year
<input checked="" type="checkbox"/>	Pulse Limiter	ESH3-Z2	Rohde & Schwarz	100710	2020.03.16	1 year
<input type="checkbox"/>	LISN	ESH3-Z6	Rohde & Schwarz	100378	2019.09.07	1 year
<input type="checkbox"/>	LISN	ESH3-Z6	Rohde & Schwarz	101468	2019.09.07	1 year
<input checked="" type="checkbox"/>	LISN(main)	ENV216	Rohde & Schwarz	100408	2019.10.10	1 year
<input checked="" type="checkbox"/>	LISN(sub)	LT32C/10	AFJ	32031518210	2019.09.06	1 year
<input checked="" type="checkbox"/>	TEST PROGRAM	e3_ce 20181212a (V9)	AUDIX	-	-	-
<input checked="" type="checkbox"/>	ISN	ISN T800	TESEQ	27109	2019.09.12	1 year
<input type="checkbox"/>	ISN	ENY81-CA6	Rohde & Schwarz	101565	2019.09.12	1 year
<input type="checkbox"/>	CURRENT PROBE	EZ-17	Rohde & Schwarz	100508	2019.09.06	1 year

Radiated Emission – Below 1 GHz

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	EMI TEST Receiver	ESU	Rohde & Schwarz	100092	2019.09.06	1 year
<input checked="" type="checkbox"/>	Amplifier (25 dB)	8447D	HP	2944A07684	2019.09.06	1 year
<input checked="" type="checkbox"/>	BILOG Antenna	VULB9168	SCHWARZBECK	775	2020.03.16 (KOLAS)	2 year
<input checked="" type="checkbox"/>	TEST PROGRAM	e3 20181212a (V9)	AUDIX	-	-	-

Radiated Emission – Above 1 GHz

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	EMI TEST Receiver	ESU	Rohde & Schwarz	100092	2019.09.06	1 year
<input checked="" type="checkbox"/>	Amplifier	8449B	HP	3008A00671	2019.09.06	1 year
<input checked="" type="checkbox"/>	HORN ANTENNA	3115	ETS	114105	2019.11.03 (KOLAS)	2 year
<input checked="" type="checkbox"/>	TEST PROGRAM	e3 20181212a (V9)	AUDIX	-	-	-

Harmonic Current / Voltage Variation and Flicking

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Precision Power Analyzer	PPA5511	Newtons4th Ltd	162-04957	2019.09.10	1 year
<input checked="" type="checkbox"/>	Reference Impedance Network	ES4152	NF Corp.	9074424	2019.09.07	1 year

Electrostatic Discharge

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	ESD Simulator	ESS-2000	NOISEKEN	8000C03241	2019.09.11	1 year
<input checked="" type="checkbox"/>	ESD GUN	TC-815R	NOISEKEN	ESS0564361	2019.09.11	1 year

RF Electromagnetic Field

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Signal Generator	E4432B	Agilent	MY41310632	2020.03.16	1 year
<input checked="" type="checkbox"/>	Power Meter	E4419B	Agilent	GB38410133	2020.03.16	1 year
<input checked="" type="checkbox"/>	Power Sensor	E9300A	Agilent	MY41497992	2020.03.16	1 year
<input checked="" type="checkbox"/>	Power Sensor	E9300A	Agilent	MY41497618	2020.03.16	1 year
<input checked="" type="checkbox"/>	RF POWER AMPLIFIER	ITA0300KL-300	INFINITECH	0300KL 1507 001	-	-
<input checked="" type="checkbox"/>	RF POWER AMPLIFIER	ITA2000KL-120	INFINITECH	200KL 1507 001	-	-
<input checked="" type="checkbox"/>	RF POWER AMPLIFIER	ITA4500KL-70	INFINITECH	4500KL 1507 001	-	-
<input checked="" type="checkbox"/>	RF POWER AMPLIFIER	ITA0750KL-300	INFINITECH	0750KL 1507 001	-	-
<input checked="" type="checkbox"/>	Log.-Per.Antenna (80 MHz ~ 3 GHz)	K9128	RAPA	NONE	-	-

Electrical fast transients

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Compact Generator	Compact NX	EMTEST	P1725200196	2019.09.06	1 year
<input checked="" type="checkbox"/>	AC Power Source	Variac NX	EMTEST	P1745207276	2019.09.06	1 year
<input checked="" type="checkbox"/>	Capacitive Coupling Clamp	CCI	EMTEST	P1744207071	2019.09.06	1 year

Surge

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Compact Generator	Compact NX	EMTEST	P1725200196	2019.09.06	1 year
<input checked="" type="checkbox"/>	AC Power Source	Variac NX	EMTEST	P1745207276	2019.09.06	1 year
<input checked="" type="checkbox"/>	CDN	CNV 508T5	EMTEST	P1742204978	2019.09.07	1 year
<input type="checkbox"/>	CDN	CNV 508N1	EMTEST	P1742204940	2019.09.07	1 year

Conducted disturbances, induced by radio-frequency fields

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Signal generator	SML03	R&S	103026/0013	2020.03.16	1 year
<input checked="" type="checkbox"/>	POWER METER	NRVD	R&S	101689	2020.03.16	1 year
<input checked="" type="checkbox"/>	POWER Sensor	URV5-Z2	R&S	100755	2020.03.16	1 year
<input checked="" type="checkbox"/>	POWER Sensor	URV5-Z2	R&S	100756	2020.03.16	1 year
<input checked="" type="checkbox"/>	RF Power Amplifier	FLL75A	FRANKONIA	1033	-	-
<input checked="" type="checkbox"/>	EM INJECTION CLAMP	TSIC-23	F.C.C	529	2020.03.25	1 year
<input type="checkbox"/>	CDN (M1)	TSCDN-M1-16A	F.C.C	07004	2020.03.16	1 year
<input checked="" type="checkbox"/>	CDN (M2) (main)	TSCDN-M2-16A	F.C.C	07008	2019.09.06	1 year
<input type="checkbox"/>	CDN (M2)	TSCDN-M2-16A	F.C.C	07009	2020.03.16	1 year
<input checked="" type="checkbox"/>	CDN (M3) (sub)	TSCDN-M3-16A	F.C.C	07016	2020.03.16	1 year
<input checked="" type="checkbox"/>	CDN (M3) (main)	TSCDN-M3-16A	F.C.C	07017	2019.09.06	1 year

Mains supply voltage dips, short interruptions

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Compact Generator	Compact NX	EMTEST	P1725200196	2019.09.06	1 year
<input checked="" type="checkbox"/>	AC Power Source	Variac NX	EMTEST	P1745207276	2019.09.06	1 year

Mains supply voltage variations

	Item	Model Name	Manufacturer	Serial No.	Next Cal.	Interval
<input checked="" type="checkbox"/>	Compact Generator	Compact NX	EMTEST	P1725200196	2019.09.06	1 year
<input checked="" type="checkbox"/>	AC Power Source	Variac NX	EMTEST	P1745207276	2019.09.06	1 year

APPENDIX B
PERFORMANCE CRITERIA

Performance criteria

The variety and the diversity of the apparatus within the scope of this document makes it difficult to define precise criteria for the evaluation of the immunity test results.

If as a result of the application of the tests defined in this standard, the apparatus becomes dangerous or unsafe then the apparatus shall be deemed to have failed the test.

A functional description and a definition of performance by the manufacture and noted in the test report, based on the following criteria:

Electrostatic discharge

There shall be no damage, malfunction or change of status due to the conditioning.

Flickering of an indicator during the application of discharge is permissible, providing that there is no residual change in the EUT or any change in outputs, which could be interpreted by associated equipment as a change. The EUT shall meet the acceptance criteria for the functional test (see Clause 6), after the conditioning.

Radiated electromagnetic fields

There shall be no damage, malfunction or change of status due to the conditioning.

Flickering of an indicator during the conditioning is permissible, providing that there is no residual change in the EUT or any change in outputs, which could be interpreted by associated equipment as a change, and no such flickering of indicators occurs at a field strength of 3 V/m.

For components of CCTV systems, where the status is monitored by observing the TV picture, then deterioration of the picture is allowed at 10 V/m, providing.

(a) there is no permanent damage or change to the EUT

(e.g. no corruption of memory or changes to programmable setting etc.)

(b) at 3 V/m, any deterioration of the picture is so minor that the system could still be used; and

(c) there is no observable deterioration of the picture at 1 V/m.

The EUT shall meet the acceptance criteria for the functional test(see Clause 6), after the conditioning.

Fast transient burst / slow high energy voltage surge

There shall be no damage, malfunction or change of status due to the conditioning.

Flickering of an indicator during the application of the bursts is permissible, providing that there is no residual change in the EUT or any change in outputs, which could be interpreted by associated equipment as a change. The EUT shall meet the acceptance criteria for the functional test

(see Clause 6), after the conditioning.

Slow high energy voltage surge

There shall be no damage, malfunction or change of status due to the conditioning.

Flickering of an indicator during the application of the surges is permissible, providing that there is no residual change in the EUT or any change in outputs, which could be interpreted by associated equipment as a change. The EUT shall meet the acceptance criteria for the functional test

(see Clause 6), after the conditioning.

Conducted RF immunity

There shall be no damage, malfunction or change of status due to the conditioning.

Flickering of an indicator during the conditioning is permissible, providing that there is no residual change in the EUT or any change in outputs, which could be interpreted by associated equipment as a change, and no such flickering of indicators occurs at $U_0 = 130 \text{ dB}_\mu\text{V}$.

For components of CCTV systems, where the status is monitored by observing the TV picture, then deterioration of the picture is allowed at $U_0 = 140 \text{ dB}_\mu\text{V}$, providing

- (a) there is no permanent damage or change to the EUT
(e.g. no corruption of memory or changes to programmable settings, etc.)
- (b) at $U_0 = 130 \text{ dB}_\mu\text{V}$, any deterioration of the picture is so minor that the system could still be used, and
- (c) there is no observable deterioration of the picture at $U_0 = 120 \text{ dB}_\mu\text{V}$.

The EUT shall meet the acceptance criteria for the functional test(see Clause 6), after the conditioning.

Voltage dip/interruption

There shall be no damage, malfunction or change of status due to the conditioning.

Flickering of an indicator during the conditioning is permissible, providing that there is no residual change in the EUT or any change in outputs, which could be interpreted by associated equipment as a change. The EUT shall meet the acceptance criteria for the functional test(see Clause 6), after the conditioning.

It is permitted to use ancillary equipment (e.g. A UPS) to meet the requirements of this clause. This shall be detailed in the test report and the manufacturer's installation manual.

Signaling a mains fault during the 100 % voltage reduction test is permitted.

Mains supply voltage variations

There shall be no damage, malfunction or change of status due to the different supply voltage conditions. The EUT shall meet the acceptance criteria for the functional test(see Clause 6), during the conditioning.

APPENDIX C
PHOTOGRAPHS

Conducted emission (Maximum emission configuration) / REC mode (Adapter)





Conducted emission (Maximum emission configuration) / TEL_REC mode (Adapter)





Conducted emission (Maximum emission configuration) / TEL_REC mode (POE)





Radiated emission (Maximum emission configuration)-Below 1 GHz / REC mode (Adapter)





Radiated emission (Maximum emission configuration)-Below 1 GHz / REC mode (POE)



Radiated emission (Maximum emission configuration) – Above 1GHz / REC mode (Adapter)



Radiated emission (Maximum emission configuration) – Above 1GHz / REC mode (POE)



Harmonic Current / Voltage Variation and Flicking REC mode (Adapter)




Electrostatic discharge / REC mode (Adapter)



Electrostatic discharge / REC mode (POE)





RF Electromagnetic Field / REC mode (Adapter)




RF Electromagnetic Field / REC mode (POE)




Electrical fast transients / REC mode (Adapter)



Electrical fast transients / REC mode (POE)





Surge / REC mode (Adapter)




Surge / REC mode (POE)




Conducted Disturbances, Induced by Radio-Frequency Fields / REC mode (Adapter)



Conducted Disturbances, Induced by Radio-Frequency Fields / REC mode (POE)



Main supply voltage (dips, variations) short interruptions / REC mode (Adapter)



EUT



EUT

