

ThinkPad T14s Gen 5

Harnessing the power of the Intel® Core™ Ultra 7 Processor, this new-generation ThinkPad is engineered for unparalleled multitasking capabilities. Whether you're working on graphic-intensive applications or a massive cloud-based database, the integrated Intel Arc Graphics effortlessly handles every workload with ease. With up to 64GB of memory, professionals dealing with substantial data volumes are sure to experience smooth transitions between tasks without any lags. Weighing just 1.24 kg (2.73 lbs) and featuring a battery that lasts up to 15.2 hours, this design marvel is the perfect fit for today's hybrid workforce.



Redefining possibilities with powerful performance and groundbreaking on-device AI

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

The device includes a range of smart features dedicated to enhancing your collaborative endeavors. The Dolby Audio stereo speakers provide a more engaging and richer auditory experience, while the dual-array microphones capture clearer audio by reducing background noise during real-time web conferences.

Experience unmatched download speeds and enhanced performance with the onboard Intel® Wi-Fi 7 feature. Additionally, a range of I/O ports, including USB-C 3.2 Gen 1, Thunderbolt 4, and HDMI 2.1, facilitate rapid connectivity to external monitors and peripherals.

With a starting weight of just 1.24 kg (2.73 lbs), this compact and versatile ThinkPad is the perfect companion for any bag or office space.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 15.6" Laptop Casual Backpack

- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

Lenovo Essential Wireless Keyboard & Mouse Combo

- Simple design that is comfortable for all day use and tough enough to handle spills
- Convenient and easy to use wireless connection
- Quality typing experience with quiet key strokes and a full-size number pad



PN: 4X30M39458 - US English

ThinkPad T14s Gen 5

Performance

Processor

Intel U or H Series Core Ultra 5/7 Processor (Series 1)

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Linux
Ubuntu Linux

Graphics

Intel Graphics (integrated)
Intel Arc Graphics (integrated)

Memory

16GB LPDDR5x-7467, soldered
32GB LPDDR5x-7467, soldered
64GB LPDDR5x-7467, soldered

Storage¹

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, 360° far-field, Dolby Voice*

Camera^{*}

5.0MP, with privacy shutter
5.0MP + IR discrete, with privacy shutter

Battery²

58Wh (up to 15.2 hr) battery, Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter^{*}

45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display³

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 3M DBEF5
- 400nits, 45% NTSC, touch, Eyesafe, 3M DBEF5
- 400nits, 100% sRGB, low power
- 500nits, 100% sRGB, touch, ThinkPad Privacy Guard

14" 2.8K (2880x1800) OLED AGARAS 16:10
- 400nits, 100% DCI-P3, 120Hz, DisplayHDR True Black 500, Dolby Vision, Eyesafe

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, Copilot Key, backlight

Touchpad

TrackPoint and glass-like Mylar surface touchpad
61 x 115 mm (2.4 x 4.53 inches)

Dimensions⁴

Starting at 313.6 x 219.4 x 16.6 mm (12.35 x 8.64 x 0.65 inches)

⁴The system dimensions may vary depending on configurations.

Weight⁵

Grey models: starting at 1.45 kg (3.19 lbs)
Black models: starting at 1.24 kg (2.73 lbs)

⁵The system weight is approximate and may vary depending on configurations

Color

Black
Grey

Case material

Carbon fiber hybrid or aluminium (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth^{* 6}

802.11ax (Wi-Fi 6E) or 802.11be (Wi-Fi 7), Bluetooth 5.3
Up to Intel Wi-Fi 7 BE200, 802.11be, Bluetooth 5.3

⁶Wi-Fi 6E and Wi-Fi 7 are only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10. Bluetooth 5.3 operation requires Windows 11.

WWAN^{*}

4G LTE CAT6 with embedded eSIM
5G Sub-6 GHz with embedded eSIM

NFC

Near Field Communication*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter*
IR camera for Windows Hello (facial recognition)*
Privacy Guard with Privacy Alert*
Ultrasonic Human Presence Detection*

Manageability

System Management^{* 7}

Intel vPro Enterprise*

⁷Intel vPro offers a superset of DASH's defined capabilities

Certifications

Green Certifications^{8 9 10}

ENERGY STAR 8.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 9.0
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are dependent on system OS.

¹⁰EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Intel Evo Platform*
Eyesafe Certified 2.0*
MIL-STD-810H