

# CT37 Handheld Computer

The CT37 mobile computer features a consumer phone experience with enterprise-class durability, manageability, support and lifecycle.

## Overview



Feedback

**The CT37 delivers a lightweight, user-friendly design that is built on the Mobility Edge™ platform, ensuring continuous productivity for front-line workers in retail, logistics, and healthcare.**

**The Mobility Edge™ platform is a durable, stable, secure foundation for which businesses build solutions around. The CT37 features a future compatible architecture that protects your investment, with Android support out to A18.**

**The housings on the CT37 are disinfectant ready and designed to withstand multiple cleanings from a variety of harsh cleaners. The housings stand up to multiple cleanings an hour by 34 different chemicals.**

**The CT37 is equipped with the latest 5G and Wi-Fi 6E technology, keeping you connected indoors and outdoors. 5G keeps mobile workers connected with the highest bandwidth and lowest latency available, reducing downtown and increasing productivity. The CT37 supports private 5G, CBRS, and Wi-Fi 6E, ensuring front-line workers stay connected.**

**Combined with powerful Honeywell software such as Operational Intelligence, Smart Talk unified communications and Smart Pay contactless payment, the CT37 is an ideal platform for users in retail, healthcare and transportation and logistics to build effective solutions.**

**With its hot-swappable battery feature, the CT37 eliminates interruptions for battery replacement, making it possible for extended operational use without downtime.**

**The CT37 also includes a secure element (SE) for preventing digital threats, adding a layer of physical security to the device. It ensures that sensitive information processed by applications on the SE is insulated and secured against unauthorized access.**

## Specifications

### FEATURES

#### Application

- Retail, Transportation & Logistics, Field Operations and Healthcare

#### For Use With

- Android

#### **Housing Grade**

- Disinfectant Ready Housing

#### **Features**

- Compatible with Universal Dock

#### **Camera**

- 13-megapixel color rear camera
- 8-megapixel color front camera

## **DIMENSIONS**

---

#### **Overall Dimensions**

- 167.4 mm x 76.0mm x 12.6mm (6.6 in x 3.0 in x 0.5 in)

## **SCANNING SPECIFICATIONS**

---

#### **Decode Capability**

- Honeywell FlexRange™ XLR S0803
- Standard Range Engine S0703 (1D/2D barcode symbologies)

## **NETWORK**

---

Feedback

#### **WWAN Specifications**

- 4G-LTE DL CAT-18: ~800 Mbps
- 4G-LTE UL CAT-15: ~200 Mbps
- 5G FR1: Bands 1, 2, 3, 5, 7, 8, 12, 13, 14, 20, 25, 26, 28, 29, 30, 38, 40, 41, 48, 66, 71, 77, 78, 79
- 5G NSA-DL: ~2500 Mbps, UL: ~1050 Mbps
- 5G SA-DL: ~2300 Mbps, UL: ~1050 Mbps
- AT&T FirstNet Compliant
- Global bands support, device certified with GCF-PTCRB, ATT, TMO, VZW
- LTE: Bands 1, 2, 3, 4, 5, 7, 8, 12, 13, 14, 17, 18, 19, 20, 25, 26, 28, 29, 30, 38, 39, 40, 41, 42, 43, 48, 66, 71

#### **WLAN Specifications**

- Data rates: 2.4GHz: 802.11b/g/ax – 20MHz up to 286.8Mbps; 5GHz: 802.11n/ac/ax -20MHz, 40MHz, 80MHz, 160MHz up to 2882Mbps; 802.11ax- 20MHz, 40MHz, 80MHz, 160MHz up to 2882Mbps.
- IEEE 802.11 a/b/g/n/ac/d/h/i/r/k/v/w/mc/ax, 2x2 MU-MIMO; Triband (2.4GHz, 5GHz, 6GHz); Wi-Fi 6E (801.11ax); Dual Band Simultaneous (DBS); IPv4, IPv6
- Supported EAP: TLS, PEAP, TTLS, PWD, LEAP, CCX compatible.
- WLAN Security: Enhanced open (OWE), WEP, WPA/WPA2/WPA3 (Personal and Enterprise)
- Wi-Fi certified; Wi-Fi 6E certified.

#### **GPS Specifications**

- GPS, GLONASS, Galileo, Beidou, QZSS, NavIC, Dual band GNSS-Concurrent L1/G1/E1/B1 with L5/E5a/BDSB2a, a-GPS, Supports XTRA

#### **Bluetooth Specifications**

- V5.3 Bluetooth and BLE; 2nd BLE

#### **RFID Specifications**

- Integrated NFC reader, compliant with ISO/IEC 1443A, ISO/IEC 1443 B, ISO/IEC 15693 (ICode), MIFARE 1K/4K, MIFARE DESFire, Sony FeliCa, ISO/IEC 18092 (Type F), Contactless payment support, ECP 1.0 and ECP 2.0.

## Computer Wireless Communication

- 5G, WiFi 6E, BT5.3, NFC

## SOFTWARE & FIRMWARE

### Operating System

- Each Android version guaranteed from Android 14 to 18, subject to technical feasibility confirmed by Qualcomm

## MEMORY & DATA

### Memory

- 8GB DDR5 RAM, 128GB UFS 3.1 Flash

## HARDWARE

### Scan Engine Range

- Standard Range and FlexRange

### Display Resolution

- Full High-Definition (2280 x 1080)

### Scan Engine Type

- Laser aimer

### Scan Engine Model

- Honeywell S0703 Slim Imager ; Honeywell FlexRange™ XLR S0803

Feedback

### Processor

- Qualcomm QCS4490 or QCM4490 octa-core, up to 2.4GHz

### Display Size

- Gorilla Glass™ Victus™, 6-inch

## ELECTRICAL

### Battery Capacity

- 3846mAh and 5550mAh

### Battery Types

- Hot-swappable
- Replaceable

### Battery Type

- Li-ion

## ENVIRONMENTAL

### Storage Temperature Range

- -30° to 70°C (-22°F to 158°F)

### Operating Temperature

- -10° to 50°C (14°F to 122°F)

#### **Operating Humidity**

- 5% to 95% (non-condensing)

## **STANDARDS & APPROVALS**

---

#### **Drop Specifications**

- Multiple 1.2m (4ft) drops to concrete at operating temperature per MIL-STD 810H
- Multiple 1.5m (5ft) drops to concrete at operating temperature with boot per MIL-STD 810H
- Multiple 1.5m (5ft) drops to concrete at room temperature per MIL-STD 810H
- Multiple 1.8m (6ft) drops to concrete at room temperature with boot per MIL-STD 810H

#### **Protection Ratings**

- IP68/IP65

#### **Tumble Specifications**

- 550, 0.5m (1.6 ft) tumbles
- 550, 1.0m (3.3 ft) tumbles with protective boot

Feedback

## **SERVICE TERMS**

---

#### **Warranty Duration**

- 1 year

## **OTHERS**

---

#### **Operating System Type**

- Android

#### **Camera Position**

- Front and Rear

#### **Platform**

- Mobility Edge™

---

#### **Honeywell**

Industrial Automation  
855 S Mint St  
Charlotte, NC 28202  
800-582-4263

#### **CT37 Handheld Computer**

© 2024 Honeywell International Inc.  
All rights reserved.

This document was generated on 2024-08-18 2:11:16 PM (YYYY-MM-DD, HH:mm:ss). Subject to change without notice.