


OVERVIEW



1. Power button	9. DisplayPort 1.4a
2. Optical drive *	10. HDMI 2.1 TMDS
3. Card reader *	11. 2x PS/2 ports (keyboard / mouse) *
4. Microphone (3.5mm)	12. 4x USB-A (Hi-Speed USB)
5. Headphone / microphone combo jack (3.5mm)	13. Ethernet (RJ-45)
6. USB-C (USB 5Gbps), data transfer only	14. Serial *
7. 2x USB-A (USB 5Gbps)	15. Optional ports on expansion cards *
8. 2x USB-A (USB 5Gbps)	16. Power connector

Notes:

- Items with * are only available on selected models
- More ports are available through the optional expansion cards (not shown on the sample product above)

PERFORMANCE

Processor

Processor Family

13th / 14th Generation Intel® Core™ i3 / i5 / i7 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics
Core i3-13100	4 (4 P-core + 0 E-core)	8	P-core 3.4GHz	P-core 4.5GHz	12MB	Intel® UHD Graphics 730
Core i5-13400	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.6GHz / E-core 3.3GHz	20MB	Intel® UHD Graphics 730
Core i5-13500	14 (6 P-core + 8 E-core)	20	P-core 2.5GHz / E-core 1.8GHz	P-core 4.8GHz / E-core 3.5GHz	24MB	Intel® UHD Graphics 770
Core i7-13700	16 (8 P-core + 8 E-core)	24	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.2GHz / P-core 5.1GHz / E-core 4.1GHz	30MB	Intel® UHD Graphics 770
Core i3-14100	4 (4 P-core + 0 E-core)	8	P-core 3.5GHz	P-core 4.7GHz	12MB	Intel® UHD Graphics 730
Core i5-14400	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.7GHz / E-core 3.5GHz	20MB	Intel® UHD Graphics 730
Core i5-14400F	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.7GHz / E-core 3.5GHz	20MB	-
Core i5-14500	14 (6 P-core + 8 E-core)	20	P-core 2.6GHz / E-core 1.9GHz	P-core 5.0GHz / E-core 3.7GHz	24MB	Intel® UHD Graphics 770
Core i5-14600	14 (6 P-core + 8 E-core)	20	P-core 2.7GHz / E-core 2.0GHz	P-core 5.2GHz / E-core 3.9GHz	24MB	Intel® UHD Graphics 770
Core i7-14700	20 (8 P-core + 12 E-core)	28	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.4GHz / P-core 5.3GHz / E-core 4.2GHz	33MB	Intel® UHD Graphics 770
Core i7-14700F	20 (8 P-core + 12 E-core)	28	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.4GHz / P-core 5.3GHz / E-core 4.2GHz	33MB	-
Intel® 300	2	4	3.9 GHz	-	6MB	Intel® UHD Graphics 710

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Windows® 11 IoT Enterprise LTSC 2024
- Windows® 11 DG Windows® 10 Pro 64
- Ubuntu Linux
- No preload operating system

Graphics

Graphics***[1]

Graphics	Type	Memory	Max Resolution	Connector	Key Features
Intel® UHD graphics 710	Integrated	Shared	4096x2304@60Hz(DP), 4096x2160@60Hz(HDMI®)	1x DP 1.4a (HBR2, DSC), 1x HDMI® 2.1 TMDS	DirectX® 12
Intel® UHD graphics 730	Integrated	Shared	4096x2304@60Hz(DP), 4096x2160@60Hz(HDMI®)	1x DP 1.4a (HBR2, DSC), 1x HDMI® 2.1 TMDS	DirectX® 12
Intel® UHD graphics 770	Integrated	Shared	4096x2304@60Hz(DP), 4096x2160@60Hz(HDMI®)	1x DP 1.4a (HBR2, DSC), 1x HDMI® 2.1	DirectX® 12

				TMDs	
NVIDIA® GeForce RTX™ 3050	Discrete	6GB GDDR6	7680x4320@60Hz(HDMI®), 7680x4320@120Hz(DP), 2560x1660@60Hz(DVI)	1x HDMI® 2.1 TMDs, 1x DisplayPort™ 1.4a, 1x DVI-D	DirectX® 12, OpenGL 4.6
AMD Radeon™ RX 6600 LE	Discrete	8G GDDR6	7680x4320@60Hz(HDMI®), 7680x4320@60Hz(DP)	3x DP 1.4a, 1x HDMI® 2.1 FRL	DirectX® 12, OpenGL 4.6, OpenCL 2.2
Intel® Arc™ A310 LP Graphics	Discrete	4GB GDDR6	5120x2880@60Hz(DP)	2x DisplayPort™ 1.4a	DirectX® 12, OpenGL 4.6

Notes:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

Monitor Support

Monitor Support

Supports up to 2 independent displays via onboard ports (1x DP and 1x HDMI®), more displays support via discrete graphics

Chipset

Chipset

Intel® Q670 chipset

Memory

Max Memory^[1]

Up to 64GB DDR5

Memory Slots

Two DDR5 UDIMM slots, dual-channel capable

Memory Type

- DDR5-4800
- DDR5-5200
- DDR5-5600

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Storage Support^[1]

Up to three drives, 1x 3.5" HDD + 1x 2.5" HDD + 1x M.2 SSD

- 3.5" HDD up to 2TB
- 2.5" HDD bay is only for customer self upgrade
- M.2 SSD up to 2TB each^[2]

Storage Type^{***}

Disk Type	Interface	RPM	Security
3.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	-	Opal 2.0

RAID

No support

Notes:

[1] The max capacity of each disk type is based on the test results with current Lenovo® storage offerings.

[2] 2.5" HDD bay is optional part, only for customer self upgrade purpose and the hard drive is sold separately. Two onboard SATA ports support up to two drives of 2.5" HDD, 3.5" HDD and ODD.

Removable Storage

Optical**

- DVD-ROM, SATA connector, slim (9.0mm)
- DVD burner (DVD±RW), SATA 1.5Gb/s, slim (9.0mm)
- None

Card Reader

- 3-in-1 card reader (SD, SDHC, SDXC)
- No card reader

Multi-Media**Audio Chip**

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

Single speaker, 2W x1

Power Supply**Power Supply****

Power	Type	Efficiency	Key Features
180W	Fixed	85%	100-240V, 50-60Hz
260W	Fixed	90%	100-240V, 50-60Hz
310W	Fixed	92%	100-240V, 50-60Hz
380W	Fixed	92%	100-240V, 50-60Hz

DESIGN**Input Device****Keyboard****

- EOS Wireless Keyboard, black
- Lenovo® Calliope Keyboard (USB connector), black
- Lenovo® Traditional Keyboard (USB connector), black
- No keyboard

Mouse**

- Lenovo® Calliope Mouse (USB connector), black
- EOS Wireless Mouse, Black
- No mouse

Mechanical**Form Factor**

Tower (13.6L)

Dimensions (WxDxH)^[1]

145 x 296 x 346 mm (5.7 x 11.7 x 13.6 inches)

Packaging Dimensions (WxDxH)

245 x 395 x 530 mm (9.65 x 15.55 x 20.87 inches)

Weight^[2]

Around 5.9 kg (13.0 lbs)

Packaging Weight

8.3 kg (18.29 lbs)

Case Color

Black

Bays^[3]

- 1x 2.5" disk bay (optional)
- 1x 3.5" disk bay
- 1x slim ODD bay

Expansion Slots

- One PCIe® 3.0 x16, full-height, length ≤ 209mm, height ≤ 117.5mm
- One PCIe® 3.0 x1, full-height, (length ≤ 185mm, height ≤ 100mm) or (length ≤ 118mm, height ≤ 110mm)
- Two M.2 slots (one for WLAN, one for SSD)

EOU

Toolless cover, memory, disk, optical, extension card assembly / removal

Others

- (Optional) Dust filter
- Supports Smart Power On

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[3] 2.5" HDD bay is optional part, only for customer self upgrade purpose and the hard drive is sold separately. Two onboard SATA ports support up to two drives of 2.5" HDD, 3.5" HDD and ODD.

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, Intel® Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

Optional Ethernet

- 2.5 Gigabit Ethernet, Realtek® RTL8125BGS, 1x RJ-45, PCIe® x1
- No optional Ethernet

WLAN + Bluetooth®**

- Realtek® Wi-Fi® 6 RTL8852BE, 802.11ax Dual Band 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card
- Intel® Wi-Fi® 6 AX201, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 Card
- Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, Intel® vPro® technology support, M.2 Card
- No WLAN and Bluetooth®

Ports^[1]

Front Ports

- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with 15W charging
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Optional Front Ports

1x card reader

Rear Ports^[2]

- 4x USB-A (Hi-Speed USB / USB 2.0)
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2, DSC)
- 1x Ethernet (RJ-45)

Optional Rear Ports***

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), via 2-port USB expansion card, PCIe® x1
- 1x parallel
- 1x serial
- 1x 2nd serial
- 4x serial (via 4-port serial expansion card, PCIe® x1)
- 2x PS/2

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be

slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

[2] For video ports on discrete graphics, please see graphics section.

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

- (Optional) E-lock
- (Optional) Smart Cable Clip
- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

Chassis Intrusion Switch

- Chassis intrusion switch
- No chassis intrusion switch

Fingerprint Reader

No fingerprint reader

BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Boot sequence control
- Boot without keyboard and mouse
- Certificate based BIOS authentication
- Individual USB port disablement
- Self-healing BIOS
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)
- More BIOS security features, please visit [BIOS Simulator](#)

MANAGEABILITY

System Management

System Management^[1]

- Intel® vPro® Enterprise
- Non-vPro®

Notes:

[1] Intel® vPro® offers a superset of DASH's defined capabilities.

SERVICE

Warranty^[1]

Base Warranty**

- 1-year courier or carry-in service
- 1-year limited onsite service
- 3-year limited onsite service
- No base warranty

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

ACCESSORIES

Bundled Accessories

Bundled Accessories***

- DP to DVI dongle
- DP to HDMI® dongle
- HDMI® to HDMI® cable (1.5m)
- HDMI® to VGA dongle
- Smart Cable (USB-A to USB-C®)
- None

OPERATING REQUIREMENTS

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Relative Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- (Optional) ENERGY STAR® 8.0
- (Optional) EPEAT™ Silver Registered
- (Optional) EPEAT™ Gold Registered
- ErP Lot 3
- GREENGUARD®
- RoHS compliant
- TCO Certified 9.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Other Certifications

(Optional) TÜV Rheinland® Ultra Low Noise

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected

models.

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

