

Product data sheet

Specifications



APC Replacement Battery Cartridge 33 with 2 Year Warranty

RBC33

Overview

Lead time Usually in Stock

Main

Product or Component Type Replacement battery cartridge

Battery Type Lead-Acid battery

Provided Equipment
All required connectors
Battery recycling guide
Reusable packaging
Installation guide

Batteries & Runtime

Battery blocks per string 2

Battery Slots Empty 0

Included Battery Modules 0

Device mounting Enclosed battery cabinet

Battery Voltage 24 V

RBC Quantity 1

Physical

Color Charcoal

Height 7.8 in (19.7 cm)

Width 5.9 in (14.9 cm)

Depth 2.5 in (6.4 cm)

Net Weight 11.75 lb(US) (5.33 kg)

Mounting Mode Not rack-mountable

Output

Battery Capacity 9.0 Ah

Environmental

Ambient Air Temperature for Operation 32.0000000000...104.0000000000 °F (0...40 °C)

Operating altitude 0...10000 ft

Relative Humidity 0...95 %

Ambient Air Temperature for Storage 32.0000000000...104.0000000000 °F (0...40 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Storage altitude	0...10000 ft (0.0000000000...3048.0000000000 m)
-------------------------	---

Storage Relative Humidity	0...95 %
----------------------------------	----------

Ordering and shipping details

GTIN	731304219095
-------------	--------------

Country of origin	VN
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	12.008 in (30.5 cm)
-------------------------	---------------------

Package 1 Width	4.02 in (10.2 cm)
------------------------	-------------------

Package 1 Length	9.02 in (22.9 cm)
-------------------------	-------------------

Package 1 Weight	13.03 lb(US) (5.91 kg)
-------------------------	------------------------

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov