



## **Poly TC10**

This document covers Poly TC10 (models/RMNs P030 and P030NR). Model/RMN P030NR is the non-radio version of Poly TC10.

## **Service Agreements**

Please contact your Poly Authorized Reseller for information about service agreements applicable to your product.

## **Safety, Compliance, and Disposal Information**

- This equipment is intended for indoor use only.
- This equipment is not intended to be directly connected to outdoor cables.
- Do not spray liquids directly onto the system when cleaning. Always apply the liquid first to a static-free cloth.
- Do not immerse the system in any liquids or place any liquids on it.
- Do not disassemble this system. To reduce the risk of shock and to maintain the warranty on the system, a qualified technician must perform service or repair work.
- There are no user serviceable parts inside this product.
- This equipment is not intended to be operated by children.
- Users must not service any parts in compartments that require a tool to access.
- This equipment should be used only on even surfaces.
- Keep ventilation openings free from any obstructions.
- The ambient operating temperature rating of this equipment is 0-40°C and should not be exceeded.
- In order to remove all power from this unit, disconnect all power cables, including any USB or Power over Ethernet (PoE) cables.

### ***Operating Ambient Temperature***

- Operating temperature: +32 to 104°F (0 to +40°C)
- Relative humidity: 15% to 80%, non-condensing
- Storage temperature: -4 to 140°F (-20 to +60°C)

## ***Additional Warning for Products with Power over Ethernet (PoE) Functionality***

This product is powered using Power over Ethernet. You must use an appropriately rated and approved networking device or the power injector identified for use with this product.

## **Installation Instructions**

Installation must be performed in accordance with all relevant national wiring rules.

L'Installation doit être exécutée conformément à tous les règlements nationaux applicable au filage électrique.

When using Power over Ethernet (PoE), the equipment is to be connected only to PoE networks without connections to the outside plant.

Lorsque vous utilisez une alimentation électrique par câble ethernet (PoE - Power over Ethernet), l'équipement doit être connecté uniquement aux réseaux PoE sans connexions vers l'extérieur de l'usine.

## **USA**

### ***Part 15 FCC Rules***

This device is compliant with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- This device may not cause harmful interference.
- This device must accept any interferences received, including interference that may cause undesired operation.

In accordance with part 15 of the FCC rules, the user is cautioned that any changes or modifications not expressly approved by HP Inc. could void the user's authority to operate the equipment.

### ***Class A Digital Device***

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to Part 15 of the FCC rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

#### **Responsible Party issuing FCC Supplier's Declaration of Conformity:**

HP Inc.  
1501 Page Mill Road,  
Palo Alto 94304  
USA

650-857-1501

## ***Radiation Exposure Statement***

The antenna used for this transmitter must be installed to provide a separation distance of at least 20 centimeters from all persons and must not be co-located or operating in conjunction with any other antenna or transmitter. This device with its antenna complies with FCC's RF radiation exposure limits set forth for an uncontrolled environment. To maintain compliance, this transmitter must not be co-located or operating in conjunction with any other antenna or transmitter.

## **Canada**

### ***Industry Canada Statement***

This device complies with RSS247 of the Industry Canada rules and also with ISED's license-exempt RSS regulations. Operation is subject to the two following conditions:

- (1) This device does not cause harmful interference.
- (2) This device must accept any interference received, including interference that may cause undesired operation.

Le présent appareil est conforme aux CNR d'ISED applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

- (1) le dispositif ne doit pas produire de brouillage préjudiciable, et
- (2) ce dispositif doit accepter tout brouillage reçu, y compris un brouillage susceptible de provoquer un fonctionnement indésirable.

This device for operation in band 5150-5250 MHz is only for indoor use to reduce the potential for harmful interference to co-channel mobile satellite systems.

Cet appareil destiné à fonctionner dans la bande 5150-5250 MHz est uniquement destiné à une utilisation en intérieur afin de réduire le potentiel d'interférences nuisibles aux systèmes satellites mobiles cocanaux.

This Class [A] digital apparatus complies with Canadian ICES-003.

Cet appareil numérique de la classe [A] est conforme à la norme NMB-003 du Canada.  
Certification Number IC: 1849C-P030

### ***Radiation Exposure Statement***

This equipment complies with ISED radiation exposure limits set forth for an uncontrolled environment. This equipment should be installed and operated with greater than 20 cm between the radiator and your body.

### ***Déclaration d'exposition aux radiations***

Cet équipement est conforme aux limites d'exposition aux rayonnements ISED établies pour un

environnement non contrôlé. Cet équipement doit être installé et utilisé à plus de 20 cm entre le radiateur et votre corps.

## FCC and Industry Canada Example Label

See an example of the Poly TC10 regulatory label below.

FCC ID: M72-P030

IC: 1849C-P030



## EEA

### CE Mark

P030 is marked with the CE mark. This mark indicates compliance with EU Radio Equipment Directive (RED) 2014/53/EU, RoHS Directive 2011/65/EU, and Commission Regulation 278/2009.

P030NR is marked with the CE mark. This indicates compliance with the EU EMC Directive (EMCD) 2014/30/EU, Low Voltage Directive (LVD) 2014/35/EU, RoHS Directive 2011/65/EU and Commission Regulation 278/2009.

## UK

### UKCA Mark

P030 is marked with the UKCA mark. This mark indicates compliance with the Radio Equipment Regulations 2017 (SI 2017 No.1206), The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations (SI 2012 No.3032)

P030NR is marked with the UKCA mark. This mark indicates compliance with The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations (SI 2012 No.3032), The Electrical Equipment (Safety) Regulations (SI 2016 No.1101), The Electromagnetic Compatibility Regulations (SI 2016 No.1091)

A full copy of the Declaration of Conformity for each model is available at the following Internet address: [www.hp.eu/certificates](http://www.hp.eu/certificates) (search with RMN).

## ***Poly Studio TC10 Radio Operating Frequency***

The frequency ranges in the following table apply to Poly Studio TC10 (P030)

<b>Frequency Range</b>	<b>Maximum Transmit Power</b>
2.400Ghz – 2.484Ghz	+14.2 dBm EIRP
5.180Ghz – 5.825 GHz	+14.4 dBm EIRP

### **Australia**

**Warning:** This equipment will be inoperable when mains power fails.

### ***Class A Warning***

**Warning:** This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures."

### **Brazil**

Para maiores informações consulte o site da ANATEL - [www.anatel.gov.br](http://www.anatel.gov.br)

Este equipamento não tem direito à proteção contra interferência prejudicial e não pode causar interferência em sistemas devidamente autorizados.

### **India**

#### **India RoHS**

This product, as well as its related consumables and spares, complies with the reduction in hazardous substances provisions of the "India E-waste (Management and Handling) Rule 2022". It does not contain lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers in concentrations exceeding 0.1 weight % and 0.01 weight % for cadmium, except for where allowed pursuant to the exemptions set in Schedule 2 of the Rule.

### **Japan**

Model P030 is only approved to transmit indoors within the W52 and W53 bands for Japan:

- W52(5180MHz / 5200MHz / 5220MHz / 5240MHz)
- W53(5260MHz / 5280MHz / 5300MHz / 5320MHz)

## VCCI A Statement

この装置は、クラスA機器です。この装置を住宅環境で使用すると電波妨害を引き起こすことがあります。この場合には使用者が適切な対策を講ずるよう要求されることがあります。

VCCI - A

This product can't be connected directly to the telecommunications circuits (or public wireless LANs) of any telecommunications carriers (e.g., mobile communications carriers, fixed communication carriers, or internet providers). To connect this product to the Internet, be sure to connect it via a router.

## New Zealand

### Class A Warning

**Warning:** This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures."

## China

### 用户须知

欢迎使用惠普 · 型号:P030 · P030NR · 为了您及产品的安全 · 请您务必注意如下事项：

- 1 产品要和地线相接 · 要使用有正确接地插头的电源线 · 使用中国国家规定的220V电源。
- 2 避免高温和多尘土的地方 · 否则易引起产品零部件的损坏。
- 3 避免接近高温 · 避免接近直接热源 · 如太阳光直射 · 暖气等其他发热体。
- 4 不要有异物或液体落入机内 · 以避免零部件短路。
- 5 不要将磁体放置于产品附近。

### 警告

为防止火灾或触电事故 · 请不要将该产品淋雨或者放置于潮湿处。

## Korea

이 장치는 이동전화, Wi-Fi 또는 블루투스 장치 등 무선통신장치와 매우 근접한 장소에서 사용할 경우 오작동을 일으킬 가능성이 있습니다.

해당 무선설비는 전파혼신 가능성이 있으므로 인명안전과 관련된 서비스는 할 수 없음.

해당 무선설비는 5150~5250GHz 대역에서 실내에서만 사용할 수 있음

## Taiwan

### 安全警語

- 1 不得打開產品外殼，以免造成安全問題”或“不要對本設備進行機械或電氣修改，以免造成安全問題”
- 2 請勿任意拆裝設備。任何未經授權或認證人員之設備拆裝可能造成嚴重的安全問題。任何問題，請洽您的銷售人員或經銷商尋求協助。
- 3 除非安裝手冊或使用手冊中提及，否則請勿嘗試維修您的設備。永遠遵守安裝手冊及使用手冊的說明。

### ***NCC Low Powered Device Statement***

取得審驗證明之低功率射頻器材，非經核准，公司、商號或使用者均不得擅自變更頻率、加大功率或變更原設計之特性及功能。低功率射頻器材之使用不得影響飛航安全及干擾合法通信；經發現有干擾現象時，應立即停用，並改善至無干擾時方得繼續使用。前述合法通信，指依電信管理法規定作業之無線電通信。低功率射頻器材須忍受合法通信或工業、科學及醫療用電波輻射性電機設備之干擾。

### ***5GHz U-NII Statement***

應避免影響附近雷達系統之操作。  
高增益指向性天線只得應用於固定式點對點系統。

## Mexico

La operación de este equipo está sujeta a las siguientes dos condiciones: (1) es posible que este equipo o dispositivo no cause interferencia perjudicial y (2) este equipo o dispositivo debe aceptar cualquier interferencia, incluyendo la que pueda causar su operación no deseada.

## Restriction of Hazardous Substances Directive (RoHS)

All Poly products comply with the requirements of the EU RoHS Directive. Statements of compliance can be obtained by contacting [typeapproval@poly.com](mailto:typeapproval@poly.com).

## Environmental

For the latest environmental information including Networked Standby Efficiency, battery replacement, handling, and disposal, take back, RoHS, and Reach, please visit <https://www.poly.com/us/en/company/corporate-responsibility/environment>.

## End of Life Products

Poly encourages you to recycle your end-of-life Poly products in an environmentally considerate way. We recognize our Extended Producer Responsibility (EPR), in accordance with the requirements of the European Waste Electronic and Electrical Equipment (WEEE) Directive 2012/19/EU.

All Poly products are marked with the crossed wheelie bin symbol shown below. Products that carry this symbol should be not be disposed of in the household or general waste stream. Further recycling information and detail of the options open to you, including our voluntary free global recycling service to ISO 14001 standard can be found at: <https://www.poly.com/WEEE>.

The Poly Global Producer Responsibility Statement can be found in the Environment section of the [Poly.com](https://www.poly.com) website.

## Poly Take Back

In addition to any mandated take back requirement, Poly offers free recycling of its branded products to business users. Detailed information is available at [www.poly.com/us/en/company/corporate-responsibility/environment](https://www.poly.com/us/en/company/corporate-responsibility/environment).

# Getting Help and Copyright Information

---

## **GETTING HELP**

For more information about installing, configuring, and administering Poly/Polycom products or services, go to the [Poly Online Support Center](#).

HP Inc.  
1501 Page Mill Road,  
Palo Alto 94304  
USA  
650-857-1501

© 2023 Poly. All trademarks are the property of their respective owners.