


OVERVIEW



1. SD card reader *	8. HDMI
2. Microphone (3.5mm)	9. VGA
3. Headphone (3.5mm)	10. 4x USB 2.0
4. 4x USB 3.2 Gen 1	11. 2x PS/2 ports (keyboard / mouse) *
5. 2x USB 3.2 Gen 2	12. Serial
6. 3x Audio ports (3.5mm)	13. Ethernet (RJ-45)
7. DisplayPort	14. Serial *

Notes:

- Ports with * are only available on selected models

PERFORMANCE

Processor

Processor Family

11th Generation Intel® Core™ i5 / i7 / i9 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-11500	6	12	2.7GHz	4.6GHz	12MB	DDR4-3200	Intel UHD Graphics 750
Core i5-11600	6	12	2.8GHz	4.8GHz	12MB	DDR4-3200	Intel UHD Graphics 750
Core i7-11700	8	16	2.5GHz	4.9GHz	16MB	DDR4-3200	Intel UHD Graphics 750
Core i9-11900	8	16	2.5GHz	5.2GHz	16MB	DDR4-3200	Intel UHD Graphics 750

Processor Sockets

1x FCLGA1200

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 DG Windows 10 Pro 64
- Windows 10 Pro 64
- Windows 10 Home 64
- Ubuntu Linux LTS
- Red Hat Enterprise Linux (certified only)
- No operating system

Graphics

Integrated Graphics**

- Intel UHD Graphics 630
- Intel UHD Graphics 750

Discrete Graphics Support

Supports up to one NVIDIA® GeForce RTX™ 3060, NVIDIA RTX A2000, or AMD Radeon™ Pro WX 3200

Discrete Graphics Offering***

Graphics	Memory	Power	Connector	SLI / NVlink
NVIDIA T400	2GB GDDR6	40W	3x miniDP 1.4	None
NVIDIA T400 4GB	4GB GDDR6	40W	3x miniDP 1.4	None
NVIDIA T600	4GB GDDR6	40W	4x miniDP 1.4	None
NVIDIA T1000	4GB GDDR6	50W	4x miniDP 1.4	None
NVIDIA T1000 8GB	8GB GDDR6	50W	4x miniDP 1.4	None
NVIDIA RTX A2000 12GB	12GB GDDR6	70W	4x miniDP 1.4a	None
AMD Radeon Pro WX 3200	4GB GDDR5	50W	4x miniDP 1.4	-
NVIDIA GeForce RTX 3060	12GB GDDR6	170W	3x DP 1.4a, 1x HDMI® 2.1	-

Monitor Support

Monitor Support

Supports multiple displays via onboard video ports and discrete graphics, the number of maximum monitors supported depends on the graphic card in use

Chipset

Chipset

Intel B560 chipset

Memory

ThinkStation P348 Tower

Max Memory^[1]

Up to 128GB (4x 32GB UDIMMs) DDR4-3200

Memory Type

DDR4-3200 UDIMM non-ECC

Memory Slots

Four DDR4 UDIMM slots, dual-channel capable

Memory Protection

Non-ECC

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

Up to three drives, 2x 3.5" SATA HDD + 1x M.2 SSD

- 3.5" HDD up to 4TB each
- M.2 SSD up to 1TB

Storage Type^{***}

Disk Type	Interface	RPM	Offering	Security
3.5" SATA HDD	SATA 6Gb/s	7.2K	1TB / 2TB / 4TB	-
M.2 2280 SSD	PCIe® NVMe®, PCIe 3.0 x4	-	256GB / 512GB / 1TB	Opal

Storage Controllers

Storage Controller	Type	Interface	RAID	Cache
Integrated NVMe controller	Standard	PCIe NVMe	-	None
Integrated SATA controller	Standard	SATA 6.0Gb/s	-	None

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Optical Support

Optional one 9.0mm optical drive, DVD-ROM or DVD±RW

Card Reader

- SD card reader
- No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
500W	Fixed	92%	Autosensing, 80 PLUS Platinum qualified

DESIGN

Mechanical

Form Factor

Tower (17L)

ThinkStation P348 Tower

Dimensions (WxDxH)

170 x 315.4 x 376 mm (6.7 x 12.4 x 14.8 inches)

Weight

9.48 kg (20.9 lbs, maximum configuration)

Bays

- 1x 3.5" disk bay (standard)
- 1x 2.5" disk bay (optional by 2.5" HDD cage kit)
- 1x 3.5" disk bay (optional, comes with disk or 3.5" HDD cage kit in flex bay)

Flex Bays

1x Flex bay, supports 2nd 3.5" disk bay and 9.0mm optical

M.2 Slots

Up to 1x M.2 SSD via onboard slot

Expansion Slots

- One PCIe 4.0 x16
- Two PCIe 3.0 x1

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, Realtek RTL8111K, 1x RJ-45, supports Wake-on-LAN

Optional Ethernet

Additional Ethernet options via PCIe adapter

WLAN + Bluetooth®**^[1]

- Mediatek Wi-Fi® 6 MT7921, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- Intel Wi-Fi 6 AX201, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- No WLAN and Bluetooth

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Front Ports

- 4x USB 3.2 Gen 1
- 2x USB 3.2 Gen 2
- 1x headphone (3.5mm)
- 1x microphone (3.5mm)

Optional Front Ports

None

Rear Ports^[2]

- 4x USB 2.0 (one supports Smart Power On)
- 1x VGA
- 1x HDMI
- 1x DisplayPort™
- 1x serial (9-pin)
- 1x Ethernet (RJ-45)
- 1x line-in (3.5mm)
- 1x line-out (3.5mm)
- 1x microphone (3.5mm)

Optional Rear Ports^{***}

- 2x USB 2.0
- 2x USB 3.2 Gen 1 (via 2-port USB expansion card)
- 2x PS/2

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s;
2. For video ports on discrete graphics, please see graphics section

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

Physical Locks

- (Optional) Cable lock
- (Optional) E-lock
- (Optional) Smart Cable Clip
- Kensington® Security Slot, 3 x 7 mm
- Padlock Loop

Chassis Intrusion Switch

- Chassis intrusion switch
- No chassis intrusion switch

BIOS Security

- Administrator password
- Power-on password

MANAGEABILITY

System Management

System Management^{[1][2]}

Non-vPro

Notes:

1. Intel vPro offers a superset of DASH's defined capabilities.
2. Intel vPro offers a superset of DASH's defined capabilities.

Diagnostic

Diagnostic

Lenovo UEFI Bootable Diagnostics

SERVICE

Warranty

Base Warranty^{**[1]}

- 1-year limited onsite service
- 2-year limited onsite service
- 3-year limited onsite service with 9x5 NBD (for most models)
- No base warranty

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature

- Operating: 10°C (50°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

CERTIFICATIONS

Green Certifications

Green Certifications

- (Optional) EPEAT™ Gold
- (Optional) EPEAT Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 8.0
- RoHS compliant

ISV Certifications

ISV Certifications

Please visit www.thinkworkstations.com/isv-certifications/

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

