


**OVERVIEW**



1. Headphone / microphone combo jack (3.5mm)	8. HDMI 2.1 TMDs
2. USB 3.2 Gen 2	9. USB 3.2 Gen 1 (with Smart Power On feature)
3. USB 3.2 Gen 2 (Always On and fast charge)	10. USB 3.2 Gen 2
4. USB-C 3.2 Gen 2	11. USB 3.2 Gen 2
5. Power connector	12. Ethernet (RJ-45)
6. DisplayPort 1.4	13. 2 Punch out ports or expansion card *
7. USB 3.2 Gen 1	

Notes:

- Items with \* are only available on selected models

## PERFORMANCE

### Processor

#### Processor Family

Up to one 13th Gen Intel® Core™ i3 / i5 / i7 / i9 processor, supports up to 24 cores, up to 5.6GHz

#### Processor\*\*<sup>[1]</sup>

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i3-13100	4 (4 P-core + 0 E-core)	8	P-core 3.4GHz	P-core 4.5GHz	12MB	DDR5-4800	Intel UHD Graphics 730
Core i3-13100T	4 (4 P-core + 0 E-core)	8	P-core 2.5GHz	P-core 4.2GHz	12MB	DDR5-4800	Intel UHD Graphics 730
Core i5-13400	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.6GHz / E-core 3.3GHz	20MB	DDR5-4800	Intel UHD Graphics 730
Core i5-13400T	10 (6 P-core + 4 E-core)	16	P-core 1.3GHz / E-core 1.0GHz	P-core 4.4GHz / E-core 3.0GHz	20MB	DDR5-4800	Intel UHD Graphics 730
Core i5-13500	14 (6 P-core + 8 E-core)	20	P-core 2.5GHz / E-core 1.8GHz	P-core 4.8GHz / E-core 3.5GHz	24MB	DDR5-4800	Intel UHD Graphics 770
Core i5-13500T	14 (6 P-core + 8 E-core)	20	P-core 1.6GHz / E-core 1.2GHz	P-core 4.6GHz / E-core 3.2GHz	24MB	DDR5-4800	Intel UHD Graphics 770
Core i5-13600	14 (6 P-core + 8 E-core)	20	P-core 2.7GHz / E-core 2.0GHz	P-core 5.0GHz / E-core 3.7GHz	24MB	DDR5-4800	Intel UHD Graphics 770
Core i5-13600T	14 (6 P-core + 8 E-core)	20	P-core 1.8GHz / E-core 1.3GHz	P-core 4.8GHz / E-core 3.4GHz	24MB	DDR5-4800	Intel UHD Graphics 770
Core i7-13700	16 (8 P-core + 8 E-core)	24	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.2GHz / P-core 5.1GHz / E-core 4.1GHz	30MB	DDR5-5600	Intel UHD Graphics 770
Core i7-13700T	16 (8 P-core + 8 E-core)	24	P-core 1.4GHz / E-core 1.0GHz	Max Turbo up to 4.9GHz / P-core 4.8GHz / E-core 3.6GHz	30MB	DDR5-5600	Intel UHD Graphics 770
Core i9-13900	24 (8 P-core + 16 E-core)	32	P-core 2.0GHz / E-core 1.5GHz	Max Turbo up to 5.6GHz / P-core 5.2GHz / E-core 4.2GHz	36MB	DDR5-5600	Intel UHD Graphics 770
Core i9-13900T	24 (8 P-core + 16 E-core)	32	P-core 1.1GHz / E-core 0.8GHz	Max Turbo up to 5.3GHz / P-core 5.1GHz / E-core 3.9GHz	36MB	DDR5-5600	Intel UHD Graphics 770

#### Processor Sockets

1x FCLGA1700

Notes:

[1] Intel Max Turbo frequency will vary depending on application workload and the hardware and software configurations, see <http://www.intel.com/technology/turboboost/> for more information.

### Operating System

#### Operating System\*\*

- Red Hat Enterprise Linux 9.2 (certified only, for detailed and latest information, please visit [Red Hat Certified Hardware](#))
- Ubuntu Linux LTS
- Windows® 11 DG Windows 10 Pro 64
- Windows 11 Home
- Windows 11 Pro
- No operating system

### Graphics

#### Integrated Graphics\*\*

# ThinkStation P3 Tiny

- Intel UHD Graphics 730
- Intel UHD Graphics 770

## Discrete Graphics Support<sup>[1]</sup>

Supports up to one NVIDIA® T1000 8GB

### Discrete Graphics Offering

Graphics	Memory	Power	Connector	SLI / NVLink
NVIDIA T400 4GB	4GB GDDR6	40W	3x miniDP 1.4	None
NVIDIA T1000	4GB GDDR6	50W	4x miniDP 1.4	None
NVIDIA T1000 8GB	8GB GDDR6	50W	4x miniDP 1.4	None

Notes:

[1] Discrete graphics support may vary by configurations such as processor selection or power supply wattage.

## Monitor Support

### Monitor Support

Onboard graphics supports up to 4 independent displays via (onboard DP, onboard HDMI®, punch out port 1 [VGA / HDMI / DP / USB-C®], and punch out port 2 [VGA / HDMI / DP]); the number of maximum monitors also depends on the discrete graphic card in use

## Chipset

### Chipset

Intel Q670 chipset

## Memory

### Max Memory<sup>[1]</sup>

Up to 64GB (2x 32GB DDR5 SO-DIMM)

### Memory Type

- DDR5-4800 SO-DIMM non-ECC
- DDR5-5600 SO-DIMM non-ECC<sup>[2]</sup>

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

[2] System may come with DDR5-5600 memory and will run at lower speed due to platform limitations: 1x 32GB / 2x 32GB configurations run at DDR5-5200

## Storage

### Storage Support<sup>[1]</sup>

Up to two drives, 2x M.2 SSD, up to 2TB each

### Storage Type

Disk Type	Interface	Offering	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe 4.0 x4 Performance	512GB / 1TB / 2TB	Opal 2.0

### Storage Controllers

Storage Controller	Type	Interface	RAID	Cache
Integrated NVMe controller	Standard	PCIe NVMe	0/1	None

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

## Removable Storage

### Optical Support

Optional one 9.0mm optical drive via optical drive kit, DVD-ROM or DVD±RW

## Multi-Media

### Audio Chip

High Definition (HD) Audio, Realtek® ALC256VB codec

### Speakers\*\*

- Single speaker
- Single speaker, premium

## Power Supply

### Power Supply\*\*

Power	Type	Efficiency	Key Features
170W	Adapter	90%	100V - 240V
230W	Adapter	90%	100V - 240V
300W	Adapter	90%	100V - 240V

## DESIGN

### Mechanical

#### Form Factor

Tiny (1L)

#### Dimensions (WxDxH)<sup>[1]</sup>

Models	Dimensions
Tiny only	179 x 182.9 x 37mm with rubber feet (7.0 x 7.2 x 1.5 inches with rubber feet)
Tiny & ODD	204.2 x 186.6 x 64 mm with rubber feet (8.04 x 7.35 x 2.52 inches with rubber feet)

#### Weight<sup>[2]</sup>

Models	Weight
Tiny only	1.4 kg (3 lbs, maximum configuration)

#### Bays

No bays

#### M.2 Slots

- Two M.2 PCIe Gen 4x4 slots (for SSD)
- One M.2 slot (for WLAN)

#### Expansion Slots

One PCIe 4.0 x8, low-profile<sup>[3]</sup>

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[3] Supports discrete graphic card by x16 riser card (x8 signal), and supports Ethernet card / Thunderbolt 4 / serial card by x4 riser card. Riser card comes with the expansion cards.

## CONNECTIVITY

### Network

#### Onboard Ethernet

Gigabit Ethernet, Intel Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

#### Optional Ethernet

One additional ethernet adapter support, up to one additional 2.5GbE port

- Gigabit Ethernet, Intel I350-T2, 2x RJ-45, PCIe x4

# ThinkStation P3 Tiny

- Gigabit Ethernet, Intel I350-T4, 4x RJ-45, PCIe x4
- Gigabit Ethernet, Broadcom BCM5720, 2x RJ-45, PCIe x1
- Gigabit Ethernet, Broadcom BCM5719, 4x RJ-45, PCIe x4
- 2.5 Gigabit Ethernet, Realtek RTL8125BGS, 1x RJ-45, BTB

## WLAN + Bluetooth<sup>®</sup>\*\*

- Intel Wi-Fi<sup>®</sup> 6 AX201, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1 (Bluetooth 5.2 hardware ready)
- Realtek Wi-Fi 6 RTL8852BE, 802.11ax Dual Band 2x2 Wi-Fi + Bluetooth 5.1
- Intel Wi-Fi 6E AX211, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1 (Bluetooth 5.3 hardware ready), Intel vPro<sup>®</sup> technology support<sup>[1]</sup>
- No WLAN and Bluetooth

## Notes:

[1] Bluetooth 5.3 is hardware ready but may run at a lower version due to OS limitations. Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

## Ports<sup>[1]</sup>

### Front Ports

- 1x USB 3.2 Gen 2
- 1x USB 3.2 Gen 2 (Always On and 5V@2.1A charging)
- 1x headphone / microphone combo jack (3.5mm)
- 1x USB-C 3.2 Gen 2 (support data transfer)

### Rear Ports<sup>[2]</sup>

- 2x USB 3.2 Gen 1 (one supports Smart Power On)
- 2x USB 3.2 Gen 2
- 1x HDMI 2.1 TMDS
- 1x DisplayPort<sup>™</sup> 1.4
- 1x Ethernet (RJ-45)

### Optional Rear Ports

- Punch out port 1 (one of VGA / DisplayPort / HDMI / serial / USB-C 3.2 Gen 1 with DisplayPort and PD 3.0 functions)
- Punch out port 2 (one of VGA / DisplayPort / HDMI / serial / RJ-45)
- 1x Thunderbolt<sup>™</sup> 4 (via additional PCIe adapter)
- 2x USB 3.2 Gen 1 (occupies port 1 and 2)
- 4x USB 3.2 Gen 1 (share one USB 3.2 Gen 1 bandwidth, occupy port 1 and 2)
- 2x GbE RJ-45, via additional PCIe adapter
- 4x GbE RJ-45, via additional PCIe adapter
- 4x serial, via additional PCIe adapter

## Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4<sup>®</sup> 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt 3/4: 40 Gbit/s.

[2] For video ports on discrete graphics, please see graphics section.

## SECURITY & PRIVACY

### Security

#### Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

#### Physical Locks

- (Optional) Cable lock
- Kensington<sup>®</sup> Security Slot<sup>™</sup>, 3 x 7 mm

#### Chassis Intrusion Switch

Chassis intrusion switch

## BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Boot sequence control
- Boot without keyboard and mouse
- Certificate based BIOS management
- Cover presence switch
- Self-healing BIOS
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)
- Individual USB port disablement

## MANAGEABILITY

### System Management

#### System Management<sup>[1]</sup>

- Intel vPro Enterprise with Intel AMT 16
- Non-vPro

Notes:

[1] Intel vPro offers a superset of DASH's defined capabilities.

## SERVICE

### Warranty<sup>[1]</sup>

#### Base Warranty\*\*

- 1-year limited onsite service
- 2-year limited onsite service
- 3-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

## ENVIRONMENTAL

### Operating Environment

#### Temperature

- Operating: 10°C (50°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

#### Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

#### Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

## CERTIFICATIONS

### Green Certifications<sup>[1]</sup>

#### Green Certifications

- (Optional) ENERGY STAR® 8.0
- (Optional) EPEAT™ Gold Registered<sup>[2]</sup>
- ErP Lot 3
- RoHS compliant

- TCO Certified 9.0

#### Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

[2] EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

## Other Certifications

### Mil-Spec Test

MIL-STD-810H military test passed

## ISV Certifications

### ISV Certifications

Please visit [ISV certifications for Lenovo Workstations](#)

- Feature with \*\* means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

