


OVERVIEW



1. Power button	9. DisplayPort 1.4
2. Optical drive *	10. USB-A (Hi-Speed USB) *
3. Card reader *	11. HDMI 2.1 TMDS
4. Microphone jack (3.5mm)	12. VGA
5. Headphone / microphone combo jack (3.5mm)	13. 3x USB-A (Hi-Speed USB)
6. USB-C (USB 5Gbps), with 15W charging	14. USB-A (Hi-Speed USB), with Smart Power On
7. 2x USB-A (USB 5Gbps)	15. Ethernet (RJ-45)
8. Audio-out (3.5mm)	

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

13th / 14th Generation Intel® Core™ i3 / i5 / i7 Processor, or Intel® 300 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics
Core i3-13100	4 (4 P-core + 0 E-core)	8	P-core 3.4GHz	P-core 4.5GHz	12MB	Intel® UHD Graphics 730
Core i5-13400	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.6GHz / E-core 3.3GHz	20MB	Intel® UHD Graphics 730
Core i5-13500	14 (6 P-core + 8 E-core)	20	P-core 2.5GHz / E-core 1.8GHz	P-core 4.8GHz / E-core 3.5GHz	24MB	Intel® UHD Graphics 770
Core i5-13600	14 (6 P-core + 8 E-core)	20	P-core 2.7GHz / E-core 2.0GHz	P-core 5.0GHz / E-core 3.7GHz	24MB	Intel® UHD Graphics 770
Core i7-13700	16 (8 P-core + 8 E-core)	24	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.2GHz / P-core 5.1GHz / E-core 4.1GHz	30MB	Intel® UHD Graphics 770
Core i3-14100	4 (4 P-core + 0 E-core)	8	P-core 3.5GHz	P-core 4.7GHz	5MB L2 Cache / 12MB Intel® Smart Cache	Intel® UHD Graphics 730
Core i5-14400	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.7GHz / E-core 3.5GHz	9.5MB L2 Cache / 20MB Intel® Smart Cache	Intel® UHD Graphics 730
Core i5-14500	14 (6 P-core + 8 E-core)	20	P-core 2.6GHz / E-core 1.9GHz	P-core 5.0GHz / E-core 3.7GHz	11.5MB L2 Cache / 24MB Intel® Smart Cache	Intel® UHD Graphics 770
Core i5-14600	14 (6 P-core + 8 E-core)	20	P-core 2.7GHz / E-core 2.0GHz	P-core 5.2GHz / E-core 3.9GHz	20MB L2 Cache / 24MB Intel® Smart Cache	Intel® UHD Graphics 770
Core i7-14700	20 (8 P-core + 12 E-core)	28	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.4GHz / P-core 5.3GHz / E-core 4.2GHz	28MB L2 Cache / 33MB Intel® Smart Cache	Intel® UHD Graphics 770
Intel® 300	2 (2 P-core + 0 E-core)	4	P-core 3.9GHz	-	6MB	Intel® UHD Graphics 710

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Windows® 11 DG Windows® 10 Pro 64
- Ubuntu Linux
- No preload operating system

Graphics

Graphics**[1]

Graphics	Type	Memory	Max Resolution	Connector	Key Features
Intel® UHD graphics 710	Integrated	Shared	3840×2160@60Hz(HDMI®), 1920x1200@60Hz(VGA), 4096x2304@60Hz(DP)	1x HDMI® 2.1 TMDS, 1x VGA, 1x DP 1.4	DirectX® 12
Intel® UHD graphics 730	Integrated	Shared	3840×2160@60Hz(HDMI®), 1920x1200@60Hz(VGA), 4096x2304@60Hz(DP)	1x HDMI® 2.1 TMDS, 1x VGA, 1x DP 1.4	DirectX® 12

Intel® UHD graphics 770	Integrated	Shared	3840×2160@60Hz(HDMI®), 1920x1200@60Hz(VGA), 4096x2304@60Hz(DP)	1x HDMI® 2.1 TMDS, 1x VGA, 1x DP 1.4	DirectX® 12
Intel® Arc™ A310 LP Graphics	Discrete	4GB GDDR6	3840x2160@60Hz(HDMI®), 1600x1200@60Hz(VGA)	1x HDMI® 2.1 TMDS, 1x VGA	DirectX® 12, OpenGL 4.6

Notes:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

Monitor Support

Monitor Support

Supports up to 3 independent displays via (HDMI®, DP and VGA), more displays support via discrete graphics

Chipset

Chipset

Intel® B760 chipset

Memory

Max Memory^[1]

Up to 64GB DDR5-5600

Memory Slots

Two DDR5 UDIMM slots, dual-channel capable

Memory Type^[2]

- DDR5-4800
- DDR5-5200
- DDR5-5600

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

[2] Installed memory is actually DDR5-5600 but may run as DDR5-4800 or DDR5-5200 depending on the memory support capability of processor.

Storage

Max Storage Support^{**[1]}

- Up to two drives, 1x 3.5" HDD + 1x M.2 SSD
 - 3.5" HDD up to 2TB
 - M.2 SSD up to 1TB
- For installing HDD storage, 3.5" HDD screw and grommet kit is needed.

Storage Type

Disk Type	Interface	RPM	Security
3.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	-	-
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	-	Opal 2.0

Notes:

[1] The max capacity of each disk type is based on the test results with current Lenovo® storage offerings.

Removable Storage

Optical^{**}

- DVD-ROM, SATA connector, slim (9.0mm)
- DVD burner (DVD±RW), SATA connector, slim (9.0mm)
- For installing ODD, slim ODD bracket kit is needed.
- None

Card Reader

- 3-in-1 card reader
- No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

- No speakers
- Single speaker, 1W x1

Power Supply

Power Supply**

Power	Type	Efficiency	Key Features
180W	Fixed	85%	100-240V, 50-60Hz
258W	Fixed	90%	100-240V, 50-60Hz
260W ^[1]	Fixed	90%	100-240V, 50-60Hz

Notes:

[1] Hybrid PSU sources configured for supply assurance; assembled product has maximum wattage of 258W.

DESIGN

Input Device

Keyboard**

- Lenovo® Calliope Keyboard (USB connector), black
- Lenovo® Traditional Keyboard (USB connector), black
- No keyboard

Mouse

- Lenovo® Calliope Mouse (USB connector), black
- No mouse

Mechanical

Form Factor

SFF (8.2L)

Dimensions (WxDxH)^[1]

Models	Dimensions
Models (Max Dimension)	92.5 x 291.4 x 339.5 mm (3.6 x 11.5 x 13.4 inches)

Packaging Dimensions (WxDxH)

195 x 395 x 530 mm (7.7 x 15.6 x 20.9 inches)

Weight^[2]

Around 4.2 kg (9.3 lbs)

Packaging Weight

Around 6.29 kg (13.9 lbs)

Case Color

Black (chassis), grey (bezel)

Bays

- For installing HDD or ODD, 3.5" HDD screw and grommet kit or slim ODD bracket kit is needed.
- 1x 3.5" disk bay
- 1x slim ODD bay

Expansion Slots

- One PCIe® 3.0 x16, low-profile, length ≤ 155mm, height ≤ 70mm

- One PCIe® 3.0 x1, low-profile, length ≤ 155mm, height ≤ 70mm
- Two M.2 slots (one for WLAN, one for SSD)

EOU

No support

Stand

- Vertical stand
- No stand

Others

Supports Smart Power On

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth®**

- Realtek® Wi-Fi® 6 RTL8852BE, 802.11ax Dual Band 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card
- Intel® Wi-Fi® 6 AX201, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 card
- Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3, M.2 card
- No WLAN and Bluetooth®

Onboard Ethernet

Gigabit Ethernet, Realtek® RTL8111K, 1x RJ-45, supports Wake-on-LAN

Ports^[1]

Front Ports

- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with 15W charging
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Rear Ports^[2]

- 4x USB-A (Hi-Speed USB / USB 2.0), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4
- 1x VGA
- 1x Ethernet (RJ-45)
- 1x line-out (3.5mm)

Optional Rear Ports

- 1x USB-A (Hi-Speed USB / USB 2.0)
- 1x parallel
- 1x serial
- 1x 2nd serial

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

Thunderbolt™ 5: 80 Gbit/s (bidirectional), up to 120 Gbit/s in bandwidth boost mode for video-intensive applications.

[2] For video ports on discrete graphics, please see [graphics section](#)

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

- (Optional) Coded Lock
- (Optional) Smart Cable Clip
- Kensington® Security Slot™, 3 x 7 mm

Chassis Intrusion Switch

- Chassis intrusion switch
- No chassis intrusion switch

Fingerprint Reader

No fingerprint reader

BIOS Security

- Administrator password
- Hard disk password
- Power-on password
- Absolute persistence module
- Boot sequence control
- Boot without keyboard and mouse
- Cover tamper detected
- Configuration change detection
- Individual USB port disablement
- Intel® BIOS guard
- Never crash Self-healing
- Secure wipe
- Secure boot
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)
- More BIOS security features, please visit [BIOS Simulator](#)^[1]

Notes:

[1] The BIOS simulator is just for reference. Default settings and some options may vary depending on the hardware, operating system and BIOS version.

SERVICE

Warranty^[1]

Base Warranty**

- 1-year courier or carry-in service
- 1-year limited onsite service
- No base warranty

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

ACCESSORIES

Bundled Accessories

Bundled Accessories***

- 3.5" HDD screw and grommet kit (optional, or comes with 3.5" HDD disk)
- DP to DVI dongle
- DP to Dual DP dongle
- DP to HDMI® dongle
- DP to VGA dongle

- HDMI® to HDMI® dongle
- HDMI® to VGA dongle
- Slim ODD bracket kit (optional, or comes with optical drive)
- Smart Cable (USB-A to USB-C®)
- None

OPERATING REQUIREMENTS

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Relative Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

ENVIRONMENTAL

Sustainability

Material

85% PCC ABS used in the chassis
95% PCC recycled plastic used in USB keyboard/mouse
90% PIC recycled plastic EPE cushion
30% OBP used in the device bag
FSC certified carton

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- (Optional) ENERGY STAR® 8.0
- (Optional) EPEAT™ Silver Registered
- (Optional) EPEAT™ Gold Registered
- RoHS / WEEE / REACH
- TCO Certified 9.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Other Certifications

- (Optional) TÜV Rheinland® Low Noise
- (Optional) TÜV Rheinland® Ultra Low Noise

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow



disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

