


DELL PRECISION WORKSTATIONS PRODUCT PORTFOLIO COMPARISON



Precision 3480	Precision 3580	Precision 3581
Entry-level 14"	Low price, light 15"	Best price for performance 15"
<ul style="list-style-type: none"> 14" FHD, PremierColor, Touch and ComfortView Plus options Up to Intel® Core™ i7, P28W, 14 (6P+8E) cores Up to NVIDIA A550 graphics (4GB) Up to 2TB of storage Up to 64GB DDR5 memory 4800MHz, non-ECC WiFi 6E, 4G or 5G LTE (FirstNet Ready), BT 5.3 Starting at 3.06 lbs / 1.39kg 	<ul style="list-style-type: none"> 15.6" FHD, PremierColor, Touch and ComfortView Plus options Up to Intel® Core™ i7, P28W, 14 (6P+8E) cores Up to NVIDIA RTX™ A500 graphics (4GB) Up to 3TB of storage Up to 64GB DDR5 memory 4800MHz, non-ECC WiFi 6E, 4G or 5G LTE (FirstNet Ready), BT 5.3 Starting at 3.56 lbs / 1.61 kg 	<ul style="list-style-type: none"> 15.6" FHD, PremierColor, Touch and ComfortView Plus options Up to Intel® Core™ i9, H45W, 14 (6P+8E) cores Up to NVIDIA RTX™ 2000 Ada graphics (8GB) Up to 4TB of storage Up to 64GB DDR5 4800MHz memory, non-ECC WiFi 6E, 4G or 5G LTE (FirstNet Ready), BT 5.3 Starting at 3.96 lbs / 1.79 kg



Precision 5480	Precision 5680	Precision 7680	Precision 7780
Power packed thin and light 14".	Beautiful thin and light 16".	Most powerful and scalable 16".	Most powerful and scalable 17".
<ul style="list-style-type: none"> 14" InfinityEdge 16:10 display QHD+, PremierColor with Touch, Pen and ComfortView Plus Up to Intel® Core™ i9, H 45W 14 (6P+8E) cores Up to NVIDIA RTX™ 3000 Ada graphics (8GB) Up to 4TB of storage Up to 64GB DDR5 6000MHz, non-ECC WiFi 6E, BT 5.3 Starting at 3.26 lbs / 1.48kg 	<ul style="list-style-type: none"> 16", 3-sided InfinityEdge 16:10 display UHD+ OLED with Touch, PremierColor ComfortView Plus Up to Intel® Core™ i9, 14 (6P+8E) cores Up to NVIDIA RTX™ 5000 Ada graphics (16GB) Up to 8TB of storage RAID optional 64GB, DDR5 6000MHz, non-ECC WiFi 6E, BT 5.3 Starting at 4.27 lbs / 1.3 kg 	<ul style="list-style-type: none"> 16", narrow bezel 16:10 OLED display with HDR500, PremierColor, Touch and ComfortView Plus options Up to Intel® Core™ i9, HX 55W, 24 Core (8P + 16E) cores Up to NVIDIA RTX™ 5000 Ada graphics (16GB) Up to 12TB of storage RAID 0/1/5 optional Up to 128GB (CAMM), 64GB (SODIMM), 5600MHz, optional ECC non-ECC WiFi 6E, 5G LTE (FirstNet Ready), BT 5.3 Starting at Thin: 5.75lb/ 2.6kg, Performance: 5.90 lbs/ 2.67 kg 	<ul style="list-style-type: none"> 17.3" 16:9 display with HDR400, PremierColor, ComfortView Plus options Up to Intel® Core™ i9, HX 55W, 24 Core (8P + 16E) cores Up to NVIDIA RTX™ 5000 Ada graphics (16GB) Up to 16TB of storage RAID 0/1/5/10 optional Up to 128GB (CAMM), 64GB (SODIMM), 5600MHz, optional ECC non-ECC WiFi 6E, 5G LTE (FirstNet Ready), BT 5.3 Starting at 6.73 lbs / 3.05 kg



Precision 3260 Compact	Precision 3460 SFF	Precision 3660 Tower
Workstation-class performance packed into our smallest workstation	Performance & affordability in a small form factor	Powerful and affordable tower
<ul style="list-style-type: none"> Compact, Ultra Small Form Factor Up to Intel® Core™ i9 processor, 24 (8P+16E) Cores Up to 95W NVIDIA RTX A3000 graphics (6GB) Up to 9TB storage, RAID 0/1 Up to 64GB 4800MHz ECC or NECC DDR5 memory 	<ul style="list-style-type: none"> Small Form Factor Up to Intel® Core™ i9 processor, 24 (8P+16E) cores Up to 75W AMD or NVIDIA graphics Up to 20TB storage, RAID 0/1 Up to 64GB or up to 4800MHz ECC or NECC DDR5 memory 	<ul style="list-style-type: none"> Tower Up to Intel® Core™ i9 processors, 24 (8P+16E) cores Up to 450W AMD or NVIDIA graphics Up to 28TB of storage, RAID 0/1/5/10 Up to 128GB or up to 4400MHz ECC or NECC DDR5 memory



Precision 5860 Tower	Precision 7865 Tower	Precision 7960 Tower	Precision 7960 Rack
Mid-tower with exceptional scalability	Mid-tower with full tower scalability	Powerful, made for ultimate scalability.	Ultimate performance and security in a 2U form factor.
<ul style="list-style-type: none"> Midtower Intel® Xeon® (225W) processors, up to 24 cores Up to (2) 300W AMD or NVIDIA graphics Up to 56TB storage, RAID 0/1/5/10 Up to 2TB 4800MHz DDR5 ECC memory 	<ul style="list-style-type: none"> Midtower AMD Ryzen Threadripper™ Pro processors, up to 64 cores Up to (2) 300W AMD or NVIDIA graphics Up to 56TB storage, RAID 0/1/5/10 Up to 1TB 3200MHz DDR4 memory 	<ul style="list-style-type: none"> Full Tower Intel® Xeon® (350W) processor, up to 56 cores Up to (4) 300W AMD or NVIDIA graphics Up to 152TB storage, RAID 0/1/5/10 Up to 4TB 4800MHz DDR5 ECC memory 	<ul style="list-style-type: none"> 2U Rack Up to (2) Intel® Xeon® (350W) processors, up to 56 cores each Up to (2) 300W AMD or NVIDIA graphics Up to 128TB storage, RAID 0/1/5/10 Up to 8TB 4800MHz DDR5 ECC memory

Key Technologies

Dell Optimizer for Precision	High Performance Storage	Dell Reliable Memory Technology (RMT) Pro	Dell PremierColor	User Experience	Dell Pro-Support / Pro-Support Plus	Partner Certification	VR and AI Ready
Automated performance tuning, including applications, audio, connectivity and more.	Dell Precision Ultra-Speed Drives provide outstanding performance, density, and price.	Quarantines bad memory sectors to reduce memory related errors. Also, provides alerts when memory needs replacement.	Enjoy the ultimate in color coverage and precision for color critical applications including 100% Adobe color gamut.	Features tool-less chassis, multi-thermal designs, InfinityEdge displays and more to optimize user experiences.	Professional support with guaranteed response time minimizes downtime.	Tested and certified to provide performance and reliability for key applications.	Select systems tackle emerging technology workloads such as VR and AI.