


OVERVIEW



1. USB-C 3.2 Gen 1	8. HDMI 2.1 TMDS
2. USB 3.2 Gen 2 (Always On and fast charge)	9. USB 3.2 Gen 1
3. USB 3.2 Gen 2	10. DisplayPort 1.4
4. Headphone / microphone combo jack (3.5mm)	11. Power connector
5. Ethernet (RJ-45)	12. Punch out port 1 *
6. 2x USB 3.2 Gen 2	13. Punch out port 2 *
7. 1x USB 2.0 (with smart power-on feature)	

Notes:

- Ports with * are only available on selected models

PERFORMANCE

Processor

Processor Family

Intel® Celeron®, Intel Pentium®, or 12th Generation Intel Core™ i3 / i5 / i7 / i9 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Celeron G6900T	2	2	2.8GHz	-	4MB	DDR4-3200	Intel UHD Graphics 710
Pentium Gold G7400T	2	4	3.1GHz	-	6MB	DDR4-3200	Intel UHD Graphics 710
Core i3-12100T	4 (4 P-core + 0 E-core)	8	P-core 2.2GHz	P-core 4.1GHz	12MB	DDR4-3200	Intel UHD Graphics 730
Core i3-12300T	4 (4 P-core + 0 E-core)	8	P-core 2.3GHz	P-core 4.2GHz	12MB	DDR4-3200	Intel UHD Graphics 730
Core i5-12400T	6 (6 P-core + 0 E-core)	12	P-core 1.8GHz	P-core 4.2GHz	18MB	DDR4-3200	Intel UHD Graphics 730
Core i5-12500T	6 (6 P-core + 0 E-core)	12	P-core 2.0GHz	P-core 4.4GHz	18MB	DDR4-3200	Intel UHD Graphics 770
Core i5-12600T	6 (6 P-core + 0 E-core)	12	P-core 2.1GHz	P-core 4.6GHz	18MB	DDR4-3200	Intel UHD Graphics 770
Core i7-12700T	12 (8 P-core + 4 E-core)	20	P-core 1.4GHz / E-core 1.0GHz	P-core 4.6GHz / E-core 3.4GHz	25MB	DDR4-3200	Intel UHD Graphics 770
Core i9-12900T	16 (8 P-core + 8 E-core)	24	P-core 1.4GHz / E-core 1.0GHz	P-core 4.8GHz / E-core 3.6GHz	30MB	DDR4-3200	Intel UHD Graphics 770

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 DG Windows 10 Pro 64
- Windows 10 Home 64
- Ubuntu Linux
- No operating system

Graphics

Graphics**[1]

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Intel UHD graphics 710	Integrated	Shared	1x HDMI® 2.1 TMDS, 1x DP 1.4, 2x punch out ports([2x HDMI/VGA/DP] or [USB-C® with DP function, HDMI/VGA/DP])	4096x2160@60Hz(HDMI), 1920x1200@60Hz(VGA), 4096x2160@60Hz(DP), 4096x2160@60Hz(USB-C with DP function)	DirectX® 12
Intel UHD graphics 730	Integrated	Shared	1x HDMI 2.1 TMDS, 1x DP 1.4, 2x punch out ports([2x HDMI/VGA/DP] or [USB-C with DP function, HDMI/VGA/DP])	4096x2160@60Hz(HDMI), 1920x1200@60Hz(VGA), 4096x2160@60Hz(DP), 4096x2160@60Hz(USB-C with DP function)	DirectX 12
Intel UHD graphics 770	Integrated	Shared	1x DP 1.4, 1x HDMI 2.1 TMDS, 2x punch out ports([2x HDMI/VGA/DP] or [USB-C with DP function, HDMI/VGA/DP])	4096x2160@60Hz(HDMI), 1920x1200@60Hz(VGA), 4096x2160@60Hz(DP), 4096x2160@60Hz(USB-C with DP function)	DirectX 12

Notes:

- The information of integrated graphics are not applicable for the models without integrated graphics (for the details, please refer to processor section)

Monitor Support**Monitor Support**

Supports up to 4 independent displays via (onboard DP, onboard HDMI, punch out port 1 [VGA / HDMI / DP / USB-C], and punch out port 2 [VGA / HDMI / DP])

Chipset**Chipset**

Intel Q670 chipset

Memory**Max Memory^[1]**

Up to 64GB DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Memory Type

DDR4-3200

Notes:

- The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage**Storage Support^[1]**

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 SSD up to 2TB

Storage Type^{*}**

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2242 SSD	PCIe® NVMe®, PCIe 3.0 x2	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 4.0 x4	-	Opal2

RAID

No support

Notes:

- The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage**Optical^{**}**

- DVD-ROM, slim (9.0mm), via USB external ODD box
- DVD burner (DVD±RW), slim (9.0mm), via USB external ODD box
- None

Card Reader

No card reader

Multi-Media**Audio Chip**

High Definition (HD) Audio, Realtek® ALC256VB codec

Speakers^{}**

ThinkCentre M70q Gen 3

- Single speaker, 2W x1
- Premium single speaker, 2W x1

Power Supply

Power Supply**^[1]

Power	Type	Efficiency	Key Features
65W	Adapter	89%	Autosensing
90W	Adapter	89%	Autosensing
135W	Adapter	89%	Autosensing
No power supply	-	-	-

Notes:

1. The optional 90w adapter may increase performance scores when 12500T/12400T CPUs are installed.

DESIGN

Input Device

Keyboard**

- Lenovo Calliope Keyboard (USB connector), black
- Lenovo Calliope Wireless Keyboard, black
- Lenovo Traditional Keyboard (USB connector), black
- No keyboard

Mouse**

- Lenovo Calliope Mouse (USB connector), black
- Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black
- Lenovo Fingerprint Mouse (USB connector), black
- No mouse

Mechanical

Form Factor

Tiny (1L)

Dimensions (WxDxH)

Models	Dimensions
Tiny only	179 x 182.9 x 36.5 mm with rubber feet (7.05 x 7.2 x 1.44 inches with rubber feet)
Tiny & ODD	204.2 x 186.6 x 64 mm with rubber feet (8.04 x 7.35 x 2.52 inches with rubber feet)

Packaging Dimensions (WxDxH)**

- Tiny only : 490 x 268 x 141 mm (19.29 x 10.55 x 5.55 inches)
- Tiny & ODD : 490 x 268 x 166 mm (19.29 x 10.55 x 6.54 inches)

Weight

Models	Weight
Tiny only	Around 1.25 kg (2.76 lbs)
With VESA mount & ODD box	Around 1.74 kg (3.84 lbs)

Packaging Weight**

- Tiny & ODD: 3.58 kg (7.89 lbs)
- Tiny only: 2.85 kg (6.28 lbs)

Case Color

Raven black

Bays

1x 2.5" disk bay

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

EOU

(Optional) toolless chassis open (toolless chassis screw required) and toolless M.2 SSD, HDD, memory assembly / removal

Stand

- Vertical stand
- No stand

IO Box

No IO box

Mounting

- VESA mount bracket kit, supports VESA mount 75mm and 100mm
- None

Others

- (Optional) Dust filter
- (Optional) Power adapter cage
- Supports Smart Power On

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, Intel Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

Optional Ethernet^[1]

- No optional Ethernet
- 2.5 Gigabit Ethernet, Realtek RTL8125BGS, 1x RJ-45, supports Wake-on-LAN

WLAN + Bluetooth^{®**[2]}

- Realtek RTL8822BE, 802.11ac Dual Band 1x1 Wi-Fi[®] + Bluetooth 5.2, M.2 card
- Realtek RTL8822CE, 802.11ac Dual Band 2x2 Wi-Fi + Bluetooth 5.0, M.2 card
- Intel Wireless-AC 9560, 802.11ac Dual Band 2x2 Wi-Fi + Bluetooth 5.1, M.2 card
- Intel Wi-Fi 6 AX201, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- No WLAN and Bluetooth

Notes:

1. Optional Ethernet card occupied punch out port 2
2. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Front Ports

- 1x USB 3.2 Gen 2
- 1x USB 3.2 Gen 2 (Always On and 5V@2.1A charging)
- 1x USB-C 3.2 Gen 1 (support data transfer and 5V@0.9A charging)
- 1x headphone / microphone combo jack (3.5mm)

Optional Front Ports

None

Rear Ports^[2]

- 1x USB 2.0
- 1x USB 3.2 Gen 1
- 2x USB 3.2 Gen 2
- 1x HDMI 2.1 TMDS
- 1x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)

Optional Rear Ports^{**[3]}

- Punch out port 1 (one of VGA / DisplayPort / HDMI / serial / USB-C 2.0 with DisplayPort function)
- Punch out port 2 (one of VGA / DisplayPort / HDMI / serial / RJ-45)

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file

attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s

2. For video ports on discrete graphics, please see graphics section

3. USB-C 3.2 Gen 1 only available for models with 135W adapters

Monitor Cable

Monitor Cable***

- DP to dual DP dongle
- DP to DVI-D dongle
- DP to HDMI dongle
- DP to VGA dongle
- HDMI to HDMI cable (1.5m)
- HDMI to VGA dongle
- No monitor cable

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified

Physical Locks

Kensington® Security Slot, 3 x 7 mm

Chassis Intrusion Switch

Chassis intrusion switch

Fingerprint Reader

- Touch style fingerprint reader on mouse
- No fingerprint reader

BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Boot sequence control
- Boot without keyboard and mouse
- Certificate based BIOS management
- Cover presence switch
- Self-healing BIOS
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)
- Individual USB port disablement

MANAGEABILITY

System Management

System Management^[1]

- Intel vPro Essentials
- Non-vPro

Notes:

1. Intel vPro offers a superset of DASH's defined capabilities.

SERVICE

Warranty

Base Warranty**^[1]

- 1-year depot service
- 1-year limited onsite service
- 3-year limited onsite service
- No base warranty

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

CERTIFICATIONS

Green Certifications

Green Certifications

- (Optional) EPEAT™ Gold
- ENERGY STAR® 8.0
- ErP Lot 3 and Lot 7
- TCO Certified 9.0
- RoHS compliant

Other Certifications

Other Certifications

- (Optional) TÜV Rheinland® Low Noise
- (Optional) TÜV Rheinland Ultra Low Noise

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation)

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.






intel



intel



intel



intel



intel



intel