


OVERVIEW



1. Power button	8. HDMI
2. USB-C 3.2 Gen 1	9. USB 3.2 Gen 1
3. USB 3.2 Gen 2	10. Optional port 1 (VGA is shown)
4. Headphone / microphone combo jack (3.5mm)	11. 2x USB 2.0
5. Power connector	12. Optional port 2 (serial is shown)
6. DisplayPort	13. Ethernet (RJ-45)
7. USB 3.2 Gen 1	

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ 3 / 5 / 7 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD Athlon™ Silver 3050GE	2	4	3.4GHz	3.4GHz	1MB L2 / 4MB L3	DDR4-2666	AMD Radeon™ Graphics
AMD Athlon Silver PRO 3125GE	2	4	3.4GHz	3.4GHz	1MB L2 / 4MB L3	DDR4-2666	AMD Radeon Graphics
AMD Athlon Gold PRO 3150GE	4	4	3.3GHz	3.8GHz	2MB L2 / 4MB L3	DDR4-2933	AMD Radeon Graphics
AMD Ryzen 3 3200GE	4	4	3.3GHz	3.8GHz	2MB L2 / 4MB L3	DDR4-2933	AMD Radeon Vega 8 Graphics
AMD Ryzen 3 4300GE	4	8	3.5GHz	4.0GHz	2MB L2 / 4MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 3 5300GE	4	8	3.6GHz	4.2GHz	2MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 3 PRO 4350GE	4	8	3.5GHz	4.0GHz	2MB L2 / 4MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 3 PRO 5350GE	4	8	3.6GHz	4.2GHz	2MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 5 4600GE	6	12	3.3GHz	4.2GHz	3MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 5 5600GE	6	12	3.4GHz	4.4GHz	3MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 5 PRO 3350GE	4	8	3.3GHz	3.9GHz	2MB L2 / 4MB L3	DDR4-2933	AMD Radeon Vega 11 Graphics
AMD Ryzen 5 PRO 4650GE	6	12	3.3GHz	4.2GHz	3MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 5 PRO 5650GE	6	12	3.4GHz	4.4GHz	3MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 4700GE	8	16	3.1GHz	4.3GHz	4MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 5700GE	8	16	3.2GHz	4.6GHz	4MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 PRO 4750GE	8	16	3.1GHz	4.3GHz	4MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 PRO 5750GE	8	16	3.2GHz	4.6GHz	4MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics

Operating System

Operating System

- Windows® 10 Home 64
- Windows 10 Pro 64
- Windows 10 IoT Enterprise
- Ubuntu Linux
- No operating system

Graphics

Graphics^[1]

Graphics	Type	Memory	Connector	Max Resolution	Key Features
AMD Radeon Graphics	Integrated	Shared	-	-	DirectX® 12
AMD Radeon Vega 8 Graphics	Integrated	Shared	-	-	DirectX 12
AMD Radeon Vega 11 Graphics	Integrated	Shared	-	-	DirectX 12

Notes:

- The information of integrated graphics are not applicable for the models without integrated graphics (for the details, please refer to processor section)

Monitor Support

Monitor Support

Supports up to 3 independent displays via onboard ports (DisplayPort™ + HDMI® + 2x optional ports [VGA / 2nd DP / 2nd HDMI / USB-C / 2x DP])

Chipset

Chipset

AMD PRO 500 chipset

Memory

Max Memory^[1]

Up to 64GB DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Memory Type

DDR4-3200

Notes:

- The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 SSD up to 1TB

Storage Type

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-
2.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2242 SSD	PCIe NVMe, PCIe 3.0 x2	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	Opal

Removable Storage

Optical

- DVD-ROM, slim (9.0mm), via USB external ODD box
- DVD burner (DVD±RW), slim (9.0mm), via USB external ODD box
- None

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC222 codec

Speakers

Single speaker, 1.5W x1

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
65W	Adapter	89%	Autosensing
90W	Adapter	89%	Autosensing

DESIGN

Input Device

Keyboard

- Lenovo Calliope Keyboard (USB connector), black
- Lenovo Calliope Wireless Keyboard, black
- Lenovo Traditional Keyboard (USB connector), black

Mouse

- Lenovo Calliope Mouse (USB connector), black
- Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black
- Lenovo Fingerprint Mouse (USB connector), black

Mechanical

Form Factor

Tiny (1L)

Dimensions (WxDxH)

179 x 183 x 34.5 / 37 mm with rubber feet (7.05 x 7.2 x 1.36 / 1.5 inches with rubber feet)

Weight

1.25 kg (2.76 lbs)

Case Color

Black

Bays

1x 2.5" disk bay

Expansion Slots

- One M.2 slot (for WLAN)
- One M.2 slot (for SSD)

EOU

(Optional) toolless chassis open (toolless chassis screw required) and toolless M.2 SSD, HDD, memory assembly / removal

Stand

- Vertical stand
- No stand

Mounting

- VESA mount bracket kit, supports VESA mount 75mm and 100mm
- None

CONNECTIVITY

Network

Onboard Ethernet

- Gigabit Ethernet, Realtek RTL8111HN, 1x RJ45, supports Wake-on-LAN
- Gigabit Ethernet, Realtek RTL8111FP, 1x RJ45, supports DASH and Wake-on-LAN

WLAN + Bluetooth®

- Realtek RTL8852AE, Wi-Fi® 6, 802.11ax Dual Band 2x2 Wi-Fi + Bluetooth 5.2, M.2 card
- Realtek RTL8822CE, 802.11ac Dual Band 2x2 Wi-Fi + Bluetooth 5.0, M.2 card
- Intel® Wireless-AC 9260, 802.11ac Dual Band 2x2 Wi-Fi + Bluetooth 5.1, M.2 card

ThinkCentre M75q Gen 2

- Intel Wi-Fi 6 AX200, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1, M.2 card
- No WLAN and Bluetooth

Ports^[1]

Front Ports

- 1x USB 3.2 Gen 2 (Always On and fast charge)
- 1x USB-C 3.2 Gen 1
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports^[2]

- 2x USB 2.0
- 2x USB 3.2 Gen 1
- 1x HDMI
- 1x DisplayPort
- 1x Ethernet (RJ-45)

Optional Rear Ports

- 2x USB 3.2 Gen 1 (occupies port 1 and 2)
- 4x USB 3.2 Gen 1 ports (share one USB 3.2 Gen 1 bandwidth, occupy optional port 1 and 2)
- 2x DisplayPort (occupies port 1 and 2)
- Optional port 1 (one of VGA / 2nd DisplayPort / 2nd HDMI / serial / USB-C 3.2 Gen 1 with DisplayPort function)
- Optional port 2 (serial)
- 1x parallel

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s
2. For video ports on discrete graphics, please see graphics section

Monitor Cable

Monitor Cable

- VGA Cable Tiny
- DP to dual DP dongle
- DP to DVI-D dongle
- DP to HDMI 1.4 dongle
- DP to VGA cable (1.5M)
- DP to VGA dongle
- HDMI to HDMI cable (1.5m)
- HDMI to VGA dongle
- No monitor cable

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified

Physical Locks

Kensington® Security Slot

Chassis Intrusion Switch

Chassis intrusion switch

BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Boot sequence control

- Boot without keyboard and mouse
- Individual USB port disablement

MANAGEABILITY

System Management

System Management

- DASH 1.2
- No DASH

SERVICE

Warranty

Base Warranty

- 1-year limited onsite service
- 3-year limited onsite service
- No base warranty

ENVIRONMENTAL

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: -15.2 m (-50 ft) to 3048 m (10,000 ft)
- Storage: -15.2 m (-50 ft) to 12192 m (40,000 ft)

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Gold (on some models)
- EPEAT Silver (on some models)
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO
- RoHS compliant

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed




AMD




AMD



AMD



AMD



AMD



AMD