

OVERVIEW



1. Headphone / microphone combo jack (3.5mm)	6. Kensington Security Slot
2. SD card reader	7. Power connector
3. HDMI	8. USB 4
4. 2x USB 3.2 Gen 1	9. Smart card reader *
5. Ethernet (RJ-45)	

- Notes:
- Ports with * are only available on selected models
 - Nano-SIM card slot on the rear side (not shown on the sample product above)

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ 5 / 7 PRO 6000 H Series Processor, supports processors up to 8 cores; up to 4.7GHz; up to 45W TDP

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD Ryzen 7 PRO 6850H	8	16	3.2GHz	4.7GHz	4MB L2 / 16MB L3	DDR5-4800	AMD Radeon™ 680M Graphics
AMD Ryzen 5 PRO 6650H	6	12	3.3GHz	4.5GHz	3MB L2 / 16MB L3	DDR5-4800	AMD Radeon 660M Graphics

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 Home 64 Single Language
- Windows 11 DG Windows 10 Pro 64
- Ubuntu Linux LTS
- Red Hat Enterprise Linux 8.6 (certified only, available in late 2022, for detailed and latest information, please visit [Red Hat Certified Hardware](#))
- No operating system

Graphics

Graphics**

Graphics	Type	Memory	TGP	Key Features
NVIDIA® T600 Laptop GPU	Discrete	4GB GDDR6	35W	DirectX® 12
NVIDIA T1200 Laptop GPU	Discrete	4GB GDDR6	35W	DirectX 12
NVIDIA RTX A2000 Laptop GPU	Discrete	4GB GDDR6	35W	Dynamic Boost 2.0, DirectX 12

Monitor Support

Monitor Support

Supports up to 3 independent displays (native display and 2 external monitors via HDMI® and USB-C®)

- HDMI supports up to 5120x2880@30Hz
- USB-C supports up to 5120x2880@60Hz (USB-C to DP)

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 64GB DDR5-4800

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type

DDR5-4800 non-ECC

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

Up to two drives, 2x M.2 SSD

- M.2 2280 SSD up to 4TB, 2TB each

Storage Slot

Two M.2 2280 PCIe® 4.0 x4 slots

Storage Type

Disk Type	Interface	RPM	Offering	Security
M.2 2280 SSD	PCIe NVMe®, PCIe 4.0 x4 Performance	-	512GB / 1TB / 2TB	Opal2
M.2 2280 SSD	PCIe NVMe, PCIe 4.0 x4 Value	-	256GB / 512GB / 1TB	Opal2

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Card Reader

SD card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby® Audio™

Microphone

- Dual array microphone, far-field, Dolby Voice
- No microphone

Camera**

- HD 720p, with privacy shutter, fixed focus
- IR & HD 720p hybrid, with privacy shutter, fixed focus
- No camera

Battery

Battery

Integrated Li-Polymer 68Wh battery, supports Rapid Charge (charge up to 80% in 1hr)

Power Adapter

Power Adapter^[1]

- 135W slim tip (3-pin) AC adapter, 100-240V, 50-60Hz
- No power adapter

Notes:

1. AC adapter offerings depend on the country.

DESIGN

Display

Display**^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
15.6"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	800:1	45% NTSC	170°	DC dimming
15.6"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	1200:1	100% sRGB	170°	-

15.6"	UHD (3840x2160)	None	IPS	600 nits	Anti-glare	16:9	1400:1	100% Adobe® RGB	170°	Dolby Vision™, DisplayHDR™ 400, optional X-Rite® Pantone® Factory Color Calibration, DC dimming
-------	--------------------	------	-----	----------	------------	------	--------	-----------------	------	---

- Color Calibration**
- X-Rite Pantone factory color calibration (selected UHD display)
 - No color calibration

Touchscreen

Non-touch

Notes:

1. California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

- Keyboard**
- 6-row, spill-resistant, multimedia Fn keys with Unified Communications controls, numeric keypad
- Keyboard Backlight**
- LED backlight
- UltraNav™**
- 3-button TrackPoint® pointing device and Mylar® surface multi-touch touchpad

Mechanical^[1]

- Dimensions (WxDxH)**
- 366.5 x 250 x 22.7 mm (14.43 x 9.84 x 0.89 inches)
- Weight**
- Starting at 2.26 kg (4.98 lbs)
- Case Color**
- Black
- Case Material**
- PC-ABS (top), PC-ABS (bottom)

Notes:

1. The system dimensions and weight vary depending on configurations.

CONNECTIVITY

Network

- Ethernet**
- Gigabit Ethernet, Realtek RTL8111EPV, 1x RJ-45, supports Wake-on-LAN and AMD Pro Manageability
- WLAN + Bluetooth^[1]**
- Qualcomm® NFA-725A Wi-Fi® 6E, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1
- WWAN**
- No support
- SIM Card**
- No SIM card inbox
- NFC**
- No support

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB 4 40Gbps (support data transfer and DisplayPort™ 1.4)
- 1x HDMI, up to 4K/60Hz
- 1x SD card reader
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector
- 1x Security keyhole

Optional Ports

1x Smart card reader

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s

Docking

Docking

Various docking solutions supported via USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® P15v Gen 3 \(AMD\)](#)

Monitor Cable

Monitor Cable

- (Optional) Lenovo USB-C to DisplayPort Adapter
- (Optional) Lenovo HDMI to VGA Monitor Adapter
- (Optional) Lenovo USB-C to VGA Adapter

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, with Microsoft® Pluton TPM 2.0 integrated in SoC

Physical Locks

Kensington® Security Slot™, 3 x 7 mm

Smart Card Reader

- Smart card reader
- No smart card reader

Fingerprint Reader

Touch style fingerprint reader on palm rest, match-on-chip

BIOS Security

- Power-on password
- Supervisor password
- NVMe password
- Self-healing BIOS

Other Security

- (Optional) Camera privacy shutter
- (Optional) IR camera for Windows Hello

MANAGEABILITY

System Management

System Management

AMD Pro Manageability

SERVICE

Warranty

Base Warranty**^[1]

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 1-year limited onsite service
- 3-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) limited onsite service
- No base warranty

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping packaging: -20°C (-4°F) to 60°C (140°F)
- Storage without package: 5°C (41°F) to 43°C (109°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

CERTIFICATIONS

Green Certifications

Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- TCO Certified
- RoHS compliant

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

ISV Certifications

ISV Certifications

Please visit [ISV certifications for Lenovo Workstations](#)

- Feature with ** means that only one offering listed under the feature is configured on selected models.

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

