



# SAFETY DATA SHEET

## 1. Product and Company Identification

**Product identifier** HP LaserJet CC364A-X-XC-XD Print Cartridge  
**Issue date** 10-Jul-2013  
**Revision date** 21-Sep-2015  
**Version #** 03  
**Product use** This product is a toner preparation that is used in HP LaserJet P4014 / P4015 / P4515 series printers.  
**Company identification** HP Canada Co.  
5150 Spectrum Way, Floor 6  
Mississauga, Ontario, Canada L4W 5G1  
Telephone 1-905-206-4725  
or 1-888-447-4636  
  
HP health effects line  
(Toll-free within the US) 1-800-457-4209  
(Direct) 1-760-710-0048  
HP Customer Care Line  
(Toll-free within the US) 1-800-474-6836  
(Direct) 1-208-323-2551  
Email: hpcustomer.inquiries@hp.com

## 2. Hazards Identification

**Physical hazards** Not classified.  
**Health hazards** Not classified.  
**Environmental hazards** Not classified.  
**OSHA defined hazards** Not classified.  
**Label elements**  
**Hazard symbol** None.  
**Signal word** None.  
**Hazard statement** Not available.  
**Precautionary statement**  
**Prevention** Not available.  
**Response** Not available.  
**Storage** Not available.  
**Disposal** Not available.  
**Other hazards** None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

## 3. Composition / Information on Ingredients

Non-hazardous components	CAS #	Percent
Polyester resin	Trade Secret	<55
Iron oxide	1317-61-9	<50
Silica, Amorphous, Fumed	7631-86-9	<2

## 4. First Aid Measures

**First aid procedures**  
**Eye contact** Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.  
**Skin contact** Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.  
**Inhalation** Move person to fresh air immediately. If irritation persists, consult a physician.  
**Ingestion** Rinse mouth with water. Drink one to two glasses of water. If symptoms occur, consult a physician.

---

## 5. Fire Fighting Measures

<b>Flash point</b>	Not applicable
<b>Flammable properties</b>	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.
<b>Extinguishing media</b>	
<b>Suitable extinguishing media</b>	CO <sub>2</sub> , water, or dry chemical
<b>Unsuitable extinguishing media</b>	None known.
<b>Fire fighting equipment/instructions</b>	If fire occurs in the printer, treat as an electrical fire.
<b>Specific methods</b>	None established.
<b>Explosion data</b>	
<b>Sensitivity to static discharge</b>	Not available.
<b>Sensitivity to mechanical impact</b>	Not available.
<b>Hazardous combustion products</b>	Carbon monoxide and carbon dioxide.

---

## 6. Accidental Release Measures

<b>Personal precautions</b>	Minimize dust generation and accumulation.
<b>Environmental precautions</b>	Do not flush into surface water or sanitary sewer system. See also section 13 Disposal considerations.
<b>Methods for cleaning up</b>	Not available.
<b>Other information</b>	Slowly vacuum or sweep the material into a bag or other sealed container. If a vacuum is used, the motor must be rated as dust explosion-proof. Clean remainder with a damp cloth or vacuum cleaner. Fine powder can form explosive dust-air mixtures. Dispose of in compliance with federal, state, and local regulations.

---

## 7. Handling and Storage

<b>Handling</b>	Keep out of the reach of children. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation. Keep away from excessive heat, sparks, and open flames.
<b>Storage</b>	Keep out of the reach of children. Keep tightly closed and dry. Store at room temperature. Store away from strong oxidizers.

---

## 8. Exposure Controls / Personal Protection

<b>Occupational exposure limits</b>	No exposure limits noted for ingredient(s).
<b>Biological limit values</b>	No biological exposure limits noted for the ingredient(s).
<b>Personal protective equipment</b>	
<b>General</b>	No personal respiratory protective equipment required under normal conditions of use.
<b>Exposure guidelines</b>	USA OSHA (TWA/PEL): 15 mg/m <sup>3</sup> (Total Dust), 5 mg/m <sup>3</sup> (Respirable Fraction)  ACGIH (TWA/TLV): 10 mg/m <sup>3</sup> (Inhalable Particulate), 3 mg/m <sup>3</sup> (Respirable Particulate)  Amorphous silica: USA OSHA (TWA/PEL): 20 mppcf 80 (mg/m <sup>3</sup> )/%SiO <sub>2</sub> , ACGIH (TWA/TLV): 10 mg/m <sup>3</sup>
<b>Engineering controls</b>	Use in a well ventilated area.
<b>Personal protective equipment</b>	
<b>Eye/face protection</b>	Not available.
<b>Skin protection</b>	Not available.
<b>Respiratory protection</b>	Not available.

---

## 9. Physical & Chemical Properties

<b>Appearance</b>	Fine powder
<b>Physical state</b>	Solid.
<b>Color</b>	Black.
<b>Odor</b>	Slight plastic odor
<b>Odor threshold</b>	Not available.

<b>pH</b>	Not applicable
<b>Vapor pressure</b>	Not applicable
<b>Boiling point</b>	Not applicable
<b>Melting point/Freezing point</b>	Not available.
<b>Solubility (water)</b>	Negligible in water. Partially soluble in toluene and xylene.
<b>Specific gravity</b>	1.4 - 1.8
<b>Flash point</b>	Not applicable
<b>Flammability limits in air, upper, % by volume</b>	Not available.
<b>Flammability limits in air, lower, % by volume</b>	Not flammable
<b>Auto-ignition temperature</b>	No data available
<b>VOC</b>	Not applicable
<b>Evaporation rate</b>	Not available.
<b>Viscosity</b>	Not applicable
<b>Percent volatile</b>	Negligible
<b>Partition coefficient (n-octanol/water)</b>	Not available.
<b>Softening point</b>	212 - 302 °F (100 - 150 °C)
<b>Other data</b>	
<b>Decomposition temperature</b>	> 392 °F (> 200 °C)
<b>Oxidizing properties</b>	No information available.

---

## 10. Chemical Stability & Reactivity Information

<b>Chemical stability</b>	Stable under normal storage conditions.
<b>Conditions to avoid</b>	Imaging Drum: Exposure to light
<b>Incompatible materials</b>	Strong oxidizers
<b>Hazardous decomposition products</b>	Carbon monoxide and carbon dioxide.
<b>Possibility of hazardous reactions</b>	Will not occur.

---

## 11. Toxicological Information

<b>Acute effects</b>	Based on available data, the classification criteria are not met.
<b>Skin irritation and corrosion</b>	Based on available data, the classification criteria are not met.
<b>Serious eye damage/eye irritation</b>	Based on available data, the classification criteria are not met.
<b>Respiratory or skin sensitization</b>	
<b>Skin sensitization</b>	Based on available data, the classification criteria are not met.
<b>Respiratory sensitization</b>	Based on available data, the classification criteria are not met.
<b>Carcinogenicity</b>	Based on available data, the classification criteria are not met.
<b>Germ cell mutagenicity</b>	Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium) Based on available data, the classification criteria are not met.
<b>Reproductive toxicity</b>	Based on available data, the classification criteria are not met.
<b>Specific target organ toxicity - single exposure</b>	Based on available data, the classification criteria are not met.
<b>Specific target organ toxicity - repeated exposure</b>	Based on available data, the classification criteria are not met.
<b>Aspiration hazard</b>	Based on available data, the classification criteria are not met.
<b>Further information</b>	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.

## Toxicological data

Components	Species	Test Results
Silica, Amorphous, Fumed (CAS 7631-86-9)		
<b>Acute</b>		
<i>Oral</i>		
LD50	Mouse	> 15000 mg/kg
	Rat	> 22500 mg/kg

## 12. Ecological Information

**Ecotoxicity** LL50: > 1000 mg/l, Rainbow Trout, 96.00 Hours

**Environmental effects** Not available.

**Persistence and degradability** Not available.

### Ecotoxicological data

Product	Species	Test Results
CC364A-X-XC-XD		
<b>Aquatic</b>		
Fish	LL50 Rainbow Trout	> 1000 mg/l, 96 Hours

## 13. Disposal Considerations

**Disposal instructions** Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Finely dispersed particles may form explosive mixtures in air. Dispose of in compliance with federal, state, and local regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

## 14. Transport Information

### DOT

Not regulated as dangerous goods.

### IATA

**UN number** UN2807  
**UN proper shipping name** Magnetized Material  
**Transport hazard class(es)**  
**Class** Not available.  
**Subsidiary risk** -  
**Packing group** Not applicable.  
**Environmental hazards** No.  
**Special precautions for user** Not available.

### IMDG

Not regulated as dangerous goods.

### ADR

Not regulated as dangerous goods.

**Further information** 22 or more of these cartridges shipped together in a single package (e.g., box, container), by air, are regulated as a magnetized material. These requirements do not apply to single or dual pack cartridges contained in an original HP package and shrink wrapped on a pallet for shipment by air.

## 15. Regulatory Information

**Other regulations** All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

## 16. Other Information

**HMIS® ratings** Health: 1  
Flammability: 1  
Physical hazard: 0

**NFPA ratings** Health: 1  
Flammability: 1  
Instability: 0

**Disclaimer**

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

**Prepared by**

HP

**Issue date**

10-Jul-2013

**Revision date**

21-Sep-2015

**Version #**

03

**This data sheet contains changes from the previous version in section(s):**

16. Other Information: Disclaimer

**Manufacturer information**

HP  
11311 Chinden Boulevard  
Boise, ID 83714 USA  
(Direct) 1-503-494-7199  
(Toll-free within the US) 1-800-457-4209

**Explanation of abbreviations**

<b>ACGIH</b>	American Conference of Governmental Industrial Hygienists
<b>CAS</b>	Chemical Abstracts Service
<b>CERCLA</b>	Comprehensive Environmental Response Compensation and Liability Act
<b>CFR</b>	Code of Federal Regulations
<b>COC</b>	Cleveland Open Cup
<b>DOT</b>	Department of Transportation
<b>EPCRA</b>	Emergency Planning and Community Right-to-Know Act (aka SARA)
<b>IARC</b>	International Agency for Research on Cancer
<b>NIOSH</b>	National Institute for Occupational Safety and Health
<b>NTP</b>	National Toxicology Program
<b>OSHA</b>	Occupational Safety and Health Administration
<b>PEL</b>	Permissible Exposure Limit
<b>RCRA</b>	Resource Conservation and Recovery Act
<b>REC</b>	Recommended
<b>REL</b>	Recommended Exposure Limit
<b>SARA</b>	Superfund Amendments and Reauthorization Act of 1986
<b>STEL</b>	Short-Term Exposure Limit
<b>TCLP</b>	Toxicity Characteristics Leaching Procedure
<b>TLV</b>	Threshold Limit Value
<b>TSCA</b>	Toxic Substances Control Act
<b>VOC</b>	Volatile Organic Compounds