

IdeaPad Slim 3i (14" | 15" | 16")

The smarter choice for mobility.

Impossibly slim, the Lenovo IdeaPad Slim 3i is amazingly dynamic. Crafted to fit in your fast-paced life, the robust laptop takes your work and play to places never imagined before. Available in three portable sizes, it packs speedy efficiency up to the latest Intel® Core™ 7 U-Series processors and exceptional audiovisuals on an expansive narrow-bezel display. Combined with an array of AI-driven productivity features, you've got the full works right in your hands.



Next stop: Everywhere

Move at the speed of light with the amazingly portable device that comes in three convenient sizes of 14", 15", and 16". No matter the footprint you choose, it carries from 1.37 kg so you jump from classroom to café effortlessly. Slip it into your bag and you'll hardly notice the weight as you move through your day. With two shades to choose from, show off your style in sleek Arctic Grey or cool Abyss Blue.



Your senses unleashed

Be captivated by every sight and sound on the stunning up-to-FHD IPS display coupled with front-firing speakers. With minimal bezels framing all around, say goodbye to distractions and welcome full immersion on the expansive screen of up to 88% active area ratio. Want a taller frame to fit in all your content? The 16" device offer a taller 16:10 aspect ratio for that. The stereo system is optimized by Dolby Audio® to deliver full-range, ultra-wide acoustics that fills any room. Whatever content you're focusing on, TÜV Low Blue Light (sw) makes sure your eyes stay comfortable even after a long while.



Nothing gets in its way

Rise to every challenge with up to the latest Intel® Core™ 7 U-Series processors. Tackle resource-hungry group projects, sprint through massive lecture notes, or just crush everyday tasks with blazing speed and efficiency. With ample storage of up to 1 TB storage, store your entire digital world and take it with you anywhere. And thanks to a memory of up to 16 GB, your go-to apps launch in the blink of an eye and your workflow runs uninterrupted smooth.



Does all the right things

The IdeaPad Slim 3i doesn't just move you to the right places, it does the right things to keep you productive always. Say goodbye to passwords with the optional fingerprint sensor - you can access the device securely and seamlessly with just a touch on the power button. Keep your life safe from prying eyes on up-to-FHD camera with a built-in privacy shutter. Stay powered up with Rapid Charge Boost, which gets the battery up and running in minutes. Need to make a connection? The USB Type-C™ port lets you expand your workspace or transfer data with ease.

IdeaPad Slim 3i (14" | 15" | 16")

SPECIFICATIONS

IdeaPad Slim 3 14IRU9 | IdeaPad Slim 3 15IRU9 | IdeaPad Slim 3 16IRU9*

PERFORMANCE

Processor

Intel® Core™ 7 150U
Intel® Core™ 5 120U
Intel® Core™ 3 100U

Operating System

Windows 11 Home

Graphics

UMA : Intel® Graphics

Memory

DDR5 : 8 GB / 16 GB

Storage

PCIe M.2 : 256 GB¹ / 512 GB / 1 TB

Camera & Microphone

HD/FHD Camera | Privacy Shutter |
Dual Microphone Array

Audio

2 x 1.5W User-facing Speakers, Dolby Audio®

Battery¹

47Whr Polymer

Rapid Charge Boost : 15 min. @ 2 Hours

14"

MobileMark® 2025 : Up to 7.5 Hours

1080p Video Playback : Up to 13 Hours

15"

MobileMark® 2025 : Up to 7.5 Hours

1080p Video Playback : Up to 13 Hours

16"

MobileMark® 2025 : Up to 7.5 Hours

1080p Video Playback : Up to 12.5 Hours



With Lenovo AI Engine

LENOVO SERVICES

Lenovo Premium Care Plus

Lenovo Premium Care Plus is the ultimate PC support experience with you as our priority 24/7. Enjoy personalized hardware and software support from a global network of elite technicians, along with accidental damage protection, fast repairs with onsite support, extended battery warranty, data migration assistance, and smart performance solutions that optimize PC performance and security.

Lenovo Smart Performance

Smart Performance Services within Lenovo Vantage will keep your system running at optimum performance and proactively fix issues that affect PC performance, internet performance, remove malware, and improve device security.

Lenovo Accidental Damage Protection

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your PCs and ensures your device is up and running fast.

Lenovo CO₂ Offset Services*

Offset the carbon emissions of your PC with Lenovo CO₂ Offset Services - an easy and transparent solution to offset emissions across the average lifecycle of your device. These offsets are invested in UN-approved initiatives like renewable energy or ecological projects, thus contributing towards a more sustainable future.

Lenovo Sealed Battery Warranty


Long-lasting battery life is not just a feature but a necessity to help you stay productive and connected all day long. Protect your PC's sealed battery from degradation, enjoy hassle-free battery replacement service, and safeguard your PC from future battery failure with our Sealed Battery Warranty Service.

Lenovo Warranty Extensions (Up to 3 Years Duration)

Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

* Optional.

*Example of Lenovo marketing naming convention



Intel® platform codes

Gemini Lake: IGM, Whiskey Lake: IWL, Ice Lake: IIL, Gemini Lake: IGL, Comet Lake: IML, Tiger Lake: ITL, Alder Lake: IAP, Alder Lake-HX: IAX, Alder Lake-U15: IAU, Alder Lake-P28: IAP, Alder Lake-P28/U15: IAL, Alder Lake-H45: IAH, Alder Lake-N: IAN, Raptor Lake-PX: IRP, Raptor Lake-H: IRH, Raptor Lake-HX: IRX, Alder Lake-N U9: IAM, Raptor Lake-U: IRU, Meteor Lake-P: IMP, Raptor Lake-P: IRP, Raptor Lake-P28/U15: IRL, Raptor Lake-B: IRB, Raptor Lake-B: IRZ, Meteor Lake-H: IMH.

WWW.LENOVO.COM

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, IdeaCentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Visit www.lenovo.com/lenovo/us/en/safecom/ periodically for the latest information on safe and effective computing. ©2024 Lenovo. All rights reserved.



Lenovo

DESIGN

Display

16"

16" WUXGA (1920 x 1200) IPS, 16:10, 300 nits, 45% NTSC, TÜV Low Blue Light (Software Solution) Certification

15"

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits, 45% NTSC, TÜV Low Blue Light (Software Solution) Certification, Touch

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits, 45% NTSC, TÜV Low Blue Light (Software Solution) Certification

15.6" FHD (1920 x 1080) TN, 16:9, 250 nits, 45% NTSC, TÜV Low Blue Light (Software Solution) Certification

14"

14" FHD (1920 x 1080) IPS, 16:9, 300 nits, 45% NTSC, TÜV Low Blue Light (Software Solution) Certification

14" FHD (1920 x 1080) TN, 16:9, 250 nits, 45% NTSC, TÜV Low Blue Light (Software Solution) Certification

Dimension (W x D x H)

16"

(mm) : 359.3 x 257 x as thin as 17.9

(inches) : 14.15" x 10.12" x as thin as 0.70"

15"

(mm) : 359.3 x 235 x as thin as 17.9

(inches) : 14.15" x 9.25" x as thin as 0.70"

14"

(mm) : 324.3 x 213.8 x as thin as 17.9

(inches) : 12.77" x 8.42" x as thin as 0.70"

Weight

16" : Starting at 1.74 kg (3.84 lbs)

15" : Starting at 1.62 kg (3.57 lbs)

14" : Starting at 1.37 kg (3.02 lbs)

Colors

Arctic Grey

Abyss Blue

CONNECTIVITY

WLAN

WiFi 6

Bluetooth®

Up to Bluetooth® 5.2

Input/Output (I/O) Ports

Left

1 x USB 3.2 Gen 1² Type-C™ (Full-function)

1 x USB 3.2 Gen 1² Type-A

1 x HDMI™ 1.4

1 x Audio Jack

1 x DC-In

Right

1 x USB 3.2 Gen 1² Type-A

1 x SD Card Reader

PRELOADED SOFTWARE

- Windows 11 Home/Pro
- Lenovo Vantage
- Microsoft 365 Trial
- McAfee® LiveSafe™

GREEN CERTIFICATIONS

- ENERGY STAR® 8.0
- EPEAT™ Silver Registered in the US
- MIL-STD-810H Military Test Passed

¹ All battery life claims are approximate and based on two methods of testing: MobileMark® 2025 battery life benchmark and continuous 1080p video playback on the latest update of Windows 10 (with 150 nits brightness and default volume level). Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

² The actual transfer speed of the USB 3.2 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 20 Gbit/s.

OPTIONS & ACCESSORIES



Lenovo 530 Wireless Mouse



Lenovo 15.6" Laptop Urban Backpack B530



Lenovo 110 USB Stereo Headset

McAfee® LiveSafe™

Register McAfee® to enjoy these benefits in your FREE 30-day trial.

- Award-winning Antivirus
- Password Manager
- Safe Web Browsing
- Multi-device Compatibility
- Identity Theft Protection
- Free Customer Support