



SAFETY DATA SHEET

1. Identification

Product identifier	HP Color LaserJet CC530A-AC-AD-L Black Print Cartridge
Other means of identification	Not available.
Recommended use	This product is a black toner preparation that is used in HP Color LaserJet CP2025 and CM2320 series printers.
Recommended restrictions	None known.
Company identification	Hewlett-Packard Company 3000 Hanover Street Palo Alto, CA 94304-1185 United States Telephone 650-857-5020 Hewlett-Packard health effects line (Toll-free within the US) 1-800-457-4209 (Direct) 1-760-710-0048 HP Customer Care Line (Toll-free within the US) 1-800-474-6836 (Direct) 1-208-323-2551 Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards	Not classified.	
Health hazards	Carcinogenicity	Category 2
	Specific target organ toxicity, repeated exposure	Category 1 (lung)
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	
Label elements		
Hazard symbol	None.	
Signal word	None.	
Hazard statement	Not available.	
Precautionary statement		
Prevention	Not available.	
Response	Not available.	
Storage	Not available.	
Disposal	Not available.	
Hazard(s) not otherwise classified (HNOC)	Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. This product is not classified as hazardous according to OSHA CFR 1910.1200 or EU Directive 1999/45/EC, as amended.	
Supplemental information	None.	

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Styrene acrylate copolymer		Trade Secret	<85
Wax	Wax	Trade Secret	<10
Carbon black		1333-86-4	<6
Amorphous silica	Amorphous silica	7631-86-9	<2

4. First-aid measures

Inhalation	Move person to fresh air immediately. If irritation persists, consult a physician.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.
Ingestion	Rinse mouth out with water. Drink one to two glasses of water. If symptoms occur, consult a physician.
Most important symptoms/effects, acute and delayed	Not available.

5. Fire-fighting measures

Suitable extinguishing media	CO2, water, or dry chemical
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Not applicable.
Special protective equipment and precautions for firefighters	Not available.
Fire-fighting equipment/instructions	If fire occurs in the printer, treat as an electrical fire.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Minimize dust generation and accumulation.
Methods and materials for containment and cleaning up	Not available.
Environmental precautions	Do not flush into surface water or sanitary sewer system. See also section 13 Disposal considerations.

7. Handling and storage

Precautions for safe handling	Keep out of the reach of children. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation. Keep away from excessive heat, sparks, and open flames.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Keep tightly closed and dry. Store away from strong oxidizers. Store at room temperature.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Carbon black (CAS 1333-86-4)	PEL	3.5 mg/m3

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Carbon black (CAS 1333-86-4)	TWA	3 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Amorphous silica (CAS 7631-86-9)	TWA	6 mg/m3
Carbon black (CAS 1333-86-4)	TWA	0.1 mg/m3

Biological limit values	No biological exposure limits noted for the ingredient(s).
Exposure guidelines	USA OSHA (TWA/PEL): 15 mg/m ³ (Total Dust), 5 mg/m ³ (Respirable Fraction) ACGIH (TWA/TLV): 10 mg/m ³ (Inhalable Particulate), 3 mg/m ³ (Respirable Particulate) Amorphous silica: USA OSHA (TWA/PEL): 20 mppcf 80 (mg/m ³)/%SiO ₂ , ACGIH (TWA/TLV): 10 mg/m ³ TRGS 900 (Luftgrenzwert) - 10 mg/m ³ (Einatembare partikel), 3 mg/m ³ (Alveolengängige fraktion), UK WEL: 10 mg/m ³ (Respirable Dust), 5 mg/m ³ (Inhalable Dust)

Appropriate engineering controls Use in a well ventilated area.

Individual protection measures, such as personal protective equipment

Eye/face protection	Not available.
Skin protection	
Hand protection	Not available.
Other	Not available.
Respiratory protection	Not available.
Thermal hazards	Not available.

9. Physical and chemical properties

Appearance	Fine powder
Physical state	Solid.
Color	Black.
Odor	Slight plastic odor
Odor threshold	Not available.
pH	Not applicable
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not applicable
Flash point	Not applicable
Evaporation rate	Not applicable
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not flammable
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not applicable
Solubility(ies)	
Solubility (water)	Negligible in water. Partially soluble in toluene and xylene.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not applicable
Decomposition temperature	>= 392 °F (>= 200 °C)
Viscosity	Not applicable
Other information	
Percent volatile	0 % estimated
Softening point	176 - 266 °F (80 - 130 °C)

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under normal storage conditions.
Possibility of hazardous reactions	Will not occur.
Conditions to avoid	Imaging Drum: Exposure to light
Incompatible materials	Strong oxidizers
Hazardous decomposition products	Carbon monoxide and carbon dioxide.

11. Toxicological information

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects**Acute toxicity**

Skin corrosion/irritation Not available.

Serious eye damage/eye irritation Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC and as amended.

Respiratory or skin sensitization

Respiratory sensitization Not available.

Skin sensitization Not classified as irritant, according to OSHA Hazard Communication Standard (HCS) and EU Directive 67/548/EEC and as amended.

Germ cell mutagenicity Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium)

Carcinogenicity Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint. Carbon black is present only in a bound form in this preparation. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

Carbon black (CAS 1333-86-4)

2B Possibly carcinogenic to humans.

Reproductive toxicity Not classified as toxic according to EU Directive 67/548/EEC and as amended, California Prop. 65, and DFG (Germany).

Specific target organ toxicity - single exposure Not available.

Specific target organ toxicity - repeated exposure Not available.

Aspiration hazard Not available.

Chronic effects No information available.

Further information Complete toxicity data are not available for this specific formulation
Refer to Section 2 for potential health effects and Section 4 for first aid measures.

Components	Species	Test Results
Amorphous silica (CAS 7631-86-9)		
Acute		
<i>Oral</i>		
LD50	Mouse	> 15000 mg/kg
	Rat	> 22500 mg/kg
Carbon black (CAS 1333-86-4)		
Acute		
<i>Oral</i>		
LD50	Rat	> 8000 mg/kg

12. Ecological information

Ecotoxicity LL50: > 1000 mg/l, Fish, 96.00 Hours

Product	Species	Test Results
CC530A-AC-AD-L		
Aquatic		
Fish	LL50 Fish	> 1000 mg/l, 96 Hours

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Mobility in soil Not available.

Other adverse effects This product has not been tested for ecological effects.

13. Disposal considerations

Disposal instructions Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Finely dispersed particles may form explosive mixtures in air. Dispose of in compliance with federal, state, and local regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
Delayed Hazard - Yes
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

Other federal regulations

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. Massachusetts RTK - Substance List

Carbon black (CAS 1333-86-4)

US. New Jersey Worker and Community Right-to-Know Act

Carbon black (CAS 1333-86-4)

US. Pennsylvania Worker and Community Right-to-Know Law

Carbon black (CAS 1333-86-4)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65**US - California Proposition 65 - CRT: Listed date/Carcinogenic substance**

CARBON BLACK (AIRBORNE, UNBOUND PARTICLES Listed: February 21, 2003
 OF RESPIRABLE SIZE [\leq 10 MICROMETERS]) (CAS
 1333-86-4)

Regulatory information

All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision**Issue date**

13-Mar-2015

Version #

01

Disclaimer

This Safety Data Sheet document is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Revision Information

1. Product and Company Identification: Product and Company Identification
 Composition / Information on Ingredients: Ingredients
 Physical & Chemical Properties: Multiple Properties
 Ecological Information: Ecotoxicity
 Transport Information: Agency Name, Packaging Type, and Transport Mode Selection

Manufacturer information

Hewlett-Packard Company
 11311 Chinden Boulevard
 Boise, ID 83714 USA
 (Direct) 1-503-494-7199
 (Toll-free within the US) 1-800-457-4209

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds