

# **SAFETY DATA SHEET**

### **1. Product and Company Identification**

•	-		
Product identifier	HP LaserJet Q2612A-AC-AD-AF-L Print Cartridge		
Issue date	25-Jun-2015		
Revision date	22-Sep-2015		
Version #	02		
Product use	This product is a toner preparation that is used in HP LaserJet M1005mfp/1010/1012/1015/1018/1020/1020 plus/1022/M1319fmfp/3015/3020/3030/3050/3050Z/3052/3055 series printers.		
Company identification	HP Canada Co. 5150 Spectrum Way, Floor 6 Mississauga, Ontario, Canada L4W 5G1 Telephone 1-905-206-4725 or 1-888-447-4636		
	HP health effects line (Toll-free within the US) 1-800-457-4209 (Direct) 1-760-710-0048 HP Customer Care Line (Toll-free within the US) 1-800-474-6836 (Direct) 1-208-323-2551 Email: hpcustomer.inquiries@hp.com		

### 2. Hazards Identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	Not available.
Precautionary statement	
Prevention	Not available.
Response	Not available.
Storage	Not available.
Disposal	Not available.
Other hazards	None of the ingredients have been classified as carcinogens according to EU, IARC, MAK, NTP, OSHA or ACGIH.

### 3. Composition / Information on Ingredients

#### Non-hazardous components

	Percent
Trade Secret	<55
1317-61-9	<50
7631-86-9	<3
	1317-61-9

### 4. First Aid Measures

First aid procedures	
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Inhalation	Move person to fresh air immediately. If irritation persists, consult a physician.
Ingestion	Rinse mouth with water. Drink one to two glasses of water. If symptoms occur, consult a physician.

### 5. Fire Fighting Measures

Flash point	Not applicable		
Flammable properties	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.		
Extinguishing media			
Suitable extinguishing media	CO2, water, or dry chemical		
Unsuitable extinguishing media	None known.		
Fire fighting equipment/instructions	If fire occurs in the printer, treat as an electrical fire.		
Specific methods	None established.		
Explosion data			
Sensitivity to static discharge	Not available.		
Sensitivity to mechanical impact	Not available.		
Hazardous combustion products	Carbon monoxide and carbon dioxide.		
6. Accidental Release Me	easures		
Personal precautions	Minimize dust generation and accumulation.		
Environmental precautions	Do not flush into surface water or sanitary sewer system. See also section 13 Disposal considerations.		
Methods for cleaning up	Not available.		
Other information	Slowly vacuum or sweep the material into a bag or other sealed container. If a vacuum is used, the		

ous for cleaning up	Not available.
<sup>r</sup> information	Slowly vacuum or sweep the material into a bag or other sealed container. If a vacuum is used, the motor must be rated as dust explosion-proof. Clean remainder with a damp cloth or vacuum cleaner. Fine powder can form explosive dust-air mixtures. Dispose of in compliance with federal, state, and local regulations.

# 7. Handling and Storage

Handling	Keep out of the reach of children. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation. Keep away from excessive heat, sparks, and open flames.
Storage	Keep out of the reach of children. Keep tightly closed and dry. Store at room temperature. Store away from strong oxidizers.

## 8. Exposure Controls / Personal Protection

Occupational exposure limits Biological limit values	No exposure limits noted for ingredient(s). No biological exposure limits noted for the ingredient(s).		
Personal protective equipment General Exposure guidelines	t No personal respiratory protective equipment required under normal conditions of use. USA OSHA (TWA/PEL): 15 mg/m3 (Total Dust), 5 mg/m3 (Respirable Fraction)		
	ACGIH (TWA/TLV): 10 mg/m3 (Inhalable Particulate), 3 mg/m3 (Respirable Particulate)		
	Amorphous silica: USA OSHA (TWA/PEL): 20 mppcf 80 (mg/m3)/%SiO2, ACGIH (TWA/TLV): 10 mg/m3		
Engineering controls	Use in a well ventilated area.		
Personal protective equipment			
Eye/face protection	Not available.		
Skin protection	Not available.		
Respiratory protection	Not available.		

## 9. Physical & Chemical Properties

Appearance	Fine powder
Physical state	Solid.
Color	Black.
Odor	Slight plastic odor
Odor threshold	Not available.

рН	Not applicable
Vapor pressure	Not applicable
Boiling point	Not applicable
Melting point/Freezing point	Not available.
Solubility (water)	Negligible in water. Partially soluble in toluene and xylene.
Specific gravity	1.4 - 1.8
Flash point	Not applicable
Flammability limits in air, upper, % by volume	Not available.
Flammability limits in air, lower, % by volume	Not flammable
Auto-ignition temperature	Not applicable
Evaporation rate	Not available.
Viscosity	Not applicable
Percent volatile	0 % estimated
Partition coefficient (n-octanol/water)	Not available.
Softening point	212 - 302 °F (100 - 150 °C)
Other data	
Decomposition temperature	> 392 °F (> 200 °C)
Oxidizing properties	No information available.

## 10. Chemical Stability & Reactivity Information

Chemical stability	Stable under normal storage conditions.
Conditions to avoid	Imaging Drum: Exposure to light
Incompatible materials	Strong oxidizers
Hazardous decomposition products	Carbon monoxide and carbon dioxide.
Possibility of hazardous reactions	Will not occur.

## **11.** Toxicological Information

Acute effects	Based on available dat	a, the classification criteria are	e not met.
Skin irritation and corrosion	Based on available dat	a, the classification criteria are	e not met.
Serious eye damage/eye irritation	Based on available dat	a, the classification criteria are	not met.
Respiratory or skin sensitization	on		
Skin sensitization	Based on available dat	a, the classification criteria are	not met.
<b>Respiratory sensitization</b>	Based on available dat	a, the classification criteria are	e not met.
Carcinogenicity	Based on available data, the classification criteria are not met.		
Germ cell mutagenicity	5 .	icate mutagenic potential (Ama a, the classification criteria are	es Test: Salmonella typhimurium) e not met.
Reproductive toxicity	Based on available dat	a, the classification criteria are	e not met.
Specific target organ toxicity - single exposure	Based on available dat	a, the classification criteria are	not met.
Specific target organ toxicity - repeated exposure	Based on available dat	a, the classification criteria are	not met.
Aspiration hazard	Based on available data, the classification criteria are not met.		
Further information	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.		
Toxicological data			
Components	Species		Test Results
Silica, Amorphous, Fumed (CAS 76	31-86-9)		
Acute			
Oral			
LD50	Mouse		> 15000 mg/kg

Components	Species		Test Results
	Rat		> 22500 mg/kg
12. Ecological Information	on		
Environmental effects	Not available.		
Persistence and degradability	Not available.		
Ecotoxicological data			
Product		Species	Test Results
Q2612A-AC-AD-AF-L			
Aquatic		<b>.</b>	
Fish	LL50	Rainbow Trout	> 1000 mg/l, 96 Hours
13. Disposal Consideration	ons		
Disposal instructions		icles may form explosive	st-explosion prevention measures are taken. Finely mixtures in air. Dispose of in compliance with federal, state,
	HP original ink	jet and LaserJet supplies	es recycling program enables simple, convenient recycling o . For more information and to determine if this service is ttp://www.hp.com/recycle.
14. Transport Information	on		
DOT			
Not regulated as dangerous g	oods.		
IATA			
UN number UN proper shipping name Transport hazard class(es)	UN2807 Magnetized Ma	aterial	
Class Subsidiary risk	Not available. -		
Packing group	Not applicable		
Environmental hazards Special precautions for user IMDG	No. Not available.		
Not regulated as dangerous g	oods.		
ADR			
Not regulated as dangerous goods	1_		
Further information	168 or more o are regulated	as a magnetized material	d together in a single package (e.g., box, container), by air, . These requirements do not apply to single or dual pack package and shrink wrapped on a pallet for shipment by air.
15. Regulatory Informat	ion		
Other regulations	chemical subst	tances notification laws in	uct have been notified or are exempt from notification under in the following countries: US (TSCA), EU (EINECS/ELINCS), ralia, Japan, Philippines, South Korea, New Zealand, and
16. Other Information			
HMIS® ratings	Health: 1 Flammability: Physical hazar		
NFPA ratings	Health: 1 Flammability: Instability: 0	1	
Disclaimer	current known should not be suitability for a	to HP at the time of pre construed as guaranteeir a particular application. T	by by over the product of the products of HP. Data is the most paration of this document and is believed to be accurate. It has specific properties of the products as described or his document was prepared to the requirements of the e and may not meet regulatory requirements in other

Prepared by	HP
Issue date	25-Jun-2015
Revision date	22-Sep-2015
Version #	02
This data sheet contains changes from the previous version in section(s):	16. Other Information: Disclaimer
Manufacturer information	HP 11311 Chinden Boulevard Boise, ID 83714 USA (Direct) 1-503-494-7199 (Toll-free within the US) 1-800-457-4209

#### **Explanation of abbreviations**

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds