



Twinkle® Stainless Steel Cleaner & Polish

Revision: 2020-10-05

Version: 04.0

1. IDENTIFICATION

Product name: Twinkle®
Stainless Steel Cleaner & Polish

Product Code: 991224

SDS #: MS0800281

Recommended use:

- Industrial/Institutional
- Specialty Cleaner
- This product is intended to be used neat.

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 1300 Altura Rd., Suite 125 Fort Mill, SC 29708 Phone: 1-888-352-2249 SDS Internet Address: https://sds.diversey.com	Canadian Headquarters Diversey Canada, Inc. 6150 Kennedy Road Unit 3 Mississauga, Ontario L5T 2J4 Phone: 1-800-668-7171
--	---

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Flammability	Extremely flammable aerosol, Category 1
Gases under pressure	Compressed gas



Signal word: Danger.

Hazard Statements

EXTREMELY FLAMMABLE AEROSOL. CONTAINS GAS UNDER PRESSURE; MAY EXPLODE IF HEATED.

Precautionary Statements

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not incinerate. Do not pierce or burn, even after use. Protect from sunlight. Store in a well-ventilated place. Do not expose to temperatures exceeding 50 °C (122 °F) which may cause bursting. Dispose of in accordance with all federal, state and local applicable regulations.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

Ingredient(s)	CAS #	Weight %
Propane	74-98-6	5 - 10%
Butane	106-97-8	5 - 10%
Alkyl alkanolamide	68155-20-4	> 0.1 - < 1%
Ammonium hydroxide	1336-21-6	> 0.1 - < 1%

4. FIRST AID MEASURES

Undiluted Product:

Eyes: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Skin: Wash with plenty of water for at least 15 minutes.

Inhalation: No specific first aid measures are required.

Ingestion: Rinse mouth with water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed: Not applicable.

Aggravated Medical Conditions: None known.

5. FIRE-FIGHTING MEASURES

Specific methods:

No special methods required

Suitable extinguishing media:

Dry chemical, water spray, foam, carbon dioxide.

Specific hazards:

Aerosol product - Containers may rocket or explode in heat of fire. NFPA 30B Level 3 Aerosol.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions:

Remove all sources of ignition. Contents under pressure. Do not puncture or incinerate cans.

Environmental precautions

Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

and clean-up methods:

7. HANDLING AND STORAGE

Handling: EXTREMELY FLAMMABLE AEROSOL. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. PRESSURIZED CONTAINER: Do not pierce or burn, even after use. Do not incinerate. Intentional misuse by deliberately concentrating and inhaling the contents can be harmful or fatal. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: NFPA 30B Level 3 Aerosol. Protect from sunlight. Store in a well-ventilated place. Do not expose to temperatures exceeding 50 °C (122 °F) which may cause bursting.

Aerosol Level (if applicable): Level 3

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Ingredient(s)	CAS #	ACGIH	OSHA
Propane	74-98-6		1000 ppm (TWA) 1800 mg/m ³ (TWA)
Butane	106-97-8	1000 ppm (STEL)	

Undiluted Product:

Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

It is the responsibility of the employer to determine the potential risk of exposure to hazardous chemicals for employees in the workplace in order to

determine the necessity, selection, and use of personal protective equipment.

Eye protection:	No personal protective equipment required under normal use conditions.
Hand protection:	No personal protective equipment required under normal use conditions.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Aerosol	Color: Opaque, White
Evaporation Rate: No information available	Odor: Characteristic
Odor threshold: No information available.	Boiling point/range: Not determined
Melting point/range: Not determined	Decomposition temperature: Not determined
Autoignition temperature: No information available	Solubility: Dispersible
Solubility in other solvents: No information available	Relative Density (relative to water): 0.85
Density: 7.09 lbs/gal 0.85 Kg/L	Vapor density: No information available
Bulk density: No information available	Vapor pressure: No information available.
Flash point (°F): <-20°F ≈ -29 °C	Partition coefficient (n-octanol/water): No information available
Viscosity: No information available	Elemental Phosphorus: 0.00 % by wt.
VOC: 15 % *	pH: ≈ 10.8
Flammability (Solid or Gas): Not applicable	Corrosion to metals: Not corrosive to metals
Sustained combustion: Not applicable	
Explosion limits: - upper: Not determined - lower: Not determined	

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity:	Not Applicable
Stability:	The product is stable
Hazardous decomposition products:	None reasonably foreseeable.
Materials to avoid:	Do not mix with any other product or chemical unless specified in the use directions.
Conditions to avoid:	Extremes of temperature and direct sunlight. Keep away from open flames, hot surfaces and sources of ignition.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Skin contact, Inhalation, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: Unlikely to be irritant in normal use.

Eye contact: May be mildly irritating to eyes.

Ingestion: No information available.

Inhalation: No information available.

Sensitization: No known effects.

Target Organs (SE): None known

Target Organs (RE): None known

Numerical measures of toxicity

ATE - Oral (mg/kg): >5000

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

RCRA Hazard Class (undiluted product): D001 Ignitable Waste

Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT/TDG/IMDG: The information provided below is the full transportation classification for this product. This description does not account for the package size(s) of this product, that may fall under a quantity exception, according to the applicable transportation regulations. When shipping dangerous goods, please consult with your internal, certified hazardous materials specialist to determine if any exceptions can be applied to your shipment.

DOT (Ground) Bill of Lading Description: UN1950, AEROSOLS, FLAMMABLE, 2.1

IMDG (Ocean) Bill of Lading Description: UN1950, AEROSOLS, FLAMMABLE, 2.1

15. REGULATORY INFORMATION

International Inventories at CAS# Level

TSCA

All components are listed or otherwise exempt

DSL

All components are listed or otherwise exempt



WARNING: This product can expose you to chemicals including Diethanolamine which are known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

Ingredient(s)	CAS #	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	-	-
White mineral oil	8042-47-5	X	X	-	-
Propane	74-98-6	X	X	X	-
Butane	106-97-8	X	X	X	-
Polydimethylsiloxane	63148-62-9	-	-	-	-
Alkyl alkanolamide	68155-20-4	-	-	-	-
Ammonium hydroxide	1336-21-6	X	X	X	X
Sodium benzoate	532-32-1	-	-	-	-
Diethanolamine	111-42-2	X	X	X	X
Diethyl phthalate	84-66-2	X	X	X	X

CERCLA/ SARA

Ingredient(s)	CAS #	Weight %	CERCLA/SARA RQ (lbs)	Section 302 TPQ (lbs)	Section 313
Ammonium hydroxide	1336-21-6	> 0.1 - < 1%	1000	100	X

Ingredient(s)	CAS #	NPRI
White mineral oil	8042-47-5	X
Propane	74-98-6	X

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 0
Flammability 4
Instability 0
Special Hazards -

Revision: 2020-10-05
Version: 04.0

Reason for revision: Not applicable
Prepared by: North American Regulatory Affairs
Additional advice: • Does not contain an added fragrance

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.