

Empack Spraytech Inc. 98 Walker Drive Brampton, Ontario, L6T 4H6 Canada 905-792-6571

PRODUCT: **ZGB Clear Gel Hand Sanitizer 70% Pro - 1 L** 

### **SECTION 01: IDENTIFICATION**

ZGB Clear Gel Hand Sanitizer 70% Pro - 1 L Product Identity.....

Product Item Numbers..... P1-001217

Recommended Use.....

CHEMICAL NAME AND SYNONYMS

Empack Spraytech Inc. 98 Walker Drive Manufacturer.....

Brampton Ontario Canada L6T 4H6 905-792-6571

24 hour emergency telephone number..... In Canada: Call CANUTEC (613) 996-6666 - In The United States: Call CHEMTREC (800)

424-9300. Hand sanitizer.

**SECTION 02: HAZARD IDENTIFICATION** 





CODE: P1-001217

Label Elements: Signal Word..... WARNING. Hazard Classification: Physical Hazards..... Flammable Liquids - Category 3. Eye Irritation - Category 2B. Specific Target Organ Toxicity, Single Exposure - Category 3. Health Hazards..... Environmental Hazards..... Not Classified Hazard Statement..... H226:Flammable liquid and vapour. H320:Causes eye irritation. H335:May cause respiratory irritation. Precautionary Statements: P210:Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P233:Keep container tightly closed. P240:Ground and bond container and receiving equipment. P242:Use non-sparking tools. P243:Take action to prevent static Prevention..... discharges. P241:Use explosion-proof electrical/ventilating/lighting. P261:Avoid breathing dust/fume/gas/mist/vapours/spray. P271:Use only outdoors or in a well-ventilated area. P303+P361+P353:IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water . P370+P378:In case of fire: Use CO2, dry chemicals or foam to extinguish. P305+P351+P338:IF IN EYES: Rinse cautiously with water for several Response..... minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313:If eye irritation persists: Get medical advice/attention. P304+P340:IF INHALED: Remove person to fresh air and keep comfortable for breathing. P312:Call a POISON CENTER if you feel unwell. P403+P235:Store in a well ventilated place. Keep cool. P233:Keep container tightly Storage..... closed. P405: Store locked up. P501:Dispose of contents/container in accordance with local, regional, national, and/or Disposal..... international regulations. Hazard(s) not otherwise classified (HNOC)

For external use only. Not expected to cause skin irritation. Discontinue use if rash, redness or itching occurs. KEEP OUT OF REACH OF CHILDREN. **SECTION 03: COMPOSITION / INFORMATION ON INGREDIENTS** 

CAS#

Ethyl alcohol 64-17-5 45-70

## **SECTION 04: FIRST-AID MEASURES**

The product is not expected to be skin irritant. However, if irritation persists, wash the Skin Contact..... contact skin area with soap and water.

Immediately flush eyes with plenty of water for at least 15 minutes, occasionally lifting the

upper and lower eyelids. Get medical attention if irritation persists.

WT. %

## PRODUCT: ZGB Clear Gel Hand Sanitizer 70% Pro - 1 L

# **SECTION 04: FIRST-AID MEASURES**

Ingestion is not a likely route of exposure. Do not attempt to give anything by mouth to an unconscious person. If victim is alert and not convulsing, rinse mouth out and give 1/2 to 1Ingestion..... glass of water to dilute material. DO NOT induce vomiting. If spontaneous vomiting occurs, have victim lean forward with head down to avoid breathing in of vomitus, rinse mouth and

administer more water. Obtain medical attention IMMEDIATELY. Obtain medical advice.

No specific effects have been reported. Supply fresh air if any irritations persists.

Most important symptoms/effects, acute .. Direct eye contact may cause temporary eye irritation.

and delayed Indication of immediate medical attention

Provide general supportive measures and treat symptomatically. In case of shortness of breath give oxygen. Keep victim warm. Keep victim under observation. Symptoms may be delayed.

CODE: P1-001217

### **SECTION 05: FIRE-FIGHTING MEASURES**

General Fire Hazards..... Use as directed. Flammable.

Suitable Extinguishing Media..... Dry chemical powder. Carbon dioxide. Foam, water spray or fog.

Unsuitable Extinguishing Media..... None in particular.

Specific Hazards Arising from the Chemical None known.

Special Protective Equipment and ......

and special treatment needed

Precautions for Firefighters

Firefighters must use standard protective equipment including flame retardant coat, helmet with water to prevent vapor pressure build up. Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Remove undamaged containers from immediate hazard area if it is safe to do.

### **SECTION 06: ACCIDENTAL RELEASE MEASURES**

Personal Precautions, Protective ..... Ensure adequate ventilation; avoid formation of dust. Wear protective equipment and keep **Equipment and Emergency Procedures** unprotected persons away. Use respiratory protection against the effects of dust. Contain the spill. Clean up the spill area with detergent and water. Once spilled material Methods and Materials for Containment ..

and Cleaning Up has been collected, use rags or other suitable material to clean spill area. Rags should be properly disposed off.

Environmental Precautions..... Keep out of drains, sewers, ditches, and waterways. Minimize use of water to prevent

environmental contamination.

### **SECTION 07: HANDLING AND STORAGE**

Precautions for Safe Handling..... Avoid contact with eyes. Avoid breathing vapours or spray mists of this product. Use with adequate ventilation. Keep away from heat, sparks, and open flames.

Conditions for Safe Storage including any Store in a cool, dry, well-ventilated area away from incompatible substances. Do not store

Incompatibilities in direct sunlight.

### SECTION 08: EXPOSURE CONTROLS / PERSONAL PROTECTION

	ACGIH TLV		OSHA PEL		N	IIOSH
INGREDIENTS	TWA	STEL F	PEL	STEL	REL	

1000 ppm 1000 ppm Ethyl alcohol 1000 ppm Not available 1000 ppm

Appropriate Engineering Controls..... Local exhaust ventilation required to maintain the point of use below the Threshold Limit

Value if unprotected personnel are involved. Individual Protection Measures:

Eye/Face Protection..... Prevent eye contact, wear safety glasses in the event that eye contact is possible.

Skin Protection..... Not normally required.

Respiratory Protection..... Not required on a short-term basis or if exhaust ventilation is provided. Use approved

NIOSH respirators for emergencies.

Thermal Hazards..... None Known.

General Hygiene Considerations..... When using, do not eat, drink or smoke. Always observe good personal hygiene measures,

such as washing after handling the material and before eating, drinking, and/or smoking.

Routinely wash work clothing and protective equipment prior to use

# **SECTION 09: PHYSICAL AND CHEMICAL PROPERTIES**

Physical State..... Liquid.

Clear/Transparent. Physical Appearance.....

Mild alcohol . Odour.....

Odour Threshold (ppm)..... Not available.

6.0 - 7.5.

Aerosol Vapour Pressure (psig, 21°C)..... Not applicable.

Vapour Pressure (psig)..... Not available.

Evaporation Rate (n-Butyl Acetate = 1)..... Not available.



CODE: P1-001217

### PRODUCT: ZGB Clear Gel Hand Sanitizer 70% Pro - 1 L

# **SECTION 09: PHYSICAL AND CHEMICAL PROPERTIES**

78.3. (Ethanol).

-115. Approximately. (Ethanol).

VOC Content.....Relative Density/Specific Gravity..... No data.

No data.

Solubility in water..... Soluble in water.

370. Approximately. (Ethanol).

13. Tag Closed Cup. (ASTM D-56). (Ethanol). 3.3. (Ethanol).

Auto Ignition Temperature (liquid), °C..... Flash Point (°C), Method.... Lower Explosive Limit (%, vol)..... Upper Explosive Limit (%, vol)..... 19.0. (Ethanól).

Viscosity..... 1.35 cp @ 20°C. Approximately. (Ethanol).

### **SECTION 10: STABILITY AND REACTIVITY**

Reactivity ..... Product not reactive under normal conditions of use.

Chemical Stability..... Stable at normal temperatures and pressures.

Possibility of Hazardous Reactions..... Will not occur.

Conditions to Avoid..... Avoid sources of heat and flame, and electrostatic charge.

Avoid contacting with oxidizers. Incompatible Materials..... Hazardous Decomposition Products...... Normal products of combustion.

# SECTION 11: TOXICOLOGICAL INFORMATION

**INGREDIENTS** LC50 LD50

Ethyl alcohol 31,623 ppm (Rat - 4 hrs) 7,060 mg/kg (Oral - Rat); 20,000 mg/kg (Dermal - Rabbit)

Information on Likely Routes of Exposure:

Routes of entry - Inhalation..... No. Routes of entry - Skin & Eye..... Yes. Routes of entry - Ingestion..... Yes. Routes of entry - Skin Absorption.....

Symptoms Related to the Physical, ...... Irritant effects.

Chemical and Toxicological Characteristics

No known significant effects. Acute Toxicity..... Skin Corrosion/Irritation..... Based on available data, the classification criteria are not met.

Serious Eye Damage/Eye Irritation..... Direct contact with eyes causes temporary irritation. Respiratory or Skin Sensitization..... Not expected to be a skin or respiratory sensitizers.

Germ Cell Mutagenicity..... No information is available, and no adverse effects are expected. Carcinogenicity......Reproductive Toxicity..... Not classified as carcinogenic by ACGIH, IARC, OSHA or NTP. Based on available data, the classification criteria are not met.

STOT - Single Exposure.....STOT - Repeated Exposure..... Specific target organ toxicity single exposure Category 3. May cause respiratory irritation.

Not classified.

Aspiration Hazard..... Based on available data, the classification criteria are not met.

No long term chronic effects are known or anticipated. Chronic Effects.....

# **SECTION 12: ECOLOGICAL INFORMATION**

This product contains the following ingredients:. Ethyl alcohol (CAS#: 64-17-5): Toxicity to fish: LC50 14200 mg/L, 96 hrs; Toxicity to other aquatic invertebrates: 9300 mg/L, 48 hrs; Ecotoxicity.....

Toxicity to algae: not available.

Persistence and degradability ..... The product itself has not been tested. Bioaccumulation Potential..... The product itself has not been tested. The product itself has not been tested. Mobility in Soil.....

Other Adverse Effects..... None Known.

# **SECTION 13: DISPOSAL CONSIDERATIONS**

Appropriate Disposal Methods..... Dispose in accordance with local, provincial and federal regulations.

## **SECTION 14: TRANSPORT INFORMATION**

UN 1993, FLAMMABLE LIQUID, n.o.s. (ETHANOL), Class 3, PG II . TDG (Canada- Road).....

DOT (US-Road)..... UN 1993, FLAMMABLE LIQUID, n.o.s. (ETHANOL), Class 3, PG II, LTD QTY, Consumer

# PRODUCT: ZGB Clear Gel Hand Sanitizer 70% Pro - 1 L

# **SECTION 15: REGULATORY INFORMATION**

Refer to Section 2 for a WHMIS 2015 Classification for this product. Canada Regulations:.... US Regulations..... All substances contained in this product are listed on the TSCA inventory or are exempt.

## **SECTION 16: OTHER INFORMATION**

The information contained herin is based on data considered accurate. No warranty is Disclaimer..... expressed or implied regarding the accuracy of this data or the results obtained from the use thereof. Empack assumes no responsibility for personal injury or property damage to vendees or users or third parties, caused by the material. Such vendees or users assume all risks with the use of the material. This product has been classified in accordance with the hazard criteria of the CPR and the SDS contains all the information required by the CPR. ACGIH: American Conference of Governmental Industrial Hygienists; CAS: Chemical Abbreviations.....

Abstract Service; NIOSH: National Institute for Occupational Safety and Health, OSHA: Occupational Safety and Health Administration- USA; TSCA: Toxic Substances Control Act 1976-USA; PEL: Permissible Exposure Limit; REL: Recommended Exposure Limit; TLV: Threshold Limit Value; VOC: Volatile Organic Content; WHMIS: Workplace Hazardous Materials Information System STOT: Specific Target Organ Toxicity.

CODE: P1-001217

Regulatory Affairs Prepared by ..... 2020-04-27 Latest Revision .....