Safety Data Sheet



Revision Number: 002.1

1. PRODUCT AND COMPANY IDENTIFICATION

 Product name:
 LePage Super Glue Gel Control

 Product type:
 Cyanoacrylate

 Restriction of Use:
 None identified

 Company address:
 Henkel Corporation

 One Henkel Way
 Rocky Hill, Connecticut 06067

IDH number:

1668008

Region:CanadaContact information:Telephone: (860) 571-5100MEDICAL EMERGENCY Phone: Poison Control Center1-877-671-4608 (toll free) or 1-303-592-1711TRANSPORT EMERGENCY Phone: CHEMTREC1-800-424-9300 (toll free) or 1-703-527-3887Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW		
WARNING:	BONDS SKIN IN SECONDS.	
	COMBUSTIBLE LIQUID.	
	CAUSES EYE IRRITATION.	
	MAY CAUSE RESPIRATORY IRRITATION.	

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	4
EYE IRRITATION	2B
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3



Precautionary Statements

Prevention:	Keep away from heat, sparks, open flames, hot surfaces - no smoking. Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear protective gloves, eye protection, and face protection.
Response:	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.
Storage:	Store in a well-ventilated place. Keep container tightly closed. Store in a well-ventilated place. Keep cool. Store locked up.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with Canadian Hazardous Products Regulations (WHMIS 2015) and is consistent with the provision of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

IDH number: 1668008

Product name: LePage Super Glue Gel Control

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Weight %*
Ethyl 2-cyanoacrylate	7085-85-0	80 - 90
Treated fumed silica	67762-90-7	5 - 10

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

	4. FIRST AID MEASURES
Inhalation:	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. If symptoms develop and persist, get medical attention.
Skin contact:	Do not pull bonded skin apart. Soak in warm soapy water. Gently peel apart using a blunt instrument. If skin is burned due to the rapid generation of heat by a large drop, seek medical attention. If lips are bonded, apply warm water to the lips and encourage wetting and pressure from saliva in mouth. Peel or roll lips apart. Do not pull lips apart with direct opposing force.
Eye contact:	Immediately flush with plenty of water for at least 15 minutes. Get medical attention. If eyelids are bonded closed, release eyelashes with warm water by covering with a wet pad. Do not force eye open. Cyanoacrylate will bond to eye protein and will cause a lachrymatory effect which will help to debond the adhesive. Keep eye covered until debonding is complete, usually within 1-3 days. Medical attention should be sought in case solid particles of polymerized cyanoacrylate trapped behind the eyelid caused abrasive damage.
Ingestion:	Ensure breathing passages are not obstructed. The product will polymerize rapidly and bond to the mouth making it almost impossible to swallow. Saliva will separate any solidified product in several hours. Prevent the patient from swallowing any separated mass.
Symptoms:	See Section 11.
Notes to physician:	Surgery is not necessary to separate accidentally bonded tissues. Experience has shown that bonded tissues are best treated by passive, non-surgical first aid. If rapid curing has caused thermal burns they should be treated symptomatically after adhesive is removed.
5.	FIRE FIGHTING MEASURES
Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode.

Trace amounts of toxic and/or irritating fumes may be released and the use of breathing apparatus is recommended.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Not available.

Environmental precautions:

Unusual fire or explosion hazards:

Hazardous combustion products:

Do not allow product to enter sewer or waterways.

 Clean-up methods:
 Do not use cloths for mopping up. Flood with water to complete polymerization and scrape off the floor. Cured material can be disposed of as non-hazardous waste.

 7. HANDLING AND STORAGE

 Handling:
 Avoid contact with eyes, skin and clothing. Avoid breathing vapors or mists of this product. Wash thoroughly after handling. Avoid contact with fabric or paper goods. Contact with these materials may cause rapid polymerization which can generate smoke and strong irritating vapors, and cause thermal burns.

 Storage:
 Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

Shelf Life Statement: Not available.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Ethyl 2-cyanoacrylate	0.2 ppm TWA	None	None	None
Treated fumed silica	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	15 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.	None	None
Engineering controls:	Use positive down-draft exhaust ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.			
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).			
Eye/face protection:	Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists.			
Skin protection:	Use nitrile gloves and aprons as necessary to prevent contact. Do not use PVC, nylon or cotton.			

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Gel
Color:	Clear
Odor:	Irritating
Odor threshold:	1 - 2 ppm
pH:	Not available.
Vapor pressure:	< 0.2 mm hg
Boiling point/range:	> 149 °C (> 300.2 °F)
Melting point/ range:	Not available.
Specific gravity:	1.05
Vapor density:	3
Flash point:	80 - 93 °C (176°F - 199.4 °F) Tagliabue closed cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	485 °C (905°F)
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Polymerises in presence of water.
Solubility in water:	Polymerizes on contact with water.
Partition coefficient (n-octanol/water):	Not available.
VOC content:	< 2 %; < 20 g/l (California SCAQMD Method 316B) (Estimated)
Viscosity:	Not available.

Decomposition temperature:

Not available.

	10. STABILITY AND REACTIVITY
Stability:	Stable under recommended storage conditions.
Hazardous reactions:	Rapid exothermic polymerization will occur in the presence of water, amines, alkalis and alcohols.
Hazardous decomposition products:	None
Incompatible materials:	Water, Amines, Alkalis, Alcohols.
Reactivity:	Not available.
Conditions to avoid:	Spontaneous polymerization.
	11. TOXICOLOGICAL INFORMATION
Relevant routes of exposure:	Skin, Inhalation, Eyes
Potential Health Effects/Sympto	ms
Inhalation: Skin contact:	May cause respiratory tract irritation. Exposure to vapors above the established exposure limit results in respiratory irritation, which may lead to difficulty in breathing and tightness in the chest. May cause skin irritation. May cause allergic skin reaction. Bonds skin in seconds. Cyanoacrylates have been reported to cause allergic reaction but due to rapid polymerization a
Eye contact: Ingestion:	the skin surface, an allergic response is rare. Cyanoacrylates generate heat on solidification. In rare circumstances a large drop will burn the skin. Cured adhesive does not present a health hazard even if bonded to the skin. Irritating to eyes. Causes excessive tearing. Eyelids may bond. Not expected to be harmful by ingestion. Rapidly polymerizes (solidifies) and bonds in mouth. is almost impossible to swallow.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Ethyl 2-cyanoacrylate	None	Irritant, Allergen, Respiratory
Treated fumed silica	None	Irritant

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Ethyl 2-cyanoacrylate	No	No	No
Treated fumed silica	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information:

Not available.

	13. DISPOSAL CONSIDERATIONS
	Information provided is for unused product only.
Recommended method of dispos	bal: Dispose of according to Federal, State and local governmental regulations.
	14. TRANSPORT INFORMATION
The transport information provide package/configuration.	d in this section only applies to the material/formulation itself, and is not specific to any
Canada Transportation of Danger	ous Goods - Ground
Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None
International Air Transportation (I	CAO/IATA)
Proper shipping name:	Aviation regulated liquid, n.o.s. (Cyanoacrylate ester)
Hazard class or division:	9
Identification number:	UN 3334
Packing group: Exceptions:	III Primary packs containing loss than 500ml are uprogulated by this mode of
Exceptions.	Primary packs containing less than 500ml are unregulated by this mode of transport and may be shipped unrestricted.
Water Transportation (IMO/IMDG) Proper shipping name: Hazard class or division: Identification number: Packing group:	Not regulated None None None
	15. REGULATORY INFORMATION
Canada Regulatory Information	
CEPA DSL/NDSL Status:	Contains one or more components listed on the Non-Domestic Substances List. All other components are listed on or are exempt from listing on the Domestic Substances List. Components listed on the NDSL must be tracked by all Canadian Importers of Record as required by Environment Canada. They may be imported into Canada in limited quantities. Please contact Regulatory Affairs for additional details.
Inited States Regulatory Information	
TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
	16. OTHER INFORMATION
This safety data sheet contains c	hanges from the previous version in sections: New Safety Data Sheet format.
Prepared by: Product	Safety and Regulatory Affairs
	, , ,

Issue date: 09/11/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.