



Prominence ^{TM/MC} Heavy Duty Floor Cleaner

Revision: 2020-09-06

Version: 01.0

1. IDENTIFICATION

Product name: Prominence ^{TM/MC}
Heavy Duty Floor Cleaner

Product Code: 101100677, 94996440, 94996458, 94996458W, 94996466, 95041178

SDS #: MS0801372

Recommended use:

- Floor care
- Industrial/Institutional
- This product is intended to be diluted prior to use

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 1300 Altura Rd., Suite 125 Fort Mill, SC 29708 Phone: 1-888-352-2249 SDS Internet Address: https://sds.diversey.com	Canadian Headquarters Diversey Canada, Inc. 6150 Kennedy Road Unit 3 Mississauga, Ontario L5T 2J4 Phone: 1-800-668-7171
--	---

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2A



Signal word: Warning.

Hazard Statements

CAUSES SKIN AND SERIOUS EYE IRRITATION.

Precautionary Statements

Avoid contact with eyes, skin and clothing. Wash affected areas thoroughly after handling. May cause irritation to mouth, throat and stomach. Wear chemical-resistant gloves. IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice or attention. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice or attention. Take off contaminated clothing and wash it before reuse. Dispose of in accordance with all federal, state and local applicable regulations.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product @ 1:256

This product, when diluted as stated on the label, is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and

Hazard and Precautionary Statements

None required.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

Ingredient(s)	CAS #	Weight %
Ethoxylated secondary alcohol	84133-50-6	10 - 30%
Alcohol, C9-C11, ethoxylated	68439-46-3	10 - 30%

4. FIRST AID MEASURES

Undiluted Product:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin: IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.

Inhalation: No specific first aid measures are required.

Ingestion: IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed: Not applicable.

Diluted Product:

Eyes: Rinse with plenty of water.

Skin: No specific first aid measures are required

Inhalation: No specific first aid measures are required

Ingestion: IF SWALLOWED: Call a Poison Center (1-800-851-7145) or doctor/physician if you feel unwell.

5. FIRE-FIGHTING MEASURES

Specific methods:

No special methods required

Suitable extinguishing media:

The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards:

None known.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions:

Put on appropriate personal protective equipment (see Section 8.).

Environmental precautions

Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

and clean-up methods:

7. HANDLING AND STORAGE

Handling: Avoid contact with eyes. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Keep tightly closed in a dry, cool and well-ventilated place.

Aerosol Level (if applicable): Not applicable.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Undiluted Product:

Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

It is the responsibility of the employer to determine the potential risk of exposure to hazardous chemicals for employees in the workplace in order to determine the necessity, selection, and use of personal protective equipment.

Eye protection:	No personal protective equipment required under normal use conditions.
Hand protection:	Chemical-resistant gloves.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

Diluted Product:

Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

Eye protection:	No personal protective equipment required under normal use conditions.
Hand protection:	No personal protective equipment required under normal use conditions.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Liquid

Evaporation Rate: No information available

Odor threshold: No information available.

Melting point/range: Not determined

Autoignition temperature: No information available

Solubility in other solvents: No information available

Density: Specific gravity: 1.0177 Kg/L

Bulk density: No information available

Flash point (°F): > 200 °F > 93 °C

Viscosity: 90

VOC: 0 % *

Flammability (Solid or Gas): Not applicable

Sustained combustion: Not applicable

Explosion limits: - upper: Not determined - **lower:** Not determined

Color: Clear Yellow

Odor: Citrus Slightly perfumed

Boiling point/range: Not determined

Decomposition temperature: Default (°F)

Solubility: Completely Soluble

Relative Density (relative to water): 1.0177

Vapor density: No information available

Vapor pressure: No information available.

Partition coefficient (n-octanol/water): No information available

Elemental Phosphorus: 0.00 % by wt.

pH: ≈ 8.4

Corrosion to metals: Not corrosive to metals

Dilution pH:

≈ 6.85

Dilution Flash Point (°F): > 200 °F > 93.4 °C

VOC % by wt. at use dilution: 0.0001 %

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity: Not Applicable

Stability: The product is stable

Hazardous decomposition products: None reasonably foreseeable.

Materials to avoid: Do not mix with any other product or chemical unless specified in the use directions.

Conditions to avoid: None known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Skin contact, Inhalation, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: Causes skin irritation. Symptoms may include pain (which may be delayed), redness, and/or discomfort.

Eye contact: Causes serious eye irritation. Symptoms may include pain, redness, and watering.

Ingestion: Symptoms may include stomach pain and nausea. May be irritating to mouth, throat and stomach.
Inhalation: Symptoms may include coughing and difficulty breathing. May be irritating to nose, throat, and respiratory tract.
Sensitization: No known effects.
Target Organs (SE): None known
Target Organs (RE): None known

Numerical measures of toxicity

ATE - Oral (mg/kg): >5000
ATE - Inhalatory, mists (mg/l): 11

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

Waste from residues / unused products (diluted product): This product, when diluted as stated on this SDS, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

RCRA Hazard Class (undiluted product): Not Regulated

RCRA Hazard Class (diluted product): Not Regulated

Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT/TDG/IMDG: The information provided below is the full transportation classification for this product. This description does not account for the package size(s) of this product, that may fall under a quantity exception, according to the applicable transportation regulations. When shipping dangerous goods, please consult with your internal, certified hazardous materials specialist to determine if any exceptions can be applied to your shipment.

DOT (Ground) Bill of Lading Description: NOT REGULATED

15. REGULATORY INFORMATION

International Inventories at CAS# Level

Ingredient(s)	CAS #	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	-	-
Ethoxylated secondary alcohol	84133-50-6	-	-	-	-
Alcohol, C9-C11, ethoxylated	68439-46-3	-	-	-	-
Alanine, N,N-bis(carboxymethyl)-, trisodium salt	164462-16-2	-	-	-	-
Fatty acids, C8-18 and C18 unsaturated	67701-05-7	-	-	-	-

16. OTHER INFORMATION

NFPA (National Fire Protection Association)
Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 2
Flammability 0
Instability 0
Special Hazards -

Diluted Product:

Health 0
Flammability 0
Instability 0
Special Hazards -

Revision: 2020-09-06
Version: 01.0

Reason for revision: Not applicable
Prepared by: North American Regulatory Affairs
Additional advice: • Contains an added fragrance, see "Odor" heading in section 9 for specific description

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.