



Crew® Super Blue™/MC

Version Number: 2

Preparation date: 2018-06-12

1. IDENTIFICATION

Product name: Crew® Super Blue™/MC
Product Code: 94476081
SDS #: MS0801210
Recommended use:

- Industrial/Institutional
- Acid Cleaner
- Restroom Care
- This product is intended to be used neat.

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 2415 Cascade Pointe Blvd. Charlotte, NC 28208 Phone: 1-888-352-2249 SDS Internet Address: https://sds.diversey.com	Canadian Headquarters Diversey Canada, Inc. 3755 Laird Road Units 8-11 Mississauga, Ontario L5L 0B3 Phone: 1-800-668-7171
---	---

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 1



Signal Word: **Danger.**

Hazard and Precautionary Statements

CAUSES SKIN IRRITATION. CAUSES SERIOUS EYE DAMAGE.

Causes burns/ serious damage to mouth, throat and stomach. Keep container tightly closed. Avoid contact with eyes, skin and clothing. Wash affected areas thoroughly after handling. Wear chemical-splash goggles and chemical-resistant gloves. IF SWALLOWED: Rinse mouth. DO NOT induce vomiting unless directed to do so by medical personnel. Drink a cupful of milk or water. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice or attention. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. Immediately call a Poison Center (1-800-851-7145) or physician. Take off contaminated clothing and wash it before reuse. Dispose of in accordance with all federal, state and local applicable regulations. SUPPLEMENTAL INFORMATION: DO NOT MIX WITH AMMONIA, BLEACH OR OTHER CHLORINATED COMPOUNDS. Mix only with water. Can react to release hazardous gases. May vigorously react with strong alkaline products resulting in spattering and excessive heat.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

Ingredient(s)	CAS #	Weight %
Alcohol ethoxylates	68439-46-3	3 - < 5%
Oxalic acid	6153-56-6	1 - < 3%
Dodecylbenzene sulfonic acid	68584-22-5	1 - < 3%

*Exact percentages are being withheld as trade secret information

4. FIRST AID MEASURES

Undiluted Product:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes.

Skin: IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.

Inhalation: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Ingestion: IF SWALLOWED: Rinse mouth. DO NOT induce vomiting unless directed to do so by medical personnel. Drink a cupful of milk or water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed: Not applicable.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required
Suitable extinguishing media: Not applicable.
Specific hazards: Corrosive material (See sections 8 and 10).

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Put on appropriate personal protective equipment (see Section 8.).
Environmental precautions and clean-up methods: Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Avoid contact with skin, eyes and clothing. Wash thoroughly after handling. Do not taste or swallow. Product residue may remain on/in empty containers. All precautions for handling the product must be used in handling the empty container and residue. Avoid breathing vapors or mists. Use only with adequate ventilation. Remove and wash contaminated clothing and footwear before re-use. Mix only with water. DO NOT MIX WITH AMMONIA, BLEACH, OR OTHER CHLORINATED COMPOUNDS. Can react to release hazardous gases. May vigorously react with strong alkaline products resulting in spattering and excessive heat. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Keep tightly closed in a dry, cool and well-ventilated place.

Aerosol Level (if applicable): Not applicable.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Ingredient(s)	CAS #	ACGIH	OSHA
Oxalic acid	6153-56-6	2 mg/m ³ (STEL) 1 mg/m ³ (TWA)	-

Undiluted Product:

Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

Eye protection:	Chemical-splash goggles.
Hand protection:	Chemical-resistant gloves.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Liquid	Color: Clear Medium Blue
Evaporation Rate: No information available	Odor: Citrus Slightly perfumed
Odor threshold: No information available.	Boiling point/range: Not determined
Melting point/range: Not determined	Decomposition temperature: Not determined
Autoignition temperature: No information available	Solubility: Completely Soluble
Solubility in other solvents: No information available	Relative Density (relative to water): 1.007
Density: 8.4 lbs/gal 1.007 Kg/L	Vapor density: No information available
Bulk density: No information available	Vapor pressure: No information available.
Flash point (°F): > 200 °F > 93.4 °C	Partition coefficient (n-octanol/water): No information available
Viscosity: 20 cP	Elemental Phosphorus: 0.00 % by wt.
VOC: 0 % *	pH: 1.25
Flammability (Solid or Gas): Not applicable	Corrosion to metals: Not determined
Sustained combustion: Not applicable	
Explosion limits: - upper: Not determined - lower: Not determined	

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity:	Not Applicable
Stability:	The product is stable
Possibility of hazardous reactions:	May vigorously react with strong alkaline products resulting in spattering and excessive heat.
Hazardous decomposition products:	None reasonably foreseeable.
Materials to avoid:	Strong bases. Ammonia. Do not mix with chlorinated products (such as bleach). Do not mix with any other product or chemical unless specified in the use directions.
Conditions to avoid:	No information available.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Skin contact, Inhalation, Ingestion, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: Causes skin irritation. Symptoms may include pain (which may be delayed), redness, and/or discomfort.

Eye contact: Corrosive. Causes serious eye damage. Symptoms may include pain, burning sensation, redness, watering, blurred vision or loss of vision.

Ingestion: Causes burns/ serious damage to mouth, throat and stomach. Symptoms may include stomach pain and nausea.

Inhalation: May cause irritation and corrosive effects to nose, throat and respiratory tract. Symptoms may include coughing and difficulty breathing.

Sensitization: No known effects.

Target Organs (SE): None known

Target Organs (RE): None known

Numerical measures of toxicity

ATE - Oral (mg/kg): >2000

ATE - Dermal (mg/kg): >2000

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

RCRA Hazard Class (undiluted product): D002 Corrosive Waste

Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT (Ground) Bill of Lading Description: NOT REGULATED

IMDG (Ocean) Bill of Lading Description: NOT REGULATED

15. REGULATORY INFORMATION

International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL).

RIGHT TO KNOW (RTK)

Ingredient(s)	CAS #	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	-	-
Alcohol ethoxylates	68439-46-3	-	-	-	-
Oxalic acid	6153-56-6	X	X	X	-
Dodecylbenzene sulfonic acid	68584-22-5	-	-	-	-

CERCLA/ SARA

Canadian Regulations

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 3

Flammability 0

Instability 0

Version Number: 2

Preparation date: 2018-06-12

Reason for revision:

Not applicable

Prepared by:

NAPRAC

Additional advice:

• Contains an added fragrance, see "Odor" heading in section 9 for specific description

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.