

OVERVIEW



1. SD Express 7.0 card reader	5. HDMI
2. Thunderbolt 4	6. 2x Thunderbolt 5
3. USB-A (USB 10Gbps), Always On	7. Headphone / microphone combo jack (3.5mm)
4. Kensington Nano Security Slot	

PERFORMANCE

Processor

Processor Family

Intel® H Series Core Ultra 5 / 7 / 9 Processor (Series 2); supports up to 16 cores; up to 5.4GHz; base TDP ratings of up to 70W (without discrete GPU loading) / 35W (with discrete GPU loading)

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	Intel® vPro® Eligibility	NPU	Overall TOPS
Core Ultra 7 255H	16 (6 P-core + 8 E-core + 2 LPE-core)	16	P-core 2GHz / E-core 1.5GHz / LPE-core 700MHz	P-core 5.1GHz / E-core 4.4GHz / LPE-core 2.5GHz	24MB	Intel® Arc™ 140T GPU, up to 74 TOPS	-	Intel® AI Boost, up to 13 TOPS	Up to 96 TOPS
Core Ultra 7 265H	16 (6 P-core + 8 E-core + 2 LPE-core)	16	P-core 2.2GHz / E-core 1.7GHz / LPE-core 700MHz	P-core 5.3GHz / E-core 4.5GHz / LPE-core 2.5GHz	24MB	Intel® Arc™ 140T GPU, up to 75 TOPS	Intel® vPro® Enterprise	Intel® AI Boost, up to 13 TOPS	Up to 97 TOPS
Core Ultra 9 285H	16 (6 P-core + 8 E-core + 2 LPE-core)	16	P-core 2.9GHz / E-core 2.7GHz / LPE-core 1GHz	P-core 5.4GHz / E-core 4.5GHz / LPE-core 2.5GHz	24MB	Intel® Arc™ 140T GPU, up to 77 TOPS	Intel® vPro® Enterprise	Intel® AI Boost, up to 13 TOPS	Up to 99 TOPS

AI (Artificial Intelligence)

AI PC Category

AI PC

NPU

Integrated Intel® AI Boost, up to 13 TOPS

Operating System

Operating System

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Ubuntu Linux

Graphics

Graphics**

Graphics	Type	Memory	TGP
NVIDIA® GeForce RTX™ 5060 8GB GDDR7 Laptop GPU	Discrete	8GB GDDR7	60W (non-boost); 75W (boost)
NVIDIA® GeForce RTX™ 5070 8GB GDDR7 Laptop GPU	Discrete	8GB GDDR7	60W (non-boost); 75W (boost)

Monitor Support

Monitor Support

Supports up to 4 independent displays (native display and 3 external monitors via Thunderbolt™ 5, Thunderbolt™ 4, and HDMI®).

Max resolution for multiple external display:

- 3x 3840x2160@60Hz (Thunderbolt™ 5, Thunderbolt™ 4, and HDMI®)

Max resolution for single external display:

- Thunderbolt™ 4 supports up to 7680x4320@60Hz or 3840x2160@240Hz
- Thunderbolt™ 5 supports up to 7680x4320@60Hz or 3840x2160@240Hz
- HDMI® supports up to 7680x4320@60Hz or 3840x2160@240Hz

Chipset

Chipset

Intel® SoC (System on Chip) platform

Memory

Max Memory

Up to 64GB (1x 64GB LPCAMM2), upgradable

Memory Slots

One LPCAMM2 connector, dual-channel

Memory Type

LPDDR5x-7467, maximum transfer speeds of up to 7467 MT/s, 16GB / 32GB / 64GB memory modules are available

Storage

Max Storage Support^[1]

Up to two M.2 2280 Gen 5 Performance SSD; up to 8TB, 4TB each

Storage Slot^[2]

Two M.2 2280 PCIe® 4.0 x4 slots

Storage Type

Disk Type	Interface	Offering	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB	Opal 2.0
M.2 2280 SSD	PCIe® NVMe®, PCIe® 5.0 x4 Performance ^[3]	512GB / 1TB / 2TB / 4TB	Opal 2.0

RAID

RAID 0/1 support

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

[2] The actual data transfer rate of the following PCIe® interface also depends on the capabilities of the connected PCIe® device. The listed values represent theoretical maximums.

PCIe® 3.0 (x2 / x4): 2 GB/s (16 Gbps) / 4 GB/s (32 Gbps);

PCIe® 4.0 (x2 / x4): 4 GB/s (32 Gbps) / 8 GB/s (64 Gbps);

PCIe® 5.0 (x2 / x4): 8 GB/s (64 Gbps) / 16 GB/s (128 Gbps).

[3] Gen 5 SSD on M.2 PCIe® 4.0 slot will run on PCIe® 4.0 protocols.

Removable Storage

Card Reader

SD Express 7.0 card reader

Multi-Media

Audio Chip

SoundWire®, Cirrus Logic® CS42L43 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Microphone

- Dual-microphone array, far-field, Dolby Voice®
- No microphone (for special bid model)

Camera**

- 5.0MP + IR, with privacy shutter, fixed focus, Computer Vision Human Presence Detection on Image Signal Processor (ISP), temporal noise reduction
- 5.0MP + IR with privacy shutter, fixed focus, temporal noise reduction

Battery

Battery

90Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr)

Power Adapter

Power Adapter^[1]

140W USB-C® GaN (3-pin) AC adapter, supports PD 3.1, 100-240V, 50-60Hz

Notes:

[1] AC adapter offerings depend on the country.

DESIGN

Display

Display**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
16"	WUXGA (1920x1200)	Non-touch	IPS	500nits	Anti-glare	16:10	1200:1	100% sRGB	60Hz	89° / 89° / 89° / 89°	91.7% screen to body ratio, X-Rite® Factory Color Calibration, Low power, TÜV Low Blue Light, Eyesafe® 2.0 Certified, DC dimming
16"	3.2K (3200x2000)	Add-on Film Touch	Tandem OLED	SDR 600nits / HDR 1500nits (peak)	Anti-glare, anti-reflection, anti-smudge	16:10	100,000:1	100% DCI-P3	40-120Hz VRR	85° / 85° / 85° / 85°	90.9% screen to body ratio, DisplayHDR™ 600, Dolby Vision®, Eyesafe® Certified 2.0, TÜV Low Blue Light, X-Rite® Factory Color Calibration, PWM dimming
16"	WQUXGA (3840x2400)	Non-touch	IPS	800nits	Anti-glare	16:10	1500:1	100% DCI-P3	60Hz	85° / 85° / 85° / 85°	91.7% screen to body ratio, DisplayHDR™ 400, Dolby Vision®, Eyesafe® Certified 2.0, TÜV Low Blue Light, X-Rite® Factory Color Calibration, DC dimming

Touchscreen

- Add-on Film Touch, supports 10-point touch (Tandem OLED models)
- Non-touch

Screen-to-Body Ratio**

- 90.9% (Tandem OLED models)
- 91.7% (IPS models)

Color Calibration

X-Rite® factory color calibration

Input Device**Pen**

- Lenovo® Yoga® Pen
- No pen (purchase separately)
- No support (non-touch display doesn't support pen input)

Keyboard

6-row, spill-resistant, multimedia Fn keys, Copilot key

Keyboard Backlight

LED backlight

UltraNav™

3-button TrackPoint® pointing device and glass surface multi-touch Haptic Touchpad, 85 x 135 mm (3.35 x 5.31 inches)

Mechanical**Dimensions (WxDxH)^[1]**

354.3 × 241.0 × 9.9 / 15.8 (front / rear), 20.6 (maximum) mm
13.95 × 9.49 × 0.39 / 0.62 (front / rear), 0.81 (maximum) inches

Weight^[2]

Starting at 1.84 kg / 4.06 lbs

Case Color

Black

Case Material

Aluminium (top), aluminium (bottom)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY**Network****WLAN + Bluetooth®**^[1]**

- Intel® Wi-Fi® 7 BE201, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.4
- Intel® Wi-Fi® 7 BE201, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.4, Intel® vPro® technology support

WWAN

No support

SIM Card

No physical SIM card inbox

Ethernet

No onboard Ethernet, supports optional Lenovo® USB-C® to Ethernet Adapter (2.5Gbps)

NFC

- Near Field Communication
- No support

Notes:

[1] Bluetooth® may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

Ports^[1]**Standard Ports**

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 2x Thunderbolt™ 5, with USB PD 3.1 and DisplayPort™ 2.1, 140W input / 15W output
- 1x Thunderbolt™ 4, with DisplayPort™ 2.1 and USB PD 3.1, 140W input / 15W output
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x SD Express 7.0 card reader

Optional Ports

1x 2.5GbE RJ-45, via Lenovo® USB-C® to Ethernet Adapter (2.5Gbps)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

Thunderbolt™ 5: 80 Gbit/s (bidirectional), up to 120 Gbit/s in bandwidth boost mode for video-intensive applications.

Docking

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® T1g Gen 8](#)

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

No smart card reader

Fingerprint Reader

Touch style fingerprint reader integrated in power button, match-on-chip

BIOS Security

- NVMe® password
- Power-on password
- Supervisor password
- Self-healing BIOS

Other Security

- Bottom cover tamper detection
- Camera privacy shutter
- Computer Vision-based User Presence Sensing on Image Signal Processor (ISP)
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

System Management

- Intel® vPro® Enterprise
- Non-vPro®

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 1-year limited onsite service
- 3-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) limited onsite service
- No base warranty

ACCESSORIES

Bundled Accessories

Bundled Accessories^[1]

- Lenovo® HDMI® to VGA Monitor Adapter
- Lenovo® USB-C® to DisplayPort™ Adapter
- Lenovo® USB-C® to Ethernet Adapter (2.5Gbps)
- Lenovo® USB-C® to VGA Adapter

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for ThinkPad® T1g Gen 8](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping packaging: -20°C (-4°F) to 60°C (140°F)
- Storage without package: 5°C (41°F) to 43°C (109°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ENVIRONMENTAL

Sustainability

Material^[1]

90% Recycled Magnesium Aluminum C Cover
75% Recycled Aluminum A Cover
55% Recycled Aluminum D Cover
50% PCC Plastic D Cover (Attached Internal Components)
90% PCC Plastic 140W AC Adapter
46% Total PCC Plastic
Plastic Free Packaging with 90% Recycled and / or FSC Certified Content

Notes:

[1] PCC: Post Consumer Content, recycled materials from customers.

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified, generation 10

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ registration and ENERGY STAR® certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.

Other Certifications**Mil-Spec Test**

MIL-STD-810H military test passed

Other Certifications

- Eyesafe® Certified 2.0
- (Optional) Intel® Evo™ Platform
- TÜV Rheinland® Low Blue Light

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

