

As required by COMMISSION REGULATION (EU) 2019/1782 of 1 October 2019 laying down ecodesign requirements for external power supplies pursuant to Directive 2009/125/EC of the European Parliament and of the Council and repealing Commission Regulation (EC) No 278/2009 (ErP Lot7) for the external power supply of the product.

Information published	Value and precision	Unit
Manufacturer's name	Lenovo	-
Model identifier	<i>FSP240-A12C14</i>	-
Input voltage	100-240	V
Input AC frequency	50-60	Hz
Output voltage	12.2	V
Output current	20.0	A
Output power	240.0	W
Average active efficiency	92.73	%
Efficiency at low load (10 %)	87.35	%
No-load power consumption	0.13	W

Information published	Value and precision	Unit
Manufacturer's name	Lenovo	-
Model identifier	<i>GA240SD1-12020000</i>	-
Input voltage	100-240	V
Input AC frequency	50-60	Hz
Output voltage	12.2	V
Output current	20.0	A
Output power	240.0	W
Average active efficiency	93.21	%
Efficiency at low load (10 %)	79.0	%
No-load power consumption	0.097	W