

# Product data sheet

Specifications



## APC Back-UPS CS 350VA, 120V, 6 NEMA outlets (4 surge)

BK350

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	210 W
Rated power in VA	350 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	3 NEMA 5-15R 3 NEMA 5-15R surge
Cable length	6 ft (1.8 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Cord management straps User Manual USB cable

### Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	8 h
RBC Quantity	1
Battery Voltage	12 V
Battery Capacity	7.0 Ah
Battery Charge Power (Watts)	10 W rated
Battery power in VAH	86 VAh capacity 84 VAh runtime
Battery life	4...6 year(s)
Replacement battery	<a href="#">RBC2</a>

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

<b>Battery graph comments</b>	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
-------------------------------	--

---

<b>Extendable Run Time</b>	0
----------------------------	---

## General

---

<b>Number of power module free slots</b>	0
--	---

---

<b>Number of power module filled slots</b>	0
--	---

---

<b>Redundant</b>	No
------------------	----

## Physical

---

<b>color</b>	Beige
--------------	-------

---

<b>Height</b>	6.5 in (16.5 cm)
---------------	------------------

---

<b>Width</b>	3.6 in (9.1 cm)
--------------	-----------------

---

<b>Depth</b>	11.2 in (28.4 cm)
--------------	-------------------

---

<b>Net Weight</b>	12.52 lb(US) (5.68 kg)
-------------------	------------------------

---

<b>Mounting Location</b>	Front
--------------------------	-------

---

<b>Mounting preference</b>	No preference
----------------------------	---------------

---

<b>Mounting Mode</b>	Not rack-mountable
----------------------	--------------------

---

<b>Two post mountable</b>	0
---------------------------	---

---

<b>USB compatible</b>	Yes
-----------------------	-----

## Input

---

<b>Input Frequency</b>	50/60 Hz +/- 3 Hz auto-sensing
------------------------	--------------------------------

---

<b>Efficiency at full load</b>	98...140 V
--------------------------------	------------

## Output

---

<b>Max Configurable Power (Watts)</b>	210 W
---------------------------------------	-------

---

<b>Output Frequency (sync to mains)</b>	50/60 Hz +/- 3 Hz sync to mains
---	---------------------------------

---

<b>Topology</b>	Standby
-----------------	---------

---

<b>Waveform Type</b>	Stepped approximation to a sinewave
----------------------	-------------------------------------

---

<b>Maximum output current</b>	10 A
-------------------------------	------

---

<b>Maximum configurable power in VA</b>	350 VA
---	--------

---

<b>Transfer Time</b>	8ms typical : 12ms maximum
----------------------	----------------------------

## Conformance

---

<b>Product Certifications</b>	California (CEC) Battery Charger ENERGY STAR V2.0 (USA) TÜV
-------------------------------	---

---

<b>Equipment protection policy</b>	Lifetime : \$100000
------------------------------------	---------------------

## Environmental

---

<b>Ambient Air Temperature for Operation</b>	32...104 °F (0...40 °C)
--	-------------------------

Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Acoustic level	45 dBA
Online Thermal Dissipation	20 Btu/h

## Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rating	1020 J
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : mee
Let Through Voltage Rating	300 V

## Ordering and shipping details

GTIN	731304016298
------	--------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.4 in (26.3 cm)
Package 1 Width	14.06 in (35.7 cm)
Package 1 Length	6.9 in (17.5 cm)
Package 1 Weight	14.02 lb(US) (6.36 kg)
SCC14	10731304016295

## Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


## Resource performance

 Energy Efficient Product

 Take-Back Program Available

## Well-being performance

 Mercury Free

 Rohs Exemption Information Yes

## Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

**California Proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)