


OVERVIEW



1. Smart card reader *	5. 2x Thunderbolt 4
2. USB-A (USB 5Gbps)	6. HDMI
3. USB-A (USB 5Gbps), Always On	7. Headphone / microphone combo jack (3.5mm)
4. Kensington Nano Security Slot	8. Nano-SIM card slot *

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

Intel® U or H Series Core™ Ultra 5 / 7 Processor (Series 1)

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	AI Engine
Core™ Ultra 5 125U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 1.3GHz / E-core 800MHz / LPE-core 700MHz	P-core 4.3GHz / E-core 3.6GHz / LPE-core 2.1GHz	12MB	Intel® Graphics	Intel® AI Boost
Core™ Ultra 5 135U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 1.6GHz / E-core 1.1GHz / LPE-core 700MHz	P-core 4.4GHz / E-core 3.6GHz / LPE-core 2.1GHz	12MB	Intel® Graphics	Intel® AI Boost
Core™ Ultra 7 155H	16 (6 P-core + 8 E-core + 2 LPE-core)	22	P-core 1.4GHz / E-core 900MHz / LPE-core 700MHz	P-core 4.8GHz / E-core 3.8GHz / LPE-core 2.5GHz	24MB	Intel® Arc™ Graphics	Intel® AI Boost
Core™ Ultra 7 155U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 1.7GHz / E-core 1.2GHz / LPE-core 700MHz	P-core 4.8GHz / E-core 3.8GHz / LPE-core 2.1GHz	12MB	Intel® Graphics	Intel® AI Boost
Core™ Ultra 7 165H	16 (6 P-core + 8 E-core + 2 LPE-core)	22	P-core 1.4GHz / E-core 900MHz / LPE-core 700MHz	P-core 5.0GHz / E-core 3.8GHz / LPE-core 2.5GHz	24MB	Intel® Arc™ Graphics	Intel® AI Boost
Core™ Ultra 7 165U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 1.7GHz / E-core 1.2GHz / LPE-core 700MHz	P-core 4.9GHz / E-core 3.8GHz / LPE-core 2.1GHz	12MB	Intel® Graphics	Intel® AI Boost

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Windows® 11 DG Windows® 10 Pro 64^[1]
- Linux^[2]
- Ubuntu Linux^[3]
- No preload operating system

Notes:

[1] Windows® 11 DG Windows® 10 Pro 64 is for special bid only.

[2], [3] Some features may not be supported on the system with Linux preload, including but not limited to Intel® RST RAID, MIPI computer vision camera, WWAN, Human Presence Detection, etc.

Graphics

Graphics**

Graphics	Type	Memory	Key Features
Intel® Arc™ Graphics	Integrated	Shared	DirectX® 12.1
Intel® Graphics	Integrated	Shared	DirectX® 12.1

Monitor Support

Monitor Support^[1]

Supports up to 4 independent displays (native display and 3 external monitors via HDMI® and Thunderbolt™)

- HDMI® supports up to 4K@60Hz
- Thunderbolt™ supports up to 8K@60Hz^[2]

Notes:

[1] Refresh rates >60hz also supported, however max resolution will be limited.

[2] 8K resolution support needs 2 display pipes. That is, simultaneous display number will "-1" when 8K resolution displayed.

Chipset

Chipset

Intel® SoC (System on Chip) platform

Memory

Max Memory

- 16GB soldered memory, not upgradable
- 32GB soldered memory, not upgradable
- 64GB soldered memory, not upgradable

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Memory Type

LPDDR5x-6400^[1]

Notes:

[1] Installed memory is actually 7500MHz but run at 6400MHz due to platform limitation.

Storage

Storage Support^[1]

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Storage Type**

Disk Type	Interface	Offering	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB	Opal 2.0
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4 Performance	512GB / 1TB / 2TB	Opal 2.0

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

Removable Storage

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby® Audio™

Microphone

Dual-microphone array, 360° far-field, Dolby® Voice®

Camera**

- 5.0MP + IR discrete, with privacy shutter, fixed focus
- 5.0MP, with privacy shutter, fixed focus

Battery

Battery

Integrated Li-Polymer 58Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter

Battery Life^[1]

ThinkPad T14s Gen 5

Configuration 1 (max battery life)

MobileMark® 25: up to 15.2 hr with 746 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 14.5 hr / 33.4 hr @200nits
Local video playback: up to 21.4 hr @150nits

Alternate configuration 2

MobileMark® 25: up to 14.5 hr with 663 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 14.2 hr / 33.6 hr @200nits
Local video playback: up to 22.2 hr @150nits

Alternate configuration 3

MobileMark® 25: up to 14.3 hr with 664 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 12.0 hr / 25.2 hr @200nits
Local video playback: up to 20.4 hr @150nits

Notes:

- [1] Configuration 1 (max battery life): WUXGA low power (non-touch), Intel® Core™ Ultra 7 155H, 16GB LPDDR5x, Win 11, 58Wh battery, best power efficiency power mode
- Alternate configuration 2: WUXGA low power (non-touch), Intel® Core™ Ultra 5 135U, 16GB LPDDR5x, Win 11, 58Wh battery, best power efficiency power mode
- Alternate configuration 3: WUXGA (non-touch), Intel® Core™ Ultra 5 135U, 16GB LPDDR5x, Win 11, 58Wh battery, best power efficiency power mode

All battery life claims are approximate maximum and based on results using [MobileMark® 25](#), JEITA 3.0, continuous 1080p local video playback (using default Media Player in Fullscreen mode with 150nits brightness and default volume level), or Google Power Load Test (PLT) battery-life benchmark tests.

Actual battery life will vary depending on many factors such as product configuration, software, wireless functionality, power management settings, and screen brightness.

The maximum capacity of the battery will decrease with time, ambient temperature and use. Refer to [Microsoft® link](#) for more information about the Windows® Performance power slider.

Power Adapter

Power Adapter**[1]

- 45W USB-C® (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 45W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® slim (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® slim (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

- [1] AC adapter offerings depend on the country.

DESIGN

Display

Display**[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
14"	WUXGA (1920x1200)	None	IPS ^[2]	400nits	Anti-glare	16:10	800:1	45% NTSC	60Hz	85°/85°/85°/85°	88% screen to body ratio, 3M™ DBEF5
14"	WUXGA (1920x1200)	Multi-touch	IPS ^[3]	400nits	Anti-glare	16:10	800:1	45% NTSC	60Hz	85°/85°/85°/85°	Eyesafe® Certified 2.0, 88% screen to body ratio, 3M™ DBEF5
14"	WUXGA	None	IPS ^[4]	400nits	Anti-	16:10	800:1	100%	60Hz	85°/85°/85°/85°	Low power,

ThinkPad T14s Gen 5

	(1920x1200)				glare			sRGB			88% screen to body ratio
14"	WUXGA (1920x1200)	Multi-touch	IPS ^[5]	500nits	Anti-glare	16:10	1500:1	100% sRGB	60Hz	89°/89°/89°/89°	ThinkPad® Privacy Guard, 88% screen to body ratio
14"	2.8K (2880x1800)	None	OLED	400nits	Anti-glare, anti-reflection, anti-smudge	16:10	100,000:1	100% DCI-P3	120Hz	85°/85°/85°/85°	DisplayHDR™ True Black 500, Dolby® Vision®, Eyesafe® Certified 2.0, 88% screen to body ratio

Touchscreen

- On-cell multi-touch, supports 10-point touch
- Non-touch

Notes:

- [1] 3M™ DBEF5 (Dual Brightness Enhancement Film) improves the experience with higher brightness and lower energy.
 [2], [3], [4], [5] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device

Keyboard

6-row, spill-resistant, multimedia Fn keys

Keyboard Backlight

LED backlight

UltraNav™

TrackPoint® pointing device, double-tap to open the TrackPoint® Quick Menu
 Glass-like Mylar® surface multi-touch touchpad, 61 x 115 mm (2.40 x 4.53 inches)

Mechanical

Dimensions (WxDxH)^[1]

Models	Dimensions
Models with grey cover	313.6 x 219.4 x 16.6 mm (12.35 x 8.64 x 0.65 inches)
Models with black cover	313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

Weight^[2]

Models	Weight
Models with grey cover	Starting at 1.45 kg (3.19 lbs)
Models with black cover	Starting at 1.24 kg (2.73 lbs)

Case Color**

- Black
- Grey

Case Material**

- Grey models: aluminium (top), aluminium (bottom)
- Black models: carbon fiber hybrid (top), aluminium (bottom)

Notes:

- [1] The system dimensions may vary depending on configurations.
 [2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

No onboard Ethernet^[1]

WLAN + Bluetooth[®]**^[2]

- Intel[®] Wi-Fi[®] 6E AX211, 802.11ax 2x2 Wi-Fi[®] + Bluetooth[®] 5.3^[3]
- Intel[®] Wi-Fi[®] 7 BE200, 802.11be 2x2 Wi-Fi[®] + Bluetooth[®] 5.3 (Bluetooth[®] 5.4 hardware ready)^[4]

WWAN**

- Wireless WAN upgradable to 4G (with antenna ready)
- Wireless WAN upgradable to 4G or 5G (with antenna ready)
- Quectel EM061K-GL, 4G LTE CAT6, M.2 Card, with embedded eSIM functionality
- Quectel RM520N-GL, 5G Sub-6 GHz, M.2 Card, with embedded eSIM functionality
- No support

SIM Card

No physical SIM card inbox

NFC

- Near Field Communication
- No support

Notes:

[1] Ethernet support via optional Lenovo[®] USB-C[®] to Ethernet Adapter.

[2] Bluetooth[®] may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

[3] Wi-Fi[®] 6E full features might be limited by country-level restrictions.

Wi-Fi[®] 6E is only enabled on Windows[®] 11 and operates as Wi-Fi[®] 6 with Windows[®] 10.

6GHz Wi-Fi[®] 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi[®] 6E, and the regional regulatory certifications & spectrum allocation.

Bluetooth[®] 5.3 operation requires Windows[®] 11. For more information please see [General Bluetooth[®] Support Information on Microsoft[®]](#).

[4] Wi-Fi[®] 7 is only enabled on Windows[®] 11 and operates as Wi-Fi[®] 6 with Windows[®] 10.

6GHz Wi-Fi[®] 7 operation is subject to the regulation rules in each country.

Bluetooth[®] 5.3 operation requires Windows[®] 11. For more information please see [General Bluetooth[®] Support Information on Microsoft[®]](#).

Ports^[1]

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C[®] (Thunderbolt™ 4 / USB4[®] 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI[®] 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports***

- 1x Smart card reader
- 1x Nano-SIM card slot (WWAN support models)

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

Docking

Docking

Various docking solutions supported via Thunderbolt™ / USB-C[®].

For more compatible docking solutions, please visit [Docking for ThinkPad[®] T14s Gen 5](#)

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

- Smart card reader
- No smart card reader

Fingerprint Reader

- Touch style fingerprint reader integrated in power button, match-on-chip
- No fingerprint reader

BIOS Security

- Power-on password
- Supervisor password
- System management password
- NVMe® password
- FIDO (Fast Identity Online) authentication
- Certificate based BIOS authentication
- Self-healing BIOS

Other Security

- (Optional) IR camera for Windows® Hello (facial recognition)
- (Optional) Camera privacy shutter
- (Optional) Privacy Guard with Privacy Alert
- Ultrasonic Human Presence Detection (IR camera models)^[1]

Notes:

[1] Ultrasonic HPD is disabled by default.

MANAGEABILITY

System Management

System Management

- Intel® vPro® Enterprise^[1]
- Non-vPro®

Notes:

[1] Intel® vPro® offers a superset of DASH's defined capabilities.

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 1-year limited onsite service
- 3-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) limited onsite service
- No base warranty

ENVIRONMENTAL

Sustainability

Material

Carbon fiber plate (50% PIC foam core) + PC / GF (30% recycled) or 50% recycled aluminum on top cover
90% recycled magnesium on keyboard frame
55% recycled aluminum on bottom cover

- 85% PCC recycled plastic used in backlit keycaps
- 90% PCC recycled plastic used in speaker enclosure
- 90% recycled plastic used in the 58Wh battery frame
- 90% PCC recycled plastic used in standard 45W and 65W adapter
- 95% PCC recycled plastic used in cable holders
- Plastic free packaging with FSC certified paper

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping package: -20°C (-4°F) to 60°C (140°F)
- Storage without package: 5°C (41°F) to 43°C (109°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ACCESSORIES

Bundled Accessories

Bundled Accessories^{***[1]}

- Lenovo® HDMI® to VGA Monitor Adapter
- Lenovo® USB-C® to DisplayPort™ Adapter
- Lenovo® USB-C® to Ethernet Adapter (1Gbps)
- Lenovo® USB-C® to VGA Adapter
- None

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for ThinkPad® T14s Gen 5](#).

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered^[3]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 9.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

[2] EPEAT™ registration and ENERGY STAR® certification are dependent on system OS. Please visit [epeat.net](#) and [energystar.gov](#) for more information.

[3] EPEAT™ is registered where applicable, please see [epeat.net](#) for registration status by country.

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- (Optional) Intel® Evo™ Platform
- (Optional) Eyesafe® Certified 2.0

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

